

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Not recommended  
for new design

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

# 2SC5894

## Silicon NPN Epitaxial High Frequency Low Noise Amplifier / Oscillator


REJ03G0764-0200  
(Previous ADE-208-1605A)  
Rev.2.00  
Aug.10.2005

### Features

- High gain bandwidth product  
 $f_T = 20 \text{ GHz typ.}$
- High power gain and low noise figure;  
 $PG = 17.5 \text{ dB typ.}, NF = 1.8 \text{ dB typ. at } f = 1.8 \text{ GHz}$

### Outline

RENESAS Package code: PTSP0004ZA-A  
(Package name: CMPAK-4)



1. Emitter
2. Collector
3. Emitter
4. Base

Note: Marking is "WJ-".

### Absolute Maximum Ratings

( $T_a = 25^\circ\text{C}$ )

Item	Symbol	Ratings	Unit
Collector to base voltage	$V_{CBO}$	12	V
Collector to emitter voltage	$V_{CEO}$	4.0	V
Emitter to base voltage	$V_{EBO}$	1.5	V
Collector current	$I_C$	12	mA
Collector power dissipation	$P_C$	50	mW
Junction temperature	$T_j$	150	$^\circ\text{C}$
Storage temperature	$T_{stg}$	-55 to +150	$^\circ\text{C}$


## Electrical Characteristics






(Ta = 25°C)


Item	Symbol	Min	Typ	Max	Unit	Test conditions
Collector cutoff current	$I_{CBO}$	—	—	1	$\mu A$	$V_{CB} = 12 V, I_E = 0$
Collector cutoff current	$I_{CEO}$	—	—	1	$\mu A$	$V_{CE} = 4 V, R_{BE} = \infty$
Emitter cutoff current	$I_{EBO}$	—	—	10	$\mu A$	$V_{EB} = 1.5 V, I_C = 0$
DC current transfer ratio	$h_{FE}$	70	110	150		$V_{CE} = 2 V, I_C = 10 mA$
Collector output capacitance	$C_{ob}$	—	0.16	0.4	pF	$V_{CB} = 2 V, I_E = 0, f = 1 MHz$
Gain bandwidth product	$f_T$	16	20	—	GHz	$V_{CE} = 2 V, I_C = 10 mA$ $f = 2 GHz$
Power gain	PG	13	17.5	—	dB	$V_{CE} = 2 V, I_C = 10 mA,$ $f = 1.8 GHz$
Noise figure	NF	—	1.8	2.4	dB	$V_{CE} = 2 V, I_C = 3 mA,$ $f = 1.8 GHz$

Not recommend  
for new design


Main Characteristics









Condition:  $V_{CE} = 2\text{ V}$ ,  $Z_O = 50\ \Omega$   
 100 to 2900 MHz (200 MHz Step)  
 ◎—○ ( $I_C = 10\text{ mA}$ )



Condition:  $V_{CE} = 2\text{ V}$ ,  $Z_O = 50\ \Omega$   
 100 to 2900 MHz (200 MHz Step)  
 ◎—○ ( $I_C = 10\text{ mA}$ )



Condition:  $V_{CE} = 2\text{ V}$ ,  $Z_O = 50\ \Omega$   
 100 to 2900 MHz (200 MHz Step)  
 ◎—○ ( $I_C = 10\text{ mA}$ )



Condition:  $V_{CE} = 2\text{ V}$ ,  $Z_O = 50\ \Omega$   
 100 to 2900 MHz (200 MHz Step)  
 ◎—○ ( $I_C = 10\text{ mA}$ )

## Sparameter

 $(V_{CE} = 2V, I_C = 3mA, Z_o = 50\Omega)$ 

f (MHz)	S11		S21		S12		S22	
	MAG	ANG	MAG	ANG	MAG	ANG	MAG	ANG
100	0.890	-4.5	9.05	175.5	0.0030	85.7	0.992	-2.0
200	0.892	-9.2	8.88	171.1	0.0064	89.8	0.994	-4.5
300	0.910	-13.9	8.84	166.5	0.0105	91.0	0.991	-6.7
400	0.885	-18.7	8.69	162.1	0.0139	90.5	0.984	-9.4
500	0.876	-23.6	8.57	157.8	0.0185	87.8	0.978	-12.0
600	0.857	-28.5	8.45	153.4	0.0231	84.4	0.966	-14.6
700	0.838	-33.6	8.46	149.2	0.0271	81.0	0.953	-17.2
800	0.825	-38.3	8.13	145.0	0.0316	77.6	0.935	-19.5
900	0.801	-43.0	7.93	141.1	0.0355	73.4	0.914	-21.8
1000	0.776	-47.5	7.56	137.4	0.0392	70.9	0.895	-23.6
1100	0.793	-52.0	7.27	133.2	0.0432	66.5	0.872	-25.9
1200	0.728	-56.8	7.35	129.9	0.0459	63.5	0.849	-28.0
1300	0.700	-61.3	7.15	126.4	0.0487	60.5	0.827	-29.9
1400	0.674	-65.6	6.94	123.1	0.0510	57.0	0.804	-31.4
1500	0.649	-69.7	6.73	120.0	0.0531	54.5	0.783	-33.0
1600	0.624	-74.0	6.54	117.0	0.0555	52.5	0.763	-34.6
1700	0.598	-78.1	6.34	113.9	0.0576	50.7	0.741	-35.9
1800	0.567	-82.7	6.22	111.0	0.0581	48.6	0.719	-37.3
1900	0.554	-86.7	6.00	107.8	0.0610	45.8	0.699	-38.4
2000	0.526	-89.8	5.81	106.2	0.0613	44.9	0.685	-39.6
2100	0.501	-95.3	5.67	102.5	0.0624	42.4	0.660	-40.5
2200	0.487	-97.3	5.33	101.4	0.0642	40.6	0.657	-41.3
2300	0.471	-102.5	5.32	98.0	0.0646	39.5	0.629	-42.4
2400	0.455	-106.5	5.17	95.6	0.0658	38.0	0.615	-43.4
2500	0.434	-111.3	5.08	93.1	0.0663	36.1	0.596	-44.4
2600	0.424	-114.1	4.87	91.5	0.0666	35.2	0.590	-45.2
2700	0.405	-119.3	4.79	88.7	0.0665	35.1	0.572	-46.0
2800	0.396	-121.9	4.63	87.6	0.0677	33.4	0.567	-47.1
2900	0.385	-127.7	4.56	84.3	0.0685	32.2	0.547	-47.5
3000	0.374	-132.6	4.49	81.6	0.0677	31.1	0.530	-48.1




f (MHz)	S11		S21		S12		S22	
	MAG	ANG	MAG	ANG	MAG	ANG	MAG	ANG
100	0.831	-5.8	13.33	174.2	0.0032	85.5	0.988	-2.4
200	0.835	-11.9	13.12	168.6	0.0065	90.4	0.989	-5.4
300	0.844	-18.0	13.04	162.9	0.0101	89.2	0.985	-8.2
400	0.821	-24.2	12.70	157.4	0.0133	88.6	0.974	-11.4
500	0.804	-30.4	12.41	152.0	0.0174	84.4	0.962	-14.5
600	0.779	-36.7	12.07	146.7	0.0216	81.4	0.944	-17.6
700	0.747	-42.7	11.79	141.8	0.0253	77.7	0.921	-20.5
800	0.727	-48.7	11.27	136.8	0.0291	73.9	0.894	-23.1
900	0.695	-54.4	10.82	132.4	0.0319	69.5	0.865	-25.5
1000	0.666	-59.9	10.26	128.0	0.0350	67.6	0.838	-27.4
1100	0.661	-64.8	9.78	123.8	0.0383	62.8	0.808	-29.6
1200	0.601	-70.4	9.57	120.3	0.0399	60.6	0.778	-31.5
1300	0.570	-75.5	9.16	116.7	0.0421	57.8	0.753	-33.1
1400	0.542	-80.3	8.78	113.4	0.0439	55.3	0.726	-34.4
1500	0.516	-85.0	8.40	110.3	0.0454	53.3	0.702	-35.7
1600	0.491	-89.6	8.06	107.4	0.0476	52.5	0.680	-36.8
1700	0.466	-94.2	7.74	104.5	0.0489	50.1	0.658	-37.8
1800	0.440	-99.2	7.48	101.7	0.0492	49.1	0.636	-38.7
1900	0.423	-103.7	7.17	98.9	0.0509	46.8	0.616	-39.5
2000	0.403	-107.6	6.88	97.2	0.0521	46.0	0.603	-40.4
2100	0.383	-113.4	6.65	93.9	0.0522	43.8	0.580	-40.8
2200	0.373	-116.2	6.30	92.6	0.0539	42.9	0.575	-41.5
2300	0.358	-121.5	6.18	89.8	0.0543	42.5	0.553	-42.2
2400	0.347	-125.9	5.97	87.7	0.0554	40.9	0.540	-42.8
2500	0.333	-131.2	5.81	85.5	0.0557	40.7	0.524	-43.5
2600	0.326	-134.6	5.57	83.9	0.0558	40.4	0.519	-44.0
2700	0.314	-140.2	5.43	81.5	0.0579	39.8	0.505	-44.6
2800	0.311	-143.3	5.24	80.3	0.0586	38.4	0.500	-45.4
2900	0.304	-149.0	5.12	77.6	0.0593	38.0	0.484	-45.6
3000	0.301	-153.8	5.00	75.4	0.0585	37.0	0.471	-46.1

$(V_{CE} = 2V, I_C = 10mA, Z_o = 50\Omega)$ 

f (MHz)	S11		S21		S12		S22	
	MAG	ANG	MAG	ANG	MAG	ANG	MAG	ANG
100	0.730	-8.4	20.44	172.0	0.0032	93.3	0.978	-3.0
200	0.728	-17.0	20.06	164.3	0.0060	87.1	0.977	-6.8
300	0.722	-25.5	19.61	156.7	0.0090	88.5	0.967	-10.4
400	0.694	-34.2	18.78	149.4	0.0123	86.4	0.946	-14.4
500	0.666	-42.6	17.90	142.5	0.0158	79.7	0.922	-18.2
600	0.630	-50.8	16.93	136.0	0.0191	77.0	0.888	-21.6
700	0.590	-58.5	15.94	130.4	0.0219	73.3	0.853	-24.5
800	0.559	-65.8	14.95	124.9	0.0250	70.9	0.815	-27.0
900	0.523	-72.5	13.98	120.2	0.0271	66.4	0.776	-29.2
1000	0.491	-79.2	13.06	115.8	0.0294	65.3	0.742	-30.7
1100	0.472	-84.8	12.25	111.8	0.0310	62.0	0.709	-32.5
1200	0.430	-91.4	11.57	108.4	0.0331	60.2	0.678	-33.5
1300	0.403	-97.2	10.90	105.2	0.0337	58.6	0.651	-34.5
1400	0.381	-102.9	10.29	102.2	0.0359	56.6	0.627	-35.2
1500	0.360	-108.2	9.73	99.4	0.0365	55.4	0.604	-35.9
1600	0.342	-113.7	9.22	96.8	0.0386	55.2	0.585	-36.5
1700	0.325	-119.0	8.77	94.3	0.0400	53.6	0.566	-36.9
1800	0.309	-124.8	8.36	91.9	0.0404	53.5	0.549	-37.3
1900	0.299	-130.0	7.97	89.6	0.0423	51.8	0.533	-37.6
2000	0.289	-134.9	7.61	87.8	0.0437	52.4	0.522	-38.0
2100	0.279	-140.9	7.28	85.3	0.0439	50.0	0.505	-38.2
2200	0.274	-144.7	6.95	83.7	0.0451	50.0	0.498	-38.6
2300	0.268	-150.1	6.72	81.7	0.0464	49.2	0.484	-39.0
2400	0.264	-154.8	6.46	79.8	0.0478	48.9	0.475	-39.5
2500	0.262	-160.0	6.23	77.9	0.0483	48.5	0.464	-39.8
2600	0.260	-163.9	6.00	76.4	0.0494	47.9	0.458	-40.2
2700	0.258	-169.2	5.80	74.5	0.0510	48.6	0.449	-40.6
2800	0.259	-172.6	5.60	73.1	0.0516	47.4	0.445	-41.1
2900	0.261	-177.2	5.43	71.1	0.0525	47.0	0.434	-41.5
3000	0.263	178.8	5.27	69.3	0.0533	46.4	0.427	-41.8

### Package Dimensions



### Ordering Information

Part Name	Quantity	Shipping Container
2SC5894WJ-TL-E	3000	φ 178 mm Reel, 8 mm Emboss Taping

Note: For some grades, production may be terminated. Please contact the Renesas sales office to check the state of production before ordering the product.

## Renesas Technology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.  
The information described here may contain technical inaccuracies or typographical errors.  
Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.  
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.  
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.



### RENESAS SALES OFFICES

<http://www.renesas.com>

Refer to "<http://www.renesas.com/en/network>" for the latest and detailed information.

#### Renesas Technology America, Inc.

450 Holger Way, San Jose, CA 95134-1368, U.S.A  
Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

#### Renesas Technology Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.  
Tel: <44> (1628) 585-100, Fax: <44> (1628) 585-900

#### Renesas Technology Hong Kong Ltd.

7th Floor, North Tower, World Finance Centre, Harbour City, 1 Canton Road, Tsimshatsui, Kowloon, Hong Kong  
Tel: <852> 2265-6688, Fax: <852> 2730-6071

#### Renesas Technology Taiwan Co., Ltd.

10th Floor, No.99, Fushing North Road, Taipei, Taiwan  
Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

#### Renesas Technology (Shanghai) Co., Ltd.

Unit2607 Ruijing Building, No.205 Maoming Road (S), Shanghai 200020, China  
Tel: <86> (21) 6472-1001, Fax: <86> (21) 6415-2952

#### Renesas Technology Singapore Pte. Ltd.

1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632  
Tel: <65> 6213-0200, Fax: <65> 6278-8001

#### Renesas Technology Korea Co., Ltd.

Kukje Center Bldg. 18th Fl., 191, 2-ka, Hangang-ro, Yongsan-ku, Seoul 140-702, Korea  
Tel: <82> 2-796-3115, Fax: <82> 2-796-2145

#### Renesas Technology Malaysia Sdn. Bhd.

Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No.18, Jalan Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia  
Tel: <603> 7955-9390, Fax: <603> 7955-9510