

KGF16N05D

N-Channel 5.5V Dual Power MOSFET

FN8810
Rev 0.00
January 27, 2016

The KGF16N05D is a dual 5.5V, 1.9mΩ, chip-scale, N-channel Power MOSFET. The device uses technology that uniquely integrates low cost CMOS and WLCSP fabrication processes. The chip scale package offers small area, low vertical profile and is fully compatible with standard SMT assembly processes. The KGF16N05D device offers unprecedented low on-resistance and total gate charge, outperforming conventional trench MOSFETs and enabling high frequency, low voltage switching. The device offers extremely high power density, reducing the board size of DC/DC converters and other power management systems.

Features

- Industry leading figures of merit: $r_{DS(ON)} \times Q_g$ and $r_{DS(ON)} \times Q_{gd}$
- Low profile/small footprint chip scale WLCSP package
- High frequency switching
- Known Good FET (KGF) Quality Assurance Process
- Low thermal resistance

Applications

- Point-of-load DC/DC converters
- Portable electronics
- OR'ing diodes

PRODUCT SUMMARY (PER FET)			
I_D	$T_A = +25^\circ C$	8A	Maximum
$V_{(BR)DSS}$	$I_D = 5mA$	5.5V	Minimum
$r_{DS(ON)}$	$V_{GS} = 4.5V$	1.9mΩ	Typical
$r_{DS(ON)}$	$V_{GS} = 4.5V$ (in Parallel)	0.95mΩ	Typical
Q_g	$V_{GS} = 4.5V$	5.5nC	Typical
Q_{gd}	$I_D = 4A$	0.9nC	Typical




FIGURE 1. EQUIVALENT CIRCUIT





FIGURE 2. WLCSP, DIE SIZE 2.475mmx1.170mm

Ordering Information

PART NUMBER	PART MARKING	TEMP RANGE (°C)	PACKAGE (RoHS Compliant)
KGF16N05D-400	AM	-55°C to +150°C	20 Bump WLCSP

Pin Configuration

KGF16N05D
(20 BUMP WLCSP)
BOTTOM VIEW



Pin Descriptions

PIN #	PIN NAME	DESCRIPTION
1	G1	Gate of MOSFET 1
2, 3, 4, 5	D1	Drain of MOSFET 1
6, 7, 8, 9, 10, 11, 12, 13, 14, 15	S	Source of both MOSFETs
16, 17, 18, 19	D2	Drain of MOSFET 2
20	G2	Gate of MOSFET 2

Absolute Maximum Ratings (Note 1)

Drain-to-Source Voltage (V_{DS})	5.5V
Gate-to-Source Voltage (V_{GS})	$\pm 5.5V$
Drain Current ($I_{D1} + I_{D2}$)	
Continuous (I_D)	16A
Pulsed (I_{DM})	40A
Single Pulse Avalanche Current (I_{AS}), ($I_{D1} + I_{D2}$)	
$L \leq 50\mu H$, $R_G \leq 25\Omega$	10A

Thermal Information

Thermal Resistance (Typical) (Note 2)	θ_{JA} ($^{\circ}C/W$)	θ_{JP} ($^{\circ}C/W$)
WLCSP Package	50	10
Maximum Power Dissipation (P_D) (Note 2)		
$T_A = +25^{\circ}C$	2.5W	
$T_A = +70^{\circ}C$	1.6W	
Junction and Storage Temperature Range (T_J , T_{stg})	-55 $^{\circ}C$ to +150 $^{\circ}C$	
Pb-Free Reflow Profile	see TB493	

CAUTION: Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions may adversely impact product reliability and result in failures not covered by warranty.

NOTES:

- $T_J = +25^{\circ}C$ unless otherwise noted.
- When mounted on 1 inch square 2oz copper clad FR-4.

Electrical Characteristics Specifications are for single MOSFET unless otherwise specified. $T_J = +25^{\circ}C$ unless otherwise noted.

SYMBOL	PARAMETER	TEST CONDITIONS	MIN (Note 3)	TYP	MAX (Note 3)	UNIT
$V_{(BR)DSS}$	Drain-to-Source Breakdown Voltage	$V_{GS} = 0V$, $I_D = 5mA$	5.5			V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 4V$, $V_{GS} = 0V$, $T_J = +25^{\circ}C$			0.01	mA
		$V_{DS} = 5V$, $V_{GS} = 0V$, $T_J = +25^{\circ}C$			0.1	mA
		$V_{DS} = 5V$, $V_{GS} = 0V$, $T_J = +125^{\circ}C$			1.0	mA
I_{GSS}	Gate-to-Body Leakage	$V_{GS} = 5.5V$, $V_{DS} = 0V$			75	nA
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}$, $I_D = 250\mu A$	0.6	0.7	0.9	V
$r_{DS(ON)}$	Drain-to-Source On-State Resistance (per MOSFET)	$V_{GS} = 3.5V$, $I_D = 8A$		2.1		m Ω
		$V_{GS} = 4.5V$, $I_D = 8A$		1.9		m Ω
$r_{DS(ON)}$	Drain-to-Source On-State Resistance (in Parallel)	$V_{GS} = 3.5V$, $I_D = 8A$		1.05		m Ω
		$V_{GS} = 4.5V$, $I_D = 8A$		0.95		m Ω
C_{iss}	Input Capacitance	$V_{DS} = 5V$, $V_{GS} = 0V$, $f = 1MHz$		600		pF
C_{oss}	Output Capacitance			840		pF
C_{rss}	Reverse Transfer Capacitance			215		pF
C_{iss}	Input Capacitance	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$		660		pF
C_{oss}	Output Capacitance			1130		pF
C_{rss}	Reverse Transfer Capacitance			265		pF
R_g	Gate Resistance	$V_{DS} = 0V$, $f = 1MHz$		1.0		Ω
Q_g	Total Gate Charge	$V_{GS} = 3.5V$, $I_D = 4A$, $V_{DS} = 4V$		4.3		nC
Q_{gs}	Gate-to-Source Charge			0.6		nC
Q_{gd}	Gate-to-Drain Charge			0.9		nC
Q_g	Total Gate Charge	$V_{GS} = 4.5V$, $I_D = 4A$, $V_{DS} = 4V$		5.5		nC
t_{rr}	Source-to-Drain Reverse Recovery Time	$I_S = 3A$, $di/dt = 33A/\mu s$		69		ns
V_{SD}	Diode Forward Voltage	$I_S = 5A$, $V_{GS} = 0V$		0.65	1.00	V

NOTE:

- Compliance to datasheet limits is assured by one or more methods: production test, characterization and/or design.

Typical Performance Curves




FIGURE 3. OUTPUT CHARACTERISTICS




FIGURE 4. TRANSFER CHARACTERISTICS




FIGURE 5. DRAIN-TO-SOURCE ON-STATE RESISTANCE vs DRAIN CURRENT




FIGURE 6. DRAIN-TO-SOURCE ON-STATE RESISTANCE vs JUNCTION TEMPERATURE




FIGURE 7. DRAIN-TO-SOURCE ON-STATE RESISTANCE vs GATE-TO-SOURCE VOLTAGE




FIGURE 8. GATE THRESHOLD VOLTAGE vs JUNCTION TEMPERATURE

Typical Performance Curves (Continued)




FIGURE 9. SOURCE-TO-DRAIN DIODE FORWARD VOLTAGE




FIGURE 10. DRAIN-TO-SOURCE BREAKDOWN VOLTAGE vs JUNCTION TEMPERATURE




FIGURE 11. GATE CHARGE




FIGURE 12. CAPACITANCE




FIGURE 13. MAXIMUM RATED FORWARD BIASED SAFE OPERATING AREA (IN PARALLEL)

Typical Performance Curves (Continued)




FIGURE 14. TRANSIENT THERMAL RESPONSE, JUNCTION-TO-AMBIENT (IN PARALLEL)

Revision History

The revision history provided is for informational purposes only and is believed to be accurate, but not warranted. Please go to the web to make sure that you have the latest revision.

DATE	REVISION	CHANGE
January 27, 2016	FN8810.0	Initial release

About Intersil

Intersil Corporation is a leading provider of innovative power management and precision analog solutions. The company's products address some of the largest markets within the industrial and infrastructure, mobile computing and high-end consumer markets.

For the most updated datasheet, application notes, related documentation and related parts, please see the respective product information page found at www.intersil.com.

You may report errors or suggestions for improving this datasheet by visiting www.intersil.com/ask.

Reliability reports are also available from our website at www.intersil.com/support.

© Copyright Intersil Americas LLC 2016. All Rights Reserved.

All trademarks and registered trademarks are the property of their respective owners.

For additional products, see www.intersil.com/en/products.html

Intersil products are manufactured, assembled and tested utilizing ISO9001 quality systems as noted in the quality certifications found at www.intersil.com/en/support/qualandreliability.html

Intersil products are sold by description only. Intersil may modify the circuit design and/or specifications of products at any time without notice, provided that such modification does not, in Intersil's sole judgment, affect the form, fit or function of the product. Accordingly, the reader is cautioned to verify that datasheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.

For information regarding Intersil Corporation and its products, see www.intersil.com

Dimensional Outline and Pad Layout

Side View



Pad-up View

