QUICKSWITCH® PRODUCTS 2.5V / 3.3V 20-BIT HIGH BANDWIDTH BUS SWITCH WITH PRECHARGED OUTPUTS

IDTQS3VH16800

FEATURES:

- N channel FET switches with no parasitic diode to Vcc
 - Isolation under power-off conditions
 - No DC path to Vcc or GND
 - 5V tolerant in OFF and ON state
- 5V tolerant I/Os
- · B port precharged to user-selectable VBIAS
- Low Ron 4Ω typical
- · Flat Ron characteristics over operating range
- Rail-to-rail switching 0 5V
- · Bidirectional dataflow with near-zero delay: no added ground bounce
- Excellent Row matching between channels
- Vcc operation: 2.3V to 3.6V
- · High bandwidth up to 500MHz
- · LVTTL-compatible control Inputs
- · Undershoot Clamp Diodes on all switch and control Inputs
- · Low I/O capacitance, 4pF typical
- Available in TSSOP package

APPLICATIONS:

- Hot-swapping
- 10/100 Base-T, Ethernet LAN switch
- Low distortion analog switch
- · Replaces mechanical relay
- ATM 25/155 switching


DESCRIPTION:


The QS3VH16800 HotSwitch is a 20-bit high bandwidth bus switch. The QS3VH16800 has very low ON resistance, resulting in under 250ps propagation delay through the switch. The QS3VH16800 precharges the B port to a user selectable bias voltage (VBIAS) to minimize live insertion noise. The switches can be turned ON under the control of the LVTTL-compatible Output Enable signal for bidirectional data flow with no added delay or ground bounce. It can be used as two 10-bit bus switches or one 20-bit bus switch. In the OFF and ON states, the switches are 5V-tolerant. In the OFF state, the switches offer very high impedence at the terminals.

The combination of near-zero propagation delay, high OFF impedance, and over-voltage tolerance makes the QS3VH16800 ideal for high performance communications applications.

The QS3VH16800 is characterized for operation from -40 $^{\circ}$ C to +85 $^{\circ}$ C.

FUNCTIONAL BLOCK DIAGRAM






The IDT logo is a registered trademark of Integrated Device Technology, Inc.

INDUSTRIAL TEMPERATURE RANGE

JUNE 2013

DSC-5961/9

PIN CONFIGURATION



TSSOP TOP VIEW

ABSOLUTE MAXIMUM RATINGS(1)

Symbol	Description	Max	Unit
VTERM ⁽²⁾	SupplyVoltage to Ground	-0.5 to +4.6	V
VTERM ⁽³⁾	DC Switch Voltage Vs	-0.5 to +5.5	V
VTERM ⁽³⁾	DC Input Voltage VIN	-0.5 to +5.5	V
VAC	AC Input Voltage (pulse width ≤20ns)	- 3	٧
Іоит	DC Output Current (max. sink current/pin)	120	mA
Tstg	Storage Temperature	-65 to +150	°C

NOTES:

- 1. Stresses greater than those listed under ABSOLUTE MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.
- 2. Vcc terminals.
- 3. All terminals except Vcc .

CAPACITANCE (TA = +25°C, F = 1MHz, VIN = 0V, VOUT = 0V)

Symbol	Parameter ⁽¹⁾	Тур.	Max.	Unit
CIN	Control Inputs	3	5	pF
CI/O	Quickswitch Channels (Switch OFF)	4	6	pF
	VBIAS = OPEN			
CI/O	Quickswitch Channels (Switch ON)	8	12	pF

NOTE:

1. This parameter is guaranteed but not production tested.

PIN DESCRIPTION

Pin Names	I/O	Description
ŌĒx		Bus Switch Enable
VBIAS	_	Bias Voltage
Ax	I/O	Bus A
Вх	I/O	Bus B

FUNCTION TABLE (EACH 10-BIT BUS SWITCH)(1)

ŌĒx	Вх	Function
L	Ax	Connect
Н	VBIAS	Disconnect Ax = Z

NOTE:

1. H = HIGH Voltage Level

L = LOW Voltage Level

Z = High-Impedence

DC ELECTRICAL CHARACTERISTICS OVER OPERATING RANGE

Following Conditions Apply Unless Otherwise Specified:

Industrial: TA = -40°C to +85°C, Vcc = 3.3V ± 0.3 V


Symbol	Parameter	Test	Conditions		Min.	Typ. ⁽¹⁾	Max.	Unit
VIH	Input HIGH Voltage	Guaranteed Logic HIGH	Vcc = 2.3V to	2.7V	1.7	_	_	V
		for Control Inputs	Vcc = 2.7V to	3.6V	2	_	_	
VIL	Input LOW Voltage	Guaranteed Logic LOW	Vcc = 2.3V to	2.7V	_	_	0.7	V
		for Control Inputs	Vcc = 2.7V to	3.6V	_	_	0.8	
VBIAS	Bias Voltage	Vcc = 3.3V to 3.6V, lo = 0	•		0	_	5	V
		Vcc = 2.3V to 2.7V, lo = 0	Vcc = 2.3V to 2.7V, lo = 0		0	_	3.3	
lo	Bias Current ⁽²⁾	VCC = 3.3V, VBIAS = 2.4V, VO = 0, $\overline{\text{OEx}}$ = HIGH		0.25	_	_	mA	
lin	Input Leakage Current (Control Inputs)	$0V \le VIN \le VCC$		_	_	±1	μΑ	
loz	Off-State Current (Hi-Z)	0V ≤ Vouт ≤ 5V, Switches OFF		_	_	±1	μΑ	
loff	Data Input/Output Power Off Leakage	VIN or VOUT 0V to 5V, VCC = 0V		_	_	±1	μΑ	
		Vcc = 2.3V	VIN = 0V	Ion = 30mA	_	6	8	
Ron	Switch ON Resistance	Typ. at Vcc = 2.5V	VIN = 1.7V	Ion = 15mA	_	7	9	Ω
		Vcc = 3V	VIN = 0V	Ion = 30mA	_	4	6	
			VIN = 2.4V	ION = 15mA	_	5	8	

NOTES:

- 1. Typical values are at Vcc = 3.3V and TA = 25°C.
- 2. Bias resistance is $5K\Omega$ typical at Vcc = 3.3V; VBIAS = 2.4V at 25°C.

TYPICAL ON RESISTANCE vs Vin AT Vcc = 3.3V






POWER SUPPLY CHARACTERISTICS

Symbol	Parameter	Test Conditions ⁽¹⁾	Min.	Тур.	Max.	Unit
Iccq	Quiescent Power Supply Current	Vcc = Max., Vin = GND or Vcc, f = 0	-	1.5	3	mA
Δlcc	Power Supply Current ^(2,3) per Input HIGH	Vcc = Max., Vin = 3V, f = 0 per Control Input	_	_	30	μΑ
ICCD	Dynamic Power Supply Current ⁽⁴⁾	Vcc = 3.3V, A and B Pins Open, Control Inputs	See Typical I	CCD vs Enable	Frequency gra	ph below
		Toggling @ 50% Duty Cycle				

NOTES:

- 1. For conditions shown as Min. or Max., use the appropriate values specified under DC Electrical Characteristics.
- 2. Per input driven at the specified level. A and B pins do not contribute to Δlcc.
- 3. This parameter is guaranteed but not tested.
- 4. This parameter represents the current required to switch internal capacitance at the specified frequency. The A and B inputs do not contribute to the Dynamic Power Supply Current. This parameter is guaranteed but not production tested.

TYPICAL ICCD vs ENABLE FREQUENCY CURVE AT Vcc = 3.3V



ENABLE FREQUENCY (MHz)

SWITCHING CHARACTERISTICS OVER OPERATING RANGE


 $T_A = -40$ °C to +85°C

			Vcc = 2.5	5 ± 0.2V ⁽¹⁾	Vcc = 3.3	± 0.3V ⁽¹⁾	
Symbol	Parameter	Test Conditions	Min. ⁽⁴⁾	Max.	Min. ⁽⁴⁾	Max.	Unit
t PLH	Data Propagation Delay ^(2,3)			0.2	_	0.2	ns
t PHL	Ax to Bx or Bx to Ax						
tPZL	Switch Turn-On Delay	VBIAS = 3V	1.5	8.5	1.5	8	ns
t PZH	OEx to Ax/Bx	VBIAS = GND					
tPLZ	Switch Turn-Off Delay	VBIAS = 3V	1.5	7.5	1.5	7.5	ns
t PHZ	OEx to Ax/Bx	VBIAS = GND					
fOEx	Operating Frequency - Enable ^(2,5)	VBIAS = OPEN		10	_	20	MHz
	(OEx)						


NOTES:

- 1. See Test Conditions under TEST CIRCUITS AND WAVEFORMS.
- 2. This parameter is guaranteed but not production tested.
- 3. The bus switch contributes no propagation delay other than the RC delay of the ON resistance of the switch and the load capacitance. The time constant for the switch alone is of the order of 0.2ns at C_L = 50pF. Since this time constant is much smaller than the rise and fall times of typical driving signals, it adds very little propagation delay to the system. Propagation delay of the bus switch, when used in a system, is determined by the driving circuit on the driving side of the switch and its interaction with the load on the driven side.
- 4. Minimums are guaranteed but not production tested.
- 5. Maximum toggle frequency for $\overline{\text{OEx}}$ control input (pass voltage > Vcc, Vin = 5V, RLOAD \geq 1M Ω , no CLOAD).


SOME APPLICATIONS FOR HOTSWITCH PRODUCTS



Rail-to-Rail Switching



Fast Ethernet Data Switching (LAN Switch)




Hot Swapping

TEST CIRCUITS AND WAVEFORMS

TEST CONDITIONS

Symbol	$Vcc^{(1)}= 3.3V \pm 0.3V$	Vcc ⁽²⁾ = 2.5V ± 0.2V	Unit
VLOAD	6	2 x Vcc	V
VIH	3	Vcc	V
VT	1.5	Vcc/2	V
VLZ	300	150	mV
VHZ	300	150	mV
CL	50	30	pF



Test Circuits for All Outputs

DEFINITIONS:

CL = Load capacitance: includes jig and probe capacitance.


RT = Termination resistance: should be equal to ZouT of the Pulse Generator.

NOTES:


- 1. Pulse Generator for All Pulses: Rate \leq 10MHz; tF \leq 2.5ns; tR \leq 2.5ns.
- 2. Pulse Generator for All Pulses: Rate \leq 10MHz; tF \leq 2ns; tR \leq 2ns.

SWITCH POSITION

Test	Switch
tplz/tpzl	VLOAD
tphz/tpzh	GND
tPD	Open



Propagation Delay




NOTE:

1. Diagram shown for input Control Enable-LOW and input Control Disable-HIGH.

Enable and Disable Times

ORDERING INFORMATION



IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.