

μPC271, 311

High Performance Comparator

R03DS0151EJ0100 Rev.1.00 2019.10.1

DESCRIPTION

The $\mu PC271$ and $\mu PC311$ are high-performance general-purpose comparators that have the same input characteristics as general-purpose operational amplifiers and can directly drive standard logic circuits such as TTL, CMOS, and HNIL. Its power supply voltage range is flexible whereby it exhibits excellent characteristics not only in a 5 V single power supply but also in \pm 15 V power supply which is equivalent to an operational amplifier.

These products are equipped with a strobe terminal and input offset adjustment terminals, thus they can be widely applied to various voltage comparison circuits.

Depending on the operating ambient temperature, the μ PC271 is suitable for communication application while the μ PC311 is suitable for general-purpose usage.

FEATURES

Input Offset Voltage ±2 mV (TYP.)
 Input Bias Current 100 nA (TYP.)
 Pulse Response Time 200 ns (TYP.)


- Equipped with a Strobe Terminal, ideal for interfacing with logic circuits.
- Two output circuit formats are possible. (open collector, emitter follower)
- Large output current capacity to directly drive the LEDs and lamps.

ORDERING INFORMATION

Ordering Name	Package
μPC271G2-A	8-pin plastic SOP (5.72 mm (225 mil))
μPC311G2-A	8-pin plastic SOP (5.72 mm (225 mil))

EQUIVALENT CIRCUIT

PIN CONFIGURATION (Top View)



ABSOLUTE MAXIMUM RATING $(T_A = 25 \, ^{\circ}C)$

PARAMETER	SYMBOL	μPC271G2	μPC311G2	UNIT
Power Supply Voltage Note1	V + - V -	-0.3 to +36		V
Differential Input Voltage	V _{ID}	±30		V
Input Voltage Note2	Note2 V ₁ V ₂ -0.3 to V ⁺ +0.3		o V + +0.3	V
Output to Negative Supply Voltage Note3	Vo – V -	-0.3 t	o +40	V
Ground to Negative Supply Voltage Note3 V _{GND}		-0.3 to +30		V
Total Power Dissipation Note4	PT	440		mW
Output Short Circuit Duration Note5		10		s
Operating Ambient Temperature	TA	-40 to +85	-20 to +80	°C
Storage Temperature	T _{stg}	-55 to +125		°C

[Note] 1. Note that reverse connections of the power supply may damage the ICs.

- 2. The input terminal must be applied within the input voltage range to avoid deterioration or damaging the device characteristic. Do not exceed the ratings including during transient state such as ON/OFF, etc. The Comparator input voltage must operate within the electrical characteristics range of input common-mode voltage.
- 3. The output terminal and GND terminal must be apply within the output voltage range to avoid deteriorating or damaging the device characteristic. The GND terminal must be less than V⁺. Do not exceed the ratings including during transient state such as ON/OFF, etc.
- 4. This is the value at $T_A \le +25$ °C. De-rate value at -4.4 mW/°C when $T_A > 25$ °C.
- 5. Pay attention to output terminal current and GND terminal current. Please use the total loss and the de-rating value from Note 4.

RECOMMENDED OPERATING CONDITIONS

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT
Power Supply Voltage (Dual Supply)	V ±	±4		±16	V
Power Supply Voltage (V - = GND)	V *	+5		+32	V


ELECTRICAL CHARACTERISTICS ($V^{\pm} = \pm 15 \text{ V}, T_A = 25 ^{\circ}\text{C}$)

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Input Offset Voltage Note6	V _{IO}		±2.0	±7.5	mV	$V^{+} - V^{-} = 5 V \text{ to } 30 V, R_{S} \le 50 kΩ$
Input Offset Current Note6	lio		±6.0	±50	nA	V ⁺ - V ⁻ = 5 V to 30 V
Input Bias Current	lΒ		100	250	nA	V + - V - = 5 V to 30 V
Voltage Gain	Av		200000			R _L = 1.0 kΩ
Pulse Response Time			200		ns	Input step 100 mV, Overdrive 5 mV
Output Saturation Voltage	Vol		0.75	1.5	V	V _I ≤ -10 mV, I _O = 50 mA
Strobe Operating Current			3.0		mA	
Output Leakage Current	lo leak		0.2	50	nA	V _I ≥ 10 mV, V _O = 35 V
Positive Supply Current	I *		5.1	7.5	mA	I _O = 0 A
Negative Supply Current	1-		4.1	5.0	mA	I _O = 0 A
Input Offset Voltage Note6	Vio			±10	mV	$V^+ - V^- = 5 V \text{ to } 30 V, R_S \le 50 kΩ,$ $T_A = 0 \text{ to } +70 °C$
Input Offset Current Note6	I _{IO}			±70	nA	$V^+ - V^- = 5 V \text{ to } 30 V, T_A = 0 \text{ to } +70^{\circ}\text{C}$
Input Bias Current	I _B			300	nA	$V^+ - V^- = 5 V \text{ to } 30 V, T_A = 0 \text{ to } +70^{\circ}\text{C}$
Common Mode Input Voltage Range	Vісм	+13.0 -14.5	+13.8 -14.7		٧	
Output Saturation Voltage	Vol		0.23	0.4	V	$V^{+} \ge 4.5 \text{ V}, \text{ V}^{-} = 0 \text{ V}, \text{ V}_{I} \le -10 \text{ mV},$ $I_{O} = 8 \text{ mA}$

[Note] 6. The difference of the input voltage and the input bias current when the load current is 1 mA and the output is inverted.

CIRCUIT CONNECTION EXAMPLE (1)

• BALANCE terminal, BALANCE/STROBE terminal




Note Use either pin 5 and pin 6 open (no offset adjustment), the offset adjustment circuit, the strobe circuit (pin 5 open) or the common mode slew rate increase method as shown in above figures. In other cases, malfunction, characteristic deterioration or damage may occur.


CIRCUIT CONNECTION EXAMPLE (2)


APPLICATION CIRCUIT EXAMPLE


• Output terminal, GND terminal





TYPICAL PERFORMANCE CHARACTERISTICS (T_A = 25 °C, TYP.) (Reference Value)














USE WITH PRECAUTIONS

Power Supply (Dual Power Supply / Single Power Supply)

The comparator operates when a predetermine voltage is applied between $V^+ - V^-$. Therefore, while it operates from a single power supply ($V^- = GND$), it is not possible to operate the input near GND. So please be careful of the common-mode input voltage range.

Ratings of input pin voltage

When the voltage of input pin exceeds the absolute maximum rating, the parasitic diode within the IC may conduct, causing characteristics degradation or damage. Therefore, please use the input pin within the power supply voltage range. In addition, if it exceeds the power supply voltage, it is recommended to make a clamping circuit using a diode with low forward voltage (e.g.: Schottky diode) as protection.

Range of common-mode input voltage

When the power supply voltage does not meet the condition of electrical characteristics, the range of common-mode input voltage is as follows.

$$V_{ICM}$$
 (TYP.) : $V^- + 0.3$ to $V^+ - 1.2$ [V] ($T_A = 25$ °C)

During designing, do include some margin by considering characteristics variation and temperature characteristics, etc.

Handling of ICs


When stress is added to the ICs due to warpage or bending of a board, the characteristic may fluctuate due to piezoelectric (piezo) effect. Therefore, please pay attention to warpage or bending of a board.

PACKAGE DRAWINGS

8-PIN PLASTIC SOP

JEITA Package code	RENESAS code	Previous code	MASS (TYP.) [g]
P-SOP8-0225-1.27	PRSP0008DL-A	S8GM-50-225B	0.08

Unit: mm



NOTE

Each lead centerline is located within 0.12 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
Α	5.2 ^{+0.17} -0.20
	-0.20
В	0.78 MAX
С	1.27 (T.P)
D	0.42 ^{+0.08} _{-0.07}
	-0.07
Е	0.1 ±0.1
F	1.59 ±0.21
G	1.49
Н	6.5 ±0.3
1	4.4 ±0.15
J	1.1 ±0.2
K	0.17 ^{+0.08} _{-0.07}
K	-0.07
L	0.6 ±0.2
М	0.12
N	0.10
Р	3° +7° -3°
	-3°

Notice

- Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
- Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application
- arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.

 No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.

 You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.

 Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the

product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic

"standard": Computers; once equipment; communications equipment; test and measurement equipment; audio and visual equipment; nome electronic appliances; machine tools; personal electronic equipment; fundistrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment, tellness expressly designated as a high reliability product or a product for harsh environments in a Renessa Electronics data sheet or other Renessa Electronics document, Renessa Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renessa Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renessa Electronics product that is inconsistent with any Renessa Electronics data sheet, user's manual or other Renessa Electronics oductment.

When using Renessa Electronics region to the latest product information (data sheets, user's manuals, application potes. "General Notes for Handling and Using Semiconductor Devices" in the

- When using Reneasa Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified
- ranges.

 Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult
- and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.

 Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable
- products in compliance with the timese application laws and regulations. Tendeds Lectionics and the second laws and regulations.

 Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or
- 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
- any in advance of the contents and continuous set rothin intils occurred.

 11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.

 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
 (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
 (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

以下"注意事项"为从英语原稿翻译的中文译文,仅作为参考译文,英文版的"Notice"具有正式效力。

注意事项

- ★文档中所记载的关于电路、软件和其他相关信息仅用于说明半导体产品的操作和应用实例。用户如在产品或系统设计中应用本文档中的电路、软件和相关信息或将此等内容用于其他目的时,请自行负责。对于用户或第三方因使用上述电路、软件或信息而遭受的任何损失和损害,瑞萨电子做不承担任何责任。
 瑞萨电子在此明确声明,对于因使用瑞萨电子产品或本文档中所述技术信息(包括但不限于产品数据、图、表、程序、算法、应用实例)而造成的与第三方专利、版权或其他知识产权相关的侵权或任何其他索赔,瑞萨电子不作任何保证并概不承担责任。
 本文档师记载的内容不应视为对瑞萨电子或其他人所有的专利、版权或其他知识产权作出任何明示、默示或其它方式的许可及授权。
 用户不得对瑞萨电子的任何产品进行全部或部分更改、修改、复制或反向工程。对于用户或第三方因上述更改、修改、复制或对瑞萨电子产品进行反向工程的行为而遭受的任何损失或损害,瑞萨电子概不承担任何事任。

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

Refer to "http://www.renesas.com/" for the latest and detailed information.

Renesas Electronics America Inc. 1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A. Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited 9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3 Tel: +1-905-237-2004

Renesas Electronics (China) Co., Ltd.
Room 101-T01, Floor 1, Building 7, Yard No. 7, 8th Street, Shangdi, Haidian District, Beijing 100085, China
Tel: +86-10-8253-1155, Fax. +86-10-8235-7679

Reneasa Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai 200333, China
Tet: +862-12226-0688, Fax. +862-12226-0699

Reneasa Electronics Malaysia Sdn.Bhd.
Unit No 3A-1 Level 3A Tower 8 UOA Business Park, No 1 Jalan Pengaturcara U1/51A, Seksyen U1, 40150
Shah Alam, Selangor, Malaysia
Tel: +60-3-5022-1286, Fax: +60-3-5022-1290

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon,

Hong Kong Tel: +852-2265-6688, Fax: +852 2886-9022

Renesas Electronics Taiwan Co., Ltd. 13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics India Pvt. Ltd. No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India Tel: +91-80-67208700

Renesas Electronics Singapore Pte. Ltd. 80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949 Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Korea Co., Ltd. 17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea Tel: +82-2-558-3737, Fax: +82-2-558-5338

© 2019 Renesas Electronics Corporation. All rights reserved.