

ROM number	
------------	--

**RENESAS ELECTRONICS
SINGLE-CHIP 16-BIT MICROCOMPUTER
R5F2L38CCDXXXFP
ROM PROGRAMMING CONFIRMATION FORM**

Receipt	Date:	
	Section mgr signature	PIC signature

Note: Please fill in all items marked *.

* Applicant	Company Name	TEL	Applicant signature	Submitted by
	Date issued	Year / Month / Date		()

*** 1. Mask file**

Please kindly verify and confirm the mask file in the submitted CD-R prior to submission.
Please submit mask files on CD-R. And the number of the mask file must be 1 mask file per one CD-R.

Part Number R5F2L38CCDXXXFP

File Code

--	--	--	--	--	--	--	--

 (hexadecimal notation)

Mask file name

--	--	--	--	--	--	--	--

 .MSK (no more than 8 characters)

*** 2. Mask option**

Set the mask option in the mask file generating utility as follows:

Address : 10h Data : 01h

*** 3. ROM data which must be set by user**

Check the option function select registers (OFS, OFS2) and ID code areas to be set for appropriate values as ROM data.

OFS register OFS2 register ID code areas

CAUTION:

Note 1 : ROM order of this product programs the Data Flash area.


Note 2 : ROM data confirmation request

ROM programming will be processed based on the mask file generated by the mask file generating utility. Only in case when ROM data programmed in the actual mass produced product differs from that of above mentioned mask file, RENESAS takes the responsibility. There is no Engineering Sample, thus please confirm the ROM data at the receipt of the Initial product delivery.

Should you find any problem, please return immediately. 2 weeks without technical error feedback towards RENESAS will automatically be regarded as acceptance of products.

Note 3 : Mark specification

Please refer to Fig. 1 about mark specification.



yyy : ROM number
XXXXXXX : Lot number

Fig. 1

RENESAS ELECTRONICS SINGLE-CHIP 16-BIT MICROCOMPUTER R5F2L38CCDXXXFP

ROM PROGRAMMING CONFIRMATION FORM

Usage conditions

For our reference of new products, please reply to the following questions about the usage of the products you ordered.

(1) What is the voltage of power supply (Vcc) you use?

Typ. = V

Min. = V

Max. = V

(2) What is the ambient temperature you use?

Typ. = °C

Min. = °C

Max. = °C

(3) On which condition will you use Reset? (Plural answers are possible.)

Hardware Reset

Power-on reset Reset

Voltage monitor 0 Reset

Watchdog timer Reset

Software Reset

(4) On which condition will you use Voltage monitor 0 Circuit?

Use

Not use

Voltage Detection 0 Level Select

3.80V

2.85V

2.35V

1.90V

(5) On which condition will you use Voltage monitor 1 Circuit?

Use

Not use

Voltage Detection 1 Level Select

2.20V

2.35V

2.50V

2.65V

2.80V

2.95V

3.10V

3.25V

3.40V

3.55V

3.70V

3.85V

4.00V

4.15V

4.30V

4.45V

(6) Will you use Voltage monitor 2 Circuit?

Use

Not use

(7) On which condition will you use High-speed clock?

High-Speed On-Chip Oscillator

Use

Not use

Frequency

40MHz

36.864MHz

32MHz

Division ratio

Divide-by- mode

XIN-XOUT Oscillates

Use

Not use

External clock input

Oscillator type

Crystal Oscillator

Ceramic resonator

Others (

Frequency

f(XIN) = MHz

Load capacity

XIN side = pF

XOUT side = pF

Internal feedback resistance

Use

Not use

Oscillation stop detection

Use

Not use

(8) On which condition will you use Low-speed clock?

Use

Not use

Low-speed on-chip oscillator

Oscillator type

Crystal Oscillator

Others (

Frequency

f(XCIN) = kHz

Load capacity

XCIN side = pF

XCOUT side = pF

Internal feedback resistance

Use

Not use

**RENESAS ELECTRONICS
SINGLE-CHIP 16-BIT MICROCOMPUTER
R5F2L38CCDXXXFP**

ROM PROGRAMMING CONFIRMATION FORM

(9) On which condition will you use System clock division ratio?

- No division mode Divide-by-2 mode Divide-by-4 mode
 Divide-by-8 mode Divide-by-16 mode

(10) Which Power control mode will you use? (Plural answers are possible.)

- Wait mode Stop mode Power-off mode

(11) Will you use Flash memory?

- | | | |
|-----------------------------------|------------------------------|--|
| CPU rewrite mode | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| ROM code protect | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Low-Current-Consumption Read Mode | <input type="checkbox"/> Use | CPU clock frequency = _____kΩ <input type="checkbox"/> Not use |
| Erase-suspend | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| BGO function | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |

(12) Which timer mode will you use?

- | | | |
|-----------------|---|---|
| Timer RA | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Operation mode | <input type="checkbox"/> Timer mode <input type="checkbox"/> Pulse output mode <input type="checkbox"/> Event counter mode
<input type="checkbox"/> Pulse width measurement mode <input type="checkbox"/> Pulse period measurement mode | |
| Count source | <input type="checkbox"/> f1 <input type="checkbox"/> f2 <input type="checkbox"/> f8 <input type="checkbox"/> fOCO <input type="checkbox"/> fC32 <input type="checkbox"/> fC | |
| Timer RB | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Operation mode | <input type="checkbox"/> Timer mode <input type="checkbox"/> Programmable one-shot generation mode
<input type="checkbox"/> Programmable waveform generation n <input type="checkbox"/> Programmable wait one-shot generation mode | |
| Count source | <input type="checkbox"/> f1 <input type="checkbox"/> f2 <input type="checkbox"/> f8 <input type="checkbox"/> Timer RA under flow | |
| Timer RC | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Operation mode | <input type="checkbox"/> Timer mode <input type="checkbox"/> Input capture function <input type="checkbox"/> Output compare function
<input type="checkbox"/> PWM mode <input type="checkbox"/> PWM2 mode | |
| Count source | <input type="checkbox"/> f1 <input type="checkbox"/> f2 <input type="checkbox"/> f4 <input type="checkbox"/> f8 <input type="checkbox"/> f32 <input type="checkbox"/> fOCO40M
<input type="checkbox"/> fOCO-F <input type="checkbox"/> TRCCLK | |
| Timer RD | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Count | <input type="checkbox"/> Up count <input type="checkbox"/> Down count | |
| Operation mode | <input type="checkbox"/> Timer mode <input type="checkbox"/> Input capture function <input type="checkbox"/> Output compare function
<input type="checkbox"/> PWM mode <input type="checkbox"/> Reset synchronous PWM mode <input type="checkbox"/> Complimentary PWM mode
<input type="checkbox"/> PWM3 mode | |
| Operation Clock | <input type="checkbox"/> f1 <input type="checkbox"/> f2 <input type="checkbox"/> f4 <input type="checkbox"/> f8 <input type="checkbox"/> f32 <input type="checkbox"/> fC2
<input type="checkbox"/> fOCO40M <input type="checkbox"/> fOCO-F <input type="checkbox"/> TRDCLK | |
| Timer RE | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Operation mode | <input type="checkbox"/> Output compare mode | <input type="checkbox"/> Real-time clock mode |
| Operation Clock | <input type="checkbox"/> f4 <input type="checkbox"/> f8 <input type="checkbox"/> f32 <input type="checkbox"/> fC4 | |
| Timer RG | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Count | <input type="checkbox"/> Up count <input type="checkbox"/> Down count | |
| Operation mode | <input type="checkbox"/> Timer mode <input type="checkbox"/> Input capture function <input type="checkbox"/> Output compare function
<input type="checkbox"/> PWM mode | |
| Operation Clock | <input type="checkbox"/> f1 <input type="checkbox"/> f2 <input type="checkbox"/> f4 <input type="checkbox"/> f8 <input type="checkbox"/> f32 <input type="checkbox"/> fC2
<input type="checkbox"/> fOCO40M <input type="checkbox"/> TRGCLKA <input type="checkbox"/> TRGCLKB | |

**RENESAS ELECTRONICS
SINGLE-CHIP 16-BIT MICROCOMPUTER
R5F2L38CCDXXXFP**

ROM PROGRAMMING CONFIRMATION FORM

(13) On which condition will you use UART?

- | | | |
|---|---|--|
| UART0 | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Operation mode | <input type="checkbox"/> Clock synchronous serial I/O mode | <input type="checkbox"/> Clock non-synchronous serial I/O mode |
| UART1 | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Operation mode | <input type="checkbox"/> Clock synchronous serial I/O mode | <input type="checkbox"/> Clock non-synchronous serial I/O mode |
| UART2 | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Operation mode | <input type="checkbox"/> Clock synchronous serial I/O mode | <input type="checkbox"/> Clock non-synchronous serial I/O mode |
| | <input type="checkbox"/> I2C mode | <input type="checkbox"/> Multiprocessor communication function |
| Synchronous Serial Communication Unit (SSU) | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Operation mode | <input type="checkbox"/> Clock synchronous communication mode | <input type="checkbox"/> 4 lines bus communication mode |
| I2C bus Interface | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Operation mode | <input type="checkbox"/> I2C bus interface mode | <input type="checkbox"/> Clock synchronous serial mode |
| LIN Module | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| | <input type="checkbox"/> Master mode | <input type="checkbox"/> Slave mode |

(14) On which condition will you use DTC?

- | | | |
|------------------|--------------------------------------|--------------------------------------|
| Transfer mode | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| | <input type="checkbox"/> Normal mode | <input type="checkbox"/> Repeat mode |
| Transfer times = | <input type="text"/> | |

(15) On which condition will you use A/D converter?

- | | | | | |
|----------------------------|--|--|---|---|
| A/D input pin | <input type="checkbox"/> Use | <input type="checkbox"/> Not use | | |
| Conversion mode | Number of A/D input pins used = _____ pins | | | |
| A/D clock source | <input type="checkbox"/> 8bit A/D | <input type="checkbox"/> 10bit A/D | | |
| Division ratio | <input type="checkbox"/> f1 | <input type="checkbox"/> fOCO-F | | |
| A/D Trigger | <input type="checkbox"/> No division | <input type="checkbox"/> In frequency/2 | <input type="checkbox"/> In frequency/4 | <input type="checkbox"/> In frequency/8 |
| A/D Operation mode | <input type="checkbox"/> Software | <input type="checkbox"/> Timer RD | <input type="checkbox"/> Timer RC | <input type="checkbox"/> External Trigger |
| | <input type="checkbox"/> Not use | | | |
| | <input type="checkbox"/> Single mode | <input type="checkbox"/> Repeat mode0 | <input type="checkbox"/> Repeat mode1 | |
| | <input type="checkbox"/> Single sweep mode | <input type="checkbox"/> Repeat sweep mode | Sweep pin = _____ pins | |
| Disconnection-detection as | <input type="checkbox"/> Use | <input type="checkbox"/> Not use | | |

(16) Will you use D/A converter?

- | | |
|------------------------------|----------------------------------|
| <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
|------------------------------|----------------------------------|

(17) On which condition will you use ComparatorB?

- | | | |
|----------------|------------------------------|----------------------------------|
| Comparator B1 | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Digital Filter | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Comparator B3 | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |
| Digital Filter | <input type="checkbox"/> Use | <input type="checkbox"/> Not use |

