

# Analog input current vs AVcc (AN8-AN11)

Prepared on Sep. 07, 2007

R8C/28-29 Group

Topr = 25 degrees C

AVcc-Vss: 0.1uF Vref-Vss: 0.1uF


ANIN-Vss: 0.1uF

AVcc=Vref

Xin=10MHz  $\phi_{AD}$ =5MHz sample and hold=on Repeat mode

— Analog input = 0V

— Analog input = AVcc



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.