

---

January 31, 2013

## Product Specifications of the PS9332L and PS9332L2

- 1) Built-in active Miller clamp
- 2) Peak output current: 2.0 A
- 3) High speed switching: tPLH, tPHL = 200 ns (max)
- 4) Low pulse width distortion: |tPHL - tPLH| = 75 ns (max)
- 5) Low propagation delay time: PDD = 90 ns (max)
- 6) Low operating current: ICCH, ICCL = 2.5 mA (max)
- 7) Low LED threshold input current: IFLH = 5 mA (max)
- 8) High operating temperature: from -40 to 125 degree C
- 9) Small package: 8 pin-SDIP (8 mm Long creepage distance)
- 10) Safety standard approval: UL, VDE, CSA, SEMKO
- 11) High common mode transient immunity: CMH, CML =  $\pm 50$  kV/ $\mu$ s (min)
- 12) Embossed tape product available: PS9332L/L2-E3: 2000pcs/reel