

General Description

The HXR42400 Trans-impedance and Limiting Amplifier array for LR4 parallel optical applications supports data rates up to 28Gbps and optical reach above +10km. Together with a four-channel photo diode array or discrete detectors, high-capacity, high-availability optical links can be designed for long reach telecom or datacom applications.

The 3.3V SiGe device integrates the Trans-impedance pre-amplifier, the limiting post-amplifier and a versatile CML output stage for four optical channels. Available in die form.

Applications

- Ethernet 100GBASE-LR4 for 10km reach
- 128G Fibre Channel modules
- Long reach Ethernet optical modules
- Long reach InfiniBand EDR optical modules
- Proprietary multi-channel optical modules

Features

- 40 μ App receiver sensitivity for 10^{-12} BER at 28Gbps (LR4: +10km reach)
- Better than 2.4 mApp overload
- 150mW per channel power consumption if operated with an external CDR
- Adjustable output swing size and pre-emphasis in limiting mode
- Adjustable signal detect threshold
- Independent, per channel RSSI
- Optimized for isolated and common cathode photo-detector arrays from multiple vendors
- 750um pitch for high speed I/O channels
- QSFP MSA compliance
- Ethernet compliance

Ordering Information

Part Number	Temp Range	Pin-Package
HXR42400-DNU ¹ HXR42400-TNU ²	-5°C to +95°C	Bare Die: 1.975 x 3.350mm
HXR42400EVB	Room temp	Evaluation Board

For price, delivery schedules, and to place orders, please contact IDT: www.IDT.com/go/sales

Notes:

¹ – Waffle Pack

² – Blue Tape

Block Diagram




Figure 1: Block diagram

**Corporate Headquarters**

6024 Silver Creek Valley Road
San Jose, CA 95138
www.IDT.com

Sales

1-800-345-7015 or 408-284-8200
Fax: 408-284-2775
www.IDT.com/go/sales

Tech Support

www.IDT.com/go/support

DISCLAIMER Integrated Device Technology, Inc. (IDT) and its affiliated companies (herein referred to as "IDT") reserve the right to modify the products and/or specifications described herein at any time, without notice, at IDT's sole discretion. Performance specifications and operating parameters of the described products are determined in an independent state and are not guaranteed to perform the same way when installed in customer products. The information contained herein is provided without representation or warranty of any kind, whether express or implied, including, but not limited to, the suitability of IDT's products for any particular purpose, an implied warranty of merchantability, or non-infringement of the intellectual property rights of others. This document is presented only as a guide and does not convey any license under intellectual property rights of IDT or any third parties.

IDT's products are not intended for use in applications involving extreme environmental conditions or in life support systems or similar devices where the failure or malfunction of an IDT product can be reasonably expected to significantly affect the health or safety of users. Anyone using an IDT product in such a manner does so at their own risk, absent an express, written agreement by IDT.

Integrated Device Technology, IDT and the IDT logo are trademarks or registered trademarks of IDT and its subsidiaries in the United States and other countries. Other trademarks used herein are the property of IDT or their respective third party owners. For datasheet type definitions and a glossary of common terms, visit www.idt.com/go/glossary. All contents of this document are copyright of Integrated Device Technology, Inc. All rights reserved.