

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

# SuperH RISC engine C/C++ Compiler Package

APPLICATION NOTE : < Reference > Data of Library

This document publishes the number of execution cycles of mathematical function library and runtime routine(runtime library) , for the SuperH RISC engine C/C++ Compiler V.9.03

## 1. Mathematical Function Library

### 1.1 Condition of measurement

**Compiler** : SuperH RISC engine C/C++ Compiler V.9.03.00

**Build Condition** : A standard library is created with the condition of showing in Table 1.1.

Table 1.1 The Conditions for Creating a Standard Library

Condition	Options for Creating Library						
	cpu	pic	endian	denormal	round	fpu	double=float
1	sh1	–	big	–	–	–	None
2	sh2	0	big	–	–	–	None
3	sh3	0	big	–	–	–	None
4	sh2e	0	big	–	–	–	None
5	sh4	0	big	off	zero	None	–
6	sh4	0	big	off	zero	single	–
7	sh4	0	big	off	zero	double	–
8	sh4a	0	big	off	zero	None	–
9	sh4a	0	big	off	zero	single	–
10	sh4a	0	big	off	zero	double	–
11	sh2a	0	big	–	–	–	None
12	sh2afpu	0	big	off	zero	None	–
13	sh2afpu	0	big	off	zero	single	–
14	sh2afpu	0	big	off	zero	double	–

## 1.2 Number of Execution Cycles

Table 1.2 Execution Speed of Floating Point Library Functions (SH-1, SH-2, SH-3)

CPU	SH-1	SH-2	SH-3	
Conditions for Creating Library	1	2	3	
Single-precision	sinf	710	335	264
	cosf	711	336	266
	tanf	1,065	464	416
	asinf	3,407	3,258	3,486
	acosf	3,531	3,382	3,625
	atanf	741	337	309
	logf	793	315	326
	sqrtf	510	161	155
	expf	675	310	252
	powf	5,784	5,352	5,740
Double-precision	sin	3,600	3,003	3,277
	cos	3,593	2,996	3,277
	tan	5,031	4,327	4,650
	asin	9,311	8,570	9,115
	acos	9,457	8,716	9,323
	atan	6,204	5,570	6,023
	log	5,903	5,131	5,523
	sqrt	1,894	1,894	1,917
	exp	6,429	5,447	5,879
	pow	12,678	10,850	11,731

Note: Cycle units. The error margin is included in measurements.

**Table 1.3 Execution Speed of Floating Point Library Functions (SH-2E)**

	CPU	SH-2E
<b>Conditions for Creating Library</b>		<b>4</b>
Single-precision	sinf	96
	cosf	92
	tanf	118
	asinf	185
	acosf	195
	atanf	99
	logf	115
	sqrtf	172
	expf	134
	powf	650
Double-precision	sin	4,665
	cos	4,589
	tan	6,449
	asin	7,877
	acos	7,264
	atan	6,698
	log	6,472
	sqrt	1,894
	exp	5,947
pow	10,850	

Note: Cycle units. The error margin is included in measurements.

**Table 1.4 Execution Speed of Floating Point Library Functions (SH-4)**

CPU		SH-4		
Conditions for Creating Library		5	6	7
Single-precision	sinf	76	70	248
	cosf	70	67	245
	tanf	84	82	337
	asinf	75	72	368
	acosf	74	73	360
	atanf	76	71	300
	logf	87	82	338
	sqrtf	-*	-*	-*
	expf	103	94	347
	powf	528	506	913
Double-precision	sin	329	70	248
	cos	311	67	245
	tan	418	82	337
	asin	538	72	368
	acos	501	73	360
	atan	425	71	300
	log	404	82	338
	sqrt	-*	-*	-*
	exp	398	94	347
	pow	1,589	506	913

Note: Cycle units. The error margin is included in measurements.

\*The SH-4 supports the sqrt instruction, and so the sqrt function was omitted.

**Table 1.5 Execution Speed of Floating Point Library Functions (SH-4A)**

CPU		SH-4A		
Conditions for Creating Library	8	9	10	
Single-precision	sinf	108	103	224
	cosf	105	102	224
	tanf	125	124	297
	asinf	106	100	309
	acosf	109	106	307
	atanf	113	106	233
	logf	117	115	259
	sqrtf	-*	-*	-*
	expf	143	136	299
	powf	593	578	839
Double-precision	sin	280	103	224
	cos	265	102	224
	tan	353	124	297
	asin	448	102	308
	acos	420	106	307
	atan	332	105	235
	log	310	115	259
	sqrt	-*	-*	-*
	exp	336	136	298
	pow	1,254	578	839

Note: Cycle units. The error margin is included in measurements.

\*The SH-4A supports the sqrt instruction, and so the sqrt function was omitted.

**Table 1.6 Execution Speed of Floating Point Library Functions (SH-2A,SH2A-FPU)**

CPU		SH-2A		SH2A-FPU	
Conditions for Creating Library		11	12	13	14
Single-precision	sinf	175	80	76	246
	cosf	177	74	71	242
	tanf	275	88	88	336
	asinf	2,510	78	75	364
	acosf	2,607	73	74	353
	atanf	202	77	72	297
	logf	225	89	89	329
	sqrtf	100	-*	-*	-*
	expf	172	104	97	348
	powf	3,940	541	521	960
Double-precision	sin	2,232	298	76	246
	cos	2,227	287	71	242
	tan	3,353	389	88	336
	asin	6,914	472	75	364
	acos	7,027	444	74	353
	atan	4,409	373	72	297
	log	3,950	387	89	329
	sqrt	1,621	-*	-*	-*
	exp	4,123	386	97	348
	pow	8,254	1,313	521	960

Note: Cycle units. The error margin is included in measurements.

\*The SH2A-FPU supports the sqrt instruction, and so the sqrt function was omitted.

## 2. Runtime Routine(Runtime Library)

### 2.1 Condition of measurement

**Compiler** : SuperH RISC engine C/C++ Compiler V.9.03.00

**Build Condition** : A runtime library is created with the condition of showing in Table 2.1.

Table 2.1 Library Creation Options

	cpu	pic	endian	denormaliaztion	round	fpu	double=float
SH-1	sh1	-	big	-	-	-	None
SH-2	sh2	1	big	-	-	-	None
SH-2A	sh2a	1	big	-	-	-	None
SH-3	sh3	1	big	-	-	-	None
SH-4	sh4	0	big	off	zero	None	-
SH-4A	sh4a	0	big	off	zero	None	-

## 2.2 Number of Execution Cycles

Table 2.2 List of Runtime Routine Speeds/FPL Speeds (1)

No.	Type	Function Name	Stack Size	Number of Execution Cycles					
				SH-1	SH-2	SH-2A	SH-3	SH-4	SH-4A
1.1	Multiply	_muli	12	38	-	-	-	-	-
2.1	Divide	_divbs	4	38	38	-	26	24	24
2.2		_divbu	0	28	28	-	19	18	18
2.3		_divws	4	49	50	-	34	31	31
2.4		_divwu	0	39	39	-	26	25	26
2.5		_divls	12	37 / 109	39 / 109	-	26 / 73	20 / 50	21 / 61
2.6		_divlsp	12	-	84	-	-	-	-
2.7		_divlspnm	8	-	57	-	-	-	-
2.8	Integer operations	_divlu	8	31 / 82	33 / 84	-	22 / 56	17 / 50	19 / 50
3.1		Remainder	_modbs	8	57	60	-	40	33
3.2	_modbu		4	39	40	-	27	23	25
3.3		_modws	8	66	69	-	46	39	39
3.4		_modwu	4	49	50	-	34	29	31
3.5		_modls	12	45 / 95	47 / 97	-	31 / 65	23 / 57	23 / 56
3.6		_modlsp	12	-	84	-	-	-	-
3.7		_modlspnm	8	-	57	-	-	-	-
3.8		_modlu	8	34 / 72	36 / 71	-	24 / 48	18 / 43	20 / 46

Note: Cycle units. The error margin is included in measurements.

The routine that processing is greatly different depending on the input value publishes each of the maximum pattern and the minimum pattern. [minimum/maximum]

**Table 2.2 List of Runtime Routine Speeds/FPL Speeds (2)**

No.	Type	Function Name	Stack Size	Number of Execution Cycles					
				SH-1	SH-2	SH-2A	SH-3	SH-4	SH-4A
4.1	Add	<u>_adds</u>	24	129	139	60	80	-	-
4.2	Post Increment	<u>_addd_a</u>	40	243	265	114	159	-	-
	Post Decrement								
5.1	Subtract	<u>_subs</u>	24	135	145	64	84	-	-
5.2		<u>_subd_a</u>	40	251	274	119	167	-	-
6.1	Multiply	<u>_muls</u>	24	144	125	62	86	-	-
6.2		<u>_muld_a</u>	60	379	318	151	210	-	-
7.1	Divide	<u>_divs</u>	20	175	192	93	120	-	-
7.2	Floating point operations	<u>_divd_a</u>	56	536	512	265	325	-	-
8.1	Compare	<u>_eqs</u>	20	16	17	9	11	-	-
8.2		<u>_eqd_a</u>	32	90	108	50	69	-	-
8.3		<u>_nes</u>	20	16	17	9	11	-	-
8.4		<u>_ned_a</u>	32	90	108	50	69	-	-
8.5		<u>_gts</u>	20	33	36	16	24	-	-
8.6		<u>_gtd_a</u>	32	90	108	50	70	-	-
8.7		<u>_lts</u>	20	33	36	16	24	-	-
8.8		<u>_ltd_a</u>	32	90	108	50	70	-	-
8.9		<u>_ges</u>	20	33	36	16	24	-	-
8.10		<u>_ged_a</u>	32	90	108	50	70	-	-
8.11		<u>_les</u>	20	33	36	16	24	-	-
8.12		<u>_led_a</u>	32	90	108	50	70	-	-

Note: Cycle units. The error margin is included in measurements.

**Table 2.2 List of Runtime Routine Speeds/FPL Speeds (3)**

No.	Type	Function Name	Stack Size	Number of Execution Cycles					
				SH-1	SH-2	SH-2A	SH-3	SH-4	SH-4A
9.1	Convert sign	<u>_negs</u>	0	7	7	4	5	-	-
9.2		<u>_negd_a</u>	12	30	39	18	26	-	-
10.1	Convert	<u>_stod_a</u>	12	66	73	35	50	-	-
10.2		<u>_dtos_a</u>	20	122	128	61	82	-	-
10.3		<u>_stoi</u>	12	50	63	21	31	-	-
10.4		<u>_dtoi_a</u>	20	148	141	72	86	-	-
10.5		<u>_stou</u>	12	50	63	21	31	-	-
10.6		<u>_dtou_a</u>	20	148	141	72	86	-	-
10.7		<u>_itos</u>	12	88	91	45	59	-	-
10.8		<u>_itod_a</u>	12	189	179	96	110	-	-
10.9		<u>_utos</u>	8	81	82	46	52	-	-
10.10		<u>_utod_a</u>	8	99	96	51	61	-	-

Note: Cycle units. The error margin is included in measurements.

**Table 2.2 List of Runtime Routine Speeds/FPL Speeds (4)**

No.	Type	Function Name	Stack Size	Number of Execution Cycles					
				SH-1	SH-2	SH-2A	SH-3	SH-4	SH-4A
11.1	Move area	_quick_evn_mv vn	4	12+3*(n/4)					
11.2		_quick_mvsn	8	17+3*(n/4) (n<=64) 24+1.625*(n/4) (n>=68)					
11.3		_quick_odd_mv vn	4	12+3*(n/4)					
11.4		_slow_mvsn	12	21+5*n+3*((n-1)/4)					
12.1	Compare character	_quick_strcmp 1	0	26+7*(n/4)+5*((n-1)%4)					
12.2	string	_slow_strcmp1	0	35+7*n					
13.1	Copy	_quick_strcpy	16	30+6*(n/4)+4*((n-1)%4)					
13.2	character string	_slow_strcpy	24	24+6*n+2*((n-1)/4)					
14.1	Left-shift	_sftl	4	19 / 42	21 / 39	-	-	-	-
15.1	Right-shift	_sftsl	4	19 / 42	21 / 39	-	-	-	-
15.2		_sftra	4	20 / 43	22 / 47	-	-	-	-
15.3		_sta_sftra6	0	13	14	-	-	-	-
15.4		_sta_sftra7	0	14	15	-	-	-	-
15.5		_sta_sftra10	0	16	18	-	-	-	-
15.6		_sta_sftra11	0	17	19	-	-	-	-
15.7		_sta_sftra12	0	17	19	-	-	-	-
15.8		_sta_sftra13	0	17	19	-	-	-	-
15.9		_sta_sftra21	0	13	14	-	-	-	-
15.10		_sta_sftra27	0	13	14	-	-	-	-
15.11		_sta_sftra28	0	13	14	-	-	-	-
15.12		_sta_sftra29	0	14	15	-	-	-	-
16.1	Packed structure	_pack1_st16	4	12	13	5	10	6	8
16.2		_pack1_st32	4	18	19	8	16	8	12
16.3		_pack1_st64	4	33	35	16	30	16	22
16.4		_pack1_ld16	4	17	18	10	13	11	14
16.5		_pack1_ld32	4	29	30	17	22	18	-
16.6		_pack1_ld64	8	67	73	38	52	39	53
16.7		_bfs64sp1	60	289 / 599	333 / 580	174 / 339	205 / 392	141 / 295	163 / 266
16.8		_bfs64up1	60	289 / 599	333 / 580	174 / 339	205 / 392	141 / 295	163 / 266
16.9		_bfx64sp1	36	239 / 591	276 / 563	144 / 334	194 / 385	130 / 289	147 / 256
16.10		_bfx64up1	40	227 / 588	264 / 550	144 / 332	186 / 377	124 / 282	149 / 266

Note: Cycle units. The error margin is included in measurements.

The routine that processing is greatly different depending on the input value publishes each of the maximum pattern and the minimum pattern. [minimum/maximum]

**Table 2.2 List of Runtime Routine Speeds/FPL Speeds (5)**

No.	Type	Function Name	Stack Size	Number of Execution Cycles					
				SH-1	SH-2	SH-2A	SH-3	SH-4	SH-4A
17.1	long long	_mul64	36	134	92	40	64	48	45
17.2		_div64s	64	148 / 601	165 / 351	87 / 183	108 / 245	72 / 195	64 / 161
17.3		_div64u	60	121 / 527	137 / 326	74 / 169	90 / 227	59 / 182	51 / 152
17.4		_mod64s	64	142 /550	158 / 342	80 / 179	105 / 241	65 / 190	61 / 155
17.5		_mod64u	60	117 / 569	132 / 312	70 / 165	87 / 223	55 / 178	48 / 147
17.6		_shlld64	20	86	96	35	45	27	35
17.7		_shlrd64	20	85	94	37	48	29	40
17.8		_shard64	24	93	105	38	49	29	39
17.9		_bfs64s	52	133 / 446	157 / 404	82 / 241	79 / 266	51 /205	59 / 160
17.10		_bfs64u	52	133 / 446	157 / 404	82 / 241	79 / 266	51 /205	59 / 160
17.11		_bfx64s	24	89 / 441	105 / 392	47 / 238	71 / 262	43 / 202	42 / 151
17.12		_bfx64u	24	77 / 428	93 / 379	49 / 238	63 / 254	37 / 195	38 / 148
17.13		_cmplt64	4	23	26	12	16	13	16
17.14		_cmplt64u	4	23	26	12	16	13	16
17.15		_cmpgt64	4	23	26	12	16	13	16
17.16		_cmpgt64u	4	23	26	12	16	13	16
17.17		_cmple64	4	23	26	12	16	13	16
17.18		_cmple64u	4	23	26	12	16	13	16
17.19		_cmpge64	4	23	26	12	16	13	16
17.20		_cmpge64u	4	23	26	12	16	13	16
17.21		_convs64	20	146	147	81	97	-	-
17.22		_convs64u	20	146	147	81	97	-	-
17.23		_convf64	20	-	-	-	-	74	67
17.24		_convf64u	20	-	-	-	-	74	67
17.25		_convw64	20	175	161	86	102	-	-
17.26		_convw64u	20	175	161	86	102	-	-
17.27		_convd64	20	-	-	-	-	75	77
17.28		_convd64u	20	-	-	-	-	75	77
17.29		_conv64s	24	258	260	141	166	-	-

Note: Cycle units. The error margin is included in measurements.

The routine that processing is greatly different depending on the input value publishes each of the maximum pattern and the minimum pattern. [minimum/maximum]

**Table 2.2 List of Runtime Routine Speeds/FPL Speeds (6)**

No.	Type	Function Name	Stack Size	Number of Execution Cycles					
				SH-1	SH-2	SH-2A	SH-3	SH-4	SH-4A
17.30	long long	_conv64us	24	242	246	136	156	-	-
17.31		_conv64f	28	-	-	-	-	78	75
17.32		_conv64uf	28	-	-	-	-	71	65
17.33		_conv64w	20	164	168	88	111	-	-
17.34		_conv64uw	20	133	140	72	93	-	-
17.35		_conv64d	20	-	-	-	-	80	84
17.36		_conv64ud	20	-	-	-	-	67	70

Note: Cycle units. The error margin is included in measurements.

The routine that processing is greatly different depending on the input value publishes each of the maximum pattern and the minimum pattern. [minimum/maximum]

**Table 2.3 List of Runtime Routine Speeds/FPL Speeds**

No.	Type	Function Name	Stack Size	Number of Execution Cycles		
				SH2-DSP	SH3-DSP	SH4AL-DSP
1.1	DSP	_padd24	8	50	33	32
1.2		_padd40	8	60	38	36
1.3		_pdiv16	24	830	514	442
1.4		_pdiv32	36	1164	742	625
1.5		_pdiv24	36	2279	1446	1246
1.6		_pdiv40	36	2750	1696	1439
1.7		_pmul32	16	51	35	32
1.8		_pmul24	24	143	94	87
1.9		_pmul40	44	188	135	105
1.10		_psub24	8	50	33	32
1.11		_psub40	8	60	38	36
1.12		_pconv16s	12	19 / 199	12 / 123	20 / 102
1.13		_pconv16w	16	57 / 212	37 / 126	39 / 115
1.14		_pconv32s	12	20 / 340	12 / 196	19 / 140
1.15		_pconv32w	16	53 / 381	34 / 233	37 / 148
1.16		_pconv24s	12	18 / 280	11 / 171	19 / 116
1.17		_pconv24w	16	58 / 286	38 / 168	33 / 172
1.18		_pconv40s	16	29 / 568	18 / 339	24 / 220
1.19		_pconv40w	20	41 / 515	29 / 316	25 / 231
1.20		_pconvs16	16	71 / 1597	47 / 937	50 / 459
1.21		_pconvs32	16	70 / 1341	48 / 809	44 / 457
1.22		_pconvs24	16	104 / 1633	68 / 958	60 / 482
1.23		_pconvs40	16	106 / 1618	70 / 951	64 / 467
1.24		_pconvw16	16	86 / 12374	56 / 7223	49 / 3156
1.25		_pconvw32	20	106 / 3160	68 / 1848	59 / 853
1.26		_pconvw24	20	135 / 10354	86 / 6215	77 / 3172
1.27		_pconvw40	20	142 / 10338	91 / 6207	84 / 3160
1.28		_pcmplt40	4	30	19	17
1.29		_pcmple40	4	30	19	20
1.30		_pcmpgt40	4	30	19	20
1.31		_pcmpge40	4	30	19	20
1.32		_pcmpeq40	4	28	18	16
1.33		_pcmpne40	4	29	18	20
1.34		_pdiv16_sat	28	859	530	459
1.35		_pdiv32_sat	40	1262	790	625
1.36		_pmul32_sat	16	66	42	38

Note: Cycle units. The error margin is included in measurements.

The routine that processing is greatly different depending on the input value publishes each of the maximum pattern and the minimum pattern. [minimum/maximum]

### Website and Support <website and support,ws>

Renesas Technology Website

<http://www.renesas.com/>

Inquiries

<http://www.renesas.com/inquiry>

[csc@renesas.com](mailto:csc@renesas.com)

### Revision Record <revision history,rh>

Rev.	Date	Description	
		Page	Summary
1.00	Jun.1.07	—	First edition issued
2.00	Apr.1.08	—	Re-measurement by V.9.02.00
3.00	Oct.7.09	—	Re-measurement by V.9.03.00

**Notes regarding these materials**

1. This document is provided for reference purposes only so that Renesas customers may select the appropriate Renesas products for their use. Renesas neither makes warranties or representations with respect to the accuracy or completeness of the information contained in this document nor grants any license to any intellectual property rights or any other rights of Renesas or any third party with respect to the information in this document.
2. Renesas shall have no liability for damages or infringement of any intellectual property or other rights arising out of the use of any information in this document, including, but not limited to, product data, diagrams, charts, programs, algorithms, and application circuit examples.
3. You should not use the products or the technology described in this document for the purpose of military applications such as the development of weapons of mass destruction or for the purpose of any other military use. When exporting the products or technology described herein, you should follow the applicable export control laws and regulations, and procedures required by such laws and regulations.
4. All information included in this document such as product data, diagrams, charts, programs, algorithms, and application circuit examples, is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas products listed in this document, please confirm the latest product information with a Renesas sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas such as that disclosed through our website. (<http://www.renesas.com>)
5. Renesas has used reasonable care in compiling the information included in this document, but Renesas assumes no liability whatsoever for any damages incurred as a result of errors or omissions in the information included in this document.
6. When using or otherwise relying on the information in this document, you should evaluate the information in light of the total system before deciding about the applicability of such information to the intended application. Renesas makes no representations, warranties or guaranties regarding the suitability of its products for any particular application and specifically disclaims any liability arising out of the application and use of the information in this document or Renesas products.
7. With the exception of products specified by Renesas as suitable for automobile applications, Renesas products are not designed, manufactured or tested for applications or otherwise in systems the failure or malfunction of which may cause a direct threat to human life or create a risk of human injury or which require especially high quality and reliability such as safety systems, or equipment or systems for transportation and traffic, healthcare, combustion control, aerospace and aeronautics, nuclear power, or undersea communication transmission. If you are considering the use of our products for such purposes, please contact a Renesas sales office beforehand. Renesas shall have no liability for damages arising out of the uses set forth above.
8. Notwithstanding the preceding paragraph, you should not use Renesas products for the purposes listed below:
  - (1) artificial life support devices or systems
  - (2) surgical implantations
  - (3) healthcare intervention (e.g., excision, administration of medication, etc.)
  - (4) any other purposes that pose a direct threat to human life
 Renesas shall have no liability for damages arising out of the uses set forth in the above and purchasers who elect to use Renesas products in any of the foregoing applications shall indemnify and hold harmless Renesas Technology Corp., its affiliated companies and their officers, directors, and employees against any and all damages arising out of such applications.
9. You should use the products described herein within the range specified by Renesas, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas shall have no liability for malfunctions or damages arising out of the use of Renesas products beyond such specified ranges.
10. Although Renesas endeavors to improve the quality and reliability of its products, IC products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Please be sure to implement safety measures to guard against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other applicable measures. Among others, since the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
11. In case Renesas products listed in this document are detached from the products to which the Renesas products are attached or affixed, the risk of accident such as swallowing by infants and small children is very high. You should implement safety measures so that Renesas products may not be easily detached from your products. Renesas shall have no liability for damages arising out of such detachment.
12. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written approval from Renesas.
13. Please contact a Renesas sales office if you have any questions regarding the information contained in this document, Renesas semiconductor products, or if you have any other inquiries.