

# RZ FAMILY MICROPROCESSORS

64-Bit & 32-Bit High-performance MPUs



# THE NEXT-GENERATION PROCESSOR TO MEET THE NEEDS OF THE SMART SOCIETY HAS ARRIVED.



## CONTENTS

RZ FAMILY PORTFOLIO	04
RZ/V SERIES	06
RZ/N SERIES	14
RZ/T SERIES	24
RZ/G SERIES	34
RZ/A SERIES	44
RZ FAMILY ECOSYSTEM PARTNERS	50
RZ FAMILY PACKAGE LINEUP	51

The utilization of intelligent technology is advancing in all aspects of our lives, including electric household appliances, industrial equipment, building management, power grids, and transportation. The cloud-connected “smart society” is coming ever closer to realization. Microcontrollers are now expected to provide powerful capabilities not available previously, such as high-performance and energy-efficient control combined with interoperability with IT networks, support for human-machine interfaces, and more. To meet the demands of this new age, Renesas has drawn on its unmatched expertise in microcontrollers to create the RZ family of embedded processors. The lineup of these “next-generation processors that are as easy to use as conventional microcontrollers” to meet different customer requirements.

## The Zenith of the Renesas micro

As embedded processors to help build the next generation of advanced products, the RZ family offers features not available elsewhere and brings new value to customer applications.

### Positioning of the RZ Family

	Microcontrollers & Microprocessors, System-on-Chips (SoCs)	Analog and Power Devices
	<b>High-end 32/64-bit MPUs</b> High-resolution HMI, Industrial network & real-time control	<ul style="list-style-type: none"> <li>▪ Analog products</li> <li>▪ Clocks &amp; Timing</li> <li>▪ Interface &amp; Connectivity</li> <li>▪ Memory &amp; Logic</li> <li>▪ Power &amp; Power management</li> <li>▪ Programmable Mixed-signal, ASIC, &amp; IP products</li> </ul> <hr/> <ul style="list-style-type: none"> <li>▪ Timing</li> <li>▪ Wireless Power</li> <li>▪ Battery Management</li> <li>▪ Power Devices</li> </ul>
	<b>Advanced 32-bit MCUs</b> Arm ecosystem, Advanced security, Intelligent IoT	
	<b>High Power Efficiently 32-bit MCUs</b> Motor control, Capacitive touch, Functional safety, GUI	
	<b>RISC-V products</b> <ul style="list-style-type: none"> <li>General-purpose 64-bit MPUs (RZ/Five Group)</li> <li>Application-specific 32-bit MCUs</li> </ul>	
	<b>Ultra-low Energy 8/16-bit MCUs</b> Bluetooth® Low Energy, SubGHz, LoRa®-based Solutions Automotive actuators & sensors, Low-end ECUs	
	<b>Automotive 32-bit MCUs</b> Rich functional safety and embedded security features	
	<b>Automotive SoCs</b> Next generation of automotive computing	
		<ul style="list-style-type: none"> <li>▪ RF products</li> <li>▪ Sensor products</li> <li>▪ Space &amp; Harsh environment</li> </ul>
		<ul style="list-style-type: none"> <li>▪ Power Management</li> <li>▪ Sensors</li> <li>▪ Video &amp; Display</li> </ul>

## RZ Family Portfolio

### RZ/V Series

64-bit Cortex®-A CPU, Up to 1.8GHz  
Low-power Embedded AI  
for Vision-AI Application

### RZ/N Series

32/64-bit Cortex®-A/R/M CPU, Up to 1.2GHz  
Multi-protocol Industrial Network and TSN  
for PLC, Remote IO, Gateway

### RZ/T Series

32/64-bit Cortex®-A/R/M CPU, Up to 1.2GHz  
Real-time Control  
Multi-protocol Industrial Network and TSN, Multi-protocol Encoder I/F  
for AC servo, Actuator, Inverter

### RZ/G Series

32/64-bit Cortex®-A CPU, Up to 1.5Hz  
64-bit RISC-V CPU, Up to 1.0GHz  
for HMI and IoT Application

### RZ/A Series

32/64-bit Cortex®-A CPU, Up to 1GHz  
- DDR3L/4 (RZ/A3UL)  
- Up to 10MB Embedded RAM for HMI Application

Linux / Android™ / Multi-OS with RTOS

RTOS

<p><b>Vision AI</b> <b>RZ/V Series</b></p>	<p><b>RZ/V2M</b> 1.0GHz Dual-core Cortex-A53, DRP-AI(576-MAC), 4K-ISP</p>	<p><b>RZ/V2H</b> 1.8GHz Quad-core Cortex-A55, DRP-AI3(4K-MAC), 4K-ISP, 3D-GPU</p>		
<p><b>Industrial Network</b> <b>RZ/N Series</b></p>	<p><b>RZ/V2MA</b> 1.0GHz Dual-core Cortex-A53, DRP-AI(576-MAC), OpenCV Accelerator</p>	<p><b>RZ/V2N</b> 1.8GHz Quad-core Cortex-A55, DRP-AI3(2K-MAC), 4K-ISP, 3D-GPU</p>	<p><b>RZ/N1S</b> 500MHz Cortex-A7, 125MHz Cortex-M3, Industrial Ethernet</p>	<p><b>RZ/N2L</b> 400MHz Cortex-R52, Industrial Ethernet</p>
<p><b>Real-time Control</b> <b>RZ/T Series</b></p>	<p><b>RZ/V2L</b> 1.2GHz Dual-core Cortex-A55, DRP-AI(576-MAC), 3D-GPU</p>		<p><b>RZ/N1L</b> 125MHz Cortex-M3, Industrial Ethernet</p>	<p><b>RZ/T2H</b> 1.2GHz Quad-core Cortex-A55, 1.0GHz Dual-core Cortex-R52, 9-axis Motor Control, Industrial Ethernet</p>
<p><b>IoT Edge</b> <b>RZ/G Series</b></p>	<p><b>RZ/T2M</b> 800MHz Dual-core Cortex-R52, 2-axis Motor Control, Industrial Ethernet, OTFD</p>	<p><b>RZ/T1</b> 600MHz Cortex-R4, 150MHz Cortex-M3, 1-axis Motor Control, Industrial Ethernet</p>	<p><b>RZ/T2L</b> 800MHz Cortex-R52, 2-axis Motor Control, EtherCAT</p>	<p><b>RZ/T2M</b> 800MHz Dual-core Cortex-R52, 2-axis Motor Control, Industrial Ethernet</p>
<p><b>HMI</b> <b>RZ/G Series</b> <b>RZ/A Series</b></p>	<p><b>RZ/G3S</b> 1.1GHz Cortex-A55, 250MHz Dual-core Cortex-M33, LPDDR4/DDR4</p>	<p><b>RZ/Five</b> RISC-V, 1.0GHz AX45MP, DDR4/3L, GbEthernet, CAN-FD</p>		
<p><b>RZ/G1H</b> 1.4GHz Quad-core Cortex-A15 + Cortex-A7, DDR3, 3DG, H.264</p>	<p><b>RZ/G1M</b> 1.5GHz Dual-core Cortex-A15, DDR3L, 3DG, H.264</p>	<p><b>RZ/G2H</b> 1.5GHz Quad-core Cortex-A57 + Cortex-A53, LPDDR4, 3DG, H.264/5</p>	<p><b>RZ/A1H</b> 400MHz Cortex-A9, 10MB RAM, LCDC, JPEG, Ethernet, USB</p>	<p><b>RZ/A2M</b> 528MHz Cortex-A9, 4MB RAM, LCDC, JPEG, MIPI-CSI, Ethernet, USB</p>
<p><b>RZ/G1N</b> 1.5GHz Dual-core Cortex-A15, DDR3L, 3DG, H.264</p>	<p><b>RZ/G1E</b> 1.0GHz Dual-core Cortex-A7, DDR3, 3DG, H.264</p>	<p><b>RZ/G2M</b> 1.5GHz Dual-core Cortex-A57 + Cortex-A53, LPDDR4, 3DG, H.264/5</p>	<p><b>RZ/A1M</b> 400MHz Cortex-A9, 5MB RAM, LCDC, JPEG, Ethernet, USB</p>	<p><b>RZ/A3UL</b> 1.0GHz Cortex-A55, DDR4/3L, LCDC, GbEthernet, USB</p>
<p><b>RZ/G2N</b> 1.5GHz Dual-core Cortex-A57, LPDDR4, 3DG, H.264/5</p>	<p><b>RZ/G2E</b> 1.2GHz Dual-core Cortex-A53, DDR3L, 3DG, H.264/5</p>	<p><b>RZ/G2L</b> 1.2GHz Dual-core Cortex-A55, DDR4/3L, 3DG, H.264, CAN-FD</p>	<p><b>RZ/A1LU</b> 400MHz Cortex-A9, 3MB RAM, LCDC, JPEG, Ethernet, USB</p>	<p><b>RZ/A1L</b> 400MHz Cortex-A9, 3MB RAM, LCDC, Ethernet, USB</p>
<p><b>RZ/G2LC</b> 1.2GHz Dual-core Cortex-A55, DDR4/3L, 3DG, CAN-FD</p>	<p><b>RZ/G2UL</b> 1.0GHz Cortex-A55, DDR4/3L, CAN-FD, ADC</p>	<p><b>RZ/A1LC</b> 400MHz Cortex-A9, 2MB RAM, LCDC, Ethernet, USB</p>		

## RZ/V Series

### RZ/V Series Features

- AI performance scalability to cover wide range of applications
- Integrates Renesas original AI accelerator DRP-AI to deliver up to 80TOPS
- Realize best AI power efficiency up to 10TOPS/W
- Integrated ISP (upto 4k) and Video Codec
- Provides Vision Processing Accelerator (OpenCV) as DRP library
- Equipped with a 3D Graphics Engine for fast image rendering

\* DRP: Dynamically Reconfigurable Processor

### RZ/V Series Application



Service Robot



Smart City



Retail



Smart Home



Industrial



Access Control



AGV/AMR



AI Camera



Agriculture



Healthcare




Smart Building



Driver Monitoring System

## Features of DRP-AI

DRP-AI consists of AI-MAC (multiply-accumulate processor) and DRP (reconfigurable processor). AI processing can be executed at high speed by assigning AI-MAC for operations on the convolution layer and fully connected layer, and DRP for other complex processing such as preprocessing and pooling layer.




For more detailed technical information on DRP-AI, please refer to the following white paper.

White Paper: [Embedded AI-Accelerator DRP-AI](#)

[Next Generation Highly Power-Efficient AI Accelerator \(DRP-AI3\): 10x Faster Embedded Processing in Advanced AI for Autonomous Systems](#)

While most AI accelerators specialize only in AI inference and rely on the CPU for pre- and post-processing, DRP-AI integrates pre- and post-processing and AI inference into a single DRP-AI hardware to achieve superior AI processing performance.

	Other AI Accelerator	DRP-AI
Pre-processing	CPU	DRP-AI
Inference	AI Accelerator	DRP-AI
Post-processing	CPU	DRP-AI



## RZ/V Series Specification

Items	RZ/V2H	<b>NEW</b> RZ/V2N	RZ/V2L	RZ/V2M	RZ/V2MA
Main CPU	Cortex-A55 × 4 Cortex-R8 × 2	Cortex-A55 × 4	Cortex-A55 × 2	Cortex-A53 × 2	Cortex-A53 × 2
Sub CPU	Cortex-M33	Cortex-M33	Cortex-M33	–	–
AI Accelerator Performance (DRP-AI)	10 TOPS/W Max. 80 TOPS (Sparse model) Resnet50: 830 Inference/Sec	10 TOPS/W Max. 15 TOPS (Sparse model) Resnet50: 769 Inference/Sec	1 TOPS/W Max. 0.5 TOPS Resnet50: 17 Inference/Sec	1 TOPS/W Max. 1 TOPS Resnet50: 28 Inference/Sec	1 TOPS/W Max. 1 TOPS Resnet50: 28 Inference/Sec
ISP for Camera	4K ISP (option) (hardware)	4K ISP (option) (hardware)	Simple ISP (software)	4K ISP (hardware)	–
MIPI CSI-2 I/F	4-lane × 4ch	4-lane × 2ch	4-lane × 1ch	4-lane × 2ch	–
Computer Vision Accelerator	OpenCV Accelerator	OpenCV Accelerator	OpenCV Accelerator	–	OpenCV Accelerator
Video Codec	H.265, H.264	H.265, H.264	H.264	H.265, H.264	H.265, H.264
Graphics	3D Graphics (option)	3D Graphics (option)	3D Graphics	2D Graphics	–
Package	1368-pin FCBGA, 19mm × 19mm 0.5mm ball pitch	840-pin FCBGA, 15mm × 15mm 0.5mm ball pitch	551-pin PBGA, 21mm × 21mm 0.8mm ball pitch 456-pin PBGA, 15mm × 15mm 0.5mm ball pitch	841-pin FCBGA, 15mm × 15mm 0.5mm ball pitch	841-pin FCBGA, 15mm × 15mm 0.5mm ball pitch

## Features of ISP

Supports ISP function to realize Vision System

## ISP Comparison Table

Item		RZ/V2H	<b>NEW</b> RZ/V2N	RZ/V2L	RZ/V2M
ISP		H/W ISP Arm Mali™-C55 ISP	H/W ISP Arm Mali™-C55 ISP	S/W ISP Simple ISP by DRP library	H/W ISP 3rd party IP
Maximum Resolution		Up to 4K	Up to 4K	Up to 5M	Up to 4K
Support CMOS Sensor		User's choice	User's choice	User's choice	Select from IMX415, IMX462, IMX568, AR1335
Camera I/F		4× MIPI CSI-2 (4-lane)	2× MIPI CSI-2 (4-lane)	1× MIPI CSI-2 (4-lane), 1× Parallel	2× MIPI CSI-2 (4-lane)
Deliverables	ISP H/W Specifications	✓	✓	✓	–
	Driver/API Specifications	✓	✓	✓	✓
	Software	✓	✓	✓	✓
	Image Tuning Tool	✓	✓	✓	✓

## ISP Function

Item	RZ/V2H	<b>NEW</b> RZ/V2N	RZ/V2L	RZ/V2M
Support Image Size	3840 × 2160 p × 30 fps × 2 1920 × 1080 p × 60 fps × 2	3840 × 2160 p × 30 fps 1920 × 1080 p × 30 fps × 2	1920 × 1080 p × 15 fps	3840 × 2160 p × 30 fps 1920 × 1080 p × 30 fps × 2
AE (Auto Exposure), AWB (Auto White Balance)	✓	✓	✓	✓
Black Level Correction	✓	✓	✓	✓
Demosaic	✓	✓	✓	✓
Flicker Correction	✓	✓		✓
Obtain Focus Analysis Results	✓	✓		✓
Tone Mapping Settings	✓	✓		✓
Wide Dynamic Range Correction	✓	✓		✓
Chromatic Aberration Correction	✓	✓	✓	✓
Purple Fringing Correction	✓	✓		✓
Shading Correction	✓	✓		✓
Sharpness Correction	✓	✓	✓	✓
2D Noise Reduction	✓	✓	✓	✓
3D Noise Reduction	✓	✓	✓	
JPEG Conversion				✓
Resize	✓ (Downscale only)	✓ (Downscale only)	✓ (Downscale only)	✓



## RZ/V2M Group

### CPU

- 2× Cortex-A53 (up to 1.0GHz)

### Vision and AI

- AI Accelerator; DRP-AI at 1.0 TOPS/W class
- Image Signal Processor (ISP) of multi-stream available
- Camera Interface; 2× MIPI CSI-2
- Face and Human Detection Engine

### Video and Graphics

- H.265/H.264 Multi Codec
- JPEG Codec Engine
- 2D Graphics Engine

### Display Interface

- HDMI 1.4a

### Audio Interface

- Serial Sound Interface × 1ch

### Communication Interface

- SD Host × 2ch
- PCI-Express 2.0 (2-lane) × 1ch
- Gigabit Ethernet × 1ch
- USB3.1 Gen1 Host/Function × 1ch
- I<sup>2</sup>C Bus × 4ch
- CSI × 6ch
- UART × 2ch


### Memory Interface

- eMMC 4.5.1 × 1ch
- 32-bit LPDDR4-3200 × 1ch

### Security

- Hardware Security Engine

## RZ/V2M Group Block Diagram



## RZ/V2L Group

### CPU

- 2× Cortex-A55 or 1× Cortex-A55 (up to 1.2GHz)
- 1× Cortex-M33 (up to 200MHz)

### Vision and AI

- AI Accelerator; DRP-AI
- \* Image Signal Processor (Simple ISP) Function is provided as DRP Library
- Camera Interface; 1× MIPI CSI-2 / 1× Digital Parallel

### Video and Graphics

- H.264 Codec
- 3D Graphics Engine

### Display Interface

- MIPI DSI (4-lane)
- Digital Parallel

### Audio Interface

- Serial Sound Interface × 4ch

### Communication Interface

- Gigabit Ethernet × 2ch
- USB2.0 Host × 1ch
- USB2.0 Host/Function × 1ch
- I<sup>2</sup>C Bus × 4ch
- SCI × 2ch
- UART × 5ch


### Memory Interface

- SPI Multi I/O (8bit DDR) × 1ch
- SDHI (UHS-I) / eMMC × 1ch
- 16-bit DDR3L-1333/DDR4-1600 × 1ch

### Security

- Hardware Security Engine (Option)

## RZ/V2L Group Block Diagram






**RZ/V2N Group** NEW

- CPU**
- 4x Cortex-A55 (up to 1.8GHz)
  - 1x Cortex-M33 (up to 200MHz)
- Vision and AI**
- AI Accelerator: DRP-AI at 10TOPS/W class
  - Camera Interface: MIPI CSI-2 (1/2/4-lane) x 2ch
- Video and Graphics**
- H.265/H.264 Multi Codec
  - 3D Graphics Engine Mali-G31 (Option)
  - Image Signal Processor (ISP) Mali-C55 (Option)
  - Display OUT: MIPI DSI (1/2/4-lane) x 1ch
- Communication Interface**
- SD Host x 2ch
  - PCI-Express 3.0 (2-lane x 1)
  - Gigabit Ethernet x 2ch
  - USB3.2 x 1ch, USB2.0 x 1ch
- Memory Interface**
- eMMC 4.5.1 x 1ch
  - 32bit LPDDR4/4X-3200 x 1ch
- Security**
- Hardware Security Engine (Option)

**RZ/V2N Group Block Diagram**




**Code Generation Support: Flexible Software Package (FSP) + Smart Configurator (SC)**

(Supported products: RZ/V2L, RZ/V2H, RZ/V2N)

The FSP includes everything you'll need to start developing software: board-dependent programs, peripheral function drivers, middleware, and documentation on how to use them.


Smart Configurator is a utility based on the concept of "combining software components freely." The intuitive GUI makes it easy to configure pins and FSP driver settings and to generate source code customized for your use case. It works together with integrated development environments such as e² studio.



## Flexible Development Kits


These products are evaluation boards with RZ/V series configured as the key device and are capable of easily implementing software development such as camera sensor input image processing, low power consumption AI inference, video streaming, and etc.

### RZ/V2H Evaluation Board Kit



- P/N: RTK0EF0168C04000BJ
- LPDDR4X: 8GB × 2
- xSPI Flash Memory: 64MB
- micro SD × 2
- High Speed Interface
  - Gigabit Ethernet × 2
  - USB3.2 Gen × 2 (Host)
  - USB2.0 × 2 (OTG × 1, Host-only × 1)
  - PCIe Gen3 × 1 (4-lane) (Root Complex)
  - MIPI CSI-2 Camera Interface × 4
  - MIPI DSI Display Interface × 1

### RZ/V2N Evaluation Board Kit **NEW**



- P/N: RTK0EF0186C03000BJ
- LPDDR4X: 8GB × 1
- xSPI Flash Memory: 64MB
- eMMC × 1 or micro SD × 1
- micro SD × 1
- High Speed Interface
  - Gigabit Ethernet × 2
  - USB3.2 Gen × 1 (Host)
  - USB2.0 × 1 (OTG)
  - PCIe Gen3 × 1 (2-lane) (Root Complex)
  - MIPI CSI-2 Camera Interface × 2
  - MIPI DSI Display Interface × 1

### RZ/V2L Evaluation Board Kit




- P/N: RTK9754L23S01000BE
- P/N: RTK9754L27S01000BE (Secure Type)
- DDR4 SDRAM: 2GB
- eMMC: 64GB
- QSPI NOR Flash: 512MB
- microSD × 1
- A/D Converter Interface

### RZ/V2M Evaluation Board Kit



- P/N: V2M\_EVK
- CMOS image sensor equipped board included (SONY/IMX415, CS mount equipped)
- LPDDR4: 32Gbit
- eMMC: 16GB
- HDMI Type-A × 1
- USB3.1 Gen1 Type-C × 1
- microSD × 1

### RZ/V2MA Evaluation Board Kit



- P/N: SBEV-RZ/V2MA-KIT
- LPDDR4: 32Gbit
- eMMC: 16GB
- Ethernet × 1
- USB3.1 Gen1 Type-C × 1
- microSD × 1
- PCIe × 4 slot (2-lane available)

### “Easy to Use” with AI SDK

Visit the webpage below for the latest information on AI SDK  
[https://renesas-rz.github.io/rzv\\_ai\\_sdk/latest/](https://renesas-rz.github.io/rzv_ai_sdk/latest/)




AI SDK eliminates complex build tasks and enables immediate AI evaluation

**Renesas RZ/V AI 5.00**

The best solution for starting your AI applications.

Provided by Renesas Electronics Corporation



**Get the Board and Software**

AI Applications Overview >

AI SDK Overview >

To keep you updated, Watch our GitHub repository


▼ AI SDK

▶ Key Features

## AI Applications and AI SDK on RZ/V series

*The best solution for starting your AI applications.*

AI Applications and AI SDK are quick and easy solutions for starting AI. It provides various AI applications for free.



- 1 Choose AI Application based on your use case.
- 2 Deploy Application with AI SDK. Application Source code build is also available.
- 3 Run Application on the Board.

The customers only need to select their use case w/o requiring AI training. Provided as a free Open-Source Software on Github and can be used in MP.


#### Agriculture



#### Smart Building



#### Smart City



#### Smart Home





#### Industrial



#### Retail



#### Healthcare



## RZ/N Series

### RZ/N Series Features

1. Provides optimized microcontrollers for a variety of industrial network applications
2. Integrated Ethernet switch and EtherCAT slave controller alongside support for major Industrial Ethernet protocols and TSN
3. Redundant network configuration reduces network downtime to zero

#### 1. Provides optimized microcontrollers for a variety of industrial network applications

The RZ/N2H is optimized for industrial controller equipment such as PLC, DCS, CNC and motion controller. It integrates Quad Arm® Cortex®-A55 cores (1.2GHz) for application processing and two Arm Cortex-R52 cores (1.0GHz) for real-time control. The flexible Ethernet functionalities supporting TSN execute both industrial Ethernet controller and device. Also, RZ/N2H can support up to 6-axis motor control, suitable for applications requiring multi-axis.


The RZ/N2L is optimized for the role of dedicated network companion chip, simplifying the task of adding network functionality to industrial equipment. Since it handles network-related processing independently of the external CPU, Industrial Ethernet support can be implemented without the need to make major changes to the existing application software.


### RZ/N2 Specification

Item	RZ/N2H	RZ/N2L
Application Core	Cortex-A55 1.2GHz ×4	–
Realtime Core	Cortex-R52 1.0GHz ×2	Cortex-R52 400MHz
DDR	LPDDR4-3200 32-bit	–
Industrial Ethernet	4 Ether ports 3 GMAC Ethernet Switch ESC, TSN	3 Ether ports 1 GMAC Ethernet Switch ESC, TSN
Motor Control	Up to 6-axis	–
PCIe	PCIe (Gen3) ×2	–
HMI	Parallel RGB	–
Host IF	Serial	Serial / Parallel
Package	FCBGA 576-pin (23mm × 23mm)	FBGA 225-pin (23mm × 23mm) FBGA 121-pin (10mm × 10mm)

### 2. Integrated Ethernet switch and EtherCAT slave controller alongside support for major Industrial Ethernet protocols and TSN

A wide range of Industrial Ethernet protocols are supported. Separating application processing and network processing allows for more efficient application control.

 : RZ/N hardware  
 : Software



### 3. Redundant network configuration reduces network downtime to zero

Advanced redundant network configuration support helps eliminate network downtime.

- Redundant network connections: Parallel Redundancy Protocol (PRP)
- Looped network connections: HSR (High-availability Seamless Redundancy), DLR (Device Level Ring), RSTP (Rapid Spanning Trees)

### RZ/N Series Application



## RZ/N2H Group

### CPU core

- Arm® Cortex®-A55, Quad/Dual/Single-core  
Max operating frequency: 1.2GHz  
L1 I/D-cache 32KB per core, L3 cache 1MB
- Arm® Cortex®-R52, Dual-core  
Max operating frequency: 1.0GHz  
L1 I/D-cache 16KB,  
Tightly Coupled Memory (TCM): 512KB (w/ ECC) + 64KB (w/ ECC) per core

### Features

- On-chip system SRAM 2.0MB (w/ ECC)
- LPDDR4-3200 32-bit
- SD/eMMC
- Motor Control Peripherals (Support up to 6-axis)
  - PWM Timer: MTU3 9ch
  - PWM Timer: GPT 56ch
  - $\Delta\Sigma$  interface: 23ch
  - 12-bit ADC: 3units
  - Encoder IF: 14ch
  - Trigonometric function unit
- Industrial Ethernet
  - Ethernet Switch w/ TSN
  - 3ch Gigabit Ethernet MAC w/ TSN
  - 4x Ethernet ports
  - EtherCAT Slave Controller (ESC)
- PCI Express Gen3
- Serial host interface
- LCD Controller
- CAN-FD
- USB2.0
- SPI, SCI, I<sup>2</sup>C
- xSPI


### Safety functions

- Register write protection, input clock oscillation stop detection, and CRC
- Isolated peripheral function access via MPU

### Package

- 576-pin FCBGA (21mm × 21mm, 0.8mm pitch)
- T<sub>j</sub> = -40°C to +125°C

## RZ/N2H Group Block Diagram



## RZ/N2H Product Lineup

Security	R9A09G087M48GBG	R9A09G087M28GBG	R9A09G087M08GBG
Non-Security	R9A09G087M44GBG	R9A09G087M24GBG	R9A09G087M04GBG
Cortex-A55	Quad	Dual	Single
Cortex-R52	Two CPUs		
Package	FCBGA 576-pin, 21mm × 21mm, 0.8mm pitch		
Power Supply	0.8V, 1.1V, 1.8V, 3.3V		
Operating Temperature	T <sub>j</sub> = -40°C to +125°C		



## RZ/N2L Group

### CPU core

- Arm® Cortex®-R52
- Operating frequency: 400MHz/200MHz
- Single-precision/double-precision floating-point unit

### On-chip memory

- Tightly Coupled Memory: 128KB (w/ ECC) + 128KB (w/ ECC)
- 1.5MB on-chip RAM (with ECC)

### Features

- TSN support
- 3-port Gigabit Ethernet switch
- EtherCAT slave controller
- Parallel host/serial host interface
- PWM timer
- $\Delta\Sigma$  interface
- ADC
- Trigonometric function unit
- CAN-FD
- USB2.0
- SPI, SCI, I<sup>2</sup>C
- xSPI


### Safety functions

- Register write protection, input clock oscillation stop detection, and CRC
- Isolated peripheral function access via MPU

### Package

- 225-pin FBGA (13mm × 13mm, 0.8mm pitch)
- 121-pin FBGA (10mm × 10mm, 0.8mm pitch)
- T<sub>j</sub> = -45°C to +125°C

## RZ/N2L Group Block Diagram



## RZ/N2L Product Lineup

Item	R9A07G084M08GBG	R9A07G084M04GBG	R9A07G084M08GBA	R9A07G084M04GBA
CPU	Cortex®-R52 (Max 400MHz)			
Tightly Coupled Memory	ATCM 128KB (w/ECC) / BTCM 128KB (w/ECC)			
RAM	1.5MB (w/ECC)			
External bus	8, 16bit		Not Supported	
Host I/F	Serial Host	OSPI/QSPI		QSPI
	Parallel Host	8, 16bit		Not Supported
Industrial Ethernet Protocol	EtherCAT®, PROFINET RT/IRT, EtherNet/IP™, TSN (IEC/IEEE 60802 Industrial Profile), CC-Link IE Field Basic, OPC UA over TSN			
Ether Port	3 ports		2 ports	
Motor Control Peripherals	PWM Timer (MTU3, GPT), ADC*, $\Delta\Sigma$ Interface, Trigonometric function unit			
Security	Supported	Not Supported	Supported	Not Supported
Power	1.1V, 1.8V, 3.3V			
Operating Temperature	T <sub>j</sub> = -40 to +125°C			
Package	FBGA		FBGA	
Pin Count	225-pin		121-pin	
Package Information	13mm × 13mm, 0.8mm pitch		10mm × 10mm, 0.8mm pitch	

\* 225-pin only

## RZ/N1D Group

### CPU core

- Arm® Cortex®-A7 dual-core processor
- Operating frequency: 500MHz

### Cache memory

- L1 I-cache: 16KB × 2, D-cache: 16KB × 2
- L2: 256KB

### Internal memory

- 2MB (ECC)

### External memory

- DDR2/DDR3 controller
- Quad I/O SPI
- SDIO eMMC
- NAND flash controller

### R-IN engine

- Arm® Cortex®-M3
- Operating frequency: 125MHz
- HW-RTOS accelerator
- Ethernet accelerator

### Main Ethernet communication functions

- EtherCAT slave controller
- Sercos® III slave controller
- HSR switch (400-pin)
- 5-port Ethernet switch

### Other communication functions

- UART × 8 channels
- I<sup>2</sup>C × 2 channels
- USB Host/Function × 1 channel, Host 1 channel
- SPI × 6 channels (master × 4 channels, slave × 2 channels)
- CAN

### Other functions

- LCD controller
- ADC: 12-bit × 8 channels × 2 units (400-pin)
- ADC: 12-bit × 8 channels × 1 unit (324-pin)
- PWM timer, GPT


### Package

- 400-pin: LFBGA, 17mm × 17mm, 0.8mm pin pitch
- 324-pin: LFBGA, 15mm × 15mm, 0.8mm pin pitch


### Operating temperature

- T<sub>j</sub> = -40°C to +110°C

## RZ/N1D Group Block Diagram



## Application example: Programmable logic controller block diagram



## RZ/N1S Group

### CPU core

- Arm® Cortex®-A7 single-core processor
- Operating frequency: 500MHz

### Cache memory

- L1 I-cache: 16KB, D-cache: 16KB
- L2: 128KB

### Internal memory

- 6MB (ECC)

### External memory

- Quad I/O SPI
- SDIO eMMC
- NAND flash controller

### R-IN engine

- Arm® Cortex®-M3
- Operating frequency: 125MHz
- HW-RTOS accelerator
- Ethernet accelerator

### Main Ethernet communication functions

- EtherCAT slave controller
- Sercos® III slave controller
- 5-port Ethernet switch

### Other communication functions

- UART × 8 channels
- I<sup>2</sup>C × 2 channels
- USB Host/Function × 1 channel, Host 1 channel
- SPI × 6 channels (master × 4 channels, slave × 2 channels)
- CAN

### Other functions

- LCD controller
- ADC: 12-bit × 8 channels × 1 unit
- PWM timer, GPT


### Package

- 324-pin: LFBGA, 15mm × 15mm, 0.8mm pin pitch
- 196-pin: LFBGA, 12mm × 12mm, 0.8mm pin pitch


### Operating temperature

- T<sub>j</sub> = -40°C to +110°C

## RZ/N1S Group Block Diagram



## Application example: Sensor Hub block diagram



## RZ/N1L Group

### R-IN engine

- Arm® Cortex®-M3
- Operating frequency: 125MHz
- HW-RTOS accelerator
- Ethernet accelerator

### Internal memory

- 6MB (ECC)

### External memory

- Quad I/O SPI
- SDIO eMMC
- NAND flash controller

### Main Ethernet communication functions

- EtherCAT slave controller
- Sercos® III slave controller
- GbE Ethernet switch

### Other communication functions

- UART × 8 channels
- I<sup>2</sup>C × 2 channels
- USB Host/Function × 1 channel, Host 1 channel
- SPI × 6 channels (master × 4 channels, slave × 2 channels)
- CAN × 2 channels

### Other functions

- LCD controller
- ADC: 12-bit × 8 channels × 1 unit
- PWM timer, GPT


### Package

- 196-pin: LFBGA, 12mm × 12mm, 0.8mm pin pitch





### Operating temperature

- T<sub>j</sub> = -40°C to +110°C

## RZ/N1L Group Block Diagram



## RZ/N2H, RZ/N2L: Development Environments (Integrated Development Environments)

Development environments	<ul style="list-style-type: none"> <li>• IAR Embedded Workbench® for Arm®</li> </ul> 	<ul style="list-style-type: none"> <li>• e<sup>2</sup> studio*<sup>1</sup></li> </ul> 
Compilers	<ul style="list-style-type: none"> <li>• IAR C/C++ compiler*<sup>2</sup></li> </ul>	<ul style="list-style-type: none"> <li>• GNU tool*<sup>4</sup></li> </ul>
Other tools	<ul style="list-style-type: none"> <li>• AP4 and FSP Smart Configurator code generation tools from Renesas can be used.</li> </ul>	<ul style="list-style-type: none"> <li>• Code generation function available as a plug-in.</li> </ul>
ICEs	<ul style="list-style-type: none"> <li>• I-jet™/I-jet Trace™ for Arm Cortex®-A/R/M</li> <li>• JTAGjet-Trace</li> </ul> 	<ul style="list-style-type: none"> <li>• J-Link LITE from Segger</li> <li>• J-Link series from Segger*<sup>5</sup></li> </ul> 

\*1. Eclipse-based development environment from Renesas (<http://renesas.com/e2studio>)










\*2. Two versions of the software are available for download free of charge. One limits the code size to 32KB and can be used with no time limitation. The other has no limit on code size and expires after 30 days. (<https://www.iar.com/EWARM>)

\*3. Arm CC is included in DS-5. In addition to the popularly priced DS-5 RZ/A and RZ/T editions, a fully functional evaluation version of DS-5 that expires after 30 days is available free of charge. Contact your DS-5 dealer for details.

\*4. GNU TOOLS & SUPPORT Website (<https://lvm-gcc-renesas.com/>)

\*5. Renesas does not handle ICEs from Segger. Contact a sales agent for details.

**RZ/N2H, RZ/N2L: Development Tools (Debuggers, ICEs)**

	 KMC Kyoto Microcomputer Co., Ltd.	 DTS INSIGHT Our insight, your value	 LAUTERBACH DEVELOPMENT TOOLS
Debuggers	<ul style="list-style-type: none"> <li>• PARTNER-Jet2</li> </ul> 	<ul style="list-style-type: none"> <li>• microVIEW-Xross</li> </ul> 	<ul style="list-style-type: none"> <li>• TRACE32 PowerView</li> </ul> 
ICEs		<ul style="list-style-type: none"> <li>• adviceXross</li> </ul> 	<ul style="list-style-type: none"> <li>• TRACE32 PowerDebug &amp; PowerTrace</li> </ul> 
Supported compilers	<ul style="list-style-type: none"> <li>• exeGCC from Kyoto Microcomputer</li> <li>• GNU tool*<sup>1</sup></li> <li>• Arm CC*<sup>2</sup></li> <li>• IAR C/C++ compiler,*<sup>3</sup> etc.</li> </ul>	<ul style="list-style-type: none"> <li>• Arm CC*<sup>2</sup></li> <li>• GNU tool,*<sup>1</sup> etc.</li> </ul>	<ul style="list-style-type: none"> <li>• Arm CC*<sup>2</sup></li> <li>• GNU tool*<sup>1</sup></li> <li>• IAR C/C++ compiler*<sup>3</sup> etc.</li> </ul>

\*1. GNU TOOLS & SUPPORT Website (<https://lvm-gcc-renesas.com/>)

\*2. Arm CC is included in DS-5. In addition to the popularly priced DS-5 RZ/A and RZ/T editions, a fully functional evaluation version of DS-5 that expires after 30 days is available free of charge. Contact your DS-5 dealer for details.



\*3. Two versions of the software are available for download free of charge. One limits the code size to 32KB and can be used with no time limitation. The other has no limit on code size and expires after 30 days. (<https://www.iar.com/EWARM>)

**Code Generation Support: Flexible Software Package (FSP) + Smart Configurator (SC)**

(Supported products: RZ/N2H, RZ/N2L)

The FSP includes everything you'll need to start developing software: board-dependent programs, peripheral function drivers, middleware, and documentation on how to use them.

Smart Configurator is a utility based on the concept of "combining software components freely." The intuitive GUI makes it easy to configure pins and FSP driver settings and to generate source code customized for your use case. It works together with integrated development environments such as IAR Embedded Workbench® for Arm from IAR Systems and e<sup>2</sup> studio.




## Development Kits

These products are evaluation boards with RZ/N series configured as the key device and are capable of easily implementing software development.

### RZ/N2H Evaluation Board Kit [www.renesas.com/rzn2h-evkit](http://www.renesas.com/rzn2h-evkit)


- Easy evaluation of each RZ/N2H function with Segger's on-board debugger
- Ordering number: RTK9RZN2H0S00000BJ



- 576-pin RZ/N2H MPU (R9A09G087M44GBG)
- 4 ports of Ethernet connectors
- LPDDR4: 8GB, QSPI Flash, Octa Flash, eMMC
- PCIe 2 lane, micro SD slot ×1
- Pmod™/Grove®/QWIIC®/mikroBUS™
- Three USB cables are bundled for power supply (Type C, 15V), on-board emulator connection (Micro B) and terminal debugging (Mini B).

### RZ/N2L Remote I/O Solution Kit [www.renesas.com/rzn2l-remote-io-solution](http://www.renesas.com/rzn2l-remote-io-solution)

- The RZ/N2L Remote I/O Solution Kit is a development kit for evaluating remote I/O applications which is equipped with digital I/O interface with photocoupler isolation and analog input.
- Provide sample programs for industrial network communication and DI/DO.
- Ordering number: CN032-GATEWAYREFZ



- Digital I/O interface with photocoupler isolation (IN: 8, OUT: 8)
- Analog Input interface (4-20mA: 2, 0-10V: 2)
- Support industrial network protocols: EtherCAT, EtherNet/IP
- RS485 Transceiver, CAN Transceiver, D-sub connector
- Ethernet PHY, RJ45 connector
- Memory (Quad SPI flash, EEPROM, SDRAM)

### Renesas Starter Kit+ for RZ/N2L [www.renesas.com/rskrzn2l](http://www.renesas.com/rskrzn2l)

- The board is mounted with a RZ/N2L with a 225BGA package and can be used to evaluate almost all of the device's functions.
- Emulator circuit is mounted, can start program debugging by simply connecting USB cable to PC.
- Ordering number: RTK9RZN2L0S00000BE



- 225-pin RZ/N2L MPU (R9A07G084M04GBG)
- Gigabit Ethernet PHY
- Octal flash memory
- Pmod™, Grove®, QWIIC®, and mikro-BUS™ connectors
- Pin header for external expansion
- Includes a USB power cable that can also be used to connect an emulator.

### RZ/N2L Industrial Network SOM Kit [www.renesas.com/yconnect-it-rzn2l](http://www.renesas.com/yconnect-it-rzn2l)

- YCONNECT-IT-RZN2L is a compact reference kit for evaluating applications using Industrial Ethernet communication
- Flexible power supply from either USB or 24V DC terminal or Arduino host board
- Ordering number: YCONNECT-IT-RZN2L



- 2x Gigabit Industrial Ethernet connectors
- 2x PMOD connectors
- Arduino dual-use connector
- 9-pin connector for external debugger connection and Segger J-Link OB for debugging via USB

### CONNECT IT! ETHERNET RZ/N [www.renesas.com/RZN-YConnect-It](http://www.renesas.com/RZN-YConnect-It)

- CONNECT IT! ETHERNET RZ/N is the perfect solution kit for developers new to developing with the RZ/N1.
- The kit comes with not only an evaluation board, but also a JTAG emulator and various sample software.
- It is possible to evaluate master communication / slave communication of industrial networks.



- JTAG emulator
  - IAR I-jet Lite (20-pin flat ribbon/USB cable)
- 2 USB cables
- Startup manuals
- Pin setting tool
- RZ/N Solution Kit DVD
  - User's manual
  - OS (Linux, ThreadX®(Evaluation version), HW-RTOS)
  - Software PLC Codesys
  - Protocol stacks




## RZ/T Series

### RZ/T Series Features

- High-performance, high-speed real-time control
- Integrated peripheral functions

#### High-performance, high-speed real-time control



- High-speed RAM directly coupled to the CPU allows fast processing and bypassing of the cache for reliable real-time responsiveness.
- ECC for enhanced reliability
- Assures responsive interrupt handling suitable for embedded control applications.

### RZ/T2H Features


- RZ/T2H is an advanced high-end microprocessor (MPU) equipped with Quad Arm® Cortex®-A55 cores (1.2GHz) for application processing and two Arm Cortex-R52 cores (1.0GHz) for real-time control.
- The peripheral functions are capable of controlling motors of up to 9-axis with low latency access from a Cortex-R52 CPU.
- The Ethernet functionalities supporting TSN and flexible for both industrial Ethernet controller and device.

### RZ/T2 Specification

Item	RZ/T2H	RZ/T2ME	RZ/T2M	RZ/T2L
Application Core	Cortex-A55 1.2GHz ×4	–	–	–
Realtime Core	Cortex-R52 1.0GHz ×2	Cortex-R52 800MHz ×2	Cortex-R52 800MHz ×2	Cortex-R52 800MHz
DDR	LPDDR4-3200 32-bit	–	–	–
Industrial Ethernet	4 Ether ports 3 GMAC Ethernet Switch ESC, TSN	3 Ether ports 1 GMAC Ethernet Switch ESC, TSN	3 Ether ports 1 GMAC Ethernet Switch ESC, TSN	ESC
Motor Control	GPT/MTU (for motor control)	56ch/9ch (Up to 9-axis)	7ch/9ch (2-axis)	7ch/9ch (2-axis)
	Sigma Delta I/F	30ch	6ch	6ch
	Absolute Encoder I/F	16ch	2ch	2ch
PCIe	PCIe (Gen3) ×2	–	–	–
HMI	Parallel RGB	–	–	–
On-The-Fly-Decryption	–	Supported	–	–
Host IF	Serial	–	–	Serial
Package	FCBGA 729-pin (23mm × 23mm)	FBGA 320-pin (17mm × 17mm) FBGA 225-pin (13mm × 13mm)	FBGA 320-pin (17mm × 17mm) FBGA 225-pin (13mm × 13mm) LQFP 176-pin (24mm × 24mm) LQFP 126-pin (14mm × 20mm)	FBGA 196-pin (12mm × 12mm)



■ Integrated peripheral functions



- Integrates communication ASSP that would previously have been implemented as an external device.
- Integrates encoder interface that would previously have been implemented by an FPGA or ASIC.

	EnDat 2.2	BiSS-C	NIKON A-format	FA-CODER	HIPERFACE DSL
Related specifications	Heidenhain Corp <a href="http://www.heidenhain.de">http://www.heidenhain.de</a>	iC-Haus GmbH <a href="http://www.biss-interface.com">http://www.biss-interface.com</a>	NIKON Corporation <a href="http://www.nikon.co.jp">http://www.nikon.co.jp</a>	TAMAGAWA SEIKI CO.,LTD. <a href="http://www.tamagawa-seiki.co.jp">http://www.tamagawa-seiki.co.jp</a>	SICK STEGMANN GmbH <a href="http://www.sick.com">http://www.sick.com</a>
Communication system	Clock synchronous	Clock synchronous	Asynchronous	Asynchronous	Asynchronous
Transmission link	RS-485	RS-422	RS-485	RS-485	RS-485
Supported frequencies/data transfer rates	100kHz to 16.7MHz	62.5kHz to 10MHz	2.5Mbps, 4Mbps, 6.67Mbps, 8Mbps, 16Mbps	2.5Mbps, 5Mbps	9.375Mbps
I/O pin count/signal level	4/3.3V TTL level	2 / 3.3V TTL level	3 / 3.3V TTL level	3 / 3.3V TTL level	3 / 3.3V TTL level
Compatible functions on T series	<ul style="list-style-type: none"> <li>- Propagation delay function</li> <li>- Not supported for incremental signals</li> </ul>	<ul style="list-style-type: none"> <li>- Delay compensation function</li> <li>- Supported in C mode (not supported in B mode)</li> <li>- Not supported for incremental signals</li> <li>- Supported on 1-to-1 connections (not supported on bus connections)</li> </ul>	<ul style="list-style-type: none"> <li>- Supported on 1-to-1 connections and bus connections</li> </ul>	<ul style="list-style-type: none"> <li>- Baseband NRZ code support</li> <li>- Not supported for incremental signals or synchronous Manchester code</li> </ul>	<ul style="list-style-type: none"> <li>- External synchronous communication (sync mode)</li> <li>- Asynchronous communication (free running mode)</li> <li>- Estimator function (position estimation when error occurs)</li> <li>- RSSI, quality monitoring</li> </ul>

## RZ/T Series Application

A fast Cortex-R CPU operating at 300MHz to 1000MHz and large-capacity tightly-coupled memory provide the high performance and advanced functionality required by industrial applications such as industrial motors or AC servo drives. The RZ/T series is powerful enough to handle Industrial Ethernet processing of various types while still maintaining real-time performance. Furthermore, RZ/T2H has high performance Cortex-A CPU for application processing.



## RZ/T2H Group


### CPU core

- Arm® Cortex®-A55, Quad/Dual/Single-core  
Max operating frequency: 1.2GHz  
L1 I/D-cache 32KB per core, L3 cache 1MB
- Arm® Cortex®-R52, Dual-core  
Max operating frequency: 1.0GHz  
L1 I/D-cache 16KB,  
Tightly Coupled Memory (TCM): 512KB (w/ ECC) + 64KB (w/ ECC)  
per core

### Features

- On-chip system SRAM 2.0MB (w/ ECC)
- LPDDR4-3200 32-bit
- SD/eMMC
- Motor Control Peripherals (Support up to 9-axis)
  - PWM Timer: MTU3 9ch
  - PWM Timer: GPT 56ch
  - $\Delta\Sigma$  interface: 30ch
  - 12-bit ADC: 3units
  - Encoder IF: 16ch
  - Trigonometric function unit
- Industrial Ethernet
  - 3-port Ethernet Switch w/TSN
  - 3ch Gigabit Ethernet MAC w/ TSN
  - 4x Ethernet ports
  - EtherCAT Slave Controller (ESC)
- PCI Express Gen3
- Serial host interface
- LCD Controller
- CAN-FD
- USB2.0
- SPI, SCI, I<sup>2</sup>C
- xSPI
- Safety functions
  - Register write protection, input clock oscillation stop detection, and CRC
  - Isolated peripheral function access via MPU
- Package
  - 729-pin FCBGA (23mm x 23mm, 0.8mm pitch)
  - T<sub>j</sub> = -40°C to +125°C

## RZ/T2H Group Block Diagram



## RZ/T2H Product Lineup

Security	R9A09G077M48GBG	R9A09G077M28GBG	R9A09G077M08GBG
Non-Security	R9A09G077M44GBG	R9A09G077M24GBG	R9A09G077M04GBG
Cortex-A55	Quad	Dual	Single
Cortex-R52	Two CPUs		
Package	FCBGA 729-pin, 23mm × 23mm, 0.8mm pitch		
Power Supply	0.8V, 1.1V, 1.8V, 3.3V		
Operating Temperature	Tj = -40°C to +125°C		

## RZ/T2M & T2ME Group

### CPU core

- Arm® Cortex®-R52 × 2
- Operating frequency: 800MHz/400MHz/200MHz
- Single-precision/double-precision floating-point unit

### On-chip memory

- Tightly Coupled Memory: 512KB (W/ ECC) + 64KB (W/ ECC)
- 2MB on-chip RAM (with ECC)

### Features

- Low latency peripheral port (LLPP) bus
- TSN support
- 3-port Gigabit Ethernet switch
- EtherCAT slave controller
- Encoder interface
- PWM timer
- ΔΣ interface
- ADC
- Trigonometric function unit
- xSPI
- CAN-FD
- USB2.0
- SPI, SCI, I<sup>2</sup>C


### Safety functions

- Register write protection, input clock oscillation stop detection, and CRC
- Isolated peripheral function access via MPU

### Package

- 320-pin FBGA (17mm × 17mm, 0.8mm pitch)
- 225-pin FBGA (13mm × 13mm, 0.8mm pitch)
- 176-pin LQFP (24mm × 24mm, 0.5mm pitch)
- 128-pin LQFP (14mm × 20mm, 0.5mm pitch)
- Tj = -45°C to +125°C

## RZ/T2M & T2ME Group Block Diagram



\*1: RZ/T2ME group further support UDP/IPv4 1step E2E TC

\*2: RZ/T2ME group further support On-The-Fly-Decryption

## RZ/T2M & T2ME Product Lineup

Security	R9A07G075M28GBG	R9A07G075M26GBG	R9A07G075M28G8A	R9A07G075M26G8A	R9A07G075M27G8A	—	R9A07G075M05GFP	R9A07G075M05GFA	R9A07G075M29GBG	R9A07G075M29G8A	
Non-Security	R9A07G075M24GBG	R9A07G075M22GBG	R9A07G075M24G8A	R9A07G075M22G8A	—	R9A07G075M21G8A	R9A07G075M01GFP	R9A07G075M01GFA	—	—	
CPU	Dual Cortex®-R52 (800+800MHz)						Single Cortex®-R52 (800MHz)		Dual Cortex®-R52 (800+800MHz)		
System RAM	2.0MB w/ECC						1.5MB w/ECC		2.0MB w/ECC		
TCM Memory	CPU0 : ATCM: 512KB w/ECC, BTCM: 64KB w/ECC CPU1 : ATCM: none, BTCM: none						CPU0 : ATCM: 512KB w/ECC, BTCM: 64KB w/ECC		CPU0: ATCM: 512KB w/ECC, BTCM: 64KB w/ECC CPU1: ATCM: none, BTCM: none		
ΔΣ interface	3ch × 2 units										
Encoder I/F Protocol	A-format™, BiSS-C, EnDat2.2, FA-CODER®, HIPERFACE DSL®										
Motor Control Peripherals	PWM Timer (MTU3, GPT), ΔΣ Interface, 12bit ADC, Encoder Interface, Trigonometric Accelerator										
Ethernet Port	3ports (100/1000Mbps)					None			3ports (100/1000Mbps) support UDP/IPv4 1step E2E TC		
EtherCAT Port	Max 3ports (Exclusive with Ethernet)					None			Max 3ports (Exclusive with Ethernet)		
Industrial Ethernet Protocol	EtherCAT®, PROFINET RT/IRT, EtherNet/IP™, CC-Link IE Basic, TSN (IEC/IEEE 60802 Industrial Profile), OPC UA over TSN					None			EtherCAT®, PROFINET RT/IRT, EtherNet/IP™, CC-Link IE Basic, TSN (IEC/IEEE 60802 Industrial Profile), OPC UA over TSN		
CAN	CAN FD ×2ch	Classic CAN ×2ch	CAN FD ×2ch	Classic CAN ×2ch	CAN FD ×2ch	Classic CAN ×2ch	Classic CAN ×2ch	Classic CAN ×2ch	CAN FD × 2ch		
xSPI	2ch								2ch w/ OTFD		
Package	BGA320 (17mm×17mm, 0.8mm pitch)		BGA225 (13mm×13mm, 0.8mm pitch)				QFP176 (24mm×24mm, 0.5mm pitch)	QFP128 (14mm×20mm, 0.5mm pitch)	BGA320 (17mm×17mm, 0.8mm pitch)	BGA225 (13mm×13mm, 0.8mm pitch)	
Power Supply	1.1V, 1.8V, 3.3V										
Operating Temperature	Tj = -40 to +125°C										

## RZ/T2L Group

### CPU core

- Arm® Cortex®-R52
- Operating frequency: 800MHz/400MHz/200MHz
- Single-precision/double-precision floating-point unit

### On-chip memory

- Tightly Coupled Memory: 512KB (W/ ECC) + 64KB (W/ ECC)
- 1MB on-chip RAM (with ECC)

### Features

- Low latency peripheral port (LLPP) bus
- EtherCAT slave controller
- Gigabit Ether MAC
- Encoder interface
- PWM timer
- $\Delta\Sigma$  interface
- ADC
- Trigonometric function unit
- Serial host interface
- xSPI
- CAN-FD
- USB2.0
- SPI, SCI, I<sup>2</sup>C


### Safety functions

- Register write protection, input clock oscillation stop detection, and CRC
- Isolated peripheral function access via MPU


### Package

- FBGA 196-pin (12mm × 12mm, 0.8mm pitch)
- T<sub>j</sub> = -45°C to +125°C

### Application example: AC servo system block diagram



### RZ/T2L Group Block Diagram



## RZ/T2L Product Lineup

Part Number	R9A07G074M08GBG	R9A07G074M05GBG	R9A07G074M04GBG	R9A07G074M01GBG
CPU	Cortex®-R52 (Max 800MHz)			
System RAM	1.0MB (w/ECC)			
TCM Memory	ATCM 512KB (w/ECC) / BTCM 64KB (w/ECC)			
External bus	8, 16 bit			
Peripheral functions for motor control	PWM Timer (MTU3, GPT), ADC, $\Delta\Sigma$ interface, Trigonometric function unit			
GMAC	1 ch			
Ethernet Port	3 ports			
EtherCAT	Supported	Not Supported	Supported	Not Supported
CAN	CAN-FD	CAN	CAN-FD	CAN
Security	Supported	Supported	Not Supported	Not Supported
Package	BGA196 (12mm × 12mm, 0.8mm pitch)			
Power Supply	1.1V, 1.8V, 3.3V			
Operating Temperature	T <sub>j</sub> = -40 to +125°C			

## RZ/T1 Group

### CPU core

- Arm® Cortex®-R4
- Operating frequency: 600MHz/450MHz/300Hz
- High-performance, high-speed real-time control
- Single-precision/double-precision floating-point unit
- Renesas R-IN engine ("R-IN engine")

### Arm® Cortex®-M3

- Operating frequency: 125MHz
- HW-RTOS accelerator
- R-IN engine instruction memory: 512KB (w/ ECC) + data memory: 512KB (w/ ECC)

### On-chip memory

- Tightly Coupled Memory: 512KB (w/ ECC) + 32KB (w/ ECC)
- Extended RAM instruction memory 512KB (w/ ECC) + data memory: 512KB (w/ ECC)

### Features

- Industrial Ethernet communication accelerator with multi-protocol support (R-IN engine)
- EtherCAT slave controller
- PWM timer: MTU3a, GPT
- Encoder interface (Nikon A-format™/BiSS-C/EnDat2.2/HIPERFACE DSL®/FA-CODER®)


Note: 2ch encoder support depends on the combination of the selected protocol.

- High Speed USB
- Secure boot (option)
- Safety functions
  - ECC memory
  - CRC (32-bit)
  - Independent WDT: Operating on dedicated on-chip oscillator
- ΔΣ interface
- 100Mbps EtherMAC (with Ethernet switch)
- Ethernet accelerator
- Power supply voltage: 1.2V, 3.3V

### Package

- FBGA 320-pin (17mm × 17mm, 0.8mm pitch)
- Tj = -45°C to +125°C

## RZ/T1 Group Block Diagram



## RZ/T1 Product Lineup

CPU	Tightly coupled memory	Extended RAM						
600 MHz + R-IN Engine (150MHz)	512KB+32KB	– (1MB for R-IN)					R7S910017	R7S910018
450 MHz + R-IN Engine (150MHz)	512KB+32KB	– (1MB for R-IN)					R7S910015	R7S910016
600 MHz	512KB+32KB	1MB	R7S910007	R7S910013	R7S910027	R7S910028		
450 MHz	512KB+32KB	1MB	R7S910006		R7S910025	R7S910026		
		–	R7S910002	R7S910011				
300 MHz	512KB+32KB	–			R7S910035	R7S910036		
Package			320 BGA	320 BGA	320 BGA	320 BGA	320 BGA	320 BGA
Encoder I/F			–	Yes	–	Yes	–	Yes
Industrial Ethernet			– (Standard Ethernet)		EtherCAT		Multi-protocol support	







## Utilizing the Arm® Ecosystem

### Utilizing Renesas' Experience and the Arm® Ecosystem

Customers can benefit from solutions combining Renesas' accumulated experience in the microcontroller industry and the global ecosystem of Arm® partners. Products such as development environments, OS, and middleware are available from partner companies supporting the RZ/T series.



## RZ/T Series: Development Environments (Integrated Development Environments)

		
Development environments	<ul style="list-style-type: none"> <li>IAR Embedded Workbench® for Arm®</li> </ul> 	<ul style="list-style-type: none"> <li>e² studio*1</li> </ul> 
Compilers	<ul style="list-style-type: none"> <li>IAR C/C++ compiler*2</li> </ul>	<ul style="list-style-type: none"> <li>GNU tool*4</li> </ul>
Other tools	<ul style="list-style-type: none"> <li>AP4 and FSP Smart Configurator code generation tools from Renesas can be used.</li> </ul>	<ul style="list-style-type: none"> <li>Code generation function available as a plug-in.</li> </ul>
ICEs	<ul style="list-style-type: none"> <li>I-jet™/I-jet Trace™ for Arm Cortex®-A/R/M</li> <li>JTAGjet-Trace</li> </ul> 	<ul style="list-style-type: none"> <li>J-Link LITE from Segger</li> <li>J-Link series from Segger*5</li> </ul> 

\*1. Eclipse-based development environment from Renesas (<http://renesas.com/e2studio>)













\*2. Two versions of the software are available for download free of charge. One limits the code size to 32KB and can be used with no time limitation. The other has no limit on code size and expires after 30 days. (<https://www.iar.com/EWARM>)

\*3. Arm CC is included in DS-5. In addition to the popularly priced DS-5 RZ/A and RZ/T editions, a fully functional evaluation version of DS-5 that expires after 30 days is available free of charge. Contact your DS-5 dealer for details.

\*4. GNU TOOLS & SUPPORT Website (<https://lvm-gcc-renesas.com/>)

\*5. Renesas does not handle ICEs from Segger. Contact a sales agent for details.

## RZ/T Series: Development Tools (Debuggers, ICEs)

	 Kyoto Microcomputer Co., Ltd.	 Our insight, your value	 DEVELOPMENT TOOLS	
Debuggers	<ul style="list-style-type: none"> <li>PARTNER-Jet2</li> </ul> 	<ul style="list-style-type: none"> <li>microVIEW-Xross</li> </ul> 	<ul style="list-style-type: none"> <li>TRACE32 PowerView</li> </ul> 	<ul style="list-style-type: none"> <li>CSIDE version 7</li> </ul> 
ICEs		<ul style="list-style-type: none"> <li>adviceXross</li> </ul> 	<ul style="list-style-type: none"> <li>TRACE32 PowerDebug &amp; PowerTrace</li> </ul> 	<ul style="list-style-type: none"> <li>PALMiCE4</li> </ul>  <p>JTAG model      Large capacity trace model</p>
Supported compilers	<ul style="list-style-type: none"> <li>exeGCC from Kyoto Microcomputer</li> <li>GNU tool*1</li> <li>Arm CC*2</li> <li>IAR C/C++ compiler,*3 etc.</li> </ul>	<ul style="list-style-type: none"> <li>Arm CC*2</li> <li>GNU tool,*1 etc.</li> </ul>	<ul style="list-style-type: none"> <li>Arm CC*2</li> <li>GNU tool*1</li> <li>IAR C/C++ compiler*3 etc.</li> </ul>	<ul style="list-style-type: none"> <li>Arm CC*2</li> <li>IAR C/C++ compiler*3</li> <li>GNU tool,*1 etc.</li> </ul>
Supported product	RZ/T2H, RZ/T2ME, RZ/T2M, RZ/T1	RZ/T2H, RZ/T2ME, RZ/T2M, RZ/T1	RZ/T2H, RZ/T2ME, RZ/T2M, RZ/T2L, RZ/T1	RZ/T1

\*1. GNU TOOLS & SUPPORT Website (<https://lvm-gcc-renesas.com/>)

\*2. Arm CC is included in DS-5. In addition to the popularly priced DS-5 RZ/A and RZ/T editions, a fully functional evaluation version of DS-5 that expires after 30 days is available free of charge. Contact your DS-5 dealer for details.

\*3. Two versions of the software are available for download free of charge. One limits the code size to 32KB and can be used with no time limitation. The other has no limit on code size and expires after 30 days. (<https://www.iar.com/EWARM>)

## Code Generation Support: Flexible Software Package (FSP) + Smart Configurator (SC)


(Supported products: RZ/T2H, RZ/T2ME, RZ/T2M, RZ/T2L)

The FSP includes everything you'll need to start developing software: board-dependent programs, peripheral function drivers, middleware, and documentation on how to use them.

Smart Configurator is a utility based on the concept of "combining software components freely." The intuitive GUI makes it easy to configure pins and FSP driver settings and to generate source code customized for your use case. It works together with integrated development environments such as IAR Embedded Workbench® for Arm from IAR Systems and e<sup>2</sup> studio.

**Flexible Software Package (FSP)**

FreeRTOS Real-time tasks	Connectivity FreeRTOS + TCP					
Mutexes	Hardware Abstraction Layer (HAL) Drivers					
Software timer generation	USBHS	ADC	Diffs. Signal Interface	IOPORT	POES	POEG
Stack overflow detection	SCI I2C	xSPI	GPT	CM7	ELC	GMAC
Preemptive scheduler	IC Master IC Slave	CRC	WDT	Core to Core	DMA	Ethernet Switch
Inter-task communication	MTUS	CAN CANFD	RTC	CGC	DOC	TSU
Memory management	LPM	ERROR	ICU	SHM		
Board Support Package (BSP)						





## Code Generation Support Tool: AP4

(Supported product: RZ/T1)

AP4 is a standalone tool that automatically generates peripheral function control programs (device driver programs) based on settings entered by the user. The build tool (compiler) is selectable. This makes it possible to generate peripheral function control program code to match a specific build tool and enables interoperability with integrated development environments. (<https://www.renesas.com/ap4>)

The version of AP4 that is compatible with the RZ/T1 group can generate compatible source code for IAR Embedded Workbench® for Arm® from IAR Systems, Development Studio (DS-5™) from Arm®, and e<sup>2</sup> studio (GNU Tools).






## Development Kits


RZ/T2 evaluation boards has Segger's on-board debugger and user can start evaluation immediately. AC servo solution kit and Inverter boards Kit are available for customers who want to develop servo motor control using RZ/T2 series.

### RZ/T2H Evaluation Board Kit [www.renesas.com/rzt2h-evkit](http://www.renesas.com/rzt2h-evkit)




- 729-pin RZ/T2H MPU (R9A09G077M44GBG)
- Easy evaluation of each RZ/T2H function with on-board debugger
- 4 ports of Ethernet connectors
- LPDDR4: 8GB, QSPI Flash, Octa Flash, eMMC
- PCIe 2-lane, micro SD slot x1
- Pmod™/Grove®/QWIIC®/mikroBUS™
- Motor Control up to 9-axis can be evaluated connecting with RZ/T Series Inverter Board and Bus Board
- Three USB cables are bundled for power supply (Type C, 15V), on-board emulator connection (Micro B) and terminal debugging (Mini B).
- Ordering number: RTK9RZT2HOS0000BJ

### RZ/T Series Inverter Board Kit [www.renesas.com/invb-lv-rzt-b](http://www.renesas.com/invb-lv-rzt-b)



- Kit of Inverter board, BLDC motor and cable
- Power supply: DC 24V
- By using in combination with a compatible CPU board such as RZ/T2H Evaluation Board Kit, users can immediately start evaluating motor control.
- Ordering number: RTK0EM0000S05010BJ

### Bus Board for RZ/T2H [www.renesas.com/busb-rzt2h-b](http://www.renesas.com/busb-rzt2h-b)




- Interface board for evaluating multi axis motor control with RZ/T2H.
- User can evaluate up-to 9-axis motor control with RZ/T2H by connecting RZ/T2H Evaluation Board and RZ/T Series Inverter Board Kits.
- Ordering number: RTK0EM0000Z03000BJ

### Renesas Starter Kit+ for RZ/T2M [www.renesas.com/rskrzt2m](http://www.renesas.com/rskrzt2m)



- 320-pin RZ/T2M MPU (R9A07G075M24GBG)
- Gigabit Ethernet PHY
- Octal flash memory
- Pmod™, Grove®, QWIIC®, and mikro-BUS™ connectors
- Pin header for external expansion
- Includes a USB power cable that can also be used to connect an emulator.
- Ordering number: RTK9RZT2M0S00000BE

### Renesas Starter Kit+ for RZ/T2ME [www.renesas.com/rskrzt2me](http://www.renesas.com/rskrzt2me)



- 320-pin RZ/T2ME MPU (R9A07G075M29GBG)
- Gigabit Ethernet PHY
- Octal flash memory
- Pmod™, Grove®, QWIIC®, and mikro-BUS™ connectors
- Pin header for external expansion
- Includes a USB power cable that can also be used to connect an emulator.
- Ordering number: RTK9RZT2M1S00000BE

### Renesas Starter Kit+ for RZ/T2L [www.renesas.com/rskrzt2l](http://www.renesas.com/rskrzt2l)



- 196-pin RZ/T2L MPU (R9A07G074M04GBG)
- Gigabit Ethernet PHY
- Octal flash memory
- Pmod™, Grove®, QWIIC®, and mikro-BUS™ connectors
- Pin header for external expansion
- Includes a USB power cable that can also be used to connect an emulator.
- Ordering number: RTK9RZT2L0S00000BJ

### RZ/T1-Starter-Kit-Plus [www.renesas.com/RZT1-Starter-Kit-Plus](http://www.renesas.com/RZT1-Starter-Kit-Plus)



- RZ/T1 (R7S910018)
- QSPI FlashROM: 64MB
- SDRAM: 64MB x 2
- NOR Flash: 64MB x 2
- Rich interface
- Serial, USB, CAN
- Digilent Pmod I/F (PMOD connector)
- ΔΣ I/F (DSMI connector)
- Ethernet (10/100Base, EtherCAT) I/F etc.
- Audio codec
- Includes SEGGER's simple debug probe "J-Link LITE"
- Includes LCD for debugging
- Ordering number: RTK7910018S01000BE

### AC Servo Solution Kit [www.renesas.com/AC-servo-solution-kit](http://www.renesas.com/AC-servo-solution-kit)



- Controller board (equipped with RZ/T2M, RZ/T2L or RZ/N2L)
- Inverter board that can drive 220V AC servo motor
- 220V AC Servo Motor
- Renesas offers the utility tool on a PC that can operate the motor with position or speed control by sending control commands via serial communication.

## RZ/G Series

### RZ/G3 Highlights

Inherits features such as RZ/G2's 64-bit Arm Cortex-A and CIP Linux, and enhances low power consumption, high-speed interface, and security functions.

- Connectivity
  - Equipped with PCI-Express and Gbit Ether, it enhances support for high-speed connectivity such as WiFi-6 and LTE
- Real-time sensing
  - Sub system for real-time sensing powered by Cortex®-M + RTOS, not only main system by Cortex®-A + Linux
- Less than 1mW ultra low power consumption standby mode
  - Enables less than 1mW ultra low power consumption standby and quick return in Linux applications
- Security with tamper detection
  - Enhanced security for tamper detection in addition to fundamental security features for IoT applications

### RZ/G3S Features and Specification

The RZ/G3S microprocessor is equipped with one Cortex®-A55 (1.1GHz) CPU core and two Cortex®-M33 (250MHz) CPU cores and is an entry-class device for IoT applications that supports ultra-low power consumption mode. It has interfaces suitable for IoT edge devices such as 16-bit LPDDR4 or DDR4, PCIe, CAN-FD, and 12-bit ADC.

Items	RZ/G3S
CPU Cortex-A®	1× Cortex®-A55@1.1GHz L1,L3 Parity/ECC
CPU Cortex-M®	2× Cortex®-M33@250MHz
DRAM I/F	16-bit ×1ch LPDDR4/DDR4-1600 w/ECC
USB	USB2.0×2ch (1Host, 1Host/Function/OTG)
PCIe	PCI-Express Gen2 1ch *14mm Sq Package only
Gbit Ether	2ch
CAN	2ch (support CAN-FD)
12-bit ADC	2ch
Package	359-pin, LFBGA, 14mm x 14mm, 0.5mm pitch 361-pin, LFBGA, 13mm x 13mm, 0.5mm pitch

### RZ/G2 Highlights

- High Performance
  - 64-bit Arm Cortex-A cores, plus powerful 3D graphics engine and video engine capable of supporting up to 4K UHD, to offer the highest performance
- Wide Coverage
  - Entry-level RZ/G2L Group 3 products equipped with Cortex-A55 with improved processing performance have been the RZ/G2 lineup
- High Reliability
  - Built-in Error Correction Code (ECC) for internal and external memory, which is essential for high-reliability mission critical systems
- Super Long Term Support (SLTS)
  - Applying Civil Infrastructure Platform (CIP) Linux, the Linux kernel will be provided with over 10 years of maintenance
- Verified Linux Package
  - Renesas verifies and provides a Linux package that combines CIP and Linux basic software. Minimize your Linux maintenance resources

## RZ/G2 Specification 1

Items	RZ/G2L	RZ/G2LC	RZ/G2UL
CPU (Arm® Cortex®-A)	1× or 2× Cortex®-A55@1.2GHz L1,L3 Parity/ECC	1× or 2× Cortex®-A55@1.2GHz L1,L3 Parity/ECC	1× Cortex®-A55@1.0GHz L1,L3 Parity/ECC
CPU (Arm® Cortex®-M)	1× Cortex®-M33@200MHz	1× Cortex®-M33@200MHz	1× Cortex®-M33@200MHz
DRAM I/F	16-bit ×1ch DDR4-1600/DDR3L-1333 w/ECC	16-bit ×1ch DDR4-1600/DDR3L-1333 w/ECC	16-bit ×1ch DDR4-1600/DDR3L-1333 w/ECC
Video in	1×MIPI CSI-2 or 1×Digital Parallel input	1×MIPI CSI-2	1×MIPI CSI-2
Video Codec	Support up to Full HD @30fps resolutions Encoding and Decoding: H.264	–	–
3D GFX	Arm Mali-G31 GPU @500MHz	Arm Mali-G31 GPU @500MHz	–
Display out	1×MIPI DSI or 1×Digital Parallel output	1×MIPI DSI	1×Digital Parallel output
USB	USB2.0×2ch (1Host, 1Host/Function/OTG)	USB2.0×2ch (1Host, 1Host/Function/OTG)	USB2.0×2ch (1Host, 1Host/Function/OTG)
Gbit Ether	2ch	1ch	2ch
CAN	2ch (support CAN-FD)	2ch (support CAN-FD)	2ch (support CAN-FD)
12-bit ADC	8ch	–	2ch
Package	551-pin LFBGA, 21mm×21mm, 0.8mm ball pitch 456-pin LFBGA, 15mm×15mm, 0.5mm ball pitch	361-pin LFBGA, 13mm×13mm, 0.5mm ball pitch	361-pin LFBGA, 13mm×13mm, 0.5mm ball pitch

## RZ/G2 Specification 2

Items	RZ/G2H	RZ/G2M	RZ/G2N	RZ/G2E
CPU (Arm® Cortex®-A)	4× Cortex®-A57@1.5GHz 4× Cortex®-A53@1.2GHz L1,L2 Parity/ECC	2× Cortex®-A57@1.5GHz 4× Cortex®-A53@1.2GHz L1,L2 Parity/ECC	2× Cortex®-A57@1.5GHz L1,L2 Parity/ECC	2× Cortex®-A53@1.2GHz L1,L2 Parity/ECC
CPU (Arm® Cortex®-R)	1× Cortex®-R7@800MHz L1,TCM w/ECC	1× Cortex®-R7@800MHz L1,TCM w/ECC	1× Cortex®-R7@800MHz L1,TCM w/ECC	1× Cortex®-R7@800MHz L1,TCM w/ECC
DRAM I/F	32-bit ×2ch LPDDR4(3200)	32-bit ×2ch LPDDR4(3200)	32-bit ×1ch LPDDR4(3200)	32-bit ×1ch DDR3L(1856)
Video in	2×MIPI CSI-2, 2×Digital (RGB/YCbCr) up to 8 input image can be captured	2×MIPI CSI-2, 2×Digital (RGB/YCbCr) up to 8 input image can be captured	2×MIPI CSI-2, 2×Digital (RGB/YCbCr) up to 8 input image can be captured	1×MIPI CSI-2, 1×Digital(RGB/YCbCr) up to 2 input image can be captured
Video Codec	Support up to 4k resolutions Decoding: H.265, Encoding and Decoding: H.264	Support up to 4k resolutions Decoding: H.265, Encoding and Decoding: H.264	Support up to 4k resolutions Decoding: H.265, Encoding and Decoding: H.264	Support up to FHD resolutions Decoding: H.265, Encoding and Decoding: H.264
3D GFX	PowerVR GX6650@600MHz	PowerVR GX6250@600MHz	PowerVR GE7800@600MHz	PowerVR GE8300@600MHz
Display out	1×HDMI, 1×LVDS, 1×Digital RGB	1×HDMI, 1×LVDS, 1×Digital RGB	1×HDMI, 1×LVDS, 1×Digital RGB	2×LVDS or 1×LVDS, 1×Digital RGB
USB	USB2.0×2ch (1H, 1H/F/OTG) USB3.0/2.0×1ch (DRD)	USB2.0×2ch (1H, 1H/F/OTG) USB3.0/2.0×1ch (DRD)	USB2.0×2ch (1H, 1H/F/OTG) USB3.0/2.0×1ch (DRD)	USB2.0×1ch (H/F) USB3.0/2.0×1ch (DRD)
Gbit Ether	1ch	1ch	1ch	1ch
CAN	2ch (support CAN-FD)	2ch (support CAN-FD)	2ch (support CAN-FD)	2ch (support CAN-FD)
PCIe	2ch (Rev2.0 1Lane) one of the 2ch is shared with SATA	2ch (Rev2.0 1Lane)	2ch (Rev2.0 1Lane) one of the 2ch is shared with SATA	1ch (Rev2.0 1Lane)
SATA	1ch (Pin Shared)	No	1ch (Pin Shared)	No
Package	1022-pin FCBGA, 29mm×29mm 0.8mm ball pitch	1022-pin FCBGA, 29mm×29mm 0.8mm ball pitch	1022-pin FCBGA, 29mm×29mm 0.8mm ball pitch	552-pin FCBGA, 21mm×21mm 0.8mm ball pitch

← Pin Compatible →

## RZ/Five (RISC-V) Features and Specification

The RZ/Five is an entry-class general-purpose Linux MPU with a 64-bit RISC-V architecture.

- General-purpose MPU adopting an Open Instruction Set Architecture RISC-V
- Provide development environment to easy mutual migration between ARM and RISC-V
- General-purpose MPU specialized for IoT Edge


Items	RZ/Five
CPU	64bit RISC-V CPU Core AndesCore™ AX45MP Single core 1.0 GHz
DRAM I/F	16-bit × 1ch DDR4-1600/DDR3L-1333 w/ECC
USB	USB2.0 × 2ch (1Host, 1Host/Function/OTG)
Gbit Ether	2ch : 13mm × 13mm Package 1ch : 11mm × 11mm Package
CAN	2ch (support CAN-FD)
12-bit ADC	2ch
Package	361-pin, LFBGA, 13mm × 13mm, 0.5mm pitch 266-pin, LFBGA, 11mm × 11mm, 0.5mm pitch

## Super Long Term Software Support

The Linux kernel for Renesas RZ MPUs is a Super Long Term Support (SLTS) kernel based on the Civil Infrastructure Platform (CIP). This solution meets the long-term operation needs of manufacturers of industrial infrastructure and building automation equipment. The CIP SLTS Linux kernel supports countermeasures against vulnerability to security attacks with a longterm maintenance period of 10 years or more. This reduces Linux maintenance costs and simplifies adoption of reliable industrial-grade Linux.

## Verified Linux Package(VLP) Reduces Cost and Simplifies Design


The “Verified Linux Package (VLP)” for the RZ/G series is the basic software (CIP SLTS Kernel, RZ/G Device Driver, multimedia, graphics, security, etc). This packaged software is verified by Renesas and is available from the Renesas RZ Linux platform site. With VLPs, you can start developing applications quickly while minimizing Linux maintenance resources.



## Flexible Development Kits

RZ/G2 development kits support the industry standard 96Boards specification and SMARC specification to enable evaluation and speed development with wide variety of mezzanine boards and existing carrier boards. Renesas provides circuit schematics, component BOMs, and board layout data to make it easy to spin your own custom hardware.

### RZ/G3S SMARC Module + Carrier Board II



- RZ/G3S SMARC Module
  - Size: 82mm × 80mm
  - Processor: RZ/G3S
  - Main Memory: 1GB LPDDR4 (1GB × 1)
  - QSPI NOR FLASH: 16MB
  - eMMC Memory: 64GB
  - External Storage: micro SD × 2
  - A/D Converter
  - JTAG connector


#### Carrier Board II

- Size: 190mm × 130mm
- PCIe 4-lane slot
- M.2 Key E interface, M.2 Key B interface and SIM card interface
- Gigabit Ethernet × 2
- USB2.0 × 2ch (OTG × 1ch, Host × 1ch)
- CAN-FD × 2
- External Storage: micro SD × 1
- Audio Line In × 1
- Audio Line Out × 1
- PMOD × 2
- USB-Type C for Power Input

### RZ SMARC v2.1 Module + Carrier Board



- RZ/G2L, RZ/G2LC, RZ/G2UL SMARC Module
  - Size: 82mm × 50mm
  - Processor: RZ/G2L, RZ/G2LC, RZ/G2UL
  - Main Memory: 2GB DDR4 (1GB × 2) \*G2UL: 1GB (1GB × 1)
  - QSPI NOR FLASH: 16MB
  - eMMC Memory: 64GB
  - External Storage: micro SD × 1
  - A/D Converter Interface × 2
  - JTAG connector




- RZ/Five SMARC Module
  - Size: 82mm × 50mm
  - Processor: RZ/Five
  - Main Memory: 1GB DDR4 (1GB × 1)
  - QSPI NOR FLASH: 16MB
  - eMMC Memory: 64GB
  - External Storage: micro SD × 1
  - A/D Converter Interface × 2
  - JTAG connector

#### Carrier Board


- Size: 150mm × 90mm
- Gigabit Ethernet × 2
- USB2.0 × 2ch (OTG × 1ch, Host × 1ch)
- MIPI CSI-2 Camera connector (can connect to Google Coral Camera)
- Micro HDMI (output) connector
- CAN-FD × 2
- External Storage: micro SD × 1
- Audio Line In × 1
- Audio Line Out × 1
- PMOD × 2
- USB-Type C for Power Input

### RZ/G2H, G2M, G2N Development Kit (96Boards format compatible)



- Main Memory: 4 GB DDR4
- QSPI NOR FLASH: 64MB
- I<sup>2</sup>C EEPROM: 512bytes
- External Storage: micro SD × 1
- Connectivity: USB 2.0 × 2ch, USB 3.0 × 1ch, GbE × 1
- HDMI out / LVDS out or MIPI DSI out
- Wi-Fi + BT


### RZ/G2E Development Kit (96Boards format compatible)



- Main Memory: 2 GB DDR3L
- QSPI NOR FLASH: 64MB
- I<sup>2</sup>C EEPROM: 512bytes
- External Storage: micro SD × 1
- Connectivity: USB 2.0 × 2ch, USB 3.0 × 1ch, GbE × 1
- HDMI out / LVDS out or MIPI DSI out
- Wi-Fi + BT

## RZ/G Series Application

[IoT Application] Optimized for IoT devices by taking advantage of CPU performance, various interface functions, and security functions



## RZ/G3S Group

### CPU core

- Arm® Cortex®-A55 single-core  
Max. operating frequency: 1.1GHz
- Arm® Cortex®-M33 core x2  
Max. operating frequency: 250MHz  
Cache memory (Cortex®-A55)
- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L3 cache: 256KB

### External memory

- Ability to connect LDDR4-SDRAM / DDR4-SDRAM via DDR dedicated bus
- Data bus width: 16 bits × 1 channel


### Storage interfaces

- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 2 channels
- Multimedia card interface × 1 channel (Shared with SDHI)

### Other peripheral functions

- 16-bit timer × 8 channels
- I<sup>2</sup>C bus interface × 4 channels
- Serial communication interface with FIFO (SCIF) × 6 channels
- SPI Multi I/O Bus Controller × 1 channel (4bit Double data rate)
- Serial Peripheral Interface (RSPI) × 5 channels
- Gigabit Ethernet controller × 2 channels
- Controller area network (CAN) interface × 2 channels (support CAN FD)
- 12-bit A/D converter × 8 channels
- Interrupt controller
- Clock generator (CPG): on-chip PLL
- On-chip debug function

## RZ/G3S Group Block Diagram



## RZ/Five [RISC-V] Group

### CPU core

- 64bit RISC-V CPU Core AndesCore™ AX45MP Single core 1.0GHz

### Cache memory

- L1 instruction Cache: 32KB
- L1 data cache: 32KB
- L2 cache: 256KB

### External memory

- Ability to connect DDR4-SDRAM / DDR3L-SDRAM via DDR dedicated bus
- Data bus width: 16 bits × 1 channel

### Audio functions

- Serial sound interface × 4 channels


### Storage interfaces

- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 2 channels
- Multimedia card interface × 1 channel (Shared with SDHI)

### Other peripheral functions

- 16-bit timer × 8 channels
- I<sup>2</sup>C bus interface × 4 channels
- Serial communication interface with FIFO (SCIF) × 5 channels
- Serial communication interface (SCI) × 2 channels
- SPI Multi I/O Bus Controller × 1 channel (4bit Double data rate)
- Serial Peripheral Interface (RSPI) × 3 channels
- Gigabit Ethernet controller × 2 channels
- Controller area network (CAN) interface × 2 channels (support CAN FD)
- 12-bit A/D converter × 2 channels
- Interrupt controller
- Clock generator (CPG): on-chip PLL
- On-chip debug function


## RZ/Five [RISC-V] Group Block Diagram



[HMI Application] The HMI can be made more expressive by making full use of the 3D graphics and video capabilities.



## HMI Solutions



## RZ/G2L Group

### CPU core

- Arm® Cortex®-A55, dual-core or single-core  
Max. operating frequency: 1.2GHz
- Arm® Cortex®-M33, single-core  
Max. operating frequency: 200MHz

### Cache memory (Cortex®-A55)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L3 cache: 256KB

### External memory

- Ability to connect DDR4-SDRAM / DDR3L-SDRAM via DDR dedicated bus
- Data bus width: 16 bits × 1 channel

### 3D graphics

- Arm Mali™-G31 GPU

### Video functions

- Video display interface: MIPI DSI × 1 channel or Digital parallel output × 1 channel
- Video input interface: MIPI CSI-2 × 1 channel or Digital parallel input × 1 channel
- Video codec module: VCPL4 × 1 channel
- Video image processing functions (Resizer and Color Space / Color Format Conversion)

### Audio functions

- Serial sound interface × 4 channels


### Storage interfaces

- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 2 channels
- Multimedia card interface × 1 channel (Shared with SDHI)

### Other peripheral functions

- 32-bit timer × 1 channel
- 16-bit timer × 8 channels
- PWM timer × 8 channels
- I<sup>2</sup>C bus interface × 4 channels
- Serial communication interface with FIFO (SCIF) × 5 channels
- Serial communication interface (SCI) × 2 channels
- SPI Multi I/O Bus Controller × 1 channel (8bit Double data rate)
- Serial Peripheral Interface (RSPI) × 3channels
- Gigabit Ethernet controller × 2 channels
- Controller area network (CAN) interface × 2 channels (support CAN FD)
- 12-bit A/D converter × 8 channels
- Interrupt controller
- Clock generator (CPG): on-chip PLL
- On-chip debug function

## RZ/G2L Group Block Diagram



## RZ/G2LC Group

### CPU core

- Arm® Cortex®-A55, dual-core or single-core  
Max. operating frequency: 1.2GHz
- Arm® Cortex®-M33, single-core  
Max. operating frequency: 200MHz

### Cache memory (Cortex®-A55)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L3 cache: 256KB

### External memory

- Ability to connect DDR4-SDRAM / DDR3L-SDRAM via DDR dedicated bus
- Data bus width: 16 bits × 1 channel

### 3D graphics

- Arm Mali™-G31 GPU

### Video functions

- Video display interface: MIPI DSI × 1 channel
- Video input interface: MIPI CSI-2 × 1 channel
- Video image processing functions (Resizer and Color Space / Color Format Conversion)

### Audio functions

- Serial sound interface × 2 channels


### Storage interfaces

- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 2 channels
- Multimedia card interface × 1 channel (Shared with SDHI)

### Other peripheral functions

- 32-bit timer × 1 channel
- 16-bit timer × 5 channels
- PWM timer × 4 channels
- I<sup>2</sup>C bus interface × 4 channels
- Serial communication interface with FIFO (SCIF) × 3 channels
- Serial communication interface (SCI) × 2 channels
- SPI Multi I/O Bus Controller × 1 channel (4bit Double data rate)
- Serial Peripheral Interface (RSPI) × 3channels
- Gigabit Ethernet controller × 1 channel
- Controller area network (CAN) interface × 2 channels (support CAN FD)
- Interrupt controller
- Clock generator (CPG): on-chip PLL
- On-chip debug function

## RZ/G2LC Group Block Diagram









## RZ/G2E Group

### CPU core

- Arm® Cortex®-A53, quad-core  
Max. operating frequency: 1.2GHz
- Arm® Cortex®-R7, single-core  
Max. operating frequency: 800MHz

### Cache memory (Cortex®-A53)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L2 cache: 256KB

### Cache memory (Cortex®-R7)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- I-TCM: 32KB
- D-TCM: 32KB

### External memory

- Ability to connect DDR3L-SDRAM via DDR dedicated bus
- Data bus width: 32 bits × 1 channel

### External expansion

- Ability to connect flash ROM or SRAM directly
- Data bus width: 8/16 bits
- PCI Express 2.0 : 1 Lane × 1 channel

### 3D graphics

- PowerVR™ GE8300

### Video functions

- Video display interface × 2 channels (2 channels: LVDS, 1 channel: RGB888)
- Video input interface × 3 channels (1 channels: MIPI CSI-2, 2 channels: Digital(RGB/YCbCr))

- Video codec module: VCP4 × 1 channel
- IP converter module
- Video image processing functions (color conversion, image enlargement/reduction, filtering)

### Audio functions

- Sampling rate converter × 10 channels
- Serial sound interface × 10 channels


### Storage interfaces

- USB 3.0 DRD × 1 channel
- USB 2.0 × 1 channel (Host-Function 1 channel)

### Other peripheral functions

- SD host interface × 3 channels
- Multimedia card interface × 1 channel
- 32-bit timer × 15 channels
- PWM timer × 7 channels
- I<sup>2</sup>C bus interface × 8 channels
- Serial communication interface (SCIF) × 6 channels
- Quad serial peripheral interface (QSPI) × 2 channels (boot support)
- Clock-synchronous serial interface (MSIOF) × 4 channels (SPI/IIS support)
- Ethernet controller with AVB support (support for IEEE 802.1BA, IEEE 802.1AS, IEEE 802.1Qav, and IEEE 1722)
- Controller area network (CAN) interface × 2 channels
- Interrupt controller (INTC)
- Clock generator (CPG): on-chip PLL
- On-chip debug function

## RZ/G2E Group Block Diagram





## Code Generation Support: Flexible Software Package (FSP) + Smart Configurator (SC)

(Supported products: RZ/G2L, RZ/G2LC, RZ/G2UL, RZ/G3S)

The FSP includes everything you'll need to start developing software: board-dependent programs, peripheral function drivers, middleware, and documentation on how to use them.

Smart Configurator is a utility based on the concept of "combining software components freely." The intuitive GUI makes it easy to configure pins and FSP driver settings and to generate source code customized for your use case. It works together with integrated development environments such as e<sup>2</sup> studio.




# RZ/A Series

## RZ/A Series Application



## Benefits of RZ/A Series — Develop like MCUs

RZ/A series MPUs retain the ease-of-use of Renesas MCUs due to rich integrated development environments, and deliver higher performance than MCUs.




This is an example using Free RTOS.  
 \*1 embedded Graphics Multiplatform Library  
 \*2 Guiliani Streaming Editor

### Benefits of RZ/A3UL


- 64bit CPU@1GHz RTOS MPU
  - Octal-SPI Flash/Octal-SPI RAM: For simple and low cost PCB design
  - DDR3L/DDR4: For high resolution HMI and camera use cases
- Pin-compatible RZ/A3UL (RTOS) and RZ/G2UL (Linux) for easy migration
  - The 361-pin package is pin-compatible between RZ/A3UL and RZ/G2UL

### Benefits of RZ/A1 Group, and RZ/A2M MPUs

- Eliminate the need to design a high-speed interface
- Reduced mounting area
- Reduced PCB cost
- No DRAM procurement issues
- Reduced EMI noise



- Include on-chip graphics display and camera input capabilities



### DRP Library


- RZ/A2M MPUs with DRP improve image processing performance by 10X over RZ/A1 MPUs
  - Dynamically Reconfigurable Processor (DRP) technology accelerates image processing
  - Enables hybrid e-AI solutions with DRP for image processing + CPU for inference

The RZ/A2M is designed around e-AI for smart appliances, network cameras, service robots, scanner products, and industrial equipment requiring high-speed image processing. The RZ/A2M combines a general-purpose MPU with Renesas' proprietary DRP technology for unique hybrid processing for image recognition and machine vision (MV), and AI processing works in conjunction with the Cortex®-A9, which pre-processes image data at high speed and extracts features for recognition target.

## RZ/A3UL Group

- 64-bit Arm® Cortex®-A55 (1 GHz, single core)
- 16bit DDR3L/DDR4-1600 (in line ECC)
- Octal-SPI Flash/RAM IF
- Camera IF; MIPI CSI-2 (4-lane)
- Display IF; Parallel RGB888/RGB666
- 2x Gigabit Ethernet
- 2x CAN (CAN-FD)
- 2x USB2.0 (Host, Host/Peripheral)
- 2x SDHI (UHS-I, UHS-I/MMC)


## RZ/A3UL Group Block Diagram



## RZ/A2M Group

- CPU (Arm® Cortex®-A9)
- Operating frequency: 528MHz
  - Single-precision/double-precision FPU
  - Arm® NEON™
- On-chip memory
- 4MB
- Main graphics and camera input functions
- Video display controller (VDC6): 1 channel  
LCD output: Max. WXGA  
Screen superimposition: 3 layers  
Video input: Max. XGA
  - CMOS camera input (CEU): 1 channel
  - MIPI CSI-2 interface: 1 channel
  - Distortion compensation unit (IMR): 1 channel
  - 2D graphics engine: 1 channel
  - Sprite engine: 1 channel
  - JPEG coding engine: 1 channel
- Main memory interface functions
- NOR flash, SDRAM, NAND flash
  - Serial flash: 1-bit/4-bit/8-bit: 1 channel, 8-bit: 1 channel  
(ability to run stored programs directly)
  - SD/MMC host interface: 2 channels
- Main communication functions
- USB 2.0 High Speed: 2 channels (Host/Function switchable)
  - 10M/100M EtherMAC: 2 channels
  - SCIF: 5 channels
  - I²C: 4 channels
  - SSI: 4 channels
  - RSPI: 3 channels
  - CAN-FD: 2 channels
- Optional functions
- DRP (Dynamically Reconfigurable Processor)
- Package
- 176-LFBGA (13mm×13mm, 0.8mm pitch)
  - 256-LFBGA (11mm×11mm, 0.5mm pitch)
  - 272-FBGA (17mm×17mm, 0.8mm pitch)
  - 324-FBGA (19mm×19mm, 0.8mm pitch)

## RZ/A2M Group Block Diagram



## RZ/A1H Group and RZ/A1M Group (Pin Compatible)

### CPU (Arm® Cortex®-A9)

- Operating frequency: 400MHz
- Single-precision/double-precision FPU
- Arm® NEON™

### On-chip memory

- RZ/A1H: 10MB
- RZ/A1M: 5MB

### Main graphics and camera input functions

- Video display controller (VDC5): 2 channels  
LCD output: Max. WXGA  
Screen superimposition: 4 layers  
Video input: Max. XGA (CVBS analog input supported)
- CMOS camera input (CEU): 1 channel
- PAL/NTSC decoder (DVDEC): 2 channels
- Distortion compensation unit (IMR): 1 channel
- Open VG accelerator: 1 channel
- JPEG coding engine: 1 channel

### Main memory interface functions

- NOR flash, SDRAM, NAND flash
- QSPI serial flash: 2 channels (ability to run stored programs directly)
- SD host interface: 2 channels
- MMC host interface: 1 channel

### Main communication functions

- USB 2.0 High Speed: 2 channels (Host/Function switchable)
- 10M/100M EtherMAC: 1channel
- SCIF: 8 channels
- I<sup>2</sup>C: 4 channels
- SSI: 6 channels
- RSPI: 5 channels
- Ethernet AVB: 1 channel
- CAN: 5 channels

### Package

- 256-LFBGA (11mm × 11mm, 0.5mm pitch)
- 256-LFQFP (28mm × 28mm, 0.4mm pitch)
- 324-FBGA (19mm × 19mm, 0.8mm pitch)

## RZ/A1LU Group

### CPU (Arm® Cortex®-A9)

- Operating frequency: 400MHz
- Single-precision/double-precision FPU
- Arm® NEON™

### On-chip memory

- 3MB

### Main graphics and camera input functions

- LCD controller (VDC5): 1 channel  
LCD output: Max. WXGA  
Screen superimposition: 3 layers  
Video input: Max. XGA
- CMOS camera input (CEU): 1 channel
- JPEG coding engine: 1 channel

### Main memory interface functions

- NOR flash, SDRAM
- QSPI serial flash: 1 channel (ability to run stored programs directly)
- SD host interface: 2 channels
- MMC host interface: 1 channel


### Main communication functions

- USB 2.0 High Speed: 2 channels (Host/Function switchable)
- 10M/100M EtherMAC: 1channel
- SCIF: 5 channels
- I<sup>2</sup>C: 4 channels
- SSI: 4 channels
- RSPI: 3 channels
- Ethernet AVB: 1 channel
- CAN: 2 channels


### Package

- 176-LFBGA (8mm × 8mm, 0.5mm pitch)
- 176-LFQFP (24mm × 24mm, 0.5mm pitch)
- 208-LFQFP (28mm × 28mm, 0.5mm pitch)

## RZ/A1H, and RZ/A1M Group Block Diagram



## RZ/A1LU Group Block Diagram



## RZ/A1L, RZ/A1LC Group

### CPU (Arm® Cortex®-A9)

- Operating frequency: 400MHz
- Single-precision/double-precision FPU
- Arm® NEON™

### On-chip memory

- RZ/A1L: 3MB
- RZ/A1LC: 2MB

### Main graphics and camera input functions

- LCD controller (VDC5): 1 channel  
LCD output: Max. WXGA  
Screen superimposition: 3 layers  
Video input: Max. XGA

- CMOS camera input (CEU): 1 channel

### Main memory interface functions

- NOR flash, SDRAM, NAND flash
- QSPI serial flash: 1 channel (ability to run stored programs directly)
- SD host interface: 2 channels
- MMC host interface: 1 channel


### Main communication functions

- USB 2.0 High Speed: 2 channels (Host/Function switchable)
- 10M/100M EtherMAC: 1 channel
- SCIF: 5 channels
- I<sup>2</sup>C: 4 channels
- SSI: 4 channels
- RSPI: 3 channels
- CAN: 2 channels

### Package

- 176-LFBGA (8mm × 8mm, 0.5mm pitch)
- 176-LFQFP (24mm × 24mm, 0.5mm pitch)
- 208-LFQFP (28mm × 28mm, 0.5mm pitch)
- 233-FBGA (15mm × 15mm, 0.8mm pitch)










## RZ/A1L, RZ/A1LC Group Block Diagram



\* RZ/A1L Group specification only.



## RZ/A Series: Development Environments (Integrated Development Environments)

			
Development environments	<ul style="list-style-type: none"> <li>e<sup>2</sup> studio*<sup>1</sup></li> </ul> 	<ul style="list-style-type: none"> <li>Arm® DS</li> </ul> 	<ul style="list-style-type: none"> <li>IAR Embedded Workbench® for Arm®</li> </ul> 
Compilers	<ul style="list-style-type: none"> <li>GNU Arm Embedded Toolchain</li> </ul>	<ul style="list-style-type: none"> <li>Arm Compiler</li> </ul>	<ul style="list-style-type: none"> <li>IAR C/C++ compiler*<sup>3</sup></li> </ul>
ICEs	<ul style="list-style-type: none"> <li>J-Link LITE from Segger</li> <li>J-Link series from Segger*<sup>2</sup></li> </ul> 	<ul style="list-style-type: none"> <li>DSTREAM™</li> <li>ULINKpro™</li> <li>ULINKproD™</li> <li>ULINK2™</li> </ul> 	<ul style="list-style-type: none"> <li>I-jet™/I-jet Trace™ for Arm® Cortex®-A/R/M</li> <li>JTAGjet-Trace</li> </ul> 
Supported products	RZ/A1 Group, RZ/A2M, RZ/A3UL	RZ/A2M	RZ/A1 Group, RZ/A2M

\*1: Eclipse-based development environment from Renesas (<https://www.renesas.com/e2studio>)

\*2: Renesas does not handle ICEs from Segger. Contact a sales agent for details.

\*3: A free evaluation license is available provided the 14-day time-limited evaluation or the code size-limited evaluation.

## RZ/A Series: Development Tools (Debuggers, ICEs)



	 Kyoto Microcomputer Co., Ltd.		
Debuggers	<ul style="list-style-type: none"> <li>PARTNER-Jet2</li> </ul> 	<ul style="list-style-type: none"> <li>Ozone</li> <li>e<sup>2</sup> studio</li> </ul>	<ul style="list-style-type: none"> <li>PowerView</li> </ul> 
ICEs		<ul style="list-style-type: none"> <li>J-Link Series</li> </ul> 	<ul style="list-style-type: none"> <li>PowerDebug</li> </ul> 
Supported compilers	<ul style="list-style-type: none"> <li>exeGCC from Kyoto Microcomputer</li> <li>GNU Arm Embedded Toolchain</li> <li>Arm compiler</li> <li>IAR C/C++ compiler, etc.</li> </ul>	<ul style="list-style-type: none"> <li>GNU Arm Embedded Toolchain</li> <li>Arm compiler</li> <li>IAR C/C++ compiler, etc.</li> </ul>	<ul style="list-style-type: none"> <li>GNU Arm Embedded Toolchain</li> <li>Arm compiler</li> <li>IAR C/C++ compiler, etc.</li> </ul>
Supported products	RZ/A1 Group, RZ/A2M, RZ/A3UL		

## Code Generation Support: Flexible Software Package (FSP) + Smart Configurator (SC)

(Supported product: RZ/A3UL)

The FSP includes everything you'll need to start developing software: board-dependent programs, peripheral function drivers, middleware, and documentation on how to use them.

Smart Configurator is a utility based on the concept of "combining software components freely." The intuitive GUI makes it easy to configure pins and FSP driver settings and to generate source code customized for your use case. It works together with integrated development environments such as e<sup>2</sup> studio.





# RZ Family Ecosystem Partners

Renesas is enabling a comprehensive partner ecosystem to deliver an array of software and hardware building blocks that will work out-of-the-box with [Renesas RZ Family MPUs](#). The Renesas RZ ecosystem will help accelerate the development of IoT applications, including core technologies such as security, safety, connectivity, and HMI among others.



## Expansive Third Party Solutions Portfolio

- 200+ partners, 300+ solutions and growing
- Coverage across all key IoT technologies
- Robust GTM and strong digital drumbeat



## Commercial Grade Building Block Solutions

- Commercial grade software
- Work out-of-the-box with Renesas products
- Bundling options for select solutions



## Problem Solving at Heart

- Address specific design problems
- Address specific skill-set gaps
- Customer-centric approach

## Partner Overview

The partner overview shown might not be complete since the partner network is extending almost daily. For best reference and latest data, we recommend checking our webpage at: [RZ Partner Ecosystem Solutions](#)

# RZ Family Package Lineup

Pin-type:	<b>121-LFBGA</b>	<b>128-LFQFP</b>	<b>176-LFBGA</b>	<b>176-LFBGA</b>	<b>176-LFQFP</b>	<b>176-LFQFP</b>	<b>196-LFBGA</b>
Size:	10 x 10 mm	14 x 20 mm	8 x 8 mm	13 x 13 mm	24 x 24 mm	24 x 24 mm	12 x 12 mm
Pitch:	0.80 mm	0.50 mm	0.50 mm	0.80 mm	0.50 mm	0.50 mm	0.80 mm
Thickness:	1.40 mm	1.60 mm	1.40 mm	1.40 mm	1.60 mm	1.70 mm	1.70 mm
Group:	RZ/N2L	RZ/T2M	RZ/A1L, A1LC, A1LU	RZ/A2M	RZ/T2M	RZ/A1L, A1LU	RZ/N1L, N1S, RZ/T2L
Pin-type:	<b>208-LFQFP</b>	<b>225-LFBGA</b>	<b>233-FBGA</b>	<b>256-LFBGA</b>	<b>256-LFQFP</b>	<b>266-LFBGA</b>	<b>266-LFBGA</b>
Size:	28 x 28 mm	13 x 13 mm	15 x 15 mm	11 x 11 mm	28 x 28 mm	11 x 11 mm	11 x 11 mm
Pitch:	0.50 mm	0.80 mm	0.80 mm	0.50 mm	0.40 mm	0.50 mm	0.50 mm
Thickness:	1.70 mm	1.40 mm	1.9 mm	1.40 mm	1.70 mm	1.40 mm	1.40 mm
Group:	RZ/A1L, A1LU	RZ/T2ME, T2M, RZ/N2L	RZ/A1LU	RZ/A2M, A1H, A1M	RZ/A1H, A1M	RZ/Five	RZ/Five
Pin-type:	<b>272-FBGA</b>	<b>320-FBGA</b>	<b>324-FBGA</b>	<b>324-LFBGA</b>	<b>359-LFBGA</b>	<b>361-LFBGA</b>	<b>361-LFBGA</b>
Size:	17 x 17 mm	17 x 17 mm	19 x 19 mm	15 x 15 mm	14 x 14 mm	13 x 13 mm	13 x 13 mm
Pitch:	0.8 mm	0.80 mm	0.80 mm	0.80 mm	0.50 mm	0.50 mm	0.50 mm
Thickness:	1.90 mm	2.30 mm	2.10 mm	1.70 mm	1.40 mm	1.40 mm	1.40 mm
Group:	RZ/A2M	RZ/T1	RZ/T2ME, T2M	RZ/A2M, A1H, A1M	RZ/N1D, N1S	RZ/A2M	RZ/A3UL
Pin-type:	<b>400-LFBGA</b>	<b>456-LFBGA</b>	<b>501-FBGA</b>	<b>551-LFBGA</b>	<b>552-FBGA</b>	<b>576-FCBGA</b>	<b>729-FCBGA</b>
Size:	17 x 17 mm	15 x 15 mm	21 x 21 mm	21 x 21 mm	21 x 21 mm	21 x 21 mm	23 x 23 mm
Pitch:	0.50 mm	0.50 mm	0.80 mm	0.80 mm	0.80 mm	0.80 mm	0.80 mm
Thickness:	1.40 mm	1.40 mm	1.70 mm	1.40 mm	2.3 mm	2.3 mm	2.4 mm
Group:	RZ/G2LC, G2UL, RZ/Five, RZ/A3UL	RZ/G3S	RZ/N1D	RZ/G2L, RZ/V2L	RZ/G2L, RZ/V2L	RZ/N2H	RZ/G2E, RZ/T2H
Pin-type:	<b>831-FBGA</b>	<b>841-FCBGA</b>	<b>1022-FBGA</b>	<b>1368-HFBGA</b>	<b>1368-HFBGA</b>	<b>1368-HFBGA</b>	<b>1368-HFBGA</b>
Size:	27 x 27 mm	15 x 15 mm	29 x 29 mm	19 x 19 mm	19 x 19 mm	19 x 19 mm	19 x 19 mm
Pitch:	0.80 mm	0.50 mm	0.80 mm	0.50 mm	0.50 mm	0.50 mm	0.50 mm
Thickness:	2.40 mm	1.90 mm ± 0.2 mm	2.5 mm	2.65 mm	2.65 mm	2.65 mm	2.65 mm
Group:	RZ/G1H, G1M, G1N	RZ/V2M, V2MA	RZ/G2M, G2N	RZ/G2H	RZ/V2H	RZ/V2H	RZ/V2H

Renesas Electronics Corporation TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan

#### Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
  2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
  3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
  4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
  5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
  6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
    - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
    - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
 Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
  7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
  8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
  9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
  10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
  11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
  12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
  13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
  14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.  
 (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 2020.10)

#### Contact Us

<https://www.renesas.com/contact-us>



# Renesas Electronics Corporation

[www.renesas.com](http://www.renesas.com)