

ISL70517SEH

Total Dose Testing

TR024

Rev 1.00

February 1, 2017

Introduction

This report provides results of a Total Ionizing Dose (TID) test of the [ISL70517SEH](#) instrumentation amplifier. The test was conducted in order to determine the sensitivity of the parts to the total dose environment. Irradiations were performed to 75krad(Si) at 0.01rad(Si)/s under Biased and grounded conditions and were followed by a Biased anneal at +100°C for 168 hours. The dates of the testing, including Biased anneal, were April 6, 2016 to July 22, 2016. No rejects to the SMD parametric limits were encountered.

Related Literature

- For a full list of related documents, visit our website
 - MIL-STD-883 test method 1019
 - [ISL70517SEH](#) product page

Part Description

The ISL70517SEH is a differential input, single-ended output instrumentation amplifier designed for precision Analog-to-Digital Converter (ADC) applications. The part operates over a supply range of 8V ($\pm 4V$) to 36V ($\pm 18V$) and features a differential input voltage range of $\pm 30V$. The output stage has rail-to-rail output drive capability optimized for ADC driver applications. The gain of the ISL70517SEH can be programmed from 0.1 to 10,000 via two external resistors, R_{IN} and R_{FB} . The gain accuracy is determined by the matching of R_{IN} and R_{FB} . The gain resistors use Kelvin sensing, which removes gain error terms due to PC trace resistance. The input and output stages have individual power supply pins, which enable input signals riding on a high common-mode voltage to be level shifted to a low voltage device, such as an A/D converter. The rail-to-rail output stage can be powered from the same supplies as the ADC, which preserves the ADC maximum input dynamic range and eliminates ADC input overdrive.

The companion [ISL70617SEH](#) is a differential input, differential output version of the ISL70517SEH. Total ionizing dose test results for the ISL70617SEH are discussed elsewhere.

These versatile amplifiers are suitable for a variety of general purpose applications in addition to ADC applications. Additional features not found in other instrumentation amplifiers enable high levels of DC precision and excellent AC performance. The ISL70517SEH and ISL70617SEH are offered in the 24 Ld ceramic flatpack package and their specifications are ensured across the -55°C to +125°C temperature range. The pinouts and pin description for both parts are shown in [Table 1 on page 2](#). The reader is referred to the relevant Intersil datasheets and other on-line information for further detail.

Test Description

Irradiation Facilities


Irradiations were performed using a Hopewell Designs N40 panoramic vault-type low dose rate ^{60}Co irradiator located in the Palm Bay, Florida Intersil facility. The dose rate was 0.0089rad(Si)/s (8.9mrad(Si)/s). The irradiator uses a PbAl spectrum hardening filter to shield the test board and devices under test against low energy secondary gamma radiation.

Test Fixturing

[Figure 1 on page 3](#) shows the configuration and power supply sequencing used for Biased irradiation.

TABLE 1. ISL70517SEH AND ISL70617SEH PINOUTS

PIN NUMBER	ISL70517SEH DESCRIPTION	ISL70617SEH DESCRIPTION
1	No internal connection	No internal connection
2	Internal use, do not connect	Internal use, do not connect
3	Internal use, do not connect	Internal use, do not connect
4	+R _{FB}	+R _{FB}
5	+R _{FB} sense	+R _{FB} sense
6	-R _{FB} sense	-R _{FB} sense
7	-R _{FB}	-R _{FB}
8	Ground	Ground
9	V _{CC}	V _{CC}
10	V _{CO}	V _{CO}
11	+V _{FB}	+V _{FB}
12	V _{OUT}	+V _{OUT}
13	No internal connection	-V _{OUT}
14	V _{REF}	-V _{FB}
15	V _{EO}	V _{EO}
16	V _{EE}	V _{EE}
17	No internal connection	V _{CMO}
18	-R _{IN}	-R _{IN}
19	-R _{IN} sense	-R _{IN} sense
20	+R _{IN} sense	+R _{IN} sense
21	+R _{IN}	+R _{IN}
22	Internal use, do not connect	Internal use, do not connect
23	IN-	IN-
24	IN+	IN+
Package Lid	Tied internally to terminal 8 (ground)	Tied internally to terminal 8 (ground)



V1 = +15V

V2 = -15V

All resistors are 1% 1/4W (surface mount resistors)

All capacitors are 10% 50V (surface mount ceramic chip capacitors)

FIGURE 1. ISL70517SEH, ISL70617SEH LDR SCHEMATIC

Characterization Equipment and Procedures

All electrical testing was performed outside the irradiator using production Automated Test Equipment (ATE) with data logging of all parameters at each downpoint. All downpoint electrical testing was performed at room temperature.

Experimental Matrix

Testing proceeded in accordance with the guidelines of MIL-STD-883 Test Method 1019. The experimental matrix consisted of eight samples irradiated under bias and eight samples irradiated with all pins grounded. Six control units were used.

Samples of the ISL70517SEH were drawn from fabrication lot X4J4A and were packaged in the production hermetic 24 Ld ceramic flatpack, Package Outline Drawing (POD) K24.A. The samples were processed through the standard burn-in cycle and

were screened to the SMD 5962-15246 limits at room, LOW, and HIGH temperatures before irradiation.

Downpoints

Downpoints were 0krad(Si), 10krad(Si), 30krad(Si), 50krad(Si), and 75krad(Si). The samples were subjected to a high temperature Biased anneal for 168 hours at +100 °C following irradiation.

Results

Attributes Data

Testing at low dose rate of the ISL70517SEH is complete and showed no reject devices after irradiation or anneal. [Table 2](#) summarizes the results.

TABLE 2. ISL70517SEH LOW DOSE RATE TOTAL DOSE TEST ATTRIBUTES DATA

PART	RATE	BIAS	SAMPLE SIZE	DOWNPOINT	BIN 1 (Note 1)	REJECTS
ISL70517SEH	0.0089rad(Si)/s	Figure 1	8	Pre-irradiation	8	
				10krad(Si)	8	0
				30krad(Si)	8	0
				50krad(Si)	8	0
				75krad(Si)	8	0
				Anneal, 168 hours at +100 °C	8	0
ISL70517SEH	0.0089rad(Si)/s	Grounded	8	Pre-irradiation	8	
				10krad(Si)	8	0
				30krad(Si)	8	0
				50krad(Si)	8	0
				75krad(Si)	8	0
				Anneal, 168 hours at +100 °C	8	0

NOTE:

1. Bin 1 indicates a device that passes all pre-irradiation specification limits.

Variables Data

The plots in [Figures 2](#) through [47](#) show data at all downpoints. The plots show the average tested value of key parameters as a function of total dose for each of the two irradiation conditions, Biased (B) and Unbiased (U). PA on the graphs stands for Post-

Anneal. Most of the plots also show error bars at each downpoint, representing the population minimum and maximum. The figure sequence and the symbols of the reported parameters are consistent with those used in (SMD) 5962-15246. All parameters showed excellent stability over irradiation, with no observed dose rate or bias sensitivity.

Variables Data Plots




FIGURE 2. ISL70517SEH input amplifier input offset voltage for $\pm 18V$ supplies as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-300\mu V$ to $300\mu V$.




FIGURE 3. ISL70517SEH input amplifier input offset voltage for $\pm 4V$ supplies as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-300\mu V$ to $300\mu V$.

Variables Data Plots (Continued)




FIGURE 4. ISL70517SEH input amplifier positive input bias current for $\pm 18V$ supplies as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -25nA to 25nA.




FIGURE 5. ISL70517SEH input amplifier negative input bias current for $\pm 18V$ supplies as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -25nA to 25nA.

Variables Data Plots (Continued)




FIGURE 6. ISL70517SEH input amplifier positive input bias current for $\pm 5V$ supplies as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -25nA to 25nA.




FIGURE 7. ISL70517SEH input amplifier negative input bias current for $\pm 5V$ supplies as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -25nA to 25nA.

Variables Data Plots (Continued)




FIGURE 8. ISL70517SEH input amplifier input offset current for $\pm 18V$ supplies as a function of low dose rate irradiation for the Biased (per Figure 1) and Unbiased (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-18.5nA$ to $18.5nA$.




FIGURE 9. ISL70517SEH input amplifier input offset current for $\pm 5V$ supplies as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-18.5nA$ to $18.5nA$.

Variables Data Plots (Continued)




FIGURE 10. ISL70517SEH common-mode rejection ratio, ±15V supplies, gain of 100, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -120dB maximum.




FIGURE 11. ISL70517SEH common-mode rejection ratio, ±15V supplies, gain of 1, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -97dB maximum.

Variables Data Plots (Continued)




FIGURE 12. ISL70517SEH feedback input offset voltage, ±18V supplies, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -6000μV to 6000μV.




FIGURE 13. ISL70517SEH feedback input offset voltage, ±4V supplies, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -6000μV to 6000μV.

Variables Data Plots (Continued)




FIGURE 14. ISL70517SEH feedback input bias current, $\pm 18V$ supplies, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-200nA$ to $200nA$.




FIGURE 15. ISL70517SEH feedback input bias current, $\pm 4V$ supplies, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-200nA$ to $200nA$.

Variables Data Plots (Continued)




FIGURE 16. ISL70517SEH LOW output voltage with $I_{OUT} = 0mA$ at $\pm 18V$ supplies as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 160mV maximum.




FIGURE 17. ISL70517SEH LOW output voltage with $I_{OUT} = 1.5mA$ at $\pm 18V$ supplies as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 200mV maximum.

Variables Data Plots (Continued)




FIGURE 18. ISL70517SEH LOW output voltage with $I_{OUT} = 7.5\text{mA}$ at $\pm 18\text{V}$ supplies as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 550mV maximum.




FIGURE 19. ISL70517SEH HIGH output voltage with $I_{OUT} = 0\text{mA}$ at $\pm 18\text{V}$ supplies as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -160mV minimum.

Variables Data Plots (Continued)




FIGURE 20. ISL70517SEH HIGH output voltage with $I_{OUT} = 1.5\text{mA}$ at $\pm 18\text{V}$ supplies as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -200mV minimum.




FIGURE 21. ISL70517SEH HIGH output voltage with $I_{OUT} = 7.5\text{mA}$ at $\pm 18\text{V}$ supplies as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -550mV minimum.

Variables Data Plots (Continued)




FIGURE 22. ISL70517SEH LOW output voltage with $I_{OUT} = 1.5\text{mA}$ at $\pm 4\text{V}$ supplies as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 200mV maximum.




FIGURE 23. ISL70517SEH HIGH output voltage with $I_{OUT} = 1.5\text{mA}$ at $\pm 4\text{V}$ supplies as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -200mV minimum.

Variables Data Plots (Continued)




FIGURE 24. ISL70517SEH output short-circuit current, sinking, at $\pm 18V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 20mA minimum.




FIGURE 25. ISL70517SEH output short-circuit current, sinking, at $\pm 5V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 20mA minimum.

Variables Data Plots (Continued)




FIGURE 26. ISL70517SEH output short-circuit current, sourcing, at $\pm 18V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -20mA maximum.




FIGURE 27. ISL70517SEH output short circuit current, sourcing at $\pm 5V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -20mA maximum.

Variables Data Plots (Continued)




FIGURE 28. ISL70517SEH gain error at $\pm 18V$, $V_{OUT} = \pm 10V$, $R_{FB} = 121k$, Gain = 1, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -0.02% to 0.02%.




FIGURE 29. ISL70517SEH gain error at $\pm 18V$, $V_{OUT} = \pm 10V$, $R_{FB} = 121k$, Gain = 100, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -0.045% to 0.045%.

Variables Data Plots (Continued)




FIGURE 30. ISL70517SEH gain error at $\pm 18V$, $V_{OUT} = \pm 2.5V$, $R_{FB} = 30.1k$, Gain = 1, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -0.04% to 0.04.




FIGURE 31. ISL70517SEH gain error with the input amplifier at $\pm 4V$ and the output amplifier at $\pm 1.5V$, $V_{OUT} = \pm 0.1V$, $R_{FB} = 121k$, Gain = 1, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -0.2% to 0.2%.

Variables Data Plots (Continued)




FIGURE 32. ISL70517SEH gain error with the input amplifier at $\pm 4V$ and the output amplifier at $\pm 1.5V$, $V_{OUT} = \pm 1.25V$, $R_{FB} = 121k$, Gain = 100, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -0.4% to 0.4%.




FIGURE 33. ISL70517SEH gain error with the input amplifier at $\pm 4V$ and the output amplifier at $\pm 1.5V$, $V_{OUT} = \pm 0.1V$, $R_{FB} = 30.1k$, Gain = 1, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are -0.2% to 0.2%.

Variables Data Plots (Continued)




FIGURE 34. ISL70517SEH output offset voltage at $\pm 18V$, $R_{FB} = 30.1k$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-10mV$ to $10mV$.




FIGURE 35. ISL70517SEH output offset voltage at $\pm 5V$, $R_{FB} = 30.1k$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-10mV$ to $10mV$.

Variables Data Plots (Continued)




FIGURE 36. ISL70517SEH output offset voltage at $\pm 18V$, $R_{FB} = 121k$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-40mV$ to $40mV$.




FIGURE 37. ISL70517SEH output offset voltage at $\pm 5V$, $R_{FB} = 121k$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limits are $-40mV$ to $40mV$.

Variables Data Plots (Continued)




FIGURE 38. ISL70517SEH input stage positive supply current (I_{CC}) at $\pm 4V$, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 3.0mA maximum.




FIGURE 39. ISL70517SEH input stage negative supply current (I_{EE}) at $\pm 4V$, as a function of low dose rate irradiation for the Biased (B) (per Figure 1) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -3.0mA minimum.

Variables Data Plots (Continued)




FIGURE 40. ISL70517SEH output stage positive supply current (I_{C0}) at $\pm 4V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 3.0mA maximum.




FIGURE 41. ISL70517SEH output stage negative supply current (I_{E0}) at $\pm 4V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -3.0mA minimum.

Variables Data Plots (Continued)




FIGURE 42. ISL70517SEH input stage positive supply current (I_{CC}) at $\pm 18V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 3.0mA maximum.




FIGURE 43. ISL70517SEH input stage negative supply current (I_{EE}) at $\pm 18V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -3.0mA minimum.

Variables Data Plots (Continued)




FIGURE 44. ISL70517SEH output stage positive supply current (I_{CO}) at $\pm 18V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is 3.0mA maximum.




FIGURE 45. ISL70517SEH output stage negative supply current (I_{EO}) at $\pm 18V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -3.0mA minimum.

Variables Data Plots (Continued)




FIGURE 46. ISL70517SEH input stage power supply rejection ratio, $\pm 4V$ to $\pm 18V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -110dB maximum.




FIGURE 47. ISL70517SEH output stage power supply rejection ratio, $\pm 1.5V$ to $\pm 18V$, as a function of low dose rate irradiation for the Biased (B) (per [Figure 1](#)) and Unbiased (U) (all pins grounded) cases. The error bars represent the minimum and maximum measured values. The post-irradiation SMD limit is -90dB maximum.

Conclusion

This report documents the results of a Total Ionizing Dose (TID) test of the ISL70517SEH instrumentation amplifier. The test was conducted in order to determine the sensitivity of the parts to the low dose rate total dose environment as found in nearly all space applications. Parts were tested to 75krad(Si) at .01rad(Si)/Biased and Unbiased conditions and were then subjected to a high temperature Biased anneal at +100 °C for 168 hours. ATE characterization testing showed no rejects to the SMD Group A

parametric limits (indicated by a Bin 1 category) after Biased and grounded irradiation at low dose rate and after the 168 hours +100 °C Biased anneal. Attributes data are presented in [Table 2](#), while variables data are plotted in [Figures 2](#) through [47](#). No meaningful differences between Biased and Unbiased irradiation were noted and the samples showed no significant response to the high temperature anneal.

TABLE 3. REPORTED PARAMETER

FIGURE	PARAMETER	LIMIT, LOW	LIMIT, HIGH	UNITS	NOTES
2	Input Offset Voltage	-300	300	μV	±18V
3	Input Offset Voltage	-300	300	μV	±4V
4	Positive Input Bias Current	-25	25	nA	±18V
5	Negative Input Bias Current	-25	25	nA	±18V
6	Positive Input Bias Current	-25	25	nA	±5V
7	Negative Input Bias Current	-25	25	nA	±5V
8	Input Offset Current	-18.5	18.5	nA	±18V
9	Input Offset Current	-18.5	18.5	nA	±5V
10	Common Mode Rejection Ratio	-	-120	dB	Gain = 100
11	Common Mode Rejection Ratio	-	-97	dB	Gain = 1
12	Feedback Input Offset Voltage	-6000	6000	μV	±18V
13	Feedback Input Offset Voltage	-6000	6000	μV	±4V
14	Feedback Input Bias Current	-200	200	nA	±18V
15	Feedback Input Bias Current	-200	200	nA	±4V
16	Low Output Voltage	-	160	mV	±18V, I _{OUT} = 0mA
17	Low Output Voltage	-	200	mV	±18V, I _{OUT} = 1.5mA
18	Low Output Voltage	-	550	mV	±18V, I _{OUT} = 7.5mA
19	High Output Voltage	-160	-	mV	±18V, I _{OUT} = 0mA
20	High Output Voltage	-200	-	mV	±18V, I _{OUT} = 1.5mA
21	High Output Voltage	-550	-	mV	±18V, I _{OUT} = 7.5mA
22	Low Output Voltage	-	200	mV	V _{CC} = 4V, V _{EE} = -4V, V _{CO} = 1.5V, V _{EO} = -1.5V, I _{OUT} = 1.5mA
23	High Output Voltage	-200	-	mV	
24	Output Short Circuit Current, Sinking	20	-	mA	±18V
25	Output Short Circuit Current, Sinking	20	-	mA	±5V
26	Output Short Circuit Current, Sourcing	-	-20	mA	±18V
27	Output Short Circuit Current, Sourcing	-	-20	mA	±5V
28	Gain Error	-0.02	0.02	%	V _{OUT} = ±10V, R _{FB} = 121k, G = 1
29	Gain Error	-0.045	0.045	%	V _{OUT} = ±10V, R _{FB} = 121k, G = 100
30	Gain Error	-0.04	0.04	%	V _{OUT} = ±2.5V, R _{FB} = 30.1k, G = 1
31	Gain Error, Low Supply Voltage	-0.2	0.2	%	V _{OUT} = ±0.1V, R _{FB} = 121k, G = 1
32	Gain Error, Low Supply Voltage	-0.4	0.4	%	V _{OUT} = ±1.25V, R _{FB} = 121k, G = 100
33	Gain Error, Low Supply Voltage	-0.2	0.2	%	V _{OUT} = ±0.1V, R _{FB} = 30.1k, G = 1
34	Output Offset Voltage	-10	10	mV	±18V, R _{FB} = 30.1k

TABLE 3. REPORTED PARAMETER (Continued)

FIGURE	PARAMETER	LIMIT, LOW	LIMIT, HIGH	UNITS	NOTES
35	Output Offset Voltage	-10	10	mV	$\pm 5V$, $R_{FB} = 30.1k$
36	Output Offset Voltage	-40	40	mV	$\pm 18V$, $R_{FB} = 121k$
37	Output Offset Voltage	-40	40	mV	$\pm 5V$, $R_{FB} = 121k$
38	Supply Current, I_{CC}	-	3.0	mA	$\pm 4V$
39	Supply Current, I_{EE}	-3.0	-	mA	$\pm 4V$
40	Supply Current, I_{CO}	-	3.0	mA	$\pm 4V$
41	Supply Current, I_{EO}	-3.0	-	mA	$\pm 4V$
42	Supply Current, I_{CC}	-	3.0	mA	$\pm 18V$
43	Supply Current, I_{EE}	-3.0	-	mA	$\pm 18V$
44	Supply Current, I_{CO}	-	3.0	mA	$\pm 18V$
45	Supply Current, I_{EO}	-3.0	-	mA	$\pm 18V$
46	Power Supply Rejection Ratio	-	-110	dB	Input stage PSRR
47	Power Supply Rejection Ratio	-	-90	dB	Output stage PSRR

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338