

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

Application Note

USAGE AND APPLICATION OF SILICON MEDIUM- POWER HIGH-FREQUENCY AMPLIFIER MMIC

μ PC1678G/1678GV/1679G

μ PC2708T to 2710T

μ PC2762T/2763T

μ PC2771T/2776T

[MEMO]

The information in this document will be updated without notice.

This document introduces general applications of the products in this series. The application circuits and circuit constants in this document are examples and not intended for use in actual mass production design. In addition, please take note that restrictions of the application circuit or standardization of the application circuit characteristics are not intended.

Especially, characteristics of high-frequency ICs change depending on the external components and mounting pattern. Therefore, the external circuit constants should be determined based on the required characteristics on your planned system referring to this document and characteristics should be checked before using these ICs.

• **The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.**

• No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Corporation. NEC Corporation assumes no responsibility for any errors which may appear in this document.

• NEC Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Corporation or others.

• Descriptions of circuits, software, and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software, and information in the design of the customer's equipment shall be done under the full responsibility of the customer. NEC Corporation assumes no responsibility for any losses incurred by the customer or third parties arising from the use of these circuits, software, and information.

• While NEC Corporation has been making continuous effort to enhance the reliability of its semiconductor devices, the possibility of defects cannot be eliminated entirely. To minimize risks of damage or injury to persons or property arising from a defect in an NEC semiconductor device, customers must incorporate sufficient safety measures in its design, such as redundancy, fire-containment, and anti-failure features.

• NEC devices are classified into the following three quality grades:

"Standard", "Special", and "Specific". The Specific quality grade applies only to devices developed based on a customer designated "quality assurance program" for a specific application. The recommended applications of a device depend on its quality grade, as indicated below. Customers must check the quality grade of each device before using it in a particular application.

Standard: Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots

Special: Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)

Specific: Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems or medical equipment for life support, etc.

The quality grade of NEC devices is "Standard" unless otherwise specified in NEC's Data Sheets or Data Books. If customers intend to use NEC devices for applications other than those specified for Standard quality grade, they should contact an NEC sales representative in advance.

M7 98.8

The mark ★ shows major revised points.

[MEMO]

CONTENTS

| | |
|---|-----------|
| 1. INTRODUCTION | 7 |
| 2. PRODUCT LINE-UP..... | 7 |
| 2.1 Characteristics | 7 |
| 2.2 Test Circuit..... | 9 |
| 3. THEORETICAL DESCRIPTION | 12 |
| 3.1 Description of Internal Circuit | 12 |
| 3.2 External Circuit Description..... | 13 |
| 3.3 Temperature Condition..... | 14 |
| 4. SAMPLE APPLICATION CHARACTERISTICS..... | 15 |
| 4.1 μ PC1678G, μ PC1679G..... | 17 |
| 4.2 μ PC2709T..... | 18 |
| 4.3 μ PC2776T..... | 20 |
| 4.4 μ PC2762T, μ PC2763T..... | 21 |
| 4.5 μ PC2771T..... | 23 |
| 5. APPLICATIONS | 24 |
| 6. SUMMARY | 24 |
| 7. AFTERWORD..... | 24 |
| APPENDIX. S PARAMETER REFERENCE (T_A = +25°C)..... | 25 |

Precautions for design-ins

- (1) Observe precautions for handling because of electro-static sensitive devices.
- (2) Form a ground pattern as widely as possible to minimize ground impedance (to prevent undesired oscillation).
All the ground pins must be connected together with wide ground pattern to decrease impedance difference.
- (3) The bypass capacitor should be attached to the V_{CC} pin.
- (4) The inductor must be attached between V_{CC} pin and output pin.
The inductance value should be determined in accordance with desired frequency.
- (5) The DC cut capacitor must be each attached to the input and output pins.
- (6) You should apply voltage to V_{CC} pin and output pin. You must not apply voltage to input pin nor regulate input pin voltage (e.g. direct DC pull-down).
- (7) External components cannot modify the IC's internal circuit feedback.

[MEMO]

1. INTRODUCTION

The application for high-frequency devices has recently grown to include not only TV/VCR tuners and cable TV converters but also DBS, cellular phones, pagers, and GPSs. In response to these diverse needs, NEC has developed an abundant line-up of high-frequency amplifier ICs.

This application note is intended to assist user in selecting the product that best suits their applications among NEC's line-up of silicon medium-power high-frequency amplifier ICs and as a reference for designing external circuits that unleash the products' characteristic.

See the data sheet of each product for the product ratings and specifications.

★ 2. PRODUCT LINE-UP

2.1 Characteristics

The part numbers of NEC's silicon medium-power high-frequency amplifier ICs are μ PC1678/1679, μ PC2708 to 2710, μ PC2762/2763, and μ PC2771/2776. Table 2-1 lists the characteristics of these products as measured with an NEC test circuit.

Table 2-1. Characteristics List of Silicon Medium-Power High-Frequency IC Data Sheet
($T_A = +25^\circ\text{C}$, $V_{CC} = V_{out}$, $Z_S = Z_L = 50 \Omega$)

| Part number (discrete part number) | V_{CC} (V) | f_u (GHz) | $P_{O(sat)}$ (dBm) | G_P (dB) | NF (dB) | I_{CC} (mA) | Package | Marking |
|---------------------------------------|-----------------|----------------|-----------------------|---------------|------------|------------------|---------------------------------------|---------|
| μ PC1678G | 4.5 to 5.5 | 2.0 | +17.5 | 23 | 6 | 49 | 8-pin plastic SOP (5.72 mm (225)) | 1678 |
| μ PC1678GV | | | | | | | 8-pin plastic SSOP (4.45 mm (175)) | |
| μ PC1679G | 4.5 to 5.5 | 1.8 | +15.5 | 21.5 | 6 | 40 | 8-pin plastic SOP (5.72 mm (225)) | 1679 |
| μ PC2708T | 4.5 to 5.5 | 2.9 | +10.0 | 15 | 6.5 | 26 | 6-pin minimold | C1D |
| μ PC2709T | 4.5 to 5.5 | 2.6 | +11.5 | 23 | 5 | 25 | 6-pin minimold | C1E |
| μ PC2710T | 4.5 to 5.5 | 1.2 | +13.5 | 33 | 3.5 | 22 | 6-pin minimold | C1F |
| μ PC2762T | 2.7 to 3.3 | 2.9 | +9.0 | 13 | 6.5 | 26.5 | 6-pin minimold | C1Z |
| μ PC2763T | 2.7 to 3.3 | 2.4 | +11.0 | 20 | 5.5 | 27 | 6-pin minimold | C2A |
| μ PC2771T | 2.7 to 3.3 | 2.1 | +12.5 | 21 | 6 | 36 | 6-pin minimold | C2H |
| μ PC2776T | 4.5 to 5.5 | 2.7 | +8.5 | 23 | 6 | 25 | 6-pin minimold | C2L |

Remark The above values are typical values for major characteristics.
Refer to the data sheet of each product for rating conditions.

The line-up features two power supply voltage ranges, 5 V and 3 V, and includes various power gains and output levels. 8-pin SOP, SSOP, and size 2915-size 6-pin minimold are available for packages. Figure 2-1 shows the package dimensions.

The part number is used for the marking in 8-pin packages but a three-character abbreviation is used for the marking in the 6-pin minimold package due to limited printing space. Each abbreviation corresponds to a product. Due to space limitation, the pin 1 mark is printed on the rear side in the minimold package. Figure 2-2 shows a marking example of the 6-pin minimold package.

The alphabetical characters suffixed to the part number (discrete part number) are the code that indicates the package. GV corresponds to 4.45 mm (175) SSOP, G to the conventional SOP, and T to the minimold. If two package codes exist for the same part number, such as the μ PC1678, this means that the same product is available in two different packages. Since the marking is the same on both package types, the products should be distinguished by their package size.

Taping is available as the supply medium for all products except DIP packages. Two taping codes are used according to the IC insertion orientation, 'E1' for SOP and SSOP and 'E3' for minimold. The order code should be "Discrete part number - taping code" (for example, μ PC2776T-E3). For details, refer to the data sheet of each discrete part.

Figure 2-1. Package Drawings of Silicon Medium-Power High-Frequency Amplifier ICs





Figure 2-2. Marking Example



Remark The marking example in the above figure is that of the μ PC2708T.

2.2 Test Circuit

The test circuit is shown in Figure 2-3. Note that the characteristics listed in the data sheets were obtained while the products were set to wide band and that different practical characteristics and conditions apply in the narrow band.

Measurement Method

Common conditions

Use feedthrough capacitor for the bypass capacitor

A network analyzer is used for the following parameters. (Voltage is applied to an output pin via Bias-T)

Power gain

S21 of IC after compensating for effect of input/output lines of jig

Isolation

S12 of IC after compensating for effect of input/output lines of jig

Input Return Loss

S11 of IC after compensating for effect of input/output lines of jig

Output Return Loss

S22 of IC after compensating for effect of input/output lines of jig

An NF meter is used for the following parameters.

Noise figure

NF including jig NF (Cable loss is compensated.)

A signal generator and spectrum analyzer are used for the following items.

Input/Output power characteristics


These characteristics include jig-related effects, and frequency conditions that minimize jig influence should be set. The frequency conditions shall be set to obtain a wide band power gain. (Cable loss is compensated.)

A power supply and ampere meter are used for the following items.

Circuit current


The output inductor is measured mainly via Bias-T and the inductor DC resistance is compensated.

Figure 2-3. Test Circuit




Note Refer to Table 4-1


Test Board for μPC1678G and 1679G



Test Board for μPC1678GV



Test Board Common to 6-Pin Minimold (AMP1)



Notes on printed boards

- Board material..... The following board materials are used to minimize board-related losses when measuring the intrinsic characteristics of ICs.
 μ PC1678G, μ PC1679G, μ PC1678GV, AMP1: Polyimide double-sided copper-clad board
- Back side Whole surface is GND. Through holes keep the GND characteristics of the IC mounting side.
- Specifications..... μ PC1678G, μ PC1679G, μ PC1678GV board dimensions:
50 × 50 × 0.4 mm, 35 μ m thick copper patterning on both sides
AMP1 board dimensions:
30 × 30 × 0.4 mm, 35 μ m thick copper patterning on both sides


★ 3. THEORETICAL DESCRIPTION


3.1 Description of Internal Circuit

The products in this series incorporate $50\ \Omega$ matching circuits formed by resistors on the input side. A multiple negative feedback circuit is provided to offset the variations between h_{FE} and resistance. To obtain desired RF characteristics, a two-stage configuration is employed. Products in this series use the Darlington collector output type for the internal output stage. This output stage collector is ended as an output pin that enables current supply from this pin so that a medium output can be obtained.

For the test environment, Bias-T is mainly used to verify the characteristics in the wide band because the frequency characteristics are not affected. On the other hand, by using an inductor with the minimum required value, the gain in the high-frequency range increases by the amount that the gain in the low-frequency decreases and the band shifts to high-frequency. The gain change varies depending on the effect of the two-stage peaking capacitance that is connected to the internal equivalent circuit output port. The circuit constant differs depending on the product. However, the products can be classified into five types, $\mu\text{PC1678/1679}$, $\mu\text{PC2708 to 2710}$, $\mu\text{PC2762/2763/2771}$, and μPC2776 , based on the internal circuit type. An internal equivalent circuit is shown in Figure 3-1.

Figure 3-1. Silicon Medium-Power Amplifier IC Internal Equivalent Circuit





3.2 External Circuit Description

The ICs in this series are designed to supply large current for an internal output stage transistor to obtain higher output. Therefore, RF characteristics are guaranteed by connecting an external element that offers no resistance to DC current and has high impedance in the high-frequency range. Bias-tee type test circuits are most commonly used to simplify testing and obtain reproducibility.

In actual use, you should externally connect an inductor between the output pin and V_{cc} pin. By using the external inductor, output port can keep the applied voltage and the impedance at used frequency without dropping both parameters. In addition, by using a wire-wound inductor with a self-resonance frequency close to the used frequency, the return loss on the output side may be improved.

For the electrical characteristics test circuit, a bias-tee of approximately 1000nH is used so that high impedance is maintained even in low frequency. If the impedance in the used frequency or above is kept high, the required gain can be obtained even if the inductance value is small. Therefore, the used frequency is allowed to be higher than the self-resonance frequency.

The following shows a calculation example for the used frequency f and inductance value L .

$$Z_{\text{inductor}} = 2 \pi fL$$

$$Z_L = \frac{1}{\frac{1}{Z_{\text{next}}} + \frac{1}{Z_{\text{inductor}}}} = \frac{1}{\frac{1}{Z_{\text{next}}} + \frac{1}{2 \pi fL}}$$

Here, the gain is rapidly decreased at the frequency where the Z_{inductor} is smaller than the next stage impedance Z_{next} (50 Ω for example), and a large gain is obtained at the frequency where the Z_{inductor} is larger than the next stage impedance. Accordingly, the relation between the used frequency and the minimum required inductor is as follows.

$$2 \pi fL > 50 \quad (\text{when } Z_{\text{next}} = 50 \Omega)$$

For example, the calculation of L such that $L > 8$ nH produces $f > 1$ GHz. Therefore, to obtain a flat gain for 1 GHz or higher, the inductance value must be larger than 8 nH.

Because band is limited by the input/output DC cut capacitor value, determine the capacitance value C based on the following calculation.

$$C = \frac{1}{2 \pi \cdot Z \cdot fc}$$

When using the IC in the low frequency band, C should be large value, and when using the IC in the high frequency band, C should be small value to secure the gain.

3.3 Temperature Condition

The maximum ratings of storage and operating temperatures of ICs are regulated in terms of ambient temperature. The package material is plastic so the thermal conductivity is lower than metal leads, and for this reason, the thermal resistance is defined by junction to ambient ($R_{th(j-A)}$), rather than case to ambient, which is meaningless in this case. Because the highly heat conductive metal leads (thermal resistance value between the junction and the lead is 30°C/W or smaller) are the determining factor with regard to thermal conductivity, the maximum junction temperature T_{jMAX} becomes equal to the maximum rating of the storage ambient temperature T_{STG} and the maximum ambient temperature T_{AMAX} becomes equal to the maximum value of the operating ambient temperature T_A (The storage temperature in this section means the non-biased temperature where the case temperature and ambient temperature are equal.). The relation between the power dissipation P_D and thermal resistance is as follows.

$$R_{th(j-A)} = \frac{T_{jMAX} - T_{AMAX} (\text{°C})}{P_D @ T_{AMAX} (W)}$$

The thermal resistance can be calculated since the maximum operating ambient temperature, maximum junction temperature, and power dissipation (at maximum operating ambient temperature) are defined based on the junction-to-ambient thermal resistance listed in the individual data sheet of each product.

The μ PC1678G/GV have a large circuit current so that they experience temperature rise (heat production) due to IC current loss. This condition can be applied to the above expression. Taking the μ PC1678G/GV as an example, the thermal resistance value becomes $R_{th(j-A)} = 180\text{°C/W}$ (when mounting IC on $50 \times 50 \times 1.6$ mm double-sided epoxy glass copper-clad board). Because the circuit current is 60 mA MAX. when the small signal input at $V_{CC} = 5.0$ V:

$$\begin{aligned} T_j &= T_A + P_D \times R_{th(j-A)} \\ &= T_A + 5.0 (V) \times 0.060 (A) \times 180 (\text{°C/W}) \\ &= T_A + 54 (\text{°C}) \end{aligned}$$


Since to $T_j \leq 150 (\text{°C})$,

$$T_A + 54 (\text{°C}) \leq 150 (\text{°C})$$

$$\therefore T_A \leq 96 \text{°C}$$

Therefore, the operating ambient temperature, $T_A = +85\text{°C}$ represents a margin of +11°C taking into account IC heating under these conditions.

Figure 3-2. μ PC1678G/GV Power Dissipation vs. Ambient Temperature



★ **4. SAMPLE APPLICATION CHARACTERISTICS**

Table 4-1 lists sample specifications and characteristics of inductors used for evaluation of application circuits. In this evaluation, evaluation boards with the same dimensions were used to test all the inductors within a product group (Table 4-2). The AMP1 board enables easy calibration using a network analyzer and S parameter measurement that is not affected by the jig input/output line because the input/output line is straight.


Table 4-1. Specifications of Inductors Used for Application Evaluation

| Type | Manufacturer | Product | Inductance | Q | DC resistance | Self-resonance frequency | Permissible current |
|-------------------------------------|-----------------------|--------------|------------------|---------------|-------------------------|--------------------------|---------------------|
| Wire-wound chip inductor | Murata Mfg. Co., Ltd. | LQN21A10NJ | 10 nH | 60 TYP. | 0.25 Ω or less | 100 MHz | 770 mA |
| | TOKO INC. | FSLU2520-R10 | 100 nH | 50 peak | 0.21 Ω | 730 MHz | 540 mA |
| Axial lead inductor | Taiyo Uden Co., Ltd. | LA402 type | 470 nH | 35 to 40 MIN. | 0.4 to 20 Ω MAX. | – | 35 to 400 mA MAX. |
| Manually wound coil (Enameled wire) | Self made | Self made | 50 nH to 1200 nH | – | – | – | – |

Table 4-2. Evaluation Boards Used for Application Evaluation


| Evaluated part number | Evaluation board's name and figure |
|---|--|
| μ PC1678G, μ PC1679G | μ PC1678G/79G evaluation board (Figure 4-1) |
| μ PC2709T, μ PC2776T, μ PC2762/2763T, μ PC2771T | 6-pin minimold amplifier series common board AMP1 (Figure 4-2) |

Figure 4-1. μ PC1678G/79G Evaluation Board Mounting Example



L: Manually wound coil

Figure 4-2. Application Evaluation Circuit Board (AMP1) Mounting Example




L: LQN21A10NJ or FSLV2520-R10

- Cautions 1.** The listed inductors were used to evaluate the relation between inductor parameter and IC application characteristics, and are not recommended by NEC for actual use. For actual use, we recommended that you contact the inductor supplier referring to the specifications listed in Table 4-1 and evaluate your inductor before use.
- 2.** Since NEC calibrates the evaluation board pattern, NEC's evaluation characteristics do not reflect the effect of the pattern. Therefore, you should take into account the effect of the pattern in your actual application design.

4.1 μ PC1678G, μ PC1679G

The gain vs. frequency characteristics of the μ PC1678/1679 with various inductance values are measured using a manually wound coil. Figure 4-3 shows the measured characteristics. In the case of these ICs, the gain at low frequencies and high frequencies increases and wide band is achieved when the inductance value is increased, and the frequency band near the resonance frequency becomes narrow when the inductance value is decreased.

Figure 4-3. Power Gain vs. Frequency Characteristics of μ PC1678G, μ PC1679G for Various Inductance Values (Conditions : $T_A = +25^\circ\text{C}$, $V_{CC} = V_{out} = 5.0\text{ V}$, $Z_s = Z_L = 50\ \Omega$)



4.2 μ PC2709T

To judge the characteristics of the μ PC2709T, it was compared with the μ PC2776T, which has similar electric characteristics, using a 10 nH wire-wound type chip inductor (1 GHz self-resonance frequency). The results of the μ PC2709T and μ PC2776T are shown in Figures 4-4 and 4-5, respectively. The μ PC2709T shows flat gain characteristics in the range from 1 GHz to 2.5 GHz. The μ PC2776T shows a gain decline at 2.0 GHz and higher. This is because in the μ PC2709T the peaking capacitances of the input/output stages are connected to the output pin and the peaking frequency tends to shift to high frequency due to the value of the inductor externally connected to the output pin whereas in the μ PC2776T, the gain at high frequency is little affected because only the peaking capacitance is connected only to the output stage. Expressed a different way, the μ PC2776T has smaller variations.

Figure 4-4. Frequency Characteristics of μ PC2709T Using 10 nH Inductor
(Conditions: $T_A = +25^\circ\text{C}$, $V_{CC} = V_{out} = 5.0 \text{ V}$, $Z_S = Z_L = 50 \Omega$)






Figure 4-5. Frequency Characteristics of μ PC2776T Using 10 nH Inductor
 (Conditions: $T_A = +25^\circ\text{C}$, $V_{CC} = V_{out} = 5.0\text{ V}$, $Z_S = Z_L = 50\ \Omega$)


(a) Power Gain vs. Frequency




(b) Isolation vs. Frequency



(c) Input Return Loss vs. Frequency




(d) Output Return Loss vs. Frequency



4.3 μ PC2776T

Based on the fact that the μ PC2776T, high-frequency gain is not affected by an inductor, the μ PC2776T was evaluated to obtain wide band characteristics from the VHF range to 2 GHz. A wire-wound chip inductor with the resonance frequency of 730 MHz and the inductance value of 100 nH was used to obtain a gain at 100 MHz or higher. The flat characteristics that were obtained are shown in Figure 4-6.

Figure 4-6. Frequency Characteristics of μ PC2776T Using 100 nH Inductor
 (Conditions: $T_A = +25^\circ\text{C}$, $V_{CC} = V_{out} = 5.0\text{ V}$, $Z_S = Z_L = 50\ \Omega$)



4.4 μ PC2762T, μ PC2763T

Given the fact that the μ PC2762T/2763T have a wide 3 dB bandwidth, evaluation tests were tried to obtain the gain at 2 GHz or higher. A 10 nH wire-wound chip inductor (1 GHz self-resonance frequency) was used.

Figure 4-7. Frequency Characteristics of μ PC2762T Using 10 nH Inductor
(Conditions: $T_A = +25^\circ\text{C}$, $V_{CC} = V_{out} = 3.0\text{ V}$, $Z_S = Z_L = 50\ \Omega$)






Figure 4-8. Frequency Characteristics of μ PC2763T Using 10 nH Inductor
 (Conditions: $T_A = +25^\circ\text{C}$, $V_{CC} = V_{out} = 3.0\text{ V}$, $Z_S = Z_L = 50\ \Omega$)



4.5 μ PC2771T

The μ PC2771T has been evaluated to obtain characteristics in the range between 1.4 and 1.9 GHz. A 10 nH wire-wound chip inductor (1 GHz self-resonance frequency) was used. Under these test conditions, obtaining a gain in the range between 1.4 GHz and 1.9 GHz, the 1 dB gain compression point is raised by 1 dB.

Figure 4-9. Frequency Characteristics of μ PC2771T Using 10 nH Inductor
(Conditions: $T_A = +25^\circ\text{C}$, $V_{CC} = V_{out} = 3.0\text{ V}$, $Z_S = Z_L = 50\ \Omega$)



5. APPLICATIONS

Table 5-1 shows possible applications for NEC's silicon medium-power high-frequency amplifier ICs based on their characteristics.

Table 5-1. Medium-Power Amplifier IC Applications

| Applications | Required Characteristics | Part Number |
|--|-------------------------------|--|
| Transmission stage of transceivers or cellular-phone base stations | 5 V, up to 1.0 GHz or 1.5 GHz | μ PC1678G, μ PC1678GV, μ PC1679G, μ PC2710T, μ PC2776T |
| Transmission stage of cellular phones or portable transceivers | 3 V, 0.8 GHz to 2 GHz | μ PC2762T, μ PC2763T, μ PC2771T |
| Receiver stage of BS converters or BS tuner | 5 V, 1 GHz to 2.215 GHz | μ PC2708T, μ PC2709T |
| Wireless LAN | 3 V, 2.5 GHz bandwidth | μ PC2762T, μ PC2763T |

6. SUMMARY

As explained in this application note, NEC's silicon medium-power high-frequency amplifier ICs can be useful characteristics by selecting adequate external circuit constants for the type of internal circuit and high-frequency characteristics of each IC.

7. AFTERWORD

NEC plans to develop products with higher output power and higher efficiency ASSP products.

REFERENCES

Silicon High-Frequency Wideband Amplifier MMIC Application Note (P11976E)
Data Sheets of each NEC silicon medium-power high-frequency amplifier IC

★ **APPENDIX. S PARAMETER REFERENCE (T_A = +25°C)**

μPC1678G

V_{CC} = V_{out} = 5.0 V, I_{CC} = 49 mA

| FREQUENCY MHz | S ₁₁ | | S ₂₁ | | S ₁₂ | | S ₂₂ | | K |
|------------------|-----------------|--------|-----------------|--------|-----------------|-------|-----------------|--------|------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | |
| 100.0000 | 0.078 | -173.8 | 12.298 | -4.0 | 0.023 | -6.4 | 0.555 | -3.2 | 1.40 |
| 200.0000 | 0.106 | -179.1 | 12.891 | -8.6 | 0.020 | -7.3 | 0.593 | -8.7 | 1.43 |
| 300.0000 | 0.140 | 166.3 | 13.625 | -14.8 | 0.016 | -4.7 | 0.630 | -16.4 | 1.59 |
| 400.0000 | 0.176 | 150.2 | 14.453 | -22.6 | 0.014 | 6.4 | 0.657 | -25.3 | 1.53 |
| 500.0000 | 0.212 | 132.9 | 15.257 | -31.5 | 0.014 | 23.1 | 0.673 | -35.4 | 1.38 |
| 600.0000 | 0.246 | 115.5 | 15.663 | -40.8 | 0.017 | 35.1 | 0.676 | -45.1 | 1.05 |
| 700.0000 | 0.275 | 99.2 | 16.156 | -51.3 | 0.020 | 41.0 | 0.669 | -55.0 | 0.86 |
| 800.0000 | 0.304 | 83.2 | 16.291 | -60.7 | 0.024 | 42.4 | 0.654 | -64.0 | 0.71 |
| 900.0000 | 0.323 | 68.2 | 16.289 | -71.0 | 0.027 | 41.8 | 0.627 | -72.4 | 0.65 |
| 1000.0000 | 0.403 | 53.3 | 17.096 | -80.2 | 0.030 | 47.1 | 0.660 | -76.7 | 0.45 |
| 1100.0000 | 0.408 | 37.1 | 16.669 | -90.7 | 0.036 | 43.0 | 0.646 | -85.4 | 0.44 |
| 1200.0000 | 0.421 | 22.2 | 16.591 | -100.7 | 0.036 | 41.3 | 0.639 | -93.7 | 0.44 |
| 1300.0000 | 0.436 | 6.4 | 16.370 | -111.2 | 0.041 | 36.5 | 0.660 | -101.7 | 0.41 |
| 1400.0000 | 0.449 | -8.4 | 16.056 | -121.8 | 0.042 | 33.9 | 0.670 | -109.8 | 0.40 |
| 1500.0000 | 0.463 | -25.0 | 15.852 | -131.6 | 0.045 | 28.3 | 0.690 | -118.7 | 0.40 |
| 1600.0000 | 0.474 | -41.5 | 15.332 | -142.8 | 0.049 | 25.9 | 0.717 | -127.0 | 0.41 |
| 1700.0000 | 0.472 | -58.3 | 14.865 | -154.2 | 0.048 | 22.1 | 0.734 | -136.6 | 0.45 |
| 1800.0000 | 0.468 | -76.1 | 14.169 | -164.9 | 0.049 | 15.7 | 0.763 | -146.9 | 0.48 |
| 1900.0000 | 0.457 | -92.5 | 13.229 | -176.8 | 0.048 | 13.7 | 0.783 | -156.8 | 0.54 |
| 2000.0000 | 0.447 | -109.6 | 12.144 | 172.6 | 0.048 | 8.1 | 0.806 | -167.8 | 0.58 |
| 2100.0000 | 0.447 | -126.4 | 10.947 | 162.7 | 0.049 | 4.0 | 0.830 | -178.6 | 0.64 |
| 2200.0000 | 0.434 | -142.6 | 9.853 | 153.4 | 0.047 | -2.0 | 0.843 | 170.2 | 0.69 |
| 2300.0000 | 0.429 | -158.5 | 8.796 | 146.3 | 0.044 | -6.7 | 0.842 | 159.4 | 0.77 |
| 2400.0000 | 0.427 | -173.0 | 7.894 | 139.7 | 0.040 | -9.9 | 0.843 | 148.2 | 0.86 |
| 2500.0000 | 0.422 | 172.5 | 7.048 | 133.3 | 0.036 | -12.5 | 0.825 | 137.4 | 0.99 |
| 2600.0000 | 0.419 | 158.3 | 6.363 | 128.8 | 0.027 | -17.6 | 0.785 | 125.7 | 1.34 |
| 2700.0000 | 0.416 | 145.6 | 5.881 | 125.1 | 0.023 | -17.2 | 0.744 | 117.2 | 1.71 |
| 2800.0000 | 0.400 | 136.1 | 5.387 | 121.3 | 0.018 | 4.5 | 0.701 | 109.7 | 2.34 |
| 2900.0000 | 0.402 | 126.2 | 5.223 | 116.2 | 0.018 | 11.0 | 0.681 | 103.0 | 2.53 |
| 3000.0000 | 0.406 | 118.1 | 5.030 | 113.5 | 0.020 | 28.2 | 0.645 | 96.5 | 2.45 |
| 3100.0000 | 0.397 | 109.8 | 4.675 | 107.3 | 0.022 | 35.3 | 0.616 | 90.7 | 2.47 |

μPC1678GV

V_{CC} = V_{out} = 5.0 V I_{CC} = 44 mA

| FREQUENCY MHz | S ₁₁ | | S ₂₁ | | S ₁₂ | | S ₂₂ | | K |
|------------------|-----------------|--------|-----------------|--------|-----------------|------|-----------------|--------|------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | |
| 100.0000 | 0.085 | -163.8 | 12.206 | -2.6 | 0.024 | -5.0 | 0.558 | -2.3 | 1.36 |
| 200.0000 | 0.118 | -163.3 | 12.842 | -6.0 | 0.020 | -8.1 | 0.594 | -6.6 | 1.43 |
| 300.0000 | 0.158 | -170.9 | 13.766 | -10.9 | 0.015 | -2.4 | 0.637 | -13.6 | 1.61 |
| 400.0000 | 0.184 | 176.0 | 14.731 | -17.7 | 0.016 | 11.1 | 0.667 | -21.3 | 1.39 |
| 500.0000 | 0.214 | 164.8 | 15.815 | -25.1 | 0.014 | 26.3 | 0.692 | -30.8 | 1.34 |
| 600.0000 | 0.243 | 152.4 | 16.598 | -33.9 | 0.015 | 44.5 | 0.703 | -40.2 | 1.13 |
| 700.0000 | 0.266 | 138.9 | 17.541 | -43.2 | 0.019 | 51.4 | 0.701 | -49.0 | 0.85 |
| 800.0000 | 0.293 | 125.2 | 18.057 | -52.3 | 0.024 | 56.5 | 0.689 | -57.0 | 0.69 |
| 900.0000 | 0.312 | 113.7 | 18.475 | -62.2 | 0.027 | 58.1 | 0.670 | -65.7 | 0.62 |
| 1000.0000 | 0.379 | 95.6 | 20.083 | -71.9 | 0.031 | 61.7 | 0.686 | -68.6 | 0.47 |
| 1100.0000 | 0.381 | 82.2 | 20.090 | -82.8 | 0.035 | 58.6 | 0.685 | -77.5 | 0.45 |
| 1200.0000 | 0.401 | 66.5 | 20.620 | -94.0 | 0.038 | 56.0 | 0.688 | -84.9 | 0.42 |
| 1300.0000 | 0.422 | 51.1 | 20.669 | -106.8 | 0.042 | 55.1 | 0.702 | -92.8 | 0.38 |
| 1400.0000 | 0.446 | 34.0 | 20.473 | -119.6 | 0.046 | 52.6 | 0.713 | -100.5 | 0.36 |
| 1500.0000 | 0.455 | 16.6 | 19.765 | -132.5 | 0.048 | 48.4 | 0.717 | -110.4 | 0.35 |
| 1600.0000 | 0.465 | -0.5 | 18.759 | -145.7 | 0.050 | 47.0 | 0.711 | -119.0 | 0.36 |
| 1700.0000 | 0.444 | -16.7 | 17.137 | -157.7 | 0.049 | 44.9 | 0.684 | -128.7 | 0.42 |
| 1800.0000 | 0.431 | -33.5 | 15.512 | -168.9 | 0.050 | 42.9 | 0.659 | -137.4 | 0.48 |
| 1900.0000 | 0.397 | -47.2 | 13.846 | -178.7 | 0.048 | 43.5 | 0.616 | -145.1 | 0.59 |
| 2000.0000 | 0.378 | -59.2 | 12.398 | 172.4 | 0.048 | 45.8 | 0.574 | -151.4 | 0.70 |
| 2100.0000 | 0.357 | -70.5 | 11.060 | 164.9 | 0.048 | 45.3 | 0.540 | -157.0 | 0.81 |
| 2200.0000 | 0.343 | -80.7 | 9.918 | 157.8 | 0.048 | 47.4 | 0.510 | -161.5 | 0.91 |
| 2300.0000 | 0.339 | -89.4 | 8.927 | 151.7 | 0.049 | 47.4 | 0.489 | -164.8 | 1.00 |
| 2400.0000 | 0.335 | -98.9 | 8.107 | 146.2 | 0.051 | 46.1 | 0.483 | -167.6 | 1.06 |
| 2500.0000 | 0.338 | -107.2 | 7.388 | 140.6 | 0.050 | 46.2 | 0.475 | -171.7 | 1.15 |
| 2600.0000 | 0.358 | -115.5 | 6.772 | 135.4 | 0.055 | 46.8 | 0.475 | -173.8 | 1.16 |
| 2700.0000 | 0.359 | -125.3 | 6.267 | 131.0 | 0.051 | 48.1 | 0.463 | -178.1 | 1.32 |
| 2800.0000 | 0.368 | -133.9 | 5.807 | 125.4 | 0.054 | 49.4 | 0.482 | 179.5 | 1.33 |
| 2900.0000 | 0.372 | -143.4 | 5.450 | 121.3 | 0.051 | 49.6 | 0.489 | 173.4 | 1.45 |
| 3000.0000 | 0.375 | -152.7 | 5.018 | 116.0 | 0.050 | 53.6 | 0.475 | 166.3 | 1.62 |
| 3100.0000 | 0.372 | -161.4 | 4.684 | 110.5 | 0.053 | 57.5 | 0.453 | 161.4 | 1.66 |

μPC1679G

V_{CC} = V_{out} = 5.0 V, I_{CC} = 40 mA

| FREQUENCY MHz | S ₁₁ | | S ₂₁ | | S ₁₂ | | S ₂₂ | | K |
|------------------|-----------------|--------|-----------------|--------|-----------------|-------|-----------------|--------|------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | |
| 100.0000 | 0.133 | 177.2 | 11.167 | -4.7 | 0.024 | -4.9 | 0.589 | -3.9 | 1.40 |
| 200.0000 | 0.154 | 171.2 | 11.585 | -9.8 | 0.022 | -10.3 | 0.620 | -9.7 | 1.41 |
| 300.0000 | 0.184 | 159.6 | 12.121 | -16.1 | 0.018 | -3.0 | 0.648 | -17.3 | 1.51 |
| 400.0000 | 0.217 | 147.3 | 12.690 | -23.9 | 0.015 | 4.9 | 0.669 | -25.9 | 1.63 |
| 500.0000 | 0.247 | 132.4 | 13.210 | -32.2 | 0.015 | 20.0 | 0.681 | -35.1 | 1.42 |
| 600.0000 | 0.279 | 117.7 | 13.509 | -40.9 | 0.017 | 35.5 | 0.680 | -44.3 | 1.15 |
| 700.0000 | 0.307 | 102.8 | 13.902 | -51.0 | 0.021 | 42.6 | 0.674 | -53.6 | 0.88 |
| 800.0000 | 0.333 | 88.3 | 13.966 | -59.8 | 0.026 | 44.8 | 0.659 | -62.0 | 0.71 |
| 900.0000 | 0.342 | 76.4 | 13.895 | -69.5 | 0.027 | 42.5 | 0.628 | -70.6 | 0.72 |
| 1000.0000 | 0.412 | 60.4 | 14.401 | -78.5 | 0.033 | 52.0 | 0.646 | -75.4 | 0.48 |
| 1100.0000 | 0.419 | 46.1 | 14.244 | -87.9 | 0.037 | 46.1 | 0.636 | -83.6 | 0.46 |
| 1200.0000 | 0.434 | 31.7 | 14.249 | -97.3 | 0.041 | 42.5 | 0.635 | -90.1 | 0.43 |
| 1300.0000 | 0.450 | 18.1 | 14.096 | -106.9 | 0.043 | 41.8 | 0.640 | -97.8 | 0.41 |
| 1400.0000 | 0.461 | 3.2 | 13.945 | -116.9 | 0.047 | 35.8 | 0.655 | -105.0 | 0.39 |
| 1500.0000 | 0.481 | -12.2 | 13.888 | -125.9 | 0.051 | 34.1 | 0.664 | -112.7 | 0.39 |
| 1600.0000 | 0.486 | -27.2 | 13.645 | -136.5 | 0.053 | 30.5 | 0.691 | -120.6 | 0.39 |
| 1700.0000 | 0.487 | -43.7 | 13.460 | -147.3 | 0.053 | 27.3 | 0.707 | -129.2 | 0.42 |
| 1800.0000 | 0.486 | -61.2 | 13.043 | -157.9 | 0.056 | 21.6 | 0.742 | -138.5 | 0.44 |
| 1900.0000 | 0.479 | -78.4 | 12.509 | -170.0 | 0.058 | 17.7 | 0.771 | -147.7 | 0.48 |
| 2000.0000 | 0.469 | -95.6 | 11.678 | 179.0 | 0.057 | 13.6 | 0.794 | -158.3 | 0.53 |
| 2100.0000 | 0.467 | -113.5 | 10.720 | 168.4 | 0.057 | 9.9 | 0.819 | -169.0 | 0.59 |
| 2200.0000 | 0.454 | -130.9 | 9.763 | 158.2 | 0.056 | 3.5 | 0.840 | 179.9 | 0.63 |
| 2300.0000 | 0.450 | -148.4 | 8.754 | 150.0 | 0.054 | -1.4 | 0.846 | 168.7 | 0.71 |
| 2400.0000 | 0.449 | -165.0 | 7.849 | 142.4 | 0.050 | -6.4 | 0.852 | 157.1 | 0.78 |
| 2500.0000 | 0.443 | 179.3 | 7.022 | 135.4 | 0.045 | -9.9 | 0.829 | 145.9 | 0.90 |
| 2600.0000 | 0.441 | 163.8 | 6.289 | 130.2 | 0.037 | -13.3 | 0.790 | 133.6 | 1.11 |
| 2700.0000 | 0.430 | 149.9 | 5.800 | 126.1 | 0.029 | -11.1 | 0.733 | 124.7 | 1.49 |
| 2800.0000 | 0.426 | 139.0 | 5.277 | 121.8 | 0.027 | -1.1 | 0.697 | 117.2 | 1.75 |
| 2900.0000 | 0.429 | 128.2 | 5.108 | 116.7 | 0.027 | 6.1 | 0.672 | 110.0 | 1.84 |
| 3000.0000 | 0.432 | 118.6 | 4.894 | 114.0 | 0.025 | 15.9 | 0.635 | 103.2 | 2.02 |
| 3100.0000 | 0.419 | 110.7 | 4.541 | 107.4 | 0.028 | 31.2 | 0.598 | 98.0 | 2.05 |

μ PC2708T

V_{CC} = V_{out} = 5.0 V, I_{CC} = 24 mA

| FREQUENCY MHz | S ₁₁ | | S ₂₁ | | S ₁₂ | | S ₂₂ | | K |
|------------------|-----------------|-------|-----------------|--------|-----------------|------|-----------------|-------|------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | |
| 100.0000 | 0.040 | -3.6 | 5.149 | -3.2 | 0.073 | 0.2 | 0.132 | -11.5 | 1.49 |
| 200.0000 | 0.063 | 30.7 | 5.185 | -11.6 | 0.072 | -1.3 | 0.138 | -12.1 | 1.49 |
| 400.0000 | 0.112 | 47.5 | 5.195 | -25.4 | 0.070 | -4.2 | 0.140 | -17.1 | 1.51 |
| 600.0000 | 0.162 | 49.6 | 5.205 | -38.4 | 0.068 | -5.9 | 0.144 | -21.3 | 1.52 |
| 800.0000 | 0.211 | 45.7 | 5.215 | -52.3 | 0.066 | -6.6 | 0.150 | -26.1 | 1.52 |
| 1000.0000 | 0.265 | 40.0 | 5.225 | -64.4 | 0.064 | -5.3 | 0.157 | -31.0 | 1.52 |
| 1200.0000 | 0.319 | 32.0 | 5.233 | -79.1 | 0.063 | -5.3 | 0.165 | -36.1 | 1.48 |
| 1400.0000 | 0.363 | 23.8 | 5.206 | -94.2 | 0.061 | -5.5 | 0.171 | -43.7 | 1.48 |
| 1600.0000 | 0.404 | 15.3 | 5.149 | -109.5 | 0.060 | -4.9 | 0.176 | -50.2 | 1.45 |
| 1800.0000 | 0.435 | 6.9 | 4.974 | -125.6 | 0.060 | -3.7 | 0.168 | -57.3 | 1.46 |
| 2000.0000 | 0.460 | -3.4 | 4.696 | -141.1 | 0.060 | -0.4 | 0.156 | -62.5 | 1.49 |
| 2200.0000 | 0.456 | -12.6 | 4.454 | -156.6 | 0.060 | -0.4 | 0.141 | -60.3 | 1.58 |
| 2400.0000 | 0.442 | -19.9 | 4.102 | -172.5 | 0.060 | -1.8 | 0.123 | -61.6 | 1.74 |
| 2600.0000 | 0.422 | -26.5 | 3.702 | 172.7 | 0.060 | 0.2 | 0.100 | -61.5 | 1.95 |
| 2800.0000 | 0.396 | -31.5 | 3.307 | 158.9 | 0.059 | 0.1 | 0.077 | -61.6 | 2.26 |
| 3000.0000 | 0.365 | -35.3 | 2.907 | 146.5 | 0.059 | 2.0 | 0.051 | -56.7 | 2.62 |

μ PC2709T

V_{CC} = V_{out} = 5.0 V, I_{CC} = 30 mA

| FREQUENCY MHz | S ₁₁ | | S ₂₁ | | S ₁₂ | | S ₂₂ | | K |
|------------------|-----------------|-------|-----------------|--------|-----------------|------|-----------------|--------|------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | |
| 100.0000 | 0.258 | -4.1 | 12.706 | -3.7 | 0.022 | 7.5 | 0.234 | -4.6 | 1.66 |
| 200.0000 | 0.261 | -2.9 | 12.793 | -12.2 | 0.024 | 3.1 | 0.240 | -6.9 | 1.52 |
| 400.0000 | 0.271 | -4.6 | 13.023 | -27.0 | 0.025 | 6.5 | 0.260 | -13.5 | 1.32 |
| 600.0000 | 0.275 | -8.1 | 13.305 | -41.3 | 0.026 | 10.5 | 0.288 | -22.1 | 1.29 |
| 800.0000 | 0.278 | -12.7 | 13.595 | -57.4 | 0.026 | 11.0 | 0.312 | -33.5 | 1.27 |
| 1000.0000 | 0.279 | -15.2 | 13.816 | -72.3 | 0.027 | 15.6 | 0.324 | -43.4 | 1.20 |
| 1200.0000 | 0.276 | -20.7 | 13.992 | -90.3 | 0.027 | 17.7 | 0.332 | -59.0 | 1.19 |
| 1400.0000 | 0.263 | -25.6 | 13.750 | -109.3 | 0.027 | 19.2 | 0.326 | -75.1 | 1.22 |
| 1600.0000 | 0.246 | -28.6 | 13.195 | -128.3 | 0.028 | 20.6 | 0.302 | -90.6 | 1.27 |
| 1800.0000 | 0.237 | -31.7 | 12.254 | -147.5 | 0.030 | 27.9 | 0.254 | -106.8 | 1.33 |
| 2000.0000 | 0.222 | -33.6 | 10.976 | -166.1 | 0.031 | 33.2 | 0.198 | -120.8 | 1.47 |
| 2200.0000 | 0.194 | -33.1 | 9.664 | 177.5 | 0.033 | 35.8 | 0.143 | -132.5 | 1.61 |
| 2400.0000 | 0.176 | -26.8 | 8.392 | 162.0 | 0.034 | 38.5 | 0.089 | -144.4 | 1.81 |
| 2500.0000 | 0.173 | -23.2 | 7.771 | 154.8 | 0.035 | 39.2 | 0.065 | -150.6 | 1.90 |

μ PC2710T

$V_{CC} = V_{out} = 5.0 \text{ V}$, $I_{CC} = 21 \text{ mA}$

| FREQUENCY MHz | S ₁₁ | | S ₂₁ | | S ₁₂ | | S ₂₂ | | K |
|------------------|-----------------|-------|-----------------|--------|-----------------|------|-----------------|--------|------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | |
| 100.0000 | 0.322 | -0.3 | 37.668 | -5.9 | 0.013 | 17.1 | 0.200 | -11.7 | 1.06 |
| 200.0000 | 0.346 | 3.3 | 38.808 | -17.0 | 0.012 | 19.8 | 0.208 | -15.4 | 1.07 |
| 300.0000 | 0.383 | 2.1 | 40.192 | -28.0 | 0.009 | 22.5 | 0.231 | -23.5 | 1.21 |
| 400.0000 | 0.429 | -1.7 | 41.567 | -40.4 | 0.009 | 25.1 | 0.258 | -34.2 | 1.10 |
| 500.0000 | 0.465 | -9.4 | 42.130 | -54.1 | 0.012 | 27.8 | 0.273 | -47.2 | 0.86 |
| 600.0000 | 0.486 | -17.8 | 42.282 | -68.3 | 0.013 | 30.5 | 0.305 | -60.9 | 0.79 |
| 700.0000 | 0.487 | -27.2 | 41.075 | -83.2 | 0.013 | 33.1 | 0.319 | -77.8 | 0.82 |
| 800.0000 | 0.468 | -36.5 | 39.129 | -97.9 | 0.013 | 35.8 | 0.320 | -96.2 | 0.89 |
| 900.0000 | 0.423 | -44.5 | 35.399 | -111.7 | 0.013 | 38.5 | 0.297 | -115.4 | 1.04 |
| 1000.0000 | 0.392 | -50.3 | 32.933 | -123.4 | 0.014 | 41.2 | 0.260 | -128.2 | 1.10 |
| 1100.0000 | 0.349 | -56.6 | 30.025 | -135.5 | 0.014 | 43.9 | 0.240 | -142.2 | 1.22 |
| 1200.0000 | 0.301 | -61.0 | 26.823 | -146.8 | 0.015 | 46.6 | 0.216 | -156.3 | 1.31 |
| 1300.0000 | 0.257 | -63.2 | 23.836 | -156.8 | 0.016 | 49.2 | 0.192 | -169.7 | 1.40 |
| 1400.0000 | 0.217 | -63.5 | 21.128 | -165.9 | 0.016 | 51.6 | 0.173 | 176.0 | 1.56 |
| 1500.0000 | 0.184 | -59.9 | 18.841 | -174.2 | 0.017 | 54.5 | 0.155 | 162.3 | 1.65 |

μ PC2762T

V_{CC} = V_{out} = 3.0 V, I_{CC} = 29 mA

| FREQUENCY MHz | S11 | | S21 | | S12 | | S22 | | K |
|------------------|-------|-------|-------|--------|-------|--------|-------|--------|------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | |
| 100.0000 | 0.365 | -3.1 | 4.352 | -14.3 | 0.039 | -8.0 | 0.347 | -6.8 | 2.20 |
| 200.0000 | 0.367 | -5.3 | 4.333 | -29.8 | 0.038 | -18.5 | 0.345 | -11.9 | 2.27 |
| 300.0000 | 0.371 | -8.1 | 4.359 | -44.2 | 0.038 | -24.5 | 0.343 | -15.9 | 2.29 |
| 400.0000 | 0.361 | -9.9 | 4.327 | -59.4 | 0.038 | -32.7 | 0.334 | -22.6 | 2.35 |
| 500.0000 | 0.359 | -11.9 | 4.343 | -73.1 | 0.040 | -39.6 | 0.334 | -29.0 | 2.29 |
| 600.0000 | 0.351 | -14.0 | 4.445 | -87.8 | 0.039 | -50.4 | 0.359 | -34.6 | 2.28 |
| 700.0000 | 0.350 | -17.5 | 4.498 | -102.1 | 0.041 | -58.3 | 0.377 | -37.0 | 2.19 |
| 800.0000 | 0.357 | -20.0 | 4.630 | -116.6 | 0.042 | -67.5 | 0.369 | -39.8 | 2.11 |
| 900.0000 | 0.371 | -24.0 | 4.726 | -131.8 | 0.042 | -76.1 | 0.348 | -43.6 | 2.10 |
| 1000.0000 | 0.405 | -24.5 | 4.790 | -147.5 | 0.043 | -84.4 | 0.328 | -48.6 | 2.05 |
| 1100.0000 | 0.421 | -24.5 | 4.925 | -161.9 | 0.045 | -94.0 | 0.351 | -52.5 | 1.90 |
| 1200.0000 | 0.454 | -23.0 | 5.120 | -177.7 | 0.047 | -103.3 | 0.385 | -55.7 | 1.70 |
| 1300.0000 | 0.462 | -23.0 | 5.293 | 165.7 | 0.049 | -113.6 | 0.397 | -57.9 | 1.54 |
| 1400.0000 | 0.467 | -24.7 | 5.350 | 148.3 | 0.048 | -126.1 | 0.369 | -63.8 | 1.51 |
| 1500.0000 | 0.457 | -24.3 | 5.431 | 132.6 | 0.049 | -133.5 | 0.342 | -66.4 | 1.45 |
| 1600.0000 | 0.461 | -25.0 | 5.529 | 116.2 | 0.049 | -145.2 | 0.343 | -72.7 | 1.36 |
| 1700.0000 | 0.459 | -25.2 | 5.632 | 99.0 | 0.051 | -153.6 | 0.341 | -80.1 | 1.26 |
| 1800.0000 | 0.468 | -25.7 | 5.646 | 82.5 | 0.050 | -164.1 | 0.320 | -86.2 | 1.26 |
| 1900.0000 | 0.485 | -25.6 | 5.803 | 65.6 | 0.051 | -172.7 | 0.286 | -91.3 | 1.20 |
| 2000.0000 | 0.487 | -26.8 | 5.921 | 48.0 | 0.054 | 177.1 | 0.265 | -97.7 | 1.14 |
| 2100.0000 | 0.488 | -25.9 | 5.993 | 29.9 | 0.055 | 167.8 | 0.238 | -106.3 | 1.16 |
| 2200.0000 | 0.480 | -26.7 | 6.027 | 11.0 | 0.057 | 157.1 | 0.206 | -111.3 | 1.19 |
| 2300.0000 | 0.484 | -29.5 | 5.967 | -7.6 | 0.057 | 145.6 | 0.166 | -118.0 | 1.25 |
| 2400.0000 | 0.473 | -32.9 | 5.915 | -26.4 | 0.056 | 137.3 | 0.109 | -130.8 | 1.32 |
| 2500.0000 | 0.477 | -37.4 | 5.766 | -45.5 | 0.057 | 123.5 | 0.062 | -164.2 | 1.33 |
| 2600.0000 | 0.470 | -40.7 | 5.480 | -64.5 | 0.059 | 115.2 | 0.031 | 127.3 | 1.36 |
| 2700.0000 | 0.471 | -43.1 | 5.177 | -81.9 | 0.061 | 104.9 | 0.037 | 43.5 | 1.37 |
| 2800.0000 | 0.469 | -44.2 | 4.909 | -98.6 | 0.060 | 94.5 | 0.079 | 7.1 | 1.43 |
| 2900.0000 | 0.468 | -45.5 | 4.682 | -115.3 | 0.061 | 87.8 | 0.105 | -3.0 | 1.46 |
| 3000.0000 | 0.457 | -45.8 | 4.465 | -131.9 | 0.061 | 74.7 | 0.120 | -6.4 | 1.52 |
| 3100.0000 | 0.425 | -45.8 | 4.253 | -148.2 | 0.065 | 64.2 | 0.107 | -8.9 | 1.57 |

μPC2763T

V_{CC} = V_{out} = 3.0 V, I_{CC} = 26 mA

| FREQUENCY MHz | S11 | | S21 | | S12 | | S22 | | K |
|------------------|-------|--------|--------|--------|-------|------|-------|--------|------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | |
| 100.0000 | 0.209 | -0.0 | 10.116 | -6.0 | 0.023 | 2.4 | 0.391 | -6.2 | 1.76 |
| 200.0000 | 0.210 | -0.8 | 10.149 | -11.7 | 0.023 | 6.4 | 0.389 | -12.3 | 1.74 |
| 300.0000 | 0.216 | -1.8 | 10.186 | -17.7 | 0.023 | 9.6 | 0.388 | -18.2 | 1.75 |
| 400.0000 | 0.220 | -3.2 | 10.292 | -23.6 | 0.024 | 13.1 | 0.386 | -24.1 | 1.70 |
| 500.0000 | 0.226 | -5.1 | 10.366 | -29.5 | 0.025 | 17.1 | 0.388 | -30.0 | 1.60 |
| 600.0000 | 0.232 | -6.9 | 10.467 | -35.7 | 0.026 | 20.9 | 0.389 | -36.3 | 1.56 |
| 700.0000 | 0.239 | -9.6 | 10.635 | -42.2 | 0.027 | 23.0 | 0.396 | -42.3 | 1.46 |
| 800.0000 | 0.248 | -12.3 | 10.717 | -48.8 | 0.029 | 25.9 | 0.402 | -48.5 | 1.35 |
| 900.0000 | 0.255 | -15.9 | 10.900 | -55.7 | 0.028 | 27.3 | 0.404 | -55.4 | 1.36 |
| 1000.0000 | 0.262 | -19.8 | 11.004 | -63.2 | 0.030 | 27.7 | 0.408 | -62.5 | 1.28 |
| 1100.0000 | 0.266 | -24.0 | 11.168 | -70.1 | 0.032 | 28.5 | 0.412 | -70.0 | 1.20 |
| 1200.0000 | 0.273 | -28.2 | 11.173 | -77.7 | 0.033 | 29.7 | 0.416 | -77.3 | 1.17 |
| 1300.0000 | 0.276 | -33.7 | 11.318 | -86.3 | 0.033 | 27.8 | 0.421 | -85.3 | 1.15 |
| 1400.0000 | 0.280 | -38.8 | 11.221 | -94.0 | 0.034 | 29.2 | 0.423 | -93.1 | 1.14 |
| 1500.0000 | 0.280 | -44.8 | 11.134 | -103.0 | 0.034 | 28.9 | 0.425 | -101.7 | 1.14 |
| 1600.0000 | 0.280 | -51.2 | 10.878 | -111.4 | 0.034 | 29.7 | 0.420 | -110.2 | 1.18 |
| 1700.0000 | 0.276 | -57.7 | 10.512 | -119.5 | 0.035 | 30.4 | 0.418 | -118.5 | 1.21 |
| 1800.0000 | 0.269 | -64.7 | 10.207 | -127.4 | 0.035 | 32.1 | 0.415 | -126.7 | 1.27 |
| 1900.0000 | 0.260 | -71.3 | 9.747 | -135.2 | 0.035 | 32.7 | 0.413 | -135.6 | 1.33 |
| 2000.0000 | 0.251 | -78.4 | 9.378 | -142.6 | 0.035 | 33.4 | 0.408 | -144.1 | 1.39 |
| 2100.0000 | 0.238 | -85.6 | 8.962 | -149.6 | 0.036 | 35.1 | 0.400 | -153.1 | 1.45 |
| 2200.0000 | 0.224 | -92.5 | 8.551 | -157.0 | 0.035 | 35.9 | 0.391 | -162.0 | 1.56 |
| 2300.0000 | 0.210 | -99.7 | 8.135 | -163.5 | 0.036 | 38.2 | 0.382 | -171.1 | 1.60 |
| 2400.0000 | 0.196 | -107.4 | 7.739 | -170.2 | 0.035 | 40.2 | 0.373 | -179.6 | 1.72 |
| 2500.0000 | 0.182 | -114.5 | 7.349 | -176.3 | 0.037 | 41.5 | 0.357 | 171.8 | 1.76 |
| 2600.0000 | 0.167 | -121.4 | 6.980 | 177.4 | 0.038 | 44.0 | 0.343 | 163.1 | 1.81 |
| 2700.0000 | 0.152 | -127.4 | 6.678 | 171.2 | 0.039 | 45.4 | 0.322 | 154.9 | 1.85 |
| 2800.0000 | 0.140 | -131.9 | 6.309 | 165.3 | 0.039 | 46.7 | 0.298 | 148.1 | 1.97 |
| 2900.0000 | 0.134 | -140.3 | 5.918 | 159.2 | 0.039 | 47.6 | 0.284 | 142.4 | 2.08 |
| 3000.0000 | 0.120 | -148.7 | 5.675 | 153.9 | 0.041 | 48.8 | 0.271 | 137.1 | 2.10 |

μ PC2771T

$V_{CC} = V_{out} = 3.0\text{ V}$, $I_{CC} = 36\text{ mA}$

| FREQUENCY MHz | S11 | | S21 | | S12 | | S22 | |
|------------------|-------|--------|--------|--------|-------|------|-------|--------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. |
| 100.0000 | 0.148 | 109.2 | 10.732 | -11.3 | 0.031 | 3.7 | 0.334 | -6.9 |
| 200.0000 | 0.098 | 110.8 | 10.644 | -15.4 | 0.025 | 2.2 | 0.320 | -11.9 |
| 300.0000 | 0.082 | 107.6 | 10.739 | -22.0 | 0.025 | 8.7 | 0.317 | -17.0 |
| 400.0000 | 0.083 | 86.8 | 10.898 | -28.9 | 0.025 | 0.7 | 0.323 | -23.2 |
| 500.0000 | 0.088 | 68.9 | 11.011 | -35.7 | 0.025 | 22.9 | 0.326 | -31.2 |
| 600.0000 | 0.095 | 53.0 | 11.119 | -43.5 | 0.022 | 17.1 | 0.337 | -38.8 |
| 700.0000 | 0.114 | 38.9 | 11.246 | -51.5 | 0.030 | 22.9 | 0.352 | -46.0 |
| 800.0000 | 0.129 | 33.4 | 11.330 | -59.1 | 0.034 | 10.3 | 0.355 | -53.4 |
| 900.0000 | 0.163 | 23.1 | 11.526 | -67.4 | 0.033 | 29.2 | 0.360 | -64.2 |
| 1000.0000 | 0.178 | 16.2 | 11.500 | -76.8 | 0.030 | 17.6 | 0.367 | -71.1 |
| 1100.0000 | 0.192 | 11.3 | 11.537 | -85.9 | 0.031 | 24.7 | 0.376 | -79.8 |
| 1200.0000 | 0.207 | 5.5 | 11.403 | -94.3 | 0.040 | 8.8 | 0.386 | -89.0 |
| 1300.0000 | 0.211 | 1.9 | 11.176 | -104.0 | 0.033 | 12.9 | 0.394 | -97.8 |
| 1400.0000 | 0.217 | -5.4 | 10.936 | -113.4 | 0.031 | 21.2 | 0.395 | -107.2 |
| 1500.0000 | 0.203 | -11.0 | 10.587 | -122.7 | 0.037 | 23.0 | 0.403 | -115.9 |
| 1600.0000 | 0.196 | -18.5 | 10.162 | -132.0 | 0.033 | 16.6 | 0.407 | -125.1 |
| 1700.0000 | 0.189 | -24.0 | 9.784 | -140.5 | 0.041 | 14.9 | 0.410 | -132.4 |
| 1800.0000 | 0.170 | -31.2 | 9.339 | -148.9 | 0.039 | 10.2 | 0.404 | -139.3 |
| 1900.0000 | 0.144 | -38.4 | 8.836 | -156.9 | 0.035 | 15.0 | 0.401 | -147.0 |
| 2000.0000 | 0.137 | -47.5 | 8.418 | -164.5 | 0.036 | 20.7 | 0.392 | -156.0 |
| 2100.0000 | 0.109 | -56.6 | 7.877 | -172.7 | 0.034 | 30.0 | 0.384 | -162.9 |
| 2200.0000 | 0.088 | -65.7 | 7.604 | -179.8 | 0.038 | 21.3 | 0.384 | -172.5 |
| 2300.0000 | 0.079 | -70.9 | 7.214 | 172.4 | 0.045 | 33.4 | 0.377 | -179.5 |
| 2400.0000 | 0.062 | -77.9 | 6.743 | 164.6 | 0.039 | 19.6 | 0.359 | 170.2 |
| 2500.0000 | 0.047 | -94.9 | 6.420 | 157.7 | 0.041 | 23.9 | 0.351 | 162.3 |
| 2600.0000 | 0.030 | -102.0 | 6.044 | 151.1 | 0.046 | 28.6 | 0.331 | 153.5 |
| 2700.0000 | 0.018 | -114.9 | 5.654 | 144.2 | 0.043 | 40.0 | 0.318 | 144.4 |
| 2800.0000 | 0.015 | 162.0 | 5.315 | 137.4 | 0.046 | 25.1 | 0.302 | 138.0 |
| 2900.0000 | 0.022 | 111.1 | 4.959 | 130.9 | 0.043 | 34.1 | 0.295 | 131.1 |
| 3000.0000 | 0.037 | 87.9 | 4.669 | 124.4 | 0.048 | 35.2 | 0.262 | 125.2 |

μPC2776T

V_{CC} = V_{out} = 5.0 V, I_{CC} = 28 mA

| FREQUENCY MHz | S11 | | S21 | | S12 | | S22 | | K |
|------------------|-------|--------|--------|--------|-------|--------|-------|--------|------|
| | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | MAG. | ANG. | |
| 100.000 | 0.218 | -1.2 | 14.389 | -16.1 | 0.030 | -10.4 | 0.048 | -157.8 | 1.33 |
| 200.000 | 0.223 | 1.7 | 14.257 | -33.9 | 0.029 | -24.1 | 0.045 | -148.4 | 1.34 |
| 300.000 | 0.241 | -0.5 | 14.347 | -50.2 | 0.029 | -29.3 | 0.046 | -134.9 | 1.33 |
| 400.000 | 0.245 | 1.9 | 14.369 | -67.4 | 0.029 | -40.4 | 0.069 | -131.1 | 1.32 |
| 500.000 | 0.259 | 2.0 | 14.491 | -83.4 | 0.029 | -49.3 | 0.094 | -125.0 | 1.29 |
| 600.000 | 0.270 | 2.5 | 14.879 | -101.0 | 0.030 | -58.0 | 0.119 | -116.5 | 1.23 |
| 700.000 | 0.291 | -3.1 | 14.948 | -117.9 | 0.030 | -69.5 | 0.125 | -113.1 | 1.22 |
| 800.000 | 0.322 | -7.8 | 15.268 | -135.5 | 0.029 | -78.6 | 0.131 | -127.6 | 1.19 |
| 900.000 | 0.350 | -14.3 | 15.461 | -153.1 | 0.029 | -91.9 | 0.139 | -144.5 | 1.18 |
| 1000.000 | 0.408 | -18.0 | 15.585 | -171.7 | 0.029 | -103.2 | 0.139 | -153.9 | 1.14 |
| 1100.000 | 0.451 | -19.0 | 15.913 | 170.9 | 0.028 | -112.4 | 0.141 | -144.1 | 1.14 |
| 1200.000 | 0.521 | -20.7 | 16.312 | 151.8 | 0.029 | -121.3 | 0.145 | -137.8 | 1.07 |
| 1300.000 | 0.557 | -24.3 | 16.461 | 132.3 | 0.031 | -135.5 | 0.146 | -147.0 | 1.00 |
| 1400.000 | 0.571 | -29.2 | 16.163 | 112.5 | 0.027 | -144.7 | 0.158 | -165.7 | 1.05 |
| 1500.000 | 0.573 | -32.7 | 16.013 | 93.7 | 0.027 | -155.5 | 0.183 | 176.6 | 1.06 |
| 1600.000 | 0.587 | -37.7 | 15.734 | 74.7 | 0.025 | -166.4 | 0.197 | 167.1 | 1.07 |
| 1700.000 | 0.588 | -42.2 | 15.347 | 55.4 | 0.023 | 179.0 | 0.196 | 158.8 | 1.11 |
| 1800.000 | 0.604 | -46.9 | 14.647 | 36.7 | 0.021 | 171.7 | 0.198 | 149.6 | 1.17 |
| 1900.000 | 0.609 | -50.8 | 14.289 | 19.0 | 0.019 | 162.9 | 0.232 | 140.7 | 1.21 |
| 2000.000 | 0.599 | -55.3 | 14.000 | 1.0 | 0.019 | 151.6 | 0.255 | 133.2 | 1.24 |
| 2100.000 | 0.584 | -58.6 | 13.601 | -18.1 | 0.016 | 142.7 | 0.280 | 125.8 | 1.41 |
| 2200.000 | 0.561 | -64.2 | 13.010 | -37.6 | 0.015 | 135.6 | 0.289 | 115.4 | 1.62 |
| 2300.000 | 0.544 | -71.1 | 12.289 | -55.5 | 0.011 | 127.9 | 0.304 | 109.6 | 2.21 |
| 2400.000 | 0.519 | -78.3 | 11.716 | -73.3 | 0.009 | 130.4 | 0.348 | 105.6 | 2.90 |
| 2500.000 | 0.519 | -84.6 | 11.183 | -91.2 | 0.008 | 130.4 | 0.387 | 102.5 | 3.27 |
| 2600.000 | 0.509 | -90.3 | 10.551 | -108.9 | 0.008 | 145.6 | 0.418 | 98.5 | 3.64 |
| 2700.000 | 0.504 | -97.0 | 10.005 | -126.1 | 0.012 | 163.5 | 0.430 | 94.2 | 2.44 |
| 2800.000 | 0.472 | -102.5 | 9.513 | -142.9 | 0.016 | 153.3 | 0.448 | 87.7 | 1.92 |
| 2900.000 | 0.434 | -107.5 | 9.070 | -160.4 | 0.019 | 141.0 | 0.459 | 83.6 | 1.79 |
| 3000.000 | 0.381 | -112.1 | 8.605 | -177.3 | 0.020 | 129.3 | 0.474 | 82.2 | 1.80 |
| 3100.000 | 0.330 | -117.8 | 8.196 | 165.9 | 0.021 | 122.9 | 0.478 | 82.1 | 1.96 |

[MEMO]

Facsimile Message

Although NEC has taken all possible steps to ensure that the documentation supplied to our customers is complete, bug free and up-to-date, we readily accept that errors may occur. Despite all the care and precautions we've taken, you may encounter problems in the documentation. Please complete this form whenever you'd like to report errors or suggest improvements to us.

From:

Name

Company

Tel.

FAX

Address

Thank you for your kind support.

North America

NEC Electronics Inc.
Corporate Communications Dept.
Fax: 1-800-729-9288
1-408-588-6130

Hong Kong, Philippines, Oceania

NEC Electronics Hong Kong Ltd.
Fax: +852-2886-9022/9044

Asian Nations except Philippines

NEC Electronics Singapore Pte. Ltd.
Fax: +65-250-3583

Europe

NEC Electronics (Europe) GmbH
Technical Documentation Dept.
Fax: +49-211-6503-274

Korea

NEC Electronics Hong Kong Ltd.
Seoul Branch
Fax: 02-528-4411

Japan

NEC Semiconductor Technical Hotline
Fax: 044-548-7900

South America

NEC do Brasil S.A.
Fax: +55-11-6465-6829

Taiwan

NEC Electronics Taiwan Ltd.
Fax: 02-2719-5951

I would like to report the following error/make the following suggestion:

Document title: _____

Document number: _____ Page number: _____

If possible, please fax the referenced page or drawing.

| Document Rating | Excellent | Good | Acceptable | Poor |
|--------------------|--------------------------|--------------------------|--------------------------|--------------------------|
| Clarity | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| Technical Accuracy | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |
| Organization | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> |