

RC310xx

This document describes the functional description, register organization, and byte addresses of the RC310xx. Detailed register definitions can be located by following the links in the document.

Contents

1. Functional Description	4
1.1 Power-Up, Configuration, and Serial Interfaces	4
1.2 Input Clocks	4
1.2.1 Crystal/Reference Input	4
1.2.2 Clock Inputs	4
1.2.3 Clock Input Monitors	5
1.3 APLL	5
1.3.1 APLL Lock Detector	5
1.4 DPLL	5
1.4.1 DPLL Loop Filter	5
1.5 DPLL Reference Selection	5
1.5.1 Manual Reference Selection	6
1.5.2 Automatic Reference Selection	6
1.5.3 Hitless Reference Switching	6
1.6 DPLL Operating Modes	6
1.6.1 Free-run State	6
1.6.2 Acquire State	7
1.6.3 Normal State	7
1.6.4 Holdover State	7
1.6.5 Hitless Switch State	7
1.6.6 Write-frequency State	7
1.6.7 Manual Mode	7
1.7 DPLL Lock Detector	7
1.8 Output Dividers	8
1.8.1 Integer Output Dividers	8
1.8.2 Fractional Output Dividers	8
1.9 Clock Outputs	9
1.9.1 Output Types	9
1.9.2 Output Banks	10
1.10 Output Enable Control	10
2. Serial Interfaces	11
2.1 1-Byte and 2-Byte Offset Mode	11
3. I2C Slave	12
3.1 1-Byte Offset Mode	12
3.2 2-Byte Offset Mode	12
4. SPI Slave	13
5. SMBus Slave	14
5.1 SMBus 1-Byte/2-Byte Offset Mode Programming Examples	14
6. Example of Programming Process	15

6.1	Getting Register Value from rbs Setting File	15
6.2	Example of I2C 1-Byte Offset Mode Programming	15
6.3	Example of I2C 2-Byte Offset Mode Programming	16
7.	Example of Changing Output Frequency	17
7.1	Output Frequency Calculation	17
7.2	Feedback Divider	18
7.3	Integer Output Divider	18
7.4	Fractional Output Dividers	19
8.	Example of Device Programming with the Driver	20
8.1	Example of Python Code	20
8.2	Example of DOS Batch File	20
9.	Register Organization	21
9.1	Overview	21
9.2	Register Block Offsets	21
9.3	Register Offsets	22
9.3.1	Global Address Map	22
9.3.2	SSI Address Map	22
9.3.3	Crystal Address Map	22
9.3.4	Clock Input Address Map	23
9.3.5	Clock Reference Address Map	23
9.3.6	LOS Monitor Address Map	23
9.3.7	Frequency Monitor Address Map	23
9.3.8	TDC APLL Address Map	24
9.3.9	APLL Address Map	24
9.3.10	DPLL Address Map	25
9.3.11	IOD Address Map	25
9.3.12	FOD Address Map	25
9.3.13	SSC Address Map	26
9.3.14	Output Bank Address Map	26
9.3.15	Clock Output Driver Address Map	26
9.3.16	GPI Address Map	26
9.3.17	GPIO Address Map	26
9.3.18	Interrupt Address Map	26
10.	Physical Register Addresses	27
10.1	Global Block	27
10.2	SSI Block	27
10.3	XO Block	28
10.4	CLKIN Block	28
10.5	REF Block	28
10.6	LOSMON Block	29
10.7	FREQMON Block	31
10.8	APLL Block	33
10.9	TDCAPLL Block	34
10.10	DPLL Block	34
10.11	IOD Block	36
10.12	FOD Block	37
10.13	OUT Block	38
10.14	BANK Block	39
10.15	GPI Block	39

10.16 GPIO Block	39
10.17 SSC Block	40
10.18 INT Block	40
11. Register Descriptions	41
11.1 Global Registers	41
11.2 SSI Registers	50
11.3 XO Register	53
11.4 CLKIN Register	54
11.5 REF Registers	55
11.6 LOSMON Registers	56
11.7 FREQMON Registers	58
11.8 TDC APLL Registers	60
11.9 APLL Registers	62
11.10 DPLL Registers	73
11.11 IOD Registers	81
11.12 FOD Registers	83
11.13 SSC Register	85
11.14 BANK Register	86
11.15 OUT Registers	87
11.16 GPI Registers	89
11.17 GPIO Registers	91
11.18 EEPROM Registers	93
11.19 INT Registers	97
12. Revision History	100

1. Functional Description

The RC310xx is a small-form factor, fully integrated, low-power, high-performance frequency synthesizer with jitter attenuation and network synchronization capabilities. The device is optimized to deliver excellent phase noise as required for driving Ethernet PHYs/switch, ASICs, or FPGAs. The RC310xx supports JEDEC JESD204B/C for converter synchronization, JEDEC JESD204B/C converter synchronization, IEEE1588, and SyncE for network-based synchronization.

The following sections provide an overview of the RC310xx.

1.1 Power-Up, Configuration, and Serial Interfaces

The RC310xx can be powered up and configured in three ways:

- From internal non-volatile memory using OTP user configurations (UserCfgs)
- From its slave serial interface
- From an external I2C EEPROM

The power-up sequence loads one of up to 27 *internal* UserCfgs from OTP. This configuration can be selected via external GPIO pins or by programming a field to select the default configuration to load. This is useful when external GPIO are not used to select the UserCfg at power-up. After the device is powered up, the slave serial interface can be used to select preprogrammed UserCfgs or load entirely new UserCfgs stored outside the device.

The RC310xx supports three slave serial interfaces: I2C, SPI, SMBUS, and one serial master interface (I2C).

These interfaces share the same pins so only one is available at a time. The I2C master interface that is used to load UserCfgs from an external I2C EEPROM is only active after loading an OTP UserCfg that indicates a further load from external I2C EEPROM. An external master (I2C, SPI, SMBUS) can be used to access internal registers. If the slave serial port is configured as SPI then loading from external EEPROM is not available.

1.2 Input Clocks

The RC310xx supports one crystal/reference input that is used as a reference to the analog PLL (APLL), and up to two differential or four single-ended clock inputs that is used as a reference to the digital PLL (DPLL) and support hitless reference switching.

1.2.1 Crystal/Reference Input

The crystal input supports crystal frequencies of 8MHz to 80MHz. It has programmable internal load capacitors to support crystals with CL = 6pF to 12pF. Internal crystal variants of RC310xx support a trim value in OTP that can be set during ATE to compensate for initial frequency offset of the internal crystal. The crystal input supports being overdriven with a clipped sine-wave TCXO with 0.8VPP signal.

If an external square wave clock is used to drive the XIN_REFIN pin, the default is amplitude limit is 1.2V. If [sel_ib_xo](#) is set to 0 and [xo_ib_cmos_sel](#) is set to 1 amplitude limitations are determined by the VDDX supply rail.

The crystal input can be overdriven with differential or single-ended inputs with proper external terminations. The supported frequency range is same as reference clock inputs:

- 1kHz to 650MHz in differential mode
- 1kHz to 200MHz in single-ended mode

An available LOS monitor detects the loss of signal on crystal input.

1.2.2 Clock Inputs

There are two differential clock inputs that support LVDS, HCSL, or single-ended CMOS logic levels without external terminations. LVPECL or CML clock inputs can be supported with external terminations and/or AC coupling. Internal terminations are available for both HCSL and LVDS logic levels. Additionally, HCSL input terminations support both 100ohm and 85ohm operating environments.

If the `cmos_sel` register bit is set to single-ended type, the differential inputs turn into two single-ended inputs. CLKIN0 drives `clkin0` internally, CLKIN0b drives `clkin1` internally. CLKIN1 drives `clkin2` internally, and CLKIN1b drives `clkin3` internally. If set to differential type, CLKIN0/CLKIN0b pair drives `clkin0`, while CLKIN1/CLKIN1b pair drives `clkin2`. Internal biasing is available for AC-coupled applications. The two clock inputs can be left floating when unused. An available LOS monitor detects the loss of signal on crystal input. The LOS status is stored in register bits and can also be steered to a GPIO pin. Frequency monitoring is also available on the clock inputs.

1.2.3 Clock Input Monitors

There are two types of reference clock monitors. The APLL input is monitored for Loss of Signal (LOS). While the DPLL clock inputs (CLKIN0, CLKIN0B, CLKIN1, CLKIN1B) each have LOS, activity, and frequency monitoring.

- The LOS monitor detects missing edges over a window of several reference clock periods. For the best accuracy, it is recommended to program the window to be equal to at least 8 times that of the measuring clock period.
- The frequency monitor can be configured to measure the reference over a nominal 5ms time window in order to achieve ~1ppm granularity.
- The frequency monitor can be configured to measure the reference over a nominal 0.4s time window in order to achieve ~12ppb granularity.

1.3 APLL

The APLL is fractional LC-VCO based PLL with an operating range from 9.5GHz to 10.7GHz. Any of the available input clocks can be selected to drive the APLL, and the input clock can be frequency doubled for increased performance. The APLL is temperature compensated for the utmost frequency stability. For synchronous, deterministic requirements, the APLL also supports ZDB mode where CLKIN0 is used for the feedback input.

1.3.1 APLL Lock Detector

The APLL lock detector indicates whether the APLL is locked to a functioning crystal or reference input by monitoring the phase errors. Lock status can be sent on to a GPIO pin and register `apll_lock_sts`. The falling edge of `apll_lock_sts` sets `apll_lol` event sticky bit. The `apll_lol` event also increments a 7-bit loss of lock counter that starts from power on. The counter values represents the total number of loss of lock since power on and can be read back from register `apll_lol_cnt`.

1.4 DPLL

To operate as a network synchronizer or jitter attenuator, the DPLL and APLL are nested and form a fractional-N DPLL architecture. The System APLL locks to an input clock from a crystal or a crystal oscillator and generates an output clock of approximately 10GHz. The APLL uses a fractional feedback divider with 26-b numerator and fixed 26-b denominator to generate its feedback clock. The fractional feedback divide ratio is dynamically controlled by the DPLL. The DPLL also uses the APLL's VCO clock to generate the fractional divided DPLL feedback clock. The DPLL fractional feedback divider, which is comprised of 48-b numerator and 48-b denominator, is static during normal operation. The DPLL can also be optionally disabled to operate the RC31008/31012A in synthesizer/DCO mode.

1.4.1 DPLL Loop Filter

The all-digital DPLL loop filter is a Proportional - Integral (PI) type filter with a bandwidth that is programmable from approximately 0.06Hz to 14kHz.

1.5 DPLL Reference Selection

The DPLL can lock to either of the two differential or the four single-ended input clocks. The reference selection can be either automatic or manual and when enabled, hitless switching results in negligible (< 100ps) output clock initial phase hit during reference switching or the DPLL exiting from holdover.

1.5.1 Manual Reference Selection

In manual mode, the selection is set either by register or by pin which is set by [dpll_ref_sel_mode](#)

- By register, the selection is set by [dpll_ref_sel](#)
- By pin, the selection is set by two GPI or GPIO pins assigned as DPLL_CLK_SEL[1:0] using [gpi_func](#) or [gpio_func](#).
 - 00 = clkIn0
 - 01 = clkIn1
 - 10 = clkIn2
 - 11 = clkIn3

1.5.2 Automatic Reference Selection

In automatic mode, the selection is based on clock quality statuses and priorities. The quality statuses are from clock monitors. The priorities can be re-programmed in register [ref_priority](#). If two clock inputs are programmed to the same priority, the one with lower index number takes precedence, for example, clkIn0 takes precedence over clkIn1.

The automatic reference selection can be either revertive or non-revertive, which is set in register [dpll_revertive_en](#). In revertive mode, the reference clock that is qualified and of the highest priority is always selected. If a reference clock of higher priority than the currently selected one becomes qualified, the DPLL will switch to that reference clock; if a reference clock of equal or lower priority than the currently selected one becomes qualified, the DPLL will keep the current reference clock. In non-revertive mode, if there is a higher priority reference clock coming back (from disqualified to qualified), the current selected reference clock remains selected unless it gets disqualified.

1.5.3 Hitless Reference Switching

If hitless switching is enabled by setting register [dpll_hitless_en](#) to 1, the output clock initial phase hit will be minimized (< 100ps) during reference switching or the DPLL exiting from holdover, while the input clock and output clock may no longer be aligned.

If hitless switching is disabled, the output clock phase change slope is determined by DPLL loop characteristics and phase slope limit settings in register [phase_slope_limit](#).

Minimal initial phase hit of < 100ps can only be met during reference switching when the reference clocks are of same fractional frequency offset. If they are of different fractional frequency offset (up to 200ppm), the output clock phase will track to the new reference clock. Although the initial phase hit can be minimized by setting [dpll_hitless_en](#) to 1, the total amount of output phase change and the change slope depends on the fractional frequency offset difference, the loop characteristics, and phase slope limit settings.

When [dpll_hitless_en](#) is set to 1, the [phase_offset](#) register is ignored by the DPLL and only the internally stored hitless offset affects the input-output phase offset. When [dpll_hitless_en](#) is set to 0, the hitless phase offset stored in the hitless handler is reset and the [phase_offset](#) register is used again. Hitless switching minimizes the output phase movement at the expense of a defined input – output phase offset while the use of the phase offset register enables a defined input-output phase offset at the expense of output phase movement during reference switching.

1.6 DPLL Operating Modes

The DPLL can operate in six different states: Free-run, Acquire, Normal, Holdover, Hitless-switch, and Write-frequency. The state transitions can be either manual or automatic, and are set in register [dpll_mode](#). In manual mode, the states of Free-run, Holdover, and Write-frequency can be forced in the register [dpll_mode](#).

1.6.1 Free-run State

During power-on reset or VCO calibration or in synthesizer mode, the DPLL is in the Free-run state. In this state, no reference clock is used and the output clocks are tracking the APLL reference clock.

1.6.2 Acquire State

When there is at least one qualified reference, the DPLL will track the selected qualified reference at the acquisition bandwidth and damping factor settings. If the reference clock is disqualified and no other qualified reference clock is available, the DPLL transitions to either the Free-run state or the Holdover state depending on the value of [los_to_freerun](#). When lock-detector detects a lock, DPLL transitions to the normal state.

1.6.3 Normal State

In the Normal state, the DPLL is tracking the selected reference clock with the normal locking bandwidth and damping factor settings.

If the selected reference clock is disqualified, the state machine goes to either the Holdover or the Free-run state according to [los_to_freerun](#). At a reference switch, the state machine goes via the Holdover state to the Hitless-switch state or the Acquire state.

1.6.4 Holdover State

In the Holdover state, the DPLL output frequency will be held at the instantaneous value or a value that is low pass filtered and/or restored from the holdover history registers. This can be selected through the CSR register [HOLDOVER_CNFG - Holdover Configuration](#). The initial holdover accuracy is less than 50ppb.

1.6.5 Hitless Switch State

At a Hitless reference switch or a hitless transition from the holdover state, the DPLL's TDC will measure the phase offset between the (newly) selected reference clock and the feedback clock, both of which are averaged. This offset is stored in an internal phase offset register. As a result, the output clocks will experience a minimal phase transient due to the reference switch or coming out of holdover. After the hitless switch procedure is finished, the state machine transitions to the Acquire state unless the reference clock fails.

1.6.6 Write-frequency State

In the Write-frequency mode the DPLL is not tracking any reference clock. The DPLL output frequency offset is directly controlled by the [write_freq](#) value.

1.6.7 Manual Mode

The DPLL operation can be forced to the Free-run, Holdover, and Write-frequency states by configuring register [dpll_mode](#).

1.7 DPLL Lock Detector

The DPLL lock detector declares lock when the phase from the phase detector remains within a programmable range that is set in register [dpll_lock_thresh](#) for a programmable time interval that is set in register [dpll_lock_timer](#). This indicates that the DPLL is locked to the reference clock input. Once the phase output from the phase detector has been below the lock threshold for half of the programmed lock interval, the internal lock signal is asserted and the normal loop filter bandwidth and damping is applied to the DPLL's loop filter instead of the acquire filter settings. The lock signal can be indicated on the GPIO pins and [dpll_lock_sts](#) register is asserted when the phase from the phase detector has been within the lock threshold for the full lock interval. Lock status can be sent on to pin and register [dpll_lock_sts](#).

If the phase output from the phase detector exceeds the lock threshold for more than half the lock interval time, the lock status bit is de-asserted. The loss of lock event will increment a 7-bit loss of lock counter that starts from power on. The counter values represents the total number of loss of lock since power on and can be read back from register [dpll_lol_cnt](#).

1.8 Output Dividers

The RC310xx provides four integer and three fractional output dividers.

1.8.1 Integer Output Dividers

All four IODs are identical and use a 25-bit divider to provide output frequencies from 1kHz to 650MHz derived from the VCO clock. Changing IOD values results in an immediate change to the new frequency. Glitch-less squelch and release of the IOD clock is supported with an [iod_squelch](#) bit. When enabled, this mimics a gapped clock behavior when an IOD frequency is changed.

1.8.1.1 SYSREF Generation

The RC310xx supports pulse mode SYSREF generation within each IOD. The number of pulses is programmable and SYSREF can be triggered using register programming to register bit [sysref_trig](#), or an assigned GPI or GPIO pin that can act as SYSREF_IN.

Any output that selects a SYSREF IOD must also have [out_oe_mode](#) set to 1 (asynchronous OE mode) since the IOD clock is not free running. Partial SYSREF (generating SYSREF pulses on a subset of the outputs configured for SYSREF) can be accomplished by setting [out_dis](#) to 1 on those outputs that should not send pulses. To guarantee glitchless operation, the [out_dis](#) value must not change while driving SYSREF pulse(s). The phase of each IOD in the group can be independently adjusted if skew is intended.

1.8.2 Fractional Output Dividers

There are three fractional output dividers (FOD). Each FOD can divide down the VCO clock to provide frequencies of 1kHz to 650MHz. Each FOD is implemented in two stages. The first stage is an 8-bit fractional divider with Digital Control Delay (DCD) correction followed by a divide-by-2. The DCD FOD allows a divide down of the VCO clock from 30MHz to 657MHz. The FOD's second stage divider is a 17-bit integer divider with minimum divide ratio of 4. This allows output frequencies lower than 30MHz. For output frequencies above 30MHz, this second-stage divider may be bypassed.

1.8.2.1 Spread-Spectrum Clocking (SSC)

FOD0 and FOD1 support spread-spectrum clocking.

If spreading is enabled by setting [ssc_en](#) to 1, the spread-spectrum engine generates a triangular frequency modulation on to FOD's divider ratio. The modulation amplitude is programmable in [ssc_ampl](#) register fields. The modulation can be programmed to either down spread or center spread in register [ssc_mode](#). The peak-to-peak amplitude is two times of [ssc_ampl](#) for center spreading, and one [ssc_ampl](#) for down spreading. The supported modulation frequency is from 30kHz to 63kHz. It can be set by programming register [ssc_step](#) based on the equations provided in the register description.

When turning off spread, it stops when the current spreading cycle's modulation returns to zero.

If FOD0 and FOD1 SSC are programmed to the same modulation frequency, the register bit [ssc_share](#) can be set to 1 to ensure that SSC for FOD0 and FOD1 are in phase. The modulation amplitude and mode (down or center spread) can be set differently. The spread engine of FOD0 will act as the master for the spread engine of FOD1 with respect to synchronization. The zero crossing of the spread triangles is where the synchronization occurs. If the center spread is used on FOD0, then the zero crossing of the upwards frequency ramp of the triangle is the synchronization point. When [ssc_share](#) is set to 1, then FOD1 [ssc_en](#) must be set to 1 before FOD0 [ssc_en](#) is set to 1 since FOD1 SSC will start when FOD0 [ssc_en](#) is set to 1. This restriction does not apply when loading the device configuration from OTP/EEPROM on startup, but does apply if dynamically changing these settings later through a dynamic configuration load from the OTP/EEPROM, or by writing registers from the serial interface.

The minimum output frequency that can be spread is 33MHz. A spreading output clock meets the PCIe Gen1 to Gen6 standard at 100MHz.

1.8.2.2 Sync and Phase Adjustment

Each FOD can adjust its output clock phase with a step size of 1/4 VCO period up to about ±20ns. The amount of phase adjustment is programmed in register `fod_phase`. The adjustment can be of either positive or negative directions. The phase adjustment can be applied immediately if the `fod_ph_adj_now` bit is set to 1, and/or it will be applied after each time the divider is synchronized if `fod_ph_adj_post_sync` is set to 1.

IOD phase adjustment is same as, or maybe mimics, FOD phase adjustment but with a step size of one VCO period. The amount of phase adjustment is programmed in register `iod_phase`. The phase adjustment can be applied immediately if the `iod_ph_adj_now` bit is set to 1, and/or it will be applied after each time the divider is synchronized if `iod_ph_adj_post_sync` is set to 1.

There are two sync groups, group0 and group1. An FOD or IOD can be assigned to either group or none by `fod_sync_group` or `iod_sync_group`, respectively. The DPLL feedback divider can be assigned to either group or none by `dpll_sync_group`. The dividers in the same group can be re-synchronized together after any one of them is re-programmed by writing 1 to `od_grp0_sync` or `od_grp1_sync`. To disable all clock outputs sourced from the dividers belonging to sync group 0 or 1 prior to re-programming until re-synchronization completes, first write 1 to `clr_grp0_oe` or `clr_grp1_oe`. If no divider exists in neither group then it will not re-synchronize.

Upon power-up, after OTP has been loaded and VCO calibration completes and APLL gets locked, a sync pulse is generated automatically to all dividers including FODs, IODs, and DPLL feedback divider, that are assigned to sync group 0 or 1.

A sync pulse can also be initiated by writing 1 to register `divider_sync` to synchronize all dividers assigned to group 0 and 1, or `od_grp0_sync` and `od_grp1_sync` can be used to synchronize only the dividers assigned to each group.

Writing the `apll_reinit` bit causes the power-up sequence to restart from the VCO calibration step, which will synchronize the dividers after the APLL locks.

1.8.2.3 Digitally Controlled Oscillator (DCO) Mode

In DCO mode, a frequency control word is passed directly from an external processor or FPGA to the DPLL with a step size of $1/2^{40}$ or 0.91 parts per trillion (ppt) and a full-range of ±244 parts per million (ppm) from the nominal DPLL output frequency. The frequency control word (FCW) is written to a 29-b wide `write_freq` register in two's-complement and then applied to the DPLL feedback divider. The reference clock inputs are unused in this mode. The FCW (positive or negative integer) can be calculated from Fractional Frequency Offset (FFO, in ppm) as follows and then converted to a 29-b two's-complement value.

$$FCW = \left(1 - \frac{1}{1 + \frac{FFO}{10^6}} \right) \times 2^{40}$$

1.8.2.4 Numerically Controlled Oscillator (NCO) Mode

In NCO mode, each FOD can adjust its output clock frequency with a step size of $1/2^{34}$ or 58.21ppt, and is based on incrementing the numerator while holding the 34-b denominator at a fixed value. This frequency change at the output clock is gradual and without glitches. The APLL can be in either clock synthesizer/DCO or in jitter attenuator mode.

1.9 Clock Outputs

The RC310xx supports up to 12 differential or 24 single-ended clock outputs, or any combination of differential and single-ended clock outputs. Each differential clock output can be programmed as two single-ended clock outputs.

1.9.1 Output Types

Differential outputs can be set to 85ohm HCSL, 100ohm HCSL, or LVDS. The HCSL outputs types are low-power push-pull HCSL (LPHCSL) with integrated terminations. They do not require external terminations to drive

standard HCSL inputs, such as those found in PCIe applications. HCSL outputs have programmable output swing and HCSL outputs also have two slew rate settings (2V/ns to 4V/ns and 3V/ns to 5V/ns). LVDS outputs require only a 100ohm resistor between the true and complement inputs of the clock input being driven. Both LVDS and HCSL provide output swing levels that are compatible with LVPECL and CML with external AC coupling.

If set to single-ended mode, the output pair can drive both pins. If both pins are enabled, they can be in phase or inverted phase. The single-ended outputs support CMOS swings of 1.8V, 2.5V, or 3.3V as determined by their VDDO voltage.

1.9.2 Output Banks

The RC310xx maps the internal and external frequency sources to output banks that can be programmed in register [output_bank_src](#), according to the following table. There are up to 12 clock outputs arranged in seven output banks. Each bank sits on its own VDDO (each VDDO also supplies an IOD or FOD as listed below).

Table 1. Output Bank Source Mapping

output_bank_src	Bank 0	Bank 1	Bank 2	Bank 3	Bank 4	Bank 5	Bank 6
	OUT0	OUT1	OUT[2:3]	OUT[4:7]	OUT[8:9]	OUT10	OUT11
0x0	IOD0		N/A		CLKIN1		
0x1	IOD1			N/A		XIN_REFIN	N/A
0x2	N/A				IOD2		
0x3	N/A					IOD3	
0x4	FOD0				N/A		
0x5	FOD1						
0x6	N/A			FOD2			
0x7	N/A				CLKIN0		

1.10 Output Enable Control

During the power-up sequence, the clock output drivers are tri-stated until the power supplies have stabilized, then both OUTx and OUTxb are held low. After the OTP configuration load completes, the clock output drivers can be enabled or held disabled until the APLL and/or DPLL lock according to the setting of [out_startup](#). This behavior can be overridden by setting [out_dis_group](#) to 0x7.

After power-up, the clock output driver is then enabled, either by setting the corresponding [out_dis](#) register bit or by the designated OE pin, if assigned to an OE group. The output driver is enabled when both the register bit and the OE pin are active. If configured in CMOS mode, OUTx and OUTxb can be enabled or disabled individually through [out_prog3](#) and [out_prog2](#).

There are five OE groups, each output driver can optionally be assigned to a OE group in register [out_dis_group](#). A GPI or GPIO pin can be assigned as OE pin to a OE group in register [gpi_func](#) or [gpio_func](#) or can also be assigned as a global OE (GOE) pin with the [goe](#) register bit.

2. Serial Interfaces

The RC310xx can be configured in three ways:

- From internal non-volatile memory using OTP user configurations
- From its slave serial interface and program by a master device
- From an external I2C EEPROM. The device will become master at power-up and load data from I2C EEPROM.

The RC310xx supports three slave serial interfaces: I2C, SPI, and SMBUS. The interface type is selected by the [ssi_enable](#) (0x0026[1:0]) register field. If OTP is not programmed, the device powers up in I2C 1-byte offset mode. These serial interfaces share the same pins so only one is available at a time. The I2C master interface that is used to load User Configurations from an external I2C EEPROM is only active after loading an OTP Configuration with EEPROM function enable. An external master (I2C, SPI, SMBUS) can be used to access internal registers after power-up and the configuration load process is completed.

2.1 1-Byte and 2-Byte Offset Mode

The RC310xx has a 912-byte register memory space. It also separates as four pages, and each page is 256 bytes.

The RC310xx supports 1-byte and 2-byte offset mode for all three slave serial interfaces, I2C, SPI, and SMBUS. The user can choose to operate as 1-byte or 2-byte offset mode, and can be configured through register [ssi_addr_size](#) (0x0026[2]) register field which defaults as 1-byte offset mode. These offsets are used in conjunction with the page register to access registers internal to the device. Because the I2C protocol already includes a read/write bit with the Dev Addr, all bits of the 1-byte or 2-byte offset field can be used to address internal registers.

- The 1-byte offset mode – It also called page mode where part of the address offset is provided in each transaction and another part comes from an internal page register in each serial port. For an I2C 1-byte offset mode operation example, see [Figure 1](#).
- The 2-Byte offset mode – Use two byte as the serial port providing the full offset address within each burst. For an I2C 2-byte offset mode operation example, see [Figure 2](#).

3. I2C Slave

The I2C slave protocol complies with the *I2C Specification*, version UM10204 Rev.6, 4 April 2014. The SCL_SCLK and SDA_nCS pins are 3.3V tolerant. The Dev Addr shown in the [Figure 1](#) represents the I2C bus address that the device will respond to. This 7-bit value in the i2c_addr register field defaults to 0x09 if not programmed via the OTP load.

3.1 1-Byte Offset Mode

In 1-byte mode, the lower 8 bits of the register offset address originate from the Offset Addr byte and the upper 8 bits come from the page register. The page register can be accessed at any time using an offset byte value of 0xFD. Write to 0 for page0, 1 for page1, 2 for page2, and 3 for page3.




Figure 1. I2C 1-Byte Offset Mode Slave Sequencing

3.2 2-Byte Offset Mode

In 2-byte mode, the full 16-bit register address can be obtained from the Offset Addr bytes, so the page register does not need to be set up. The MSB offset address is the page number and the LSB address is the register address.




Figure 2. I2C 2-Byte Offset Mode Slave Sequencing

Note: All serial port configuration will take effect after the write cycle is completed.

4. SPI Slave

This device supports 4-wire or 3-wire SPI operation as a selectable protocol on the serial port. The 3-wire or 4-wire mode is selected by the spi_3wire register bit. In 4-wire mode, there are separate data in and data out signals (SDI and SDO, respectively). In 3-wire mode, the SDIO signal is used as a single, bidirectional data signal.

Figure 3 shows the sequencing of address and data on the serial port in both 3-wire and 4-wire SPI mode. 4-wire SPI mode is the default. The R/W bit is high for read cycles and low for write cycles.




Figure 3. SPI Sequencing Diagram

SPI operation can be configured for the following settings through register fields: 1-byte or 2-byte offset addressing (ssi_addr_size).

In 1-byte operation, the 16-bit register address is formed by using the 7 bits of address supplied in the SPI access and taking the upper 9 bits from the page register. The page register is accessed using an offset address of 0xFD. For an 1-byte offset operation example, see [Example of I2C 1-Byte Offset Mode Programming](#).

In 2-byte operation, the 16-bit register address is formed by using the 15 bits of address supplied in the SPI access and taking the upper 1-bit from the page register. For an 2-byte offset operation example, see also [Example of I2C 2-Byte Offset Mode Programming](#).

- Data sampling on falling or rising edge of SCLK (spi_clk_sel)
- Output (read) data positioning relative to active SCLK edge (spi_del_out)

Note: SPI burst mode operation is required to ensure data integrity of multi-byte registers. When accessing a multi-byte register, all data bytes must be written or read in a single SPI burst access. Bursts can be of greater length if desired but must not extend beyond the end of the register page. An internal address pointer is incremented automatically as each data byte is written or read.

The SPI interface operating at 10MHz supports a DCO update rate of approximately 200k updates per second.

5. SMBus Slave

This device supports a standard SMBus v2.0 and v3.1 compliant interface operating at 100kHz, 400kHz, and 1MHz. The SCL_SCLK and SDA_nCS pins are 3.3V tolerant.

The SMBus interface supports block write and byte write modes. SMBus only supports 7-bit sub-addresses and the ssi_addr_size setting is ignored. A writeable page register selects the upper address bits.

The SMBus slave protocol of the RC310xx complies with the SMBus v2.0 and v3.1 standard.

In the following description, SCL refers to the SCL_SCLK pin and SDA refers to the SDA_nCS pin. [Figure 4](#) shows the sequence of states on the SMBus SDA signal for the supported modes of operation.




Figure 4. I2C Slave Timing Diagram

The Dev Addr shown in the figure represents the SMBus address that the device will respond to. This 7-bit value in the i2c_addr register field defaults to 0x09 if not programmed via the OTP load.

In SMBus, the MSB of the offset address is used to determine whether Block mode is selected, and means the address space is only 128 locations. The internal 16-bit register address is formed by using the 7 bits of address supplied in the SMBus access and taking the upper 9 bits from the page register. The page register is accessed using an offset address of 0xFD.

Read byte/word and Write byte/word are essentially the same as the reads and writes in I2C mode. The main difference is in that when this mode is selected, the MSB of the offset address to read is set to 1. Block read and Block write modes are selected when the MSB of the offset address is set to 0. In block mode, the byte count is always the first value of the data phase. The byte count is stored in the byte count register field and defaults to 0x8.

Note: Same as for I2C, external to the scope of the SMBus-specific logic, burst mode operation is required to ensure data integrity of multi-byte registers. When accessing a multi-byte register, all data bytes must be written or read in a single SMBus burst access. Bursts can be of greater length if desired, but must not extend the end of the register page (Offset Addr 0x7F). An internal address pointer is incremented automatically as each data byte is written or read.

5.1 SMBus 1-Byte/2-Byte Offset Mode Programming Examples

In 1-byte operation, same as I2C 1-byte offset mode operation. For an 1-byte offset operation example, see [Example of I2C 1-Byte Offset Mode Programming](#).

In 2-byte operation, same as I2C 2-byte offset mode operation. For an 2-byte offset operation example, see also [Example of I2C 2-Byte Offset Mode Programming](#).

6. Example of Programming Process

The following two examples show how to use the rbs setting file register value and the customer's own I2C master to program the RC310xx:

- The I2C 1-byte offset mode programming with page number for more than 256 register offset addresses.
- The I2C 2-byte offset mode programming will use the most significant offset byte for the page number. It also applies to SMBus and SPI.

There are four steps to program the RC310xx:

1. Program all register values to the device.
2. Complete a VCO calibration for the new setting.
Note: This step applies only if the VCO frequency will change.
3. Complete an output divider sync up.
4. Change synchronous serial bus setting. The setting is effective after the write cycle is completed. If no change on synchronous serial bus change, then skip this step.

6.1 Getting Register Value from rbs Setting File

The register values of a configuration can be exported from the RICBox GUI when the configuration file is loaded, or it can be retrieved from an rbs file by running a Python script on the configuration file. The register map file is a text file that can be integrated into the user's software (i.e., a head file or a data array), and it will list all of the register values at the beginning of the file (see the following example).

Offset Number	Binary Value	Hex Value	Offset Number
00	00110011	33	00
01	00010000	10	01
02	00000000	00	02
03	00000000	00	03
04	00100010	22	04
05	00000001	01	05
06	10101001	A9	06
07	00000000	00	07
08	00101010	2A	08

6.2 Example of I2C 1-Byte Offset Mode Programming

//Step 1 – Program register value

```
write 0x9 fd 00 // Change page number to page 0.
write 0x9 02 data(0x0002 to 0x0019)
write 0x9 28 data(0x0028 to 0x00F7) // Skip register 0x20 to 0x27, the synchronous
serial bus setting at the end.
write 0x9 fd 01 //Change page number to 1:
write 0x9 00 data(0x0100 to 0x01FA)
write 0x9 fd 02 //Change page number to 2:
write 0x9 00 data(0x0200 to 0x01FB)
write 0x9 fd 03 //Change page number to 3:
write 0x9 00 data(0x0300 to 0x031F)
write 0x9 fd 01 //Change page number to 1
```


//Step 2 – VCO re-calibration

```

write 0x9 3c 20 // Dummy write, delay
write 0x9 3c A0 // Apl1 re-calibrate
write 0x9 3c 20 // Dummy write, wait for the re-calibrate.
// If the master has wait function, then it can be replay by wait
// command. (Wait about 400us)

write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write
write 0x9 3c 20 // Dummy write

```

//Step 3 – Output divider sync up

```

write 0x9 fd 00 //Change page number to 0
write 0x9 11 30
write 0x9 11 32 // output divider sync up
write 0x9 11 30

```

//Step 4 – Synchronous serial bus setting

```

write 0x9 00 20 data(0x0020 to 0x0027) //change synchronous serial bus setting. It
will be affected after the write cycle completed.

```

6.3 Example of I2C 2-Byte Offset Mode Programming**//Step 1 Program register value**

```

write 0x9 00 02 data(0x0002 to 0x0019) // burst write //Skip register 0x0020 to
0x0027.
write 0x9 00 28 data(0x0028 to 0x00F7) // burst write
write 0x9 01 00 data(0x0100 to 0x01FA) // burst write
write 0x9 02 00 data(0x0200 to 0x01FB) // burst write
write 0x9 03 00 data(0x0300 to 0x031F) // burst write

```

//Step 2 VCO re-calibration

```

write 0x9 01 3c 20 // Dummy write, delay
write 0x9 01 3c 20
write 0x9 01 3c A0 // Apl1 re-calibrate. Change register 0x013C from 20 to A0 to
re-calibrate
write 0x9 01 3c 20 // Dummy write, wait for the re-calibrate.
write 0x9 01 3c 20 // Dummy write
write 0x9 01 3c 20 // Dummy write
write 0x9 01 3c 20 // Dummy write
write 0x9 01 3c 20 // Dummy write
write 0x9 01 3c 20 // Dummy write
write 0x9 01 3c 20 // Dummy write

```

```
write 0x9 01 3c 20 // Dummy write
write 0x9 01 3c 20 // Dummy write
write 0x9 01 3c 20 // Dummy write
write 0x9 01 3c 20 // Dummy write
write 0x9 01 3c 20 // Dummy write
```

//Step 3 Output divider sync up

```
write 0x9 00 11 30
write 0x9 00 11 32 // divider sync up
write 0x9 00 11 30
```

//Step 4 Synchronous serial bus setting

```
write 0x9 00 20 data(0x0020 to 0x0027) //change synchronous serial bus setting. It
will be affected after the write cycle completed.
```

7. Example of Changing Output Frequency

Changing an output frequency does not require all registers to be programmed. Changing an output frequency can be implemented by changing either or both of the following:

- VCO frequency of the APLL
- Output divider

Output dividers include integer output dividers (IODs) and fractional output dividers (FODs). Modifying only the output dividers will result in a glitchless frequency change when the last byte of output divider value is updated by an I2C block write event. The frequency change is instantaneous; one clock cycle is still the old frequency and the next clock cycle is the new frequency. Re-calibration is not required; however, if the VCO frequency is modified, it will trigger a VCO calibration. The resulting output frequency will not be glitchless.

APLL VCO frequency is determined by input clock frequency and the 27-bit Feedback divider. The VCO frequency range is between 9.5GHz and 10.7GHz. With VCO frequency in the range of 9.5GHz to 10.7GHz, the RC310xx supports an output frequency range of 1KHz to 650MHz by choosing a proper output divider value. If the desired output frequency is in an integer relationship with VCO frequency, an IOD is used; otherwise, an FOD is used. FOD provides a frequency resolution up to 1ppt (1 per trillion). There are four IODs (IOD0-3) and three FODs (FOD0-2).

Note: If the input frequency or VCO frequency is changed, then re-calibration is required. All changes made through I2C will be temporary. When power is cycled, the original configuration is loaded from OTP memory.

7.1 Output Frequency Calculation

The following formulas provide a method to calculate the desired output frequency. With output frequency determined, we then select an output divider to get the VCO frequency, which must be within 9.5GHz to 10.7GHz.

- Output Frequency = VCO Frequency / Output Divider
- VCO Frequency = Input Frequency * Doubler * (apll_fb_div_int + (apll_fb_div_frac / 2 ^ 27))

Note: If the doubler is enabled, the Doubler=2. If the doubler is disabled, the Doubler = 1.

7.2 Feedback Divider

The VCO feedback divider consists of a 10-bit integer and a 27-bit fractional portion. The offset addresses of the feedback divider register are as follows:

Integer:

- FB_INT_DIV[9:8] = 0x125[1:0]
- FB_INT_DIV[7:0] = 0x124[7:0]

Fractional:

- FB_FRAC_DIV[26:24] = 0x123[2:0]
- FB_FRAC_DIV[23:16] = 0x122[7:0]
- FB_FRAC_DIV[15:8] = 0x121[7:0]
- FB_FRAC_DIV[7:0] = 0x120[7:0]

Example: Programming a VCO frequency of 10GHz with 60MHz crystal.

With a crystal frequency of 60MHz, in order to make a VCO frequency of 10GHz:

- FB_DIV = 10GHz / (60MHz x 2) = 83.333333333333333333333333333333
- FB_INT_DIV = 83
- FB_FRAC_DIV = 0.66666666666666667 x 2²⁷ = 44,739,243 = '0h02 AA AA AB

Program the following registers will make VCO frequency = 10GHz:

- 0x125[1:0] = 0x0
- 0x124[7:0] = 0x53
- 0x123[2:0] = 0x02
- 0x122[7:0] = 0xAA
- 0x121[7:0] = 0xAA
- 0x120[7:0] = 0xAB

7.3 Integer Output Divider

Each Integer Output Divider (IOD) is 25 bits with valid values between 14 and 33,554,431 (= 2²⁵ - 1). A value smaller than 14 causes the output frequency to increase above its maximum 650MHz and the biggest value makes an output frequency below the minimum 1KHz.

IOD0 registers:

- IOD0[24] = Register 0x1C3[0]
- IOD0[23:16] = Register 0x1C2[7:0]
- IOD0[15:8] = Register 0x1C1[7:0]
- IOD0[7:0] = Register 0x1C0[7:0]

Register 0x1C3 only uses bit [0] as IOD0's MSB. All four registers must be written for the IOD value to actually change an output frequency. Register 0x1C3 has remaining bits that have other functions. Remember to keep other bits intact when modifying 0x1C3[0]. Also, read registers 0x1C0~3 to confirm the current value and to know the remaining bits in register 0xC3.

In addition, the other three IODs are taking up the register ranges listed below:

- IOD1[24:0] are in registers 0x1C8, 0x1C9, 0x1CA and 0x1CB.
- IOD2[24:0] are in registers 0x1D0, 0x1D1, 0x1D2 and 0x1D3.
- IOD3[24:0] are in registers 0x1D8, 0x1D9, 0x1DA and 0x1DB.

Example: To make OUT0 = 100MHz by change IOD0 to 100 (VCO frequency = 10GHz)

Output Frequency = VCO Frequency / Output Divider

$$100\text{MHz} = 10\text{GHz} / 100$$

Programming the following registers will change the output to 100MHz. Assuming the VCO is 10GHz.

- Register 0x1C0[7:0] value 0x64
- Register 0x1C1[7:0] value 0x00
- Register 0x1C2[7:0] value 0x00
- Register 0x1C3[0] value 0x0

7.4 Fractional Output Dividers

The fractional output divider consists of a 9-bit 1st integer, a 17-bit 2nd integer, and a 34-bit fractional portion. Together, it can provide a frequency resolution better than 1ppt. The 1st integer covers values up to 511 and is always used. The 2nd integer can cover values up to 131,071 and is used for output frequencies below 33MHz. The formula for the total divider value is as follows:

- $F_{\text{OUT}} > 33\text{MHz}$: $\text{FOD} = 1^{\text{st}} \text{ Integer} + \text{Fraction}$
- $F_{\text{OUT}} < 33\text{MHz}$: $\text{FOD} = (1^{\text{st}} \text{ Integer} + \text{Fraction}) \times 2 \times 2^{\text{nd}} \text{ Integer}$

For output frequencies above 33MHz, where the 2nd Integer is not used, the 2nd Integer value is set to 1. This causes the 2nd Integer and its additional $\times 2$ to be bypassed. Both integer and fractional registers are as follows.

1st Integer:

- FOD0 1st Integer [8] = Register 0x1E1[0]
- FOD0 1st Integer [7:0] = Register 0x1E0[7:0]

2nd Integer:

- FOD0 2nd Integer [16:15] = Register 0x1E3[1:0]
- FOD0 2nd Integer [14:7] = Register 0x1E2[7:0]
- FOD0 2nd Integer [6:0] = Register 0x1E1[7:1]

Fractional:

- FOD0 Fractional [33:30] = Register 0x1E7[3:0]
- FOD0 Fractional [29:22] = Register 0x1E6[7:0]
- FOD0 Fractional [21:14] = Register 0x1E5[7:0]
- FOD0 Fractional [13:6] = Register 0x1E4[7:0]
- FOD0 Fractional [5:0] = Register 0x1E3[7:2]

In addition, FOD1 values are carried by registers 0x1F0 to 0x1F7, and FOD2 is carried by registers in 0x200 to 0x207. For more information, see [Register Offsets](#).

Example: Setting OUT0 = 156.25MHz by programming FOD0 = 64 (VCO frequency = 10GHz)

Output Frequency = VCO Frequency / Output Divider

$$156.25\text{MHz} = 10\text{GHz} / 64$$

Program the following registers will change the output to 156.25MHz

- FOD0 Integer Register programming:
 - Register 0x1E0[7:0] value 0x40
 - Register 0x1E1[7:0] value 0x00

- Register 0x1E2[7:0] value 0x00
- Register 0x1E3[1:0] value 0x00
- FOD0 Fractional register programming:
 - Register 0x1E3[7:2] value 0x00
 - Register 0x1E4[6:0] value 0x00
 - Register 0x1E5[6:0] value 0x00
 - Register 0x1E6[6:0] value 0x00
 - Register 0x1E7[3:0] value 0x00

8. Example of Device Programming with the Driver

For PC or Linux users, they can also leverage the RC310xx Python driver to program the device. The driver will take care of the programming process.

The requirement: Install RICBox and the VC7 plug-in file, or install Python 3.9 and the VC7 driver.

8.1 Example of Python Code

Save the following code to "VC7_Config_Builder.py"

```
import rbcore
from r_drv_vc7.device_abstraction.config_builder import *
from r_drv_vc7.device_abstraction.versaclock7 import Versaclock7
from rbcore.io.ftdi import FtdiI2cSettings
## Create VC7 device. (VC7_Family, Version)
vc7 = Versaclock7( Versaclock7.create_device(r'RC21012B', 'B'))
## Connect FTDI device, I2C address = 0x9
vc7.connect(FtdiI2cSettings(index='0', address=0x09))
## Program VC7
vc7.program_settings_file(r'RC21012B065_config0.rbs')
```

8.2 Example of DOS Batch File

The RICBox VC7 plug-in file comes with the Python 3.9 environment. The following example shows the RICBox environment path. Save the following command to batch file so that it can execute the Python code.

```
Echo off
Echo Start!
C:\Users\%username%\AppData\Roaming\RICBox\venvs\VersaClock7-x64\Scripts\python
VC7_Config_Builder.py
pause
```

9. Register Organization

9.1 Overview

Register sizes are denoted as:

- byte: 8-bit
- hword: 16-bit
- word: 32-bit
- dword: 64-bit

Register types are defined in the following table.

Table 2. Register Type Definition

Type Indicator	Definition
R/W1C	Read/Write 1 to Clear
R/W1S	Read/Write 1 to Set
RO	Read-only
RW	Read/Write
WO	Write-only

9.2 Register Block Offsets

Table 3. Register Block Offsets

Block Offset	Block Name	Address Table	Registers
0x000	GLOBAL	Global Addresses	Global Registers
0x020	SSI	SSI Addresses	SSI Registers
0x02C	XO	Crystal Addresses	XO Register
0x030 += 0x004	CLKIN[0:1]	Clock Input Addresses	CLKIN Register
0x038 += 0x004	REF[0:3]	Clock Reference Addresses	REF Registers
0x050 += 0x010	LOSMON[0:4]	LOS Monitor Addresses	LOSMON Registers
0xA0 += 0x020	FREQMON[0:3]	Frequency Monitor Addresses	FREQMON Registers
0x120	APLL	APLL Addresses	APLL Registers
0x160	TDCAPLL	TDC APLL Addresses	TDC APLL Registers
0x180	DPLL	DPLL Addresses	DPLL Registers
0x1C0 += 0x008	IOD[0:3]	IOD Addresses	IOD Registers
0x1E0 += 0x010	FOD[0:2]	FOD Addresses	FOD Registers
0x240 += 0x004	OUT[0:11]	Clock Output Driver Addresses	OUT Registers
0x280 += 0x004	BANK[0:6]	Output Bank Addresses	BANK Register
0x29C += 0x004	GPI[0:3]	GPI Addresses	GPI Registers
0x2AC += 0x004	GPIO[0:4]	GPIO Addresses	GPIO Registers
0x300 += 0x004	SSC[0:1]	SSC Addresses	SSC Register
0x308	INT	Interrupt Addresses	INT Registers

9.3 Register Offsets

9.3.1 Global Address Map

Table 4. Global Addresses

Block Offset	Size	Register Name	Register Description
0x00	hword	VENDOR_ID	VENDOR_ID - Vendor ID
0x02	hword	DEVICE_ID	DEVICE_ID - Device ID
0x04	hword	DEVICE_REV	DEVICE_REV - Device Revision
0x06	hword	DEVICE_PGM	DEVICE_PGM - Device Programming
0x08	word	DEVICE_CNFG	DEVICE_CNFG - Device Configuration
0x0E	byte	PWR_CTL	PWR_CTL - Power Control
0x10	byte	REG_LOCK	REG_LOCK - Configuration Register Lock
0x11	byte	INIT_SYNC	INIT_SYNC - Initialization and Synchronization Register
0x12	hword	SW_RESET	SW_RESET - Software Reset Register
0x16	hword	MISC_CNFG	MISC_CNFG - Miscellaneous Configuration
0x1C	hword	STARTUP_STS	STARTUP_STS - Start-up Status
0x1E	hword	DEVICE_STS	DEVICE_STS - Device Status

9.3.2 SSI Address Map

Table 5. SSI Addresses

Offset	Size	Register Name	Register Description
0x00	byte	SPI_CNFG	SPI_CNFG - SPI Configuration
0x01	byte	I2C_FLTR_CNFG	I2C_FLTR_CNFG - I2C Filter Configuration
0x02	byte	I2C_TIMING_CNFG	I2C_TIMING_CNFG - I2C Timing Configuration
0x03	byte	I2C_ADDR_CNFG	I2C_ADDR_CNFG - I2C Address Configuration
0x04	byte	BYTE_CNT	BYTE_CNT - Byte Count
0x05	byte	SMB_CTL	SMB_CTL - SMBus Control
0x06	byte	SSI_GLOBAL_CNFG	SSI_GLOBAL_CNFG - SSI Global Configuration
0x07	byte	SSI_STS	SSI_STS - Serial Port Status

9.3.3 Crystal Address Map

Table 6. Crystal Addresses

Offset	Size	Register Name	Register Description
0x00	word	XO_CNFG	XO_CNFG - Crystal Configuration

9.3.4 Clock Input Address Map

Table 7. Clock Input Addresses

Offset	Size	Register Name	Register Description
0x00	hword	CLKIN_CNFG	CLKIN_CNFG - Clock Input Pad Configuration

9.3.5 Clock Reference Address Map

Table 8. Clock Reference Addresses

Offset	Size	Register Name	Register Description
0x00	word	PREDIV_CNFG	PREDIV_CNFG - Reference Clock Input Pre-divider Configuration

9.3.6 LOS Monitor Address Map

Table 9. LOS Monitor Addresses

Offset	Size	Register Name	Register Description
0x00	hword	LOSMON_WINDOW	LOSMON_WINDOW - LOS Monitor Window Configuration
0x02	hword	LOSMON_NOMINAL	LOSMON_NOMINAL - LOS Monitor Nominal Number Configuration
0x04	word	LOSMON_THRESH	LOSMON_THRESH - LOS Monitor Threshold Configuration
0x08	byte	LOSMON_QUAL	LOSMON_QUAL - LOS Monitor Qualify Counter Configuration
0x09	byte	LOSMON_STS	LOSMON_STS - LOS Monitor Status
0x0A	byte	LOSMON_EVENT	LOSMON_EVENT - LOS Monitor Event Status
0x0B	byte	LOSMON_CNT	LOSMON_CNT - LOS Monitor Count

9.3.7 Frequency Monitor Address Map

Table 10. Frequency Monitor Addresses

Offset	Size	Register Name	Register Description
0x00	word	FREQMON_WINDOW	FREQMON_WINDOW - Frequency Monitor Window Configuration
0x04	word	FREQMON_NOMINAL	FREQMON_NOMINAL - Frequency Monitor Nominal Number Configuration
0x08	dword	FREQMON_THRESH	FREQMON_THRESH - Frequency Monitor Threshold Configuration
0x10	byte	FREQMON_STS	FREQMON_STS - Frequency Monitor Status
0x11	byte	FREQMON_EVENT	FREQMON_EVENT - Frequency Monitor Event Status
0x14	word	FREQMON_OFFSET	FREQMON_OFFSET - Frequency Monitor Frequency Offset Status

9.3.8 TDC APLL Address Map

Table 11. TDC APLL Addresses

Offset	Size	Register Name	Register Description
0x00	hword	TDC_APLL_CNFG	TDC_APLL_CNFG - TDC APLL Configuration
0x02	hword	TDC_FB_DIV_FRAC	TDC_FB_DIV_FRAC - TDC APLL Feedback Divider Fraction Configuration
0x04	byte	TDC_FB_DIV_INT	TDC_FB_DIV_INT - TDC APLL Feedback Divider Integer Configuration
0x05	byte	TDC_FB_SDM_CNFG	TDC_FB_SDM_CNFG - TDC APLL Feedback SDM Configuration
0x06	byte	TDC_REF_DIV_CNFG	TDC_REF_DIV_CNFG - TDC APLL Reference Divider Configuration
0x0A	hword	TDC_FILTER_STS	TDC_FILTER_STS - TDC APLL Filter Status

9.3.9 APLL Address Map

Table 12. APLL Addresses

Offset	Size	Register Name	Register Description
0x00	word	APLL_FB_DIV_FRAC	APLL_FB_DIV_FRAC - APLL Feedback Divider Fraction Configuration
0x04	hword	APLL_FB_DIV_INT	APLL_FB_DIV_INT - APLL Feedback Divider Integer Configuration
0x06	byte	APLL_FB_SDM_CNFG	APLL_FB_SDM_CNFG - APLL Feedback SDM Configuration
0x07	byte	APLL_CNFG	APLL_CNFG - APLL Configuration
0x08	hword	CP_CNFG	CP_CNFG - APLL Charge Pump Configuration
0x0A	byte	LPF_CNFG	LPF_CNFG - APLL Loop Filter Configuration
0x0B	byte	LPF_3RD_CNFG	LPF_3RD_CNFG - APLL Loop Filter 3rd Pole Configuration
0x15	byte	APLL_REF_FB_CNFG	APLL_REF_FB_CNFG - APLL Ref and Fb Clock Configuration
0x18	word	BANK_MUX_CLK_EN	BANK_MUX_CLK_EN - Bank Mux Clock Enable
0x1F	byte	APLL_STS	APLL_STS - APLL Status
0x20	byte	APLL_EVENT	APLL_EVENT - APLL Event Status
0x21	byte	APLL_LOL_CNT	APLL_LOL_CNT - APLL Loss-of-Lock Counter
0x28	hword	ANA_SPARE_CNFG	ANA_SPARE_CNFG - Analog Spare Configuration
0x2A	hword	ANA_SPARE_STS	ANA_SPARE_STS - Analog Spare Status

9.3.10 DPLL Address Map

Table 13. DPLL Addresses

Offset	Size	Register Name	Register Description
0x00	byte	DPLL_REF_FB_CNFG	DPLL_REF_FB_CNFG - DPLL Ref and Fb Clock Configuration
0x01	byte	DPLL_MODE	DPLL_MODE - DPLL Mode Configuration
0x02	byte	DPLL_DECIMATOR	DPLL_DECIMATOR - DPLL Decimator Configuration
0x03	byte	DPLL_XTAL_OFFSET	DPLL_XTAL_OFFSET - DPLL Crystal Trim Offset Configuration
0x04	hword	HOLDOVER_CNFG	HOLDOVER_CNFG - Holdover Configuration
0x06	hword	DPLL_BANDWIDTH	DPLL_BANDWIDTH - DPLL Bandwidth Configuration
0x08	hword	DPLL_DAMPING	DPLL_DAMPING - DPLL Damping Configuration
0x0A	hword	DPLL_FB_CORR	DPLL_FB_CORR - DPLL Feedback Correction Configuration
0x0C	word	DPLL_PHASE_SLOPE_LIMIT	DPLL_PHASE_SLOPE_LIMIT - DPLL Phase Slope Limit Configuration
0x10	word	DPLL_PHASE_OFFSET	DPLL_PHASE_OFFSET - DPLL Phase Offset Configuration
0x14	word	DPLL_WRITE_FREQ	DPLL_WRITE_FREQ - DPLL Write Frequency Configuration
0x18	dword	DPLL_FB_DIV_NUM	DPLL_FB_DIV_NUM - DPLL Feedback Divider Numerator Configuration
0x20	dword	DPLL_FB_DIV_DEN	DPLL_FB_DIV_DEN - DPLL Feedback Divider Denominator Configuration
0x28	word	DPLL_FB_DIV_INT	DPLL_FB_DIV_INT - DPLL Feedback Divider Integer Configuration
0x2C	word	DPLL_LOCK	DPLL_LOCK - DPLL Lock Configuration
0x31	byte	DPLL_STS	DPLL_STS - DPLL Status
0x32	byte	DPLL_EVENT	DPLL_EVENT - DPLL Event Status
0x33	byte	DPLL_LOL_CNT	DPLL_LOL_CNT - DPLL Loss-of-Lock Counter
0x34	word	DPLL_FILTER_STS	DPLL_FILTER_STS - DPLL Filter Status
0x38	word	DPLL_PHASE_STS	DPLL_PHASE_STS - DPLL Phase Status

9.3.11 IOD Address Map

Table 14. IOD Addresses

Offset	Size	Register Name	Register Description
0x00	word	IOD_INT_CNFG	IOD_INT_CNFG - IOD Integer Ratio Configuration
0x04	hword	IOD_PHASE_CNFG	IOD_PHASE_CNFG - IOD Phase Configuration
0x06	hword	SYSREF_CNFG	SYSREF_CNFG - SYSREF Configuration

9.3.12 FOD Address Map

Table 15. FOD Addresses

Offset	Size	Register Name	Register Description
0x00	dword	FOD_INT_CNFG	FOD_INT_CNFG - FOD Integer Configuration
0x08	hword	FOD_PHASE_CNFG	FOD_PHASE_CNFG - FOD Phase Configuration

9.3.13 SSC Address Map

Table 16. SSC Addresses

Offset	Size	Register Name	Register Description
0x00	word	SSC_CNFG	SSC_CNFG - Spectrum Spreading Configuration

9.3.14 Output Bank Address Map

Table 17. Output Bank Addresses

Offset	Size	Register Name	Register Description
0x00	byte	OUT_BANK_CNFG	OUT_BANK_CNFG - Output Bank Configuration

9.3.15 Clock Output Driver Address Map

Table 18. Clock Output Driver Addresses

Offset	Size	Register Name	Register Description
0x00	byte	ODRV_EN	ODRV_EN - Output Driver Enable
0x02	hword	ODRV_CNFG	ODRV_CNFG - Output Driver Configuration

9.3.16 GPI Address Map

Table 19. GPI Addresses

Offset	Size	Register Name	Register Description
0x00	hword	GPI_CNFG	GPI_CNFG - GPI Configuration
0x02	byte	GPI_STS	GPI_STS - GPI Status

9.3.17 GPIO Address Map

Table 20. GPIO Addresses

Offset	Size	Register Name	Register Description
0x00	hword	GPIO_CNFG	GPIO_CNFG - GPIO Configuration
0x02	byte	GPIO_STS	GPIO_STS - GPIO Status

9.3.18 Interrupt Address Map

Table 21. Interrupt Addresses

Offset	Size	Register Name	Register Description
0x00	word	SCRATCH0	SCRATCH0 - Software Scratch Register 0
0x04	word	INT_EN	INT_EN - Interrupt Enable
0x08	word	INT_STS	INT_STS - Interrupt Status

10. Physical Register Addresses

10.1 Global Block

Table 22. Global Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x0	GLOBAL	VENDOR_ID[0]	RO	0x33
0x1	GLOBAL	VENDOR_ID[1]	RO	0x10
0x2	GLOBAL	DEVICE_ID[0]	RW	0x00
0x3	GLOBAL	DEVICE_ID[1]	RW	0x00
0x4	GLOBAL	DEVICE_REV[0]	RO	0x22
0x5	GLOBAL	DEVICE_REV[1]	RO	0x01
0x6	GLOBAL	DEVICE_PGM[0]	RW	0x00
0x7	GLOBAL	DEVICE_PGM[1]	RW	0x00
0x8	GLOBAL	DEVICE_CNFG[0]	RW	0x2a
0x9	GLOBAL	DEVICE_CNFG[1]	RW	0xf0
0xa	GLOBAL	DEVICE_CNFG[2]	RW	0x12
0xb	GLOBAL	DEVICE_CNFG[3]	RW	0x00
0xe	GLOBAL	PWR_CTL	RW	0x01
0x10	GLOBAL	REG_LOCK	RW	0x00
0x11	GLOBAL	INIT_SYNC	R/W1S	0x30
0x12	GLOBAL	SW_RESET[0]	RW	0x00
0x13	GLOBAL	SW_RESET[1]	RW	0x00
0x16	GLOBAL	MISC_CNFG[0]	RW	0x05
0x17	GLOBAL	MISC_CNFG[1]	RW	0x80
0x1c	GLOBAL	STARTUP_STS[0]	RO	0x00
0x1d	GLOBAL	STARTUP_STS[1]	RO	0x00
0x1e	GLOBAL	DEVICE_STS[0]	RO	0x00
0x1f	GLOBAL	DEVICE_STS[1]	RO	0x00

10.2 SSI Block

Table 23. SSI Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x20	SSI	SPI_CNFG	RW	0x00
0x21	SSI	I2C_FLTR_CNFG	RW	0x01
0x22	SSI	I2C_TIMING_CNFG	RW	0x22
0x23	SSI	I2C_ADDR_CNFG	RW	0x09
0x24	SSI	BYTE_CNT	RW	0x08
0x25	SSI	SMB_CTL	RW	0x79

Table 23. SSI Block Physical Register Addresses (Cont.)

Address	Block Name	Register	Type	Default
0x26	SSI	SSI_GLOBAL_CNFG	RW	0x01
0x27	SSI	SSI_STS	R/W1C	0x00

10.3 XO Block

Table 24. XO Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x2c	XO	XO_CNFG[0]	RW	0x45
0x2d	XO	XO_CNFG[1]	RW	0x28
0x2e	XO	XO_CNFG[2]	RW	0x68
0x2f	XO	XO_CNFG[3]	RW	0x20

10.4 CLKIN Block

Table 25. CLKIN Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x30	CLKIN[0]	CLKIN_CNFG[0]	RW	0x01
0x31	CLKIN[0]	CLKIN_CNFG[1]	RW	0x80
0x34	CLKIN[1]	CLKIN_CNFG[0]	RW	0x01
0x35	CLKIN[1]	CLKIN_CNFG[1]	RW	0x80

10.5 REF Block

Table 26. REF Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x38	REF[0]	PREDIV_CNFG[0]	RW	0x00
0x39	REF[0]	PREDIV_CNFG[1]	RW	0x00
0x3a	REF[0]	PREDIV_CNFG[2]	RW	0x50
0x3b	REF[0]	PREDIV_CNFG[3]	RW	0x00
0x3c	REF[1]	PREDIV_CNFG[0]	RW	0x00
0x3d	REF[1]	PREDIV_CNFG[1]	RW	0x00
0x3e	REF[1]	PREDIV_CNFG[2]	RW	0x50
0x3f	REF[1]	PREDIV_CNFG[3]	RW	0x00
0x40	REF[2]	PREDIV_CNFG[0]	RW	0x00
0x41	REF[2]	PREDIV_CNFG[1]	RW	0x00
0x42	REF[2]	PREDIV_CNFG[2]	RW	0x50
0x43	REF[2]	PREDIV_CNFG[3]	RW	0x00

Table 26. REF Block Physical Register Addresses (Cont.)

Address	Block Name	Register	Type	Default
0x44	REF[3]	PREDIV_CNFG[0]	RW	0x00
0x45	REF[3]	PREDIV_CNFG[1]	RW	0x00
0x46	REF[3]	PREDIV_CNFG[2]	RW	0x50
0x47	REF[3]	PREDIV_CNFG[3]	RW	0x00

10.6 LOSMON Block

Table 27. LOSMON Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x50	LOSMON[0]	LOSMON_WINDOW[0]	RW	0x00
0x51	LOSMON[0]	LOSMON_WINDOW[1]	RW	0x00
0x52	LOSMON[0]	LOSMON_NOMINAL[0]	RW	0x00
0x53	LOSMON[0]	LOSMON_NOMINAL[1]	RW	0x00
0x54	LOSMON[0]	LOSMON_THRESH[0]	RW	0x00
0x55	LOSMON[0]	LOSMON_THRESH[1]	RW	0x00
0x56	LOSMON[0]	LOSMON_THRESH[2]	RW	0x00
0x57	LOSMON[0]	LOSMON_THRESH[3]	RW	0x00
0x58	LOSMON[0]	LOSMON_QUAL	RW	0x44
0x59	LOSMON[0]	LOSMON_STS	RO	0x03
0x5a	LOSMON[0]	LOSMON_EVENT	R/W1C	0x01
0x5b	LOSMON[0]	LOSMON_CNT	RW	0x00
0x60	LOSMON[1]	LOSMON_WINDOW[0]	RW	0x00
0x61	LOSMON[1]	LOSMON_WINDOW[1]	RW	0x00
0x62	LOSMON[1]	LOSMON_NOMINAL[0]	RW	0x00
0x63	LOSMON[1]	LOSMON_NOMINAL[1]	RW	0x00
0x64	LOSMON[1]	LOSMON_THRESH[0]	RW	0x00
0x65	LOSMON[1]	LOSMON_THRESH[1]	RW	0x00
0x66	LOSMON[1]	LOSMON_THRESH[2]	RW	0x00
0x67	LOSMON[1]	LOSMON_THRESH[3]	RW	0x00
0x68	LOSMON[1]	LOSMON_QUAL	RW	0x44
0x69	LOSMON[1]	LOSMON_STS	RO	0x03
0x6a	LOSMON[1]	LOSMON_EVENT	R/W1C	0x01
0x6b	LOSMON[1]	LOSMON_CNT	RW	0x00
0x70	LOSMON[2]	LOSMON_WINDOW[0]	RW	0x00
0x71	LOSMON[2]	LOSMON_WINDOW[1]	RW	0x00
0x72	LOSMON[2]	LOSMON_NOMINAL[0]	RW	0x00
0x73	LOSMON[2]	LOSMON_NOMINAL[1]	RW	0x00

Table 27. LOSMON Block Physical Register Addresses (Cont.)

Address	Block Name	Register	Type	Default
0x74	LOSMON[2]	LOSMON_THRESH[0]	RW	0x00
0x75	LOSMON[2]	LOSMON_THRESH[1]	RW	0x00
0x76	LOSMON[2]	LOSMON_THRESH[2]	RW	0x00
0x77	LOSMON[2]	LOSMON_THRESH[3]	RW	0x00
0x78	LOSMON[2]	LOSMON_QUAL	RW	0x44
0x79	LOSMON[2]	LOSMON_STS	RO	0x03
0x7a	LOSMON[2]	LOSMON_EVENT	R/W1C	0x01
0x7b	LOSMON[2]	LOSMON_CNT	RW	0x00
0x80	LOSMON[3]	LOSMON_WINDOW[0]	RW	0x00
0x81	LOSMON[3]	LOSMON_WINDOW[1]	RW	0x00
0x82	LOSMON[3]	LOSMON_NOMINAL[0]	RW	0x00
0x83	LOSMON[3]	LOSMON_NOMINAL[1]	RW	0x00
0x84	LOSMON[3]	LOSMON_THRESH[0]	RW	0x00
0x85	LOSMON[3]	LOSMON_THRESH[1]	RW	0x00
0x86	LOSMON[3]	LOSMON_THRESH[2]	RW	0x00
0x87	LOSMON[3]	LOSMON_THRESH[3]	RW	0x00
0x88	LOSMON[3]	LOSMON_QUAL	RW	0x44
0x89	LOSMON[3]	LOSMON_STS	RO	0x03
0x8a	LOSMON[3]	LOSMON_EVENT	R/W1C	0x01
0x8b	LOSMON[3]	LOSMON_CNT	RW	0x00
0x90	LOSMON[4]	LOSMON_WINDOW[0]	RW	0x00
0x91	LOSMON[4]	LOSMON_WINDOW[1]	RW	0x00
0x92	LOSMON[4]	LOSMON_NOMINAL[0]	RW	0x00
0x93	LOSMON[4]	LOSMON_NOMINAL[1]	RW	0x00
0x94	LOSMON[4]	LOSMON_THRESH[0]	RW	0x00
0x95	LOSMON[4]	LOSMON_THRESH[1]	RW	0x00
0x96	LOSMON[4]	LOSMON_THRESH[2]	RW	0x00
0x97	LOSMON[4]	LOSMON_THRESH[3]	RW	0x00
0x98	LOSMON[4]	LOSMON_QUAL	RW	0x44
0x99	LOSMON[4]	LOSMON_STS	RO	0x03
0x9a	LOSMON[4]	LOSMON_EVENT	R/W1C	0x01
0x9b	LOSMON[4]	LOSMON_CNT	RW	0x00

10.7 FREQMON Block

Table 28. FREQMON Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0xa0	FREQMON[0]	FREQMON_WINDOW[0]	RW	0x00
0xa1	FREQMON[0]	FREQMON_WINDOW[1]	RW	0x00
0xa2	FREQMON[0]	FREQMON_WINDOW[2]	RW	0x00
0xa3	FREQMON[0]	FREQMON_WINDOW[3]	RW	0x00
0xa4	FREQMON[0]	FREQMON_NOMINAL[0]	RW	0x00
0xa5	FREQMON[0]	FREQMON_NOMINAL[1]	RW	0x00
0xa6	FREQMON[0]	FREQMON_NOMINAL[2]	RW	0x00
0xa7	FREQMON[0]	FREQMON_NOMINAL[3]	RW	0x00
0xa8	FREQMON[0]	FREQMON_THRESH[0]	RW	0x00
0xa9	FREQMON[0]	FREQMON_THRESH[1]	RW	0x00
0xaa	FREQMON[0]	FREQMON_THRESH[2]	RW	0x00
0xab	FREQMON[0]	FREQMON_THRESH[3]	RW	0x00
0xac	FREQMON[0]	FREQMON_THRESH[4]	RW	0x00
0xad	FREQMON[0]	FREQMON_THRESH[5]	RW	0x00
0xae	FREQMON[0]	FREQMON_THRESH[6]	RW	0x00
0xaf	FREQMON[0]	FREQMON_THRESH[7]	RW	0x00
0xb0	FREQMON[0]	FREQMON_STS	RO	0x01
0xb1	FREQMON[0]	FREQMON_EVENT	R/W1C	0x01
0xb4	FREQMON[0]	FREQMON_OFFSET[0]	RO	0xff
0xb5	FREQMON[0]	FREQMON_OFFSET[1]	RO	0xff
0xb6	FREQMON[0]	FREQMON_OFFSET[2]	RO	0xff
0xb7	FREQMON[0]	FREQMON_OFFSET[3]	RO	0x07
0xc0	FREQMON[1]	FREQMON_WINDOW[0]	RW	0x00
0xc1	FREQMON[1]	FREQMON_WINDOW[1]	RW	0x00
0xc2	FREQMON[1]	FREQMON_WINDOW[2]	RW	0x00
0xc3	FREQMON[1]	FREQMON_WINDOW[3]	RW	0x00
0xc4	FREQMON[1]	FREQMON_NOMINAL[0]	RW	0x00
0xc5	FREQMON[1]	FREQMON_NOMINAL[1]	RW	0x00
0xc6	FREQMON[1]	FREQMON_NOMINAL[2]	RW	0x00
0xc7	FREQMON[1]	FREQMON_NOMINAL[3]	RW	0x00
0xc8	FREQMON[1]	FREQMON_THRESH[0]	RW	0x00
0xc9	FREQMON[1]	FREQMON_THRESH[1]	RW	0x00
0xca	FREQMON[1]	FREQMON_THRESH[2]	RW	0x00
0xcb	FREQMON[1]	FREQMON_THRESH[3]	RW	0x00
0xcc	FREQMON[1]	FREQMON_THRESH[4]	RW	0x00
0xcd	FREQMON[1]	FREQMON_THRESH[5]	RW	0x00

Table 28. FREQMON Block Physical Register Addresses (Cont.)

Address	Block Name	Register	Type	Default
0xce	FREQMON[1]	FREQMON_THRESH[6]	RW	0x00
0xcf	FREQMON[1]	FREQMON_THRESH[7]	RW	0x00
0xd0	FREQMON[1]	FREQMON_STS	RO	0x01
0xd1	FREQMON[1]	FREQMON_EVENT	R/W1C	0x01
0xd4	FREQMON[1]	FREQMON_OFFSET[0]	RO	0xff
0xd5	FREQMON[1]	FREQMON_OFFSET[1]	RO	0xff
0xd6	FREQMON[1]	FREQMON_OFFSET[2]	RO	0xff
0xd7	FREQMON[1]	FREQMON_OFFSET[3]	RO	0x07
0xe0	FREQMON[2]	FREQMON_WINDOW[0]	RW	0x00
0xe1	FREQMON[2]	FREQMON_WINDOW[1]	RW	0x00
0xe2	FREQMON[2]	FREQMON_WINDOW[2]	RW	0x00
0xe3	FREQMON[2]	FREQMON_WINDOW[3]	RW	0x00
0xe4	FREQMON[2]	FREQMON_NOMINAL[0]	RW	0x00
0xe5	FREQMON[2]	FREQMON_NOMINAL[1]	RW	0x00
0xe6	FREQMON[2]	FREQMON_NOMINAL[2]	RW	0x00
0xe7	FREQMON[2]	FREQMON_NOMINAL[3]	RW	0x00
0xe8	FREQMON[2]	FREQMON_THRESH[0]	RW	0x00
0xe9	FREQMON[2]	FREQMON_THRESH[1]	RW	0x00
0xea	FREQMON[2]	FREQMON_THRESH[2]	RW	0x00
0xeb	FREQMON[2]	FREQMON_THRESH[3]	RW	0x00
0xec	FREQMON[2]	FREQMON_THRESH[4]	RW	0x00
0xed	FREQMON[2]	FREQMON_THRESH[5]	RW	0x00
0xee	FREQMON[2]	FREQMON_THRESH[6]	RW	0x00
0xef	FREQMON[2]	FREQMON_THRESH[7]	RW	0x00
0xf0	FREQMON[2]	FREQMON_STS	RO	0x01
0xf1	FREQMON[2]	FREQMON_EVENT	R/W1C	0x01
0xf4	FREQMON[2]	FREQMON_OFFSET[0]	RO	0xff
0xf5	FREQMON[2]	FREQMON_OFFSET[1]	RO	0xff
0xf6	FREQMON[2]	FREQMON_OFFSET[2]	RO	0xff
0xf7	FREQMON[2]	FREQMON_OFFSET[3]	RO	0x07
0x100	FREQMON[3]	FREQMON_WINDOW[0]	RW	0x00
0x101	FREQMON[3]	FREQMON_WINDOW[1]	RW	0x00
0x102	FREQMON[3]	FREQMON_WINDOW[2]	RW	0x00
0x103	FREQMON[3]	FREQMON_WINDOW[3]	RW	0x00
0x104	FREQMON[3]	FREQMON_NOMINAL[0]	RW	0x00
0x105	FREQMON[3]	FREQMON_NOMINAL[1]	RW	0x00
0x106	FREQMON[3]	FREQMON_NOMINAL[2]	RW	0x00

Table 28. FREQMON Block Physical Register Addresses (Cont.)

Address	Block Name	Register	Type	Default
0x107	FREQMON[3]	FREQMON_NOMINAL[3]	RW	0x00
0x108	FREQMON[3]	FREQMON_THRESH[0]	RW	0x00
0x109	FREQMON[3]	FREQMON_THRESH[1]	RW	0x00
0x10a	FREQMON[3]	FREQMON_THRESH[2]	RW	0x00
0x10b	FREQMON[3]	FREQMON_THRESH[3]	RW	0x00
0x10c	FREQMON[3]	FREQMON_THRESH[4]	RW	0x00
0x10d	FREQMON[3]	FREQMON_THRESH[5]	RW	0x00
0x10e	FREQMON[3]	FREQMON_THRESH[6]	RW	0x00
0x10f	FREQMON[3]	FREQMON_THRESH[7]	RW	0x00
0x110	FREQMON[3]	FREQMON_STS	RO	0x01
0x111	FREQMON[3]	FREQMON_EVENT	R/W1C	0x01
0x114	FREQMON[3]	FREQMON_OFFSET[0]	RO	0xff
0x115	FREQMON[3]	FREQMON_OFFSET[1]	RO	0xff
0x116	FREQMON[3]	FREQMON_OFFSET[2]	RO	0xff
0x117	FREQMON[3]	FREQMON_OFFSET[3]	RO	0x07

10.8 APLL Block

Table 29. APLL Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x120	APLL	APLL_FB_DIV_FRAC[0]	RW	0x00
0x121	APLL	APLL_FB_DIV_FRAC[1]	RW	0x00
0x122	APLL	APLL_FB_DIV_FRAC[2]	RW	0x00
0x123	APLL	APLL_FB_DIV_FRAC[3]	RW	0x00
0x124	APLL	APLL_FB_DIV_INT[0]	RW	0x69
0x125	APLL	APLL_FB_DIV_INT[1]	RW	0x00
0x126	APLL	APLL_FB_SDM_CNFG	RW	0x03
0x127	APLL	APLL_CNFG	RW	0x01
0x128	APLL	CP_CNFG[0]	RW	0x33
0x129	APLL	CP_CNFG[1]	RW	0x03
0x12a	APLL	LPF_CNFG	RW	0x74
0x12b	APLL	LPF_3RD_CNFG	RW	0x44
0x135	APLL	APLL_REF_FB_CNFG	RW	0x00
0x13f	APLL	APLL_STS	RO	0x00
0x140	APLL	APLL_EVENT	R/W1C	0x00
0x141	APLL	APLL_LOL_CNT	RW	0x00

10.9 TDCAPLL Block

Table 30. TDCAPLL Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x160	TDCAPLL	TDC_APLL_CNFG[0]	RW	0x4a
0x161	TDCAPLL	TDC_APLL_CNFG[1]	RW	0x1e
0x162	TDCAPLL	TDC_FB_DIV_FRAC[0]	RW	0x00
0x163	TDCAPLL	TDC_FB_DIV_FRAC[1]	RW	0x28
0x164	TDCAPLL	TDC_FB_DIV_INT	RW	0x24
0x165	TDCAPLL	TDC_FB_SDM_CNFG	RW	0x81
0x166	TDCAPLL	TDC_REF_DIV_CNFG	RW	0x01
0x16a	TDCAPLL	TDC_FILTER_STS[0]	RO	0x00
0x16b	TDCAPLL	TDC_FILTER_STS[1]	RO	0x00

10.10 DPLL Block

Table 31. DPLL Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x180	DPLL	DPLL_REF_FB_CNFG	RW	0x04
0x181	DPLL	DPLL_MODE	RW	0x81
0x182	DPLL	DPLL_DECIMATOR	RW	0x36
0x183	DPLL	DPLL_XTAL_OFFSET	RW	0x00
0x184	DPLL	HOLDOVER_CNFG[0]	RW	0x00
0x185	DPLL	HOLDOVER_CNFG[1]	RW	0x38
0x186	DPLL	DPLL_BANDWIDTH[0]	RW	0x58
0x187	DPLL	DPLL_BANDWIDTH[1]	RW	0x70
0x188	DPLL	DPLL_DAMPING[0]	RW	0x00
0x189	DPLL	DPLL_DAMPING[1]	RW	0x29
0x18a	DPLL	DPLL_FB_CORR[0]	RW	0x00
0x18b	DPLL	DPLL_FB_CORR[1]	RW	0x00
0x18c	DPLL	DPLL_PHASE_SLOPE_LIMIT[0]	RW	0xff
0x18d	DPLL	DPLL_PHASE_SLOPE_LIMIT[1]	RW	0xff
0x18e	DPLL	DPLL_PHASE_SLOPE_LIMIT[2]	RW	0xff
0x18f	DPLL	DPLL_PHASE_SLOPE_LIMIT[3]	RW	0x1f
0x190	DPLL	DPLL_PHASE_OFFSET[0]	RW	0x00
0x191	DPLL	DPLL_PHASE_OFFSET[1]	RW	0x00
0x192	DPLL	DPLL_PHASE_OFFSET[2]	RW	0x00
0x193	DPLL	DPLL_PHASE_OFFSET[3]	RW	0x00
0x194	DPLL	DPLL_WRITE_FREQ[0]	RW	0x00
0x195	DPLL	DPLL_WRITE_FREQ[1]	RW	0x00

Table 31. DPLL Block Physical Register Addresses (Cont.)

Address	Block Name	Register	Type	Default
0x196	DPLL	DPLL_WRITE_FREQ[2]	RW	0x00
0x197	DPLL	DPLL_WRITE_FREQ[3]	RW	0x00
0x198	DPLL	DPLL_FB_DIV_NUM[0]	RW	0x00
0x199	DPLL	DPLL_FB_DIV_NUM[1]	RW	0x00
0x19a	DPLL	DPLL_FB_DIV_NUM[2]	RW	0x00
0x19b	DPLL	DPLL_FB_DIV_NUM[3]	RW	0x00
0x19c	DPLL	DPLL_FB_DIV_NUM[4]	RW	0x00
0x19d	DPLL	DPLL_FB_DIV_NUM[5]	RW	0x00
0x1a0	DPLL	DPLL_FB_DIV_DEN[0]	RW	0x00
0x1a1	DPLL	DPLL_FB_DIV_DEN[1]	RW	0x00
0x1a2	DPLL	DPLL_FB_DIV_DEN[2]	RW	0x80
0x1a3	DPLL	DPLL_FB_DIV_DEN[3]	RW	0x00
0x1a4	DPLL	DPLL_FB_DIV_DEN[4]	RW	0x00
0x1a5	DPLL	DPLL_FB_DIV_DEN[5]	RW	0x00
0x1a8	DPLL	DPLL_FB_DIV_INT[0]	RW	0x90
0x1a9	DPLL	DPLL_FB_DIV_INT[1]	RW	0x01
0x1aa	DPLL	DPLL_FB_DIV_INT[2]	RW	0x00
0x1ac	DPLL	DPLL_LOCK[0]	RW	0x55
0x1ad	DPLL	DPLL_LOCK[1]	RW	0x01
0x1ae	DPLL	DPLL_LOCK[2]	RW	0xff
0x1af	DPLL	DPLL_LOCK[3]	RW	0x00
0x1b1	DPLL	DPLL_STS	RO	0x00
0x1b2	DPLL	DPLL_EVENT	R/W1C	0x00
0x1b3	DPLL	DPLL_LOL_CNT	RW	0x00
0x1b4	DPLL	DPLL_FILTER_STS[0]	RO	0x00
0x1b5	DPLL	DPLL_FILTER_STS[1]	RO	0x00
0x1b6	DPLL	DPLL_FILTER_STS[2]	RO	0x00
0x1b7	DPLL	DPLL_FILTER_STS[3]	RO	0x00
0x1b8	DPLL	DPLL_PHASE_STS[0]	RO	0x00
0x1b9	DPLL	DPLL_PHASE_STS[1]	RO	0x00
0x1ba	DPLL	DPLL_PHASE_STS[2]	RO	0x00
0x1bb	DPLL	DPLL_PHASE_STS[3]	RO	0x00

10.11 IOD Block

Table 32. IOD Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x1c0	IOD[0]	IOD_INT_CNFG[0]	RW	0x64
0x1c1	IOD[0]	IOD_INT_CNFG[1]	RW	0x00
0x1c2	IOD[0]	IOD_INT_CNFG[2]	RW	0x00
0x1c3	IOD[0]	IOD_INT_CNFG[3]	RW	0x00
0x1c4	IOD[0]	IOD_PHASE_CNFG[0]	RW	0x00
0x1c5	IOD[0]	IOD_PHASE_CNFG[1]	R/W1S	0x00
0x1c6	IOD[0]	SYSREF_CNFG[0]	RW	0x00
0x1c7	IOD[0]	SYSREF_CNFG[1]	RW	0x00
0x1c8	IOD[1]	IOD_INT_CNFG[0]	RW	0x64
0x1c9	IOD[1]	IOD_INT_CNFG[1]	RW	0x00
0x1ca	IOD[1]	IOD_INT_CNFG[2]	RW	0x00
0x1cb	IOD[1]	IOD_INT_CNFG[3]	RW	0x00
0x1cc	IOD[1]	IOD_PHASE_CNFG[0]	RW	0x00
0x1cd	IOD[1]	IOD_PHASE_CNFG[1]	R/W1S	0x00
0x1ce	IOD[1]	SYSREF_CNFG[0]	RW	0x00
0x1cf	IOD[1]	SYSREF_CNFG[1]	RW	0x00
0x1d0	IOD[2]	IOD_INT_CNFG[0]	RW	0x64
0x1d1	IOD[2]	IOD_INT_CNFG[1]	RW	0x00
0x1d2	IOD[2]	IOD_INT_CNFG[2]	RW	0x00
0x1d3	IOD[2]	IOD_INT_CNFG[3]	RW	0x00
0x1d4	IOD[2]	IOD_PHASE_CNFG[0]	RW	0x00
0x1d5	IOD[2]	IOD_PHASE_CNFG[1]	R/W1S	0x00
0x1d6	IOD[2]	SYSREF_CNFG[0]	RW	0x00
0x1d7	IOD[2]	SYSREF_CNFG[1]	RW	0x00
0x1d8	IOD[3]	IOD_INT_CNFG[0]	RW	0x64
0x1d9	IOD[3]	IOD_INT_CNFG[1]	RW	0x00
0x1da	IOD[3]	IOD_INT_CNFG[2]	RW	0x00
0x1db	IOD[3]	IOD_INT_CNFG[3]	RW	0x00
0x1dc	IOD[3]	IOD_PHASE_CNFG[0]	RW	0x00
0x1dd	IOD[3]	IOD_PHASE_CNFG[1]	R/W1S	0x00
0x1de	IOD[3]	SYSREF_CNFG[0]	RW	0x00
0x1df	IOD[3]	SYSREF_CNFG[1]	RW	0x00

10.12 FOD Block

Table 33. FOD Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x1e0	FOD[0]	FOD_INT_CNFG[0]	RW	0x64
0x1e1	FOD[0]	FOD_INT_CNFG[1]	RW	0x00
0x1e2	FOD[0]	FOD_INT_CNFG[2]	RW	0x00
0x1e3	FOD[0]	FOD_INT_CNFG[3]	RW	0x00
0x1e4	FOD[0]	FOD_INT_CNFG[4]	RW	0x00
0x1e5	FOD[0]	FOD_INT_CNFG[5]	RW	0x00
0x1e6	FOD[0]	FOD_INT_CNFG[6]	RW	0x00
0x1e7	FOD[0]	FOD_INT_CNFG[7]	RW	0x00
0x1e8	FOD[0]	FOD_PHASE_CNFG[0]	RW	0xf0
0x1e9	FOD[0]	FOD_PHASE_CNFG[1]	R/W1S	0x43
0x1f0	FOD[1]	FOD_INT_CNFG[0]	RW	0x64
0x1f1	FOD[1]	FOD_INT_CNFG[1]	RW	0x00
0x1f2	FOD[1]	FOD_INT_CNFG[2]	RW	0x00
0x1f3	FOD[1]	FOD_INT_CNFG[3]	RW	0x00
0x1f4	FOD[1]	FOD_INT_CNFG[4]	RW	0x00
0x1f5	FOD[1]	FOD_INT_CNFG[5]	RW	0x00
0x1f6	FOD[1]	FOD_INT_CNFG[6]	RW	0x00
0x1f7	FOD[1]	FOD_INT_CNFG[7]	RW	0x00
0x1f8	FOD[1]	FOD_PHASE_CNFG[0]	RW	0xf0
0x1f9	FOD[1]	FOD_PHASE_CNFG[1]	R/W1S	0x43
0x200	FOD[2]	FOD_INT_CNFG[0]	RW	0x64
0x201	FOD[2]	FOD_INT_CNFG[1]	RW	0x00
0x202	FOD[2]	FOD_INT_CNFG[2]	RW	0x00
0x203	FOD[2]	FOD_INT_CNFG[3]	RW	0x00
0x204	FOD[2]	FOD_INT_CNFG[4]	RW	0x00
0x205	FOD[2]	FOD_INT_CNFG[5]	RW	0x00
0x206	FOD[2]	FOD_INT_CNFG[6]	RW	0x00
0x207	FOD[2]	FOD_INT_CNFG[7]	RW	0x00
0x208	FOD[2]	FOD_PHASE_CNFG[0]	RW	0xf0
0x209	FOD[2]	FOD_PHASE_CNFG[1]	R/W1S	0x43

10.13 OUT Block

Table 34. OUT Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x240	OUT[0]	ODRV_EN	RW	0x06
0x242	OUT[0]	ODRV_CNFG[0]	RW	0x3c
0x243	OUT[0]	ODRV_CNFG[1]	RW	0x00
0x244	OUT[1]	ODRV_EN	RW	0x06
0x246	OUT[1]	ODRV_CNFG[0]	RW	0x3c
0x247	OUT[1]	ODRV_CNFG[1]	RW	0x00
0x248	OUT[2]	ODRV_EN	RW	0x06
0x24a	OUT[2]	ODRV_CNFG[0]	RW	0x3c
0x24b	OUT[2]	ODRV_CNFG[1]	RW	0x00
0x24c	OUT[3]	ODRV_EN	RW	0x06
0x24e	OUT[3]	ODRV_CNFG[0]	RW	0x3c
0x24f	OUT[3]	ODRV_CNFG[1]	RW	0x00
0x250	OUT[4]	ODRV_EN	RW	0x06
0x252	OUT[4]	ODRV_CNFG[0]	RW	0x3c
0x253	OUT[4]	ODRV_CNFG[1]	RW	0x00
0x254	OUT[5]	ODRV_EN	RW	0x06
0x256	OUT[5]	ODRV_CNFG[0]	RW	0x3c
0x257	OUT[5]	ODRV_CNFG[1]	RW	0x00
0x258	OUT[6]	ODRV_EN	RW	0x06
0x25a	OUT[6]	ODRV_CNFG[0]	RW	0x3c
0x25b	OUT[6]	ODRV_CNFG[1]	RW	0x00
0x25c	OUT[7]	ODRV_EN	RW	0x06
0x25e	OUT[7]	ODRV_CNFG[0]	RW	0x3c
0x25f	OUT[7]	ODRV_CNFG[1]	RW	0x00
0x260	OUT[8]	ODRV_EN	RW	0x06
0x262	OUT[8]	ODRV_CNFG[0]	RW	0x3c
0x263	OUT[8]	ODRV_CNFG[1]	RW	0x00
0x264	OUT[9]	ODRV_EN	RW	0x06
0x266	OUT[9]	ODRV_CNFG[0]	RW	0x3c
0x267	OUT[9]	ODRV_CNFG[1]	RW	0x00
0x268	OUT[10]	ODRV_EN	RW	0x06
0x26a	OUT[10]	ODRV_CNFG[0]	RW	0x3c
0x26b	OUT[10]	ODRV_CNFG[1]	RW	0x00
0x26c	OUT[11]	ODRV_EN	RW	0x06
0x26e	OUT[11]	ODRV_CNFG[0]	RW	0x3c
0x26f	OUT[11]	ODRV_CNFG[1]	RW	0x00

10.14 BANK Block

Table 35. BANK Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x280	BANK[0]	OUT_BANK_CNFG	RW	0x05
0x284	BANK[1]	OUT_BANK_CNFG	RW	0x05
0x288	BANK[2]	OUT_BANK_CNFG	RW	0x05
0x28c	BANK[3]	OUT_BANK_CNFG	RW	0x05
0x290	BANK[4]	OUT_BANK_CNFG	RW	0x05
0x294	BANK[5]	OUT_BANK_CNFG	RW	0x05
0x298	BANK[6]	OUT_BANK_CNFG	RW	0x05

10.15 GPI Block

Table 36. GPI Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x29c	GPI[0]	GPI_CNFG[0]	RW	0x7f
0x29d	GPI[0]	GPI_CNFG[1]	RW	0x00
0x29e	GPI[0]	GPI_STS	RO	0x00
0x2a0	GPI[1]	GPI_CNFG[0]	RW	0x7f
0x2a1	GPI[1]	GPI_CNFG[1]	RW	0x00
0x2a2	GPI[1]	GPI_STS	RO	0x00
0x2a4	GPI[2]	GPI_CNFG[0]	RW	0x7f
0x2a5	GPI[2]	GPI_CNFG[1]	RW	0x00
0x2a6	GPI[2]	GPI_STS	RO	0x00
0x2a8	GPI[3]	GPI_CNFG[0]	RW	0x7f
0x2a9	GPI[3]	GPI_CNFG[1]	RW	0x00
0x2aa	GPI[3]	GPI_STS	RO	0x00

10.16 GPIO Block

Table 37. GPIO Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x2ac	GPIO[0]	GPIO_CNFG[0]	RW	0x90
0x2ad	GPIO[0]	GPIO_CNFG[1]	RW	0x04
0x2ae	GPIO[0]	GPIO_STS	RO	0x00
0x2b0	GPIO[1]	GPIO_CNFG[0]	RW	0x90
0x2b1	GPIO[1]	GPIO_CNFG[1]	RW	0x04
0x2b2	GPIO[1]	GPIO_STS	RO	0x00
0x2b4	GPIO[2]	GPIO_CNFG[0]	RW	0x90

Table 37. GPIO Block Physical Register Addresses (Cont.)

Address	Block Name	Register	Type	Default
0x2b5	GPIO[2]	GPIO_CNFG[1]	RW	0x04
0x2b6	GPIO[2]	GPIO_STS	RO	0x00
0x2b8	GPIO[3]	GPIO_CNFG[0]	RW	0x90
0x2b9	GPIO[3]	GPIO_CNFG[1]	RW	0x04
0x2ba	GPIO[3]	GPIO_STS	RO	0x00
0x2bc	GPIO[4]	GPIO_CNFG[0]	RW	0x90
0x2bd	GPIO[4]	GPIO_CNFG[1]	RW	0x04
0x2be	GPIO[4]	GPIO_STS	RO	0x00

10.17 SSC Block

Table 38. SSC Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x300	SSC[0]	SSC_CNFG[0]	RW	0x8c
0x301	SSC[0]	SSC_CNFG[1]	RW	0x2b
0x302	SSC[0]	SSC_CNFG[2]	RW	0x51
0x303	SSC[0]	SSC_CNFG[3]	RW	0x00
0x304	SSC[1]	SSC_CNFG[0]	RW	0x8c
0x305	SSC[1]	SSC_CNFG[1]	RW	0x2b
0x306	SSC[1]	SSC_CNFG[2]	RW	0x51
0x307	SSC[1]	SSC_CNFG[3]	RW	0x00

10.18 INT Block

Table 39. INT Block Physical Register Addresses

Address	Block Name	Register	Type	Default
0x308	INT	SCRATCH0[0]	RW	0x00
0x309	INT	SCRATCH0[1]	RW	0x00
0x30a	INT	SCRATCH0[2]	RW	0x00
0x30b	INT	SCRATCH0[3]	RW	0x00
0x30c	INT	INT_EN[0]	RW	0x00
0x30d	INT	INT_EN[1]	RW	0x00
0x30e	INT	INT_EN[2]	RW	0x00
0x30f	INT	INT_EN[3]	RW	0x00
0x310	INT	INT_STS[0]	RO	0x00
0x311	INT	INT_STS[1]	RO	0x00

Table 39. INT Block Physical Register Addresses (Cont.)

Address	Block Name	Register	Type	Default
0x312	INT	INT_STS[2]	RO	0x00
0x313	INT	INT_STS[3]	RO	0x00

11. Register Descriptions

11.1 Global Registers

Table 40. VENDOR_ID - Vendor ID

Bit Field	Field Name	Type	Default Value	Description
15:12	dev_id_type	RO	0x1	Device ID Block Type. A value of 0x1 indicates that this register is followed by a 16-bit Device ID register and an 16-bit Device Revision register, and a 16-bit Device Programming register.
11	reserved	RO	0x0	Reserved.
10:0	vendor_id	RO	0x33	Vendor ID. Renesas/IDT JEDEC ID.

Table 41. DEVICE_ID - Device ID

Bit Field	Field Name	Type	Default Value	Description
15:0	device_id	RW	0x0	Device ID. For default value refer to Product Identification. This field is writeable so it can be configured from OTP.

Table 42. DEVICE_REV - Device Revision

Bit Field	Field Name	Type	Default Value	Description
15:0	device_revision	RO	0x0443	Device Revision. Decode as follows: <ul style="list-style-type: none"> ▪ 0x0111 = First silicon; not released. ▪ 0x0333 = Rev A ▪ 0x0443 = Rev B

Table 43. DEVICE_PGM - Device Programming

Bit Field	Field Name	Type	Default Value	Description
15:0	dash_code	RW	0x0	Dash Code. Decimal value assigned by IDT to identify the user configuration loaded in OTP at the factory. This field is write-able and is configured from the OTP common configuration programmed at the factory. <ul style="list-style-type: none"> ▪ 0x0 = No user configuration has been programmed at the factory

Table 44. DEVICE_CNFG - Device Configuration

Bit Field	Field Name	Type	Default Value	Description
31	reserved	RO	0x0	Reserved.
30:24	reserved	RW	0x0	Reserved.
30	float_vddo6	RW	0x0	Float VDDO6 Supply. <ul style="list-style-type: none"> Controls Iref and Ibias to the output divider LDO, output bank LDO, output divider IOD3 and output driver 11 in the VDDO6 domain. 0x0 = Reference currents enabled 0x1 = Reference currents disabled, must be set when the VDDO6 pin floats
29	float_vddo5	RW	0x0	Float VDDO5 Supply. Controls Iref and Ibias to the output divider LDO, output bank LDO, output divider IOD2 and output driver 10 in the VDDO5 domain. <ul style="list-style-type: none"> 0x0 = Reference currents enabled 0x1 = Reference currents disabled, must be set when the VDDO5 pin floats
28	float_vddo4	RW	0x0	Float VDDO4 Supply. Controls Iref and Ibias to the output divider LDO, output bank LDO, output divider FOD2 and output drivers 8/9 in the VDDO4 domain. <ul style="list-style-type: none"> 0x0 = Reference currents enabled 0x1 = Reference currents disabled, must be set when the VDDO4 pin floats
27	float_vddo3	RW	0x0	Float VDDO3 Supply. Controls Iref and Ibias to the output divider LDO, output bank LDO, output divider FOD1 and output drivers 4/5/6/7 in the VDDO3 domain. <ul style="list-style-type: none"> 0x0 = Reference currents enabled 0x1 = Reference currents disabled, must be set when the VDDO3 pin floats
26	float_vddo2	RW	0x0	Float VDDO2 Supply. Controls Iref and Ibias to the output divider LDO, output bank LDO, output divider FOD0 and output drivers 2/3 in the VDDO2 domain. <ul style="list-style-type: none"> 0x0 = Reference currents enabled 0x1 = Reference currents disabled, must be set when the VDDO2 pin floats
25	float_vddo1	RW	0x0	Float VDDO1 Supply. Controls Iref and Ibias to the output divider LDO, output bank LDO, output divider IOD1 and output driver 1 in the VDDO1 domain. <ul style="list-style-type: none"> 0x0 = Reference currents enabled 0x1 = Reference currents disabled, must be set when the VDDO1 pin floats
24	float_vddo0	RW	0x0	Float VDDO0 Supply. Controls Iref and Ibias to the output divider LDO, output bank LDO, output divider IOD0 and output driver 0 in the VDDO0 domain. <ul style="list-style-type: none"> 0x0 = Reference currents enabled 0x1 = Reference currents disabled, must be set when the VDDO0 pin floats
23	reserved	RW	0x0	Reserved.

Table 44. DEVICE_CNFG - Device Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
22	dyn_csel_deb	RW	0x0	<p>Dynamic CSEL De-bounce Interval.</p> <p>The input value across GPI/GPIO pins configured as Dynamic CSEL must be stable for this number of system clock cycles before it takes effect.</p> <ul style="list-style-type: none"> ▪ 0x0 = 8 system clock cycles (133ns) ▪ 0x1 = 256 system clock cycles (4.2us)
21:20	dpll_clk_sel_deb	RW	0x1	<p>DPLL_CLK_SEL De-bounce Interval.</p> <p>The input value across GPI/GPIO pins configured as DPLL_CLK_SEL[0] and DPLL_CLK_SEL[1] must be stable for this number of system clock cycles before it takes effect.</p> <ul style="list-style-type: none"> ▪ 0x0 = 2 system clock cycles (33ns) ▪ 0x1 = 4 system clock cycles (67ns) ▪ 0x2 = 6 system clock cycles (100ns) ▪ 0x3 = 8 system clock cycles (133ns)
19:16	sync_dis_wait	RW	0x2	<p>Divider Synchronization Output Clock Disable Wait Time.</p> <p>During the divider synchronization procedure, after de-asserting the output enable to the affected output drivers, the control logic waits for this period of time before stopping the clocks and synchronizing the dividers. If enabled, this must be set longer than the period of the slowest output clock, and longer than the SSC modulation interval.</p> <ul style="list-style-type: none"> ▪ 0x0 = 1us ▪ 0x1 = 2us ▪ 0x2 = 4us ▪ 0x3 = 8us ▪ 0x4 = 16us ▪ 0x5 = 32us ▪ 0x6 = 64us ▪ 0x7 = 128us ▪ 0x8 = 256us ▪ 0x9 = 512us ▪ 0xA = 1024us ▪ 0xB = 2048us ▪ 0xC = 4096us
15:12	pwrnd_sel	RW	0xF	<p>PWRGD/PWRDN# Pin Select.</p> <p>Selects the pin used as PWRGD/PWRDN#, or disables the functionality. If a pin is selected, the device waits for that pin to be high before loading the OTP/EEPROM UserCfg. That pin may also be assigned as a 2-level Dynamic CSEL pin with <i>gpio_func</i> and <i>gpio_type</i>, and polarity inversion must be disabled (<i>gpio_pol</i>). This setting must be programmed by the OTP/EEPROM common configuration in order to take effect during the power-up sequence.</p> <ul style="list-style-type: none"> ▪ 0x0 = GPIO0 ▪ 0x1 = GPIO1 ▪ 0x2 = GPIO2 ▪ 0x3 = GPIO3 ▪ 0x4 = GPIO4 ▪ 0x5 = GPIO ▪ 0x6 = GPI1 ▪ 0x7 = GPI2 ▪ 0x8 = GPI3 ▪ 0xF: No pin selected, associated functionality disabled

Table 44. DEVICE_CNFG - Device Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
11:6	reserved	RW	0x0	Reserved.
11	float_vddr3	RW	0x0	Float VDDR3 Supply. Controls Iref and Ibias to the Input Buffer LDO and IB2 in the VDDR3 domain (bonded to VDDR in the current 48 and 40 pin package variants). <ul style="list-style-type: none"> 0x0 = Reference currents enabled 0x1 = Reference currents disabled, must be set when the VDDR3 pin floats
10	float_vddr2	RW	0x0	Float VDDR2 Supply. Controls Iref and Ibias to the Input Buffer LDO and IB1 in the VDDR2 domain (bonded to VDDR in the current 48 and 40 pin package variants). <ul style="list-style-type: none"> 0x0 = Reference currents enabled 0x1 = Reference currents disabled, must be set when the VDDR2 pin floats
9:6	reserved	RW	0x0	Reserved.
5:4	static_csel2	RW	0x2	Static Configuration Select Bit 2. Selects the GPIO pin or fixed value used for static configuration select bit index 2. This setting must be programmed by the OTP/EEPROM common configuration in order to take effect during the power-up sequence. <ul style="list-style-type: none"> 0x0 = No pin selected, treated as Low (tri-level) 0x1 = No pin selected, treated as Mid (tri-level) 0x2 = GPIO2 (tri-level) 0x3 = No pin selected, treated as High (tri-level)
3:2	static_csel1	RW	0x2	Static Configuration Select Bit 1. Selects the GPIO pin or fixed value used for static configuration select bit index 1. This setting must be programmed by the OTP/EEPROM common configuration in order to take effect during the power-up sequence. <ul style="list-style-type: none"> 0x0 = No pin selected, treated as Low (tri-level) 0x1 = No pin selected, treated as Mid (tri-level) 0x2 = GPIO1 (tri-level) 0x3 = No pin selected, treated as High (tri-level)
1:0	static_csel0	RW	0x2	Static Configuration Select Bit 0. Selects the GPIO pin or fixed value used for static configuration select bit index 0. This setting must be programmed by the OTP/EEPROM common configuration in order to take effect during the power-up sequence. <ul style="list-style-type: none"> 0x0 = No pin selected, treated as Low (tri-level) 0x1 = No pin selected, treated as Mid (tri-level) 0x2 = GPIO0 (tri-level) 0x3 = No pin selected, treated as High (tri-level)

Table 45. PWR_CTL - Power Control

Bit Field	Field Name	Type	Default Value	Description
7:1	reserved	RO	0x0	Reserved.
0	pd_restoreb	RW	0x1	<p>Power Down Restore (Active Low). Controls the device behavior when PWRGD/PWRDN# falls to enter power down.If pd_restoreb is set to 0, it will be reset back to 1 by the reset sequence.</p> <ul style="list-style-type: none"> 0x0 = Full power-on-reset. The falling edge of the PWRGD/PWRDN# pin resets the device, including configuration registers, to the initial power-on-reset state. The startup sequence is executed. It will wait for the rising edge of the PWRGD/PWRDN# pin to re-latch static CSEL inputs and load the corresponding user configuration, as on initial power-up. 0x1 = Quick power down and power up sequence. The falling and subsequent rising edge of the PWRGD/PWRDN# pin trigger dynamic configuration loads which program the device to enter the powered down and powered up states, respectively. The startup sequence is not executed, and static CSEL inputs are not re-latched.

Table 46. REG_LOCK - Configuration Register Lock

Bit Field	Field Name	Type	Default Value	Description
7:0	reg_lock_key	RW	0x0	<p>Configuration Register Lock Key. Writing this field with 0xCB sets the config_reg_ro bit to 1. Writing this field with 0x34 clears the config_reg_ro bit to 0.</p>

Table 47. INIT_SYNC - Initialization and Synchronization Register

Bit Field	Field Name	Type	Default Value	Description
7	clr_grp1_oe	RW1S	0x0	<p>Clear Reset Sequencer Sync Group 1 Output Enable. Writing this bit to 1 clears the sync group 1 output enable from the reset sequencer. The reset sequencer will set it back to 1 after the next group 1 divider synchronization completes. This affects all outputs in banks that select a divider assigned to sync group 1. Self-cleared immediately. Must not be set to 1 at the same time as any of divider_sync, od_grp0_sync and od_grp1_sync are set to 1.</p>
6	clr_grp0_oe	RW1S	0x0	<p>Clear Reset Sequencer Sync Group 0 Output Enable. Writing this bit to 1 clears the sync group 0 output enable from the reset sequencer. The reset sequencer will set it back to 1 after the next group 0 divider synchronization completes. This affects all outputs in banks that select a divider assigned to sync group 0. Self-cleared immediately. Must not be set to 1 at the same time as any of divider_sync, od_grp0_sync and od_grp1_sync are set to 1.</p>
5	id_global_setb	RW	0x1	<p>Input Dividers Common Set. When cleared, all input dividers are held in set mode (bit is active low). This allows set and release of all dividers at roughly the same time.</p>
4	goe	RW	0x1	<p>Output Global OE. This bit allows manual CSR control of the global output OE.</p>

Table 47. INIT_SYNC - Initialization and Synchronization Register

Bit Field	Field Name	Type	Default Value	Description
3	od_grp1_sync	RW1S	0x0	Divider Group 1 Sync Trigger. Write 1 to trigger synchronization of DPLL and output dividers in group 1 as defined in dpll_sync_group , iod_sync_group and fod_sync_group . The affected output clocks will be squelched for approximately the sync_dis_wait duration. Self-cleared immediately.
2	od_grp0_sync	RW1S	0x0	Divider Group 0 Sync Trigger. Write 1 to trigger synchronization of DPLL and output dividers in group 0 as defined in dpll_sync_group , iod_sync_group and fod_sync_group . The affected output clocks will be squelched for approximately the sync_dis_wait duration. Self-cleared immediately.
1	divider_sync	RW1S	0x0	Divider Synchronization. Write 1 to trigger synchronization of DPLL and output dividers in groups 0 and 1 as defined in dpll_sync_group , iod_sync_group and fod_sync_group . The affected output clocks will be squelched for approximately the sync_dis_wait duration. Self-cleared immediately.
0	apll_reinit	RW1S	0x0	APLL Reinitialization. Writing this bit to 1 re-starts the startup sequence from the VCO calibration step, including divider synchronization. Self-cleared immediately.

Table 48. SW_RESET - Software Reset Register

Bit Field	Field Name	Type	Default Value	Description
15:12	reserved	RO	0x0	Reserved.
11	out_rst	RW	0x0	Output Driver Reset. This bit resets and disables all output drivers. Reset assertion acts asynchronously and can cause output glitches or runt pulses. Reset assertion acts synchronously.
10	config_rst	RW	0x0	Configuration Reset. Writing this bit to 1 resets the digital logic including the registers and re-starts the startup sequence at the bias calibration, if the device is not already executing the startup sequence (during the startup sequence, writes to this bit are masked). This bit can be set to 1 by the first write in a static OTP/EEPROM User Configuration in order to revert the CSRs to their default values. The static CSEL pins are not latched. If written from a User Configuration, that same User Configuration is loaded during the startup sequence. If written from the serial port, the User Configuration to load during the startup sequence is determined by the originally latched CSEL pins, as on device power-up. If written from the serial port, the reset is triggered after the serial port write transaction completes. Self-cleared by the reset.
9	dig_sw_rst	RW	0x0	Digital Logic Software Reset. Writing this bit to 1 resets all digital logic including the registers and re-starts the startup sequence at the latching of the static CSEL pins. The reset is triggered after the serial port write transaction completes. Self-cleared by the reset.
8	otp_sw_rst	RW	0x0	Configuration Loader Software Reset. The configuration loader logic is held in reset while this bit is set to 1. This bit must not be set through the OTP/EEPROM configuration, otherwise the part will become unresponsive.

Table 48. SW_RESET - Software Reset Register (Cont.)

Bit Field	Field Name	Type	Default Value	Description
7	oc_ssc_sw_rst	RW	0x0	Over-Clock and Spread-Spectrum Engine Software Reset. The over-clocking engine and both spread-spectrum blocks are held in reset while this bit is set to 1.
6	tdc_apll_dig_sw_rst	RW	0x0	TDC APLL Digital Logic Reset. The TDC APLL digital logic is held in reset while this bit is set to 1. While re-programming the TDC APLL CSRs after device start-up, tdc_apll_dig_sw_rst must be set to 1.
5	dpll_sw_rst	RW	0x0	DPLL Software Reset. The DPLL is held in reset while this bit is set to 1.
4	clkmon4_sw_rst	RW	0x0	CLKMON4 Software Reset. The Clock Monitor 4 is held in reset while this bit is set to 1. While re-programming the refin LOS monitor CSRs after device start-up, clkmon4_sw_rst must be set to 1.
3	clkmon3_sw_rst	RW	0x0	CLKMON3 Software Reset. The Clock Monitor 3 is held in reset while this bit is set to 1. While re-programming the clkin3 LOS or Frequency monitor CSRs after device start-up, clkmon3_sw_rst must be set to 1.
2	clkmon2_sw_rst	RW	0x0	CLKMON2 Software Reset. The Clock Monitor 2 is held in reset while this bit is set to 1. While re-programming the clkin2 LOS or Frequency monitor CSRs after device start-up, clkmon2_sw_rst must be set to 1.
1	clkmon1_sw_rst	RW	0x0	CLKMON1 Software Reset. The Clock Monitor 1 is held in reset while this bit is set to 1. While re-programming the clkin1 LOS or Frequency monitor CSRs after device start-up, clkmon1_sw_rst must be set to 1.
0	clkmon0_sw_rst	RW	0x0	CLKMON0 Software Reset. The Clock Monitor 0 is held in reset while this bit is set to 1. While re-programming the clkin0 LOS or Frequency monitor CSRs after device start-up, clkmon0_sw_rst must be set to 1.

Table 49. CLOCK_GATE - Clock Gate Register

Bit Field	Field Name	Type	Default Value	Description
15:7	reserved	RO	0x0	Reserved.
6	dpll_cg	RW	0x0	DPLL Clock Gate. The DPLL system clock domain is clock gated while this bit is set to 1.
5	clkmon4_cg	RW	0x0	CLKMON4 Clock Gate. The Clock Monitor 4 is clock gated while this bit is set to 1.
4	clkmon3_cg	RW	0x0	CLKMON3 Clock Gate. The Clock Monitor 3 is clock gated while this bit is set to 1.
3	clkmon2_cg	RW	0x0	CLKMON2 Clock Gate. The Clock Monitor 2 is clock gated while this bit is set to 1.
2	clkmon1_cg	RW	0x0	CLKMON1 Clock Gate. The Clock Monitor 1 is clock gated while this bit is set to 1.

Table 49. CLOCK_GATE - Clock Gate Register (Cont.)

Bit Field	Field Name	Type	Default Value	Description
1	clkmon0_cg	RW	0x0	CLKMON0 Clock Gate. The Clock Monitor 0 is clock gated while this bit is set to 1.
0	otp_cg	RW	0x0	OTP Logic Clock Gate. The OTP interface logic is clock gated while this bit is set to 1. The user must set this bit to 0 to access the OTP. This bit must not be set through the OTP config, otherwise the part will become unresponsive.

Table 50. MISC_CNFG - Miscellaneous Configuration

Bit Field	Field Name	Type	Default Value	Description
15:11	Reserved	RW	0x20	Reserved.
10	losmon_cksel	RW	0x0	LOS Monitor Measuring Clock Select. Selects the measuring clock for the LOS monitor blocks. <ul style="list-style-type: none"> 0x0 = quad system clock (nominally 240 MHz) 0x1 = TDC ring oscillator frequency divided by 2 (nominally 432MHz).
9:8	fanout_buf_mode1	RW	0x0	CLKIN1 Fan-out Buffer Mode. Configures the device to operate in fan-out buffer mode from CLKIN1. Independent from the CLKIN0 fanout_buf_mode setting. <ul style="list-style-type: none"> 0x0 = CLKIN1 Fan-out buffer mode disabled or Manual fan-out buffer mode, output banks select their clock sources according to output_bank_src. fanout_clkmode1 reads back as 0. 0x1 = Automatic fan-out buffer mode. In banks where bank_fanout_mode is set to 2 (not available on Bank 6), output bank clock source selection is based on CLKIN1 LOS and is latched at the rising edge of PERST1#. The selected mode can be read in fanout_clkmode1. 0x3 = Manual fan-out buffer mode, CLKIN1 fans out to output clocks in banks where bank_fanout_mode is set to 2. fanout_clkmode1 reads back as 1.
7:6	out_startup	RW	0x0	Output Disable on Startup until PLL locks. Controls whether the clock output drivers are disabled until the APLL or DPLL locks during the startup sequence. When output_startup is not set to 0x2, individual output clocks may be configured to ignore APLL or DPLL lock status by setting their out_dis_group to 0x7. <ul style="list-style-type: none"> 0x0 = Clock output drivers are disabled until APLL lock asserts 0x1 = Clock output drivers are disabled until DPLL lock asserts 0x2 = Clock output drivers are not disabled by APLL or DPLL lock status 0x3 = Reserved
5	ssc_share	RW	0x0	Spectrum Spreading Phase Share. When two SSC engines have the same modulation frequency, setting this bit to 1 will align the phase of FOD1 SSC to FOD0 SSC. For restrictions on enabling the SSCs when ssc_share is set to 1, see ssc_en .

Table 50. MISC_CNFG - Miscellaneous Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
4:3	fanout_buf_mode	RW	0x0	<p>CLKIN0 Fan-out Buffer Mode. Configures the device to operate in fan-out buffer mode from CLKIN0. Independent from the CLKIN1 fanout_buf_mode1 setting.</p> <ul style="list-style-type: none"> 0x0 = CLKIN0 Fan-out buffer mode disabled or Manual fan-out buffer mode, output banks select their clock sources according to output_bank_src. fanout_clkmode reads back as 0. 0x1 = Automatic fan-out buffer mode. In banks where bank_fanout_mode is set to 1, output bank clock source selection is based on CLKIN0 LOS and is latched at the rising edge of PERST#. The selected mode can be read in fanout_clkmode. 0x3 = Manual fan-out buffer mode, CLKIN0 fans out to output clocks in banks where bank_fanout_mode is set to 1. fanout_clkmode reads back as 1.
2:0	reserved	RW	0x5	Reserved

Table 51. STARTUP_STS - Start-up Status

Bit Field	Field Name	Type	Default Value	Description
15:6	reserved	RO	0x0	Reserved.
5:4	gpio2_latched	RO	0x0	<p>GPIO2 Value Latched at Startup. Value of GPIO2 latched at startup (when PWRGD/PWRDN# first becomes high, if pwrnd_sel selects a PWRGD/PWRDN# pin).</p> <ul style="list-style-type: none"> 0x0 = Tri-level low 0x1 = Tri-level mid 0x2 = Unused 0x3 = Tri-level high
3:2	gpio1_latched	RO	0x0	<p>GPIO1 Value Latched at Startup. Value of GPIO1 latched at startup (when PWRGD/PWRDN# first becomes high, if pwrnd_sel selects a PWRGD/PWRDN# pin).</p> <ul style="list-style-type: none"> 0x0 = Tri-level low 0x1 = Tri-level mid 0x2 = Unused 0x3 = Tri-level high
1:0	gpio0_latched	RO	0x0	<p>GPIO0 Value Latched at Startup. Value of GPIO0 latched at startup (when PWRGD/PWRDN# first becomes high, if pwrnd_sel selects a PWRGD/PWRDN# pin).</p> <ul style="list-style-type: none"> 0x0 = Tri-level low 0x1 = Tri-level mid 0x2 = Unused 0x3 = Tri-level high

Table 52. DEVICE_STS - Device Status

Bit Field	Field Name	Type	Default Value	Description
15	fanout_clkmode1	RO	0x0	CLKIN1 Fanout Clock Mode. Set to 1 when CLKIN1 fanout buffer mode is enabled (fanout_buf_mode1 is not set to 0x0) and CLKIN1 is passed to the output clocks.
14	fanout_clkmode	RO	0x0	CLKIN0 Fanout Clock Mode. Set to 1 when CLKIN0 fanout buffer mode is enabled (fanout_buf_mode is not set to 0x0) and CLKIN0 is passed to the output clocks.
13:10	reserved	RO	0x0	Reserved.
9	device_ready	RO	0x0	Device Ready. Set to 1 when the configuration load (OTP and/or EEPROM) completes during the startup sequence. Cleared during a dynamic configuration load.
8	config_reg_ro	RO	0x0	Configuration Register Read-only Status. When this bit is 1, writes to configuration registers are ignored. Writes to bits of type RW1C, reg_lock_key and certain RW and RW1S bits are not ignored. Use the reg_lock_key field to set/clear this bit.
7	otp_detect_se	RO	0x0	OTP Loader Detected Single-Ended Mode. When high, indicates that the OTP loader detected that the OTP image is configured for single-ended mode.
6	eeeprom_config_valid	RO	0x0	Valid EEPROM User Configuration Loaded. Indicates that the user configuration in config_loaded was successfully loaded from EEPROM. Only valid when device_ready is 1.
5	otp_config_valid	RO	0x0	Valid OTP User Configuration Loaded. Indicates that the user configuration in config_loaded was successfully loaded from OTP. Only valid when device_ready is 1.
4:0	config_loaded	RO	0x0	User Configuration Loaded. Indicates the user configuration loaded from OTP/EEPROM on start-up or a dynamic configuration load. Note that on startup, the common configuration is always loaded prior to the user configuration. Only valid when device_ready is 1.

11.2 SSI Registers

Table 53. SPI_CNFG - SPI Configuration

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3	spi_del_out	RW	0x0	SDO Delay. <ul style="list-style-type: none"> ▪ 0x0 = SDO is driven on opposite SCLK edge than the sampling edge ▪ 0x1 = SDO is delayed one half cycle of SCLK
2	reserved	RO	0x0	Reserved.

Table 53. SPI_CNFG - SPI Configuration

Bit Field	Field Name	Type	Default Value	Description
1	spi_clk_sel	RW	0x0	SDI Sampling Edge Selection. <ul style="list-style-type: none"> 0x0 = SDI is sampled on rising SCLK edge 0x1 = SDI is sampled on falling SCLK edge
0	spi_3wire	RW	0x0	Select SPI 3 or 4-wire Mode. <ul style="list-style-type: none"> 0x0 = Normal 4-wire SPI. Data is received on the GPI/GPIO pin assigned as SDI, and transmitted on the GPIO pin assigned as SDO. 0x1 = 3-wire SPI. Data is received and transmitted on the GPIO pin assigned as SDIO.

Table 54. I2C_FLTR_CNFG - I2C Filter Configuration

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3:0	i2c_spike_ftr	RW	0x1	I2C/SMBus Digital Spike Filter Duration. Controls the duration of the digital spike filters on the SCL and SDA inputs, specified in number of system clock cycles (16.7ns). 0 disables filtering.

Table 55. I2C_TIMING_CNFG - I2C Timing Configuration

Bit Field	Field Name	Type	Default Value	Description
7:4	i2c_sda_high_hold	RW	0x2	I2C/SMBus Transmit One Bit Delay. Delays transmission of 1 value by this number of 133ns periods (8 system clock cycles).
3:0	i2c_sda_low_hold	RW	0x2	I2C/SMBus Transmit Zero Bit Delay. Delays transmission of 0 value by this number of 133ns periods (8 system clock cycles).

Table 56. I2C_ADDR_CNFG - I2C Address Configuration

Bit Field	Field Name	Type	Default Value	Description
7	reserved	RO	0x0	Reserved.
6:0	i2c_addr	RW	0x09	I2C Device Address. Sets I2C or SMBus device address that the SSI will acknowledge and accept accesses on.

Table 57. BYTE_CNT - Byte Count

Bit Field	Field Name	Type	Default Value	Description
7:6	reserved	RO	0x0	Reserved.
5:0	bc	RW	0x08	Byte Count. Defines how many bytes are in an SMBus block transaction. This register is modified by the SMBus interface logic when a block transaction is processed.

Table 58. SMB_CTL - SMBus Control

Bit Field	Field Name	Type	Default Value	Description
7	reserved	RO	0x0	Reserved.
6	smb_d_to_en	RW	0x1	SMBus Data Timeout Enable. Enables the SMBus data timeout check. When this bit is set to 1, the clock timeout must also be enabled (<code>smb_to_cnt</code> is not 0). When a data timeout is detected, the <code>smb_d_to</code> bit is set to 1.
5	smb_to_en	RW	0x1	Reserved.
4:0	smb_to_cnt	RW	0x19	SMBus Timeout Duration. Sets the clock and data timeout duration in milliseconds. When this field is set to 0, the clock timeout is disabled and <code>smb_d_to_en</code> must also be set to 0 to disable the data timeout. When a clock timeout is detected, the <code>smb_to</code> bit is set to 1.

Table 59. SSI_GLOBAL_CNFG - SSI Global Configuration

Bit Field	Field Name	Type	Default Value	Description
7:5	reserved	RO	0x0	Reserved.
4:3	sda_sdi_drv	RW	0x0	I2C/SMBus Drive Strength. Selects the output driver slew rate of the SDA_nCS and SCL_SCLK pins when the serial slave interface is configured for I2C/SMBus mode (higher settings means higher drive strength). This setting does not affect the internal timing. As an I2C/SMBus slave, the external I2C/SMBus master must provide the appropriate SCL frequency and other timing requirements according to the selected speed. <ul style="list-style-type: none"> ▪ 0x0 = 1.8V Standard mode (100 kHz) or 2.5V/3.3V standard (100kHz) and Fast mode (400kHz) ▪ 0x1 = 1.8V Fast mode (400 kHz) ▪ 0x2 = Reserved ▪ 0x3 = 1.8V/2.5V/3.3V Fast mode plus (1MHz)
2	ssi_addr_size	RW	0x0	SSI Address Size. Sets the number of bytes expected when providing a CSR address. Upper address bits are taken from the SSI's page register to create a full 32-bit CSR address. <ul style="list-style-type: none"> ▪ 0x0 = 1-byte address ▪ 0x1 = 2-byte address
1:0	ssi_enable	RW	0x1	SSI Mode. <ul style="list-style-type: none"> ▪ 0x0 = SSI is disabled ▪ 0x1 = SSI is in I2C mode ▪ 0x2 = SSI is in SPI mode ▪ 0x3 = SSI is in SMBus mode

Table 60. SSI_STS - Serial Port Status

Bit Field	Field Name	Type	Default Value	Description
7:2	reserved	RO	0x0	Reserved.
1	smb_d_to	RW1C	0x0	SMBus Data Timeout. Set when the SMBus interface detects a data timeout.
0	smb_to	RW1C	0x0	SMBus Clock Timeout. Set when the SMBus interface detects a clock timeout.

11.3 XO Register

Table 61. XO_CNFG - Crystal Configuration

Bit Field	Field Name	Type	Default Value	Description
31:30	reserved	RO	0x0	Reserved.
29	xo_ib_h_div_setb	RW	0x1	XO / Input Buffer High-Frequency Divider Set. When cleared, the XO/IB high frequency divider is held in set mode (bit is active low). Unless this divider is bypassed (<code>xo_ib_h_div = 0</code>), clearing this bit will halt the <code>refin_div</code> clock.
28:24	xo_ib_h_div	RW	0x0	XO / Input Buffer High-Frequency Divide Ratio. Divide by 2 to 31. Bypass if set to 0. 1 is reserved.
23:22	en_gain	RW	0x1	XO Gain Boosting Control. Selects the number of gain boosting amplifiers enabled during startup. <ul style="list-style-type: none"> 0x0 = Gain boosting amplifiers are disabled 0x1 = One parallel amplifier is enabled 0x2 = Two parallel amplifiers are enabled 0x3 = All three parallel amplifiers are enabled
21:16	en_cap_x2	RW	0x28	XO Capacitance at X2 Terminal. Controls the internal tuning capacitance applied at the XOUT_REFINb terminal integrated crystal. The capacitance rises monotonically in steps of 0.42pF from 0pF to 26.8pF as the control setting increases from 0x00 to the maximum of 0x3F. This must be set to 0 when <code>sel_ib_xo</code> is set to 0.
15	reserved	RO	0x0	Reserved.
14	xo_buff_dis	RW	0x0	XO Buffer Disable. Forces the XO buffer to the core logic to be disabled. This setting is intended for debug purposes only. <ul style="list-style-type: none"> 0x0 = XO buffer enable is controlled by the hardware. It is enabled during the startup sequence and remains enabled until the device is power cycled. 0x1 = XO buffer is disabled
13:8	en_cap_x1	RW	0x28	XO Capacitance at X1 Terminal. Controls the internal tuning capacitance applied at the XIN_REFIN terminal integrated crystal. The capacitance rises monotonically in steps of 0.42pF from 0pF to 26.8pF as the control setting increases from 0x00 to the maximum of 0x3F. This must be set to 0 when <code>sel_ib_xo</code> is set to 0.
7	reserved	RO	0x0	Reserved.
6:4	xo_res	RW	0x4	XO Resistor Configuration. Series resistance array control for limiting driving power level.
3	xo_ib_en_dc_bias	RW	0x0	Input Buffer Internal DC Bias Enable. When the input buffer clock input signal is AC-coupled external to the device, the internal DC bias voltage must be enabled. <ul style="list-style-type: none"> 0x0 = Internal DC bias is disabled (input signal is DC-coupled) 0x1 = Internal DC bias is enabled (input signal is AC-coupled)
2	sel_ib_xo	RW	0x1	XO / Input Buffer Select. Selects the mode of the XO / Input Buffer. <ul style="list-style-type: none"> 0x0 = Input buffer 0x1 = XO

Table 61. XO_CNFG - Crystal Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
1	xo_ib_cmos_sel	RW	0x0	Input Buffer CMOS / Differential Select. Configures the input buffer for single-ended CMOS or differential input signal. <ul style="list-style-type: none"> 0x0 = Differential input is selected 0x1 = CMOS input is selected
0	xo_ib_p_n_diff_sel	RW	0x1	Input Buffer PMOS / NMOS Select. Configures the input buffer according to the common mode voltage of the provided input signal. <ul style="list-style-type: none"> 0x0 = PMOS input pair is enabled (low common mode voltage) 0x1 = NMOS input pair is enabled (higher common mode voltage)

11.4 CLKIN Register

Table 62. CLKIN_CNFG - Clock Input Pad Configuration

Bit Field	Field Name	Type	Default Value	Description
15	h_div_setb	RW	0x1	Reference Clock High-Frequency Divider Set. When cleared, the corresponding reference clock high-frequency divider is held in set mode (bit is active low). Unless this divider is bypassed (<code>h_div = 0</code>), clearing this bit will halt the <code>clkln0_div/clkln2_div</code> clock.
14:10	h_div	RW	0x0	Reference Clock High-Frequency Divide Ratio. Divide by 2 to 31. Bypass if set to 0. 1 is reserved.
9	trim_term	RW	0x0	Reference Clock Input Pad Termination Trim. Selects the HCSL and LVDS termination resistance to ground / across the inputs for modes to: <ul style="list-style-type: none"> 0x0 = 50Ω / 100Ω 0x1 = 42.5Ω / 85Ω
8	en_lvpecl	RW	0x0	Reference Clock Input Pad LVPECL Termination Enable. Enables compatible termination when the reference clock input signal is LVPECL. <ul style="list-style-type: none"> 0x0 = LVPECL input termination is disabled 0x1 = LVPECL input termination is enabled
7	en_lvds	RW	0x0	Reference Clock Input Pad LVDS Termination Enable. Enables compatible termination when the reference clock input signal is LVDS. <ul style="list-style-type: none"> 0x0 = LVDS input termination is disabled 0x1 = LVDS input termination is enabled
6	en_hcsl	RW	0x0	Reference Clock Input Pad HCSL Termination Enable. Enables compatible termination when the reference clock input signal is HCSL. <ul style="list-style-type: none"> 0x0 = HCSL input termination is disabled 0x1 = HCSL input termination is enabled
5	en_cml	RW	0x0	Reference Clock Input Pad CML Termination Enable. Enables compatible termination when the reference clock input signal is CML. <ul style="list-style-type: none"> 0x0 = CML input termination is disabled 0x1 = CML input termination is enabled

Table 62. CLKIN_CNFG - Clock Input Pad Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
4	en_dc_bias	RW	0x0	Reference Clock Input Pad Internal DC Bias Enable. When the reference clock input signal is AC-coupled external to the device, the internal DC bias voltage must be enabled. <ul style="list-style-type: none"> 0x0 = Internal DC bias is disabled (input signal is DC-coupled) 0x1 = Internal DC bias is enabled (input signal is AC-coupled)
3	en_inbuff	RW	0x0	Reference Clock Input Pad Enable. The reference clock input pad must be enabled to allow the clock to be used by the device, and should be left disabled if unused. To fully power down the input pad, en_inbuff, en_dc_bias, en_cml, en_hcsl, en_lvds, and en_lvpecl all must be set to 0. <ul style="list-style-type: none"> 0x0 = Input pad is disabled 0x1 = Input pad is enabled
2:1	cmos_sel	RW	0x0	Reference Clock Input Pad CMOS / Differential Select. Configures the reference clock input pad for two single-ended CMOS or differential input signal. <ul style="list-style-type: none"> 0x0 = Differential input is selected 0x1 = Single CMOS input is selected on positive pin 0x2 = Single CMOS input is selected on negative pin 0x3 = Dual CMOS inputs are selected
0	p_n_diff_sel	RW	0x1	Reference Clock Input Pad PMOS / NMOS Select. Configures the reference clock input pad according to the common mode voltage of the provided input signal. <ul style="list-style-type: none"> 0x0 = PMOS input pair is enabled (low common mode voltage) 0x1 = NMOS input pair is enabled (higher common mode voltage)

11.5 REF Registers

Table 63. PREDIV_CNFG - Reference Clock Input Pre-divider Configuration

Bit Field	Field Name	Type	Default Value	Description
31:26	reserved	RO	0x0	Reserved.
25:24	ref_priority	RW	0x0	Reference Clock Priority. Sets the clock's priority for DPLL reference switching. If multiple clocks are set to the same priority level, they are prioritized from the lowest numbered (clkln0) to the highest numbered (clkln3). <ul style="list-style-type: none"> 0x0 = First priority 0x1 = Second priority 0x2 = Third priority 0x3 = Fourth priority
23	reserved	RO	0x0	Reserved.
22	id_setb	RW	0x1	Input Divider Set. When cleared, the corresponding input divider is held in set mode (bit is active low). Unless this divider is bypassed (id_byp_en = 1), clearing this bit will halt the corresponding reference clock.
21	reserved	RO	0x0	Reserved.

Table 63. PREDIV_CNFG - Reference Clock Input Pre-divider Configuration

Bit Field	Field Name	Type	Default Value	Description
20	id_byp_en	RW	0x1	Reference Clock Pre-divider Bypass. Allows the input divider to be bypassed and the reference clock input is passed directly to the DPLL. Bypass must be disabled if the reference clock frequency is greater than 33MHz. <ul style="list-style-type: none"> 0x0 = Divided reference clock is selected, divide ratio is id_ratio 0x1 = Reference clock is selected, effective divide ratio is 1
19:0	id_ratio	RW	0x0	Reference Clock Pre-divider Ratio. The reference clock frequency divided by this value must be no more than 33 MHz, and must be equal to the DPLL feedback clock frequency. The minimum divide value is 2. To divide by 1 (when the input reference clock frequency is no more than 33 MHz), bypass the divider by setting id_byp_en to 1. To support hitless switching between reference clocks, they must have the same nominal frequency after the pre-divider.

11.6 LOSMON Registers

Note that before reprogramming a Loss of Signal Monitor, the corresponding [clkmon0_sw_rst](#), [clkmon1_sw_rst](#), [clkmon2_sw_rst](#), [clkmon3_sw_rst](#), or [clkmon4_sw_rst](#) bit should be set. Once programming is done, it should then be cleared.

Table 64. LOSMON_WINDOW - LOS Monitor Window Configuration

Bit Field	Field Name	Type	Default Value	Description
15:12	reserved	RO	0x0	Reserved.
11:8	los_cnt_thresh	RW	0x0	Loss-of-Signal Counter Threshold. While the Loss-of-Signal counter (los_cnt) exceeds this threshold, the los_lmt_evt bit is set.
7	reserved	RO	0x0	Reserved.
6	ref_disable	RW	0x0	Reference Clock Selection Disable. Controls whether this reference clock can be selected as the DPLL reference clock. Not applicable for LOSMON4 (XO/IB monitor). <ul style="list-style-type: none"> 0x0 = Reference clock can be selected, subject to qualification by the Loss-of-Signal and Frequency monitors, and prioritization according to ref_priority 0x1 = Reference clock cannot be selected, ref_invalid set to 1
5	los_fail_mask	RW	0x0	LOS Monitor Failure Mask. Masks the LOS monitor status contribution to ref_invalid . <ul style="list-style-type: none"> 0x0 = los_sts contributes to ref_invalid 0x1 = los_sts does not contribute to ref_invalid
4:0	los_div_ratio	RW	0x0	LOS Monitor Divide Ratio. This divide ratio must be set such that the monitored clock nominal frequency divided by los_div_ratio is less than 1/8 of the measuring clock frequency (see losmon_clkssel) to achieve 25% accuracy. One period of the divided clock is the monitoring window duration. A value of 0 or 1 means divide by 1.

Table 65. LOSMON_NOMINAL - LOS Monitor Nominal Number Configuration

Bit Field	Field Name	Type	Default Value	Description
15:0	los_nom_num	RW	0x0	LOS Monitor Nominal Cycle Count. Sets the expected number of measuring clock periods (see losmon_clkssel) within one monitor window. Set to 0x0 to disable the LOS monitor. Disabling the monitor will cause the los_sts bit to be asserted, therefore the los_fail_mask bit should also be set when this field is written to 0x0.

Table 66. LOSMON_THRESH - LOS Monitor Threshold Configuration

Bit Field	Field Name	Type	Default Value	Description
31	reserved	RO	0x0	Reserved.
30:16	los_acc_margin	RW	0x0	LOS Monitor Accept Threshold. An accepted clock monitoring window occurs when the final monitor counter value is within los_nom_num ± los_acc_margin .
15	reserved	RO	0x0	Reserved.
14:0	los_rej_margin	RW	0x0	LOS Monitor Reject Threshold. A rejected clock monitoring window occurs when the final monitor counter value is outside of los_nom_num ± los_rej_margin .

Table 67. LOSMON_QUAL - LOS Monitor Qualify Counter Configuration

Bit Field	Field Name	Type	Default Value	Description
7:4	los_good_times	RW	0x4	LOS Monitor Qualification Count. If this number of consecutive accepted clock LOS monitoring windows occur without a rejected window, then the clock is qualified and los_sts is set to 0. A value of 0 is reserved.
3:0	los_fail_times	RW	0x4	LOS Monitor Disqualification Count. If this number of rejected clock LOS monitoring windows occur without qualifying the clock, then the clock is disqualified and los_sts is set to 1. A value of 0 is reserved.

Table 68. LOSMON_STS - LOS Monitor Status

Bit Field	Field Name	Type	Default Value	Description
7:2	reserved	RO	0x0	Reserved.
1	ref_invalid	RO	0x1	Reference Clock Invalid Status. Indicates whether this reference clock is currently considered to be invalid. This occurs if the clock is disqualified by one or more of the Loss-of-Signal and Frequency monitors, or ref_disable is set to 1. <ul style="list-style-type: none"> ▪ 0x0 = Clock is valid ▪ 0x1 = Clock is invalid
0	los_sts	RO	0x1	Loss-of-Signal Status. Current value of the LOS status from the clock monitor: <ul style="list-style-type: none"> ▪ 0x0 = Clock meets the monitoring criteria ▪ 0x1 = Loss-of-signal detected

Table 69. LOSMON_EVENT - LOS Monitor Event Status

Bit Field	Field Name	Type	Default Value	Description
7:2	reserved	RO	0x0	Reserved.
1	los_lmt_evt	RW1C	0x0	Loss-of-Signal Counter Threshold Exceeded Status. Set while the Loss-of-Signal counter (los_cnt) exceeds the threshold set in los_cnt_thresh . This bit cannot be cleared by software while the condition persists. <ul style="list-style-type: none"> 0x0 = Loss-of-signal counter has not exceeded the threshold since the last time the bit was cleared 0x1 = Loss-of-signal counter exceeded the threshold since the last time the bit was cleared
0	los_evt	RW1C	0x1	Loss-of-Signal Event Status. Set while the clock monitor asserts LOS. This bit cannot be cleared by software while the LOS condition persists. This bit is set when the block comes out of reset and needs to be cleared after proper programming. <ul style="list-style-type: none"> 0x0 = Loss-of-signal not detected since the last time the bit was cleared 0x1 = Loss-of-signal detected since the last time the bit was cleared

Table 70. LOSMON_CNT - LOS Monitor Count

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3:0	los_cnt	RW	0x0	Loss-of-Signal Failure Counter. This counter increments each time the clock monitor asserts LOS and saturates at 0xF. It is cleared by writing 0x0 to it, and can be preset by writing the desired value. Preset can be used either as a debug tool or to cause a threshold alarm to happen sooner. This register can only be written if the block is not clock gated (clkmon0_cg:clkmon4_cg) or held in reset (clkmon0_sw_rst:clkmon4_sw_rst).

11.7 FREQMON Registers

Note that before reprogramming a Frequency Monitor, the corresponding [clkmon0_sw_rst](#), [clkmon1_sw_rst](#), [clkmon2_sw_rst](#), or [clkmon3_sw_rst](#) bit should be set. Once programming is done, it should then be cleared.

Table 71. FREQMON_WINDOW - Frequency Monitor Window Configuration

Bit Field	Field Name	Type	Default Value	Description
31	freq_fail_mask	RW	0x0	Frequency Monitor Failure Mask. Masks the frequency monitor status contribution to ref_invalid . <ul style="list-style-type: none"> 0x0 = freq_sts contributes to ref_invalid 0x1 = freq_sts does not contribute to ref_invalid
30:28	reserved	RO	0x0	Reserved.
27:0	freq_div_ratio	RW	0x0	Frequency Monitor Divide Ratio. This divide ratio must be set such that the monitored clock nominal frequency divided by freq_div_ratio is as close as possible to 2.5Hz, creating a 0.4s monitoring window. A value of 0 or 1 means divide by 1.

Table 72. FREQMON_NOMINAL - Frequency Monitor Nominal Number Configuration

Bit Field	Field Name	Type	Default Value	Description
31:27	reserved	RO	0x0	Reserved.
26:0	freq_nom_num	RW	0x0	Frequency Monitor Nominal Cycle Count. Sets the expected number of clock periods of the TDC ring oscillator frequency divided by 4 (nominally 216MHz) within one monitor window. Set to 0x0 to disable the frequency monitor. Disabling the monitor will cause the <code>freq_sts</code> bit to be asserted, therefore the <code>freq_fail_mask</code> bit should also be set when this field is written to 0x0.

Table 73. FREQMON_THRESH - Frequency Monitor Threshold Configuration

Bit Field	Field Name	Type	Default Value	Description
63:59	reserved	RO	0x0	Reserved.
58:32	freq_acc_margin	RW	0x0	Frequency Monitor Accept Threshold. An accepted clock monitoring window occurs when the final monitor counter value is within <code>freq_nom_num ± freq_acc_margin</code> . One accepted window qualifies the clock and <code>freq_sts</code> is set to 0.
31:27	reserved	RO	0x0	Reserved.
26:0	freq_rej_margin	RW	0x0	Frequency Monitor Reject Threshold. A rejected clock monitoring window occurs when the final monitor counter value is outside of <code>freq_nom_num ± freq_rej_margin</code> . One rejected window disqualifies the clock and <code>freq_sts</code> is set to 1.

Table 74. FREQMON_STS - Frequency Monitor Status

Bit Field	Field Name	Type	Default Value	Description
7:1	reserved	RO	0x0	Reserved.
0	freq_sts	RO	0x1	Frequency Monitor Status. Current value of the qualification status from the frequency monitor: <ul style="list-style-type: none"> ▪ 0x0 = Clock meets the monitoring criteria, clock qualified ▪ 0x1 = Failure detected, clock disqualified

Table 75. FREQMON_EVENT - Frequency Monitor Event Status

Bit Field	Field Name	Type	Default Value	Description
7:1	reserved	RO	0x0	Reserved.
0	freq_evt	RW1C	0x1	Frequency Monitor Event Status. Set while the frequency monitor disqualifies the clock. This bit cannot be cleared by software while the disqualified condition persists. This bit is set when the block comes out of reset and needs to be cleared after proper programming. <ul style="list-style-type: none"> ▪ 0x0 = Frequency monitor has not disqualified the clock since the last time the bit was cleared ▪ 0x1 = Frequency monitor has disqualified the clock since the last time the bit was cleared

Table 76. FREQMON_OFFSET - Frequency Monitor Frequency Offset Status

Bit Field	Field Name	Type	Default Value	Description
31:28	reserved	RO	0x0	Reserved.
27:0	freq_offset_sts	RO	0x7FFFFFFF	Frequency Count Status. Cycle count measured by the frequency monitor, updated at the end of each monitoring window. The count saturates to 0x7FF_FFFF when it reaches $\text{freq_nom_num} \times 2$, which typically indicates that the monitored clock is not toggling, or is less than half the expected nominal frequency. It may be converted to ppm as follows: $\text{ppm offset} = 1e6 * (\text{freq_nom_num} - \text{freq_offset_sts}) / \text{freq_offset_sts}$

11.8 TDC APLL Registers

Note that before reprogramming the TDC APLL registers, the `tdc_apll_dig_sw_rst` bit should be set. Once programming is done, it should then be cleared.

Table 77. TDC_APLL_CNFG - TDC APLL Configuration

Bit Field	Field Name	Type	Default Value	Description
15	tdc_en	RW	0x0	TDC Enable. Controls whether the TDC is enabled. Must be enabled in Jitter Attenuator mode, when enabling a reference clock LOS monitor when <code>losmon_clkssel</code> is set to 1, and when enabling a reference clock frequency monitor.
14	reserved	RO	0x0	Reserved.
13:9	tdc_kp_coef	RW	0xF	TDC APLL Proportional Filter Coefficient (Kp). The filter output is $(\text{up/down}) * 2^{Kp} + \text{integrator}$.
8:4	tdc_ki_coef	RW	0x4	TDC APLL Integral Filter Coefficient (Ki). The integrator is $(\text{up/down}) * 2^{Ki} + \text{integrator}$.
3:2	tdc_fast_lock	RW	0x2	TDC APLL Fast Lock Mode. Controls the TDC APLL lock speed by increasing the effective Ki values while the input up/down is railed. <ul style="list-style-type: none"> ▪ 0x0 = Normal lock. Ki as programmed. ▪ 0x1 = Ki increased by 2 ▪ 0x2 = Ki increased by 4 ▪ 0x3 = Ki increased by 6
1:0	tdc_dac_sdm_order	RW	0x2	TDC APLL DAC SDM (Sigma Delta Modulator) Order. Selects the order of the SDM controlling the DAC for the TDC APLL. <ul style="list-style-type: none"> ▪ 0x0 = No accumulation ▪ 0x1 = 1st order ▪ 0x2 = 2nd order ▪ 0x3 = Reserved

Table 78. TDC_FB_DIV_FRAC - TDC APLL Feedback Divider Fraction Configuration

Bit Field	Field Name	Type	Default Value	Description
15:0	tdc_fb_div_frac	RW	0x2800	TDC APLL Feedback Divider Fraction. Fraction of the TDC APLL feedback divider. The fraction is calculated as follows: $\text{tdc_fb_div_frac} / 2^{16}$.

Table 79. TDC_FB_DIV_INT - TDC APLL Feedback Divider Integer Configuration

Bit Field	Field Name	Type	Default Value	Description
7:0	tdc_fb_div_int	RW	0x24	TDC APLL Feedback Divider Integer. Integer portion of the TDC APLL feedback divider.

Table 80. TDC_FB_SDM_CNFG - TDC APLL Feedback SDM Configuration

Bit Field	Field Name	Type	Default Value	Description
7	tdc_fb_sdm_en	RW	0x1	TDC APLL Feedback SDM Enable. Enables the SDM controlling the TDC APLL feedback divider. <ul style="list-style-type: none"> 0x0 = SDM disabled, constant integer division by tdc_fb_div_int 0x1 = SDM enabled, MMD mode
6:2	reserved	RO	0x0	Reserved.
1:0	tdc_fb_sdm_order	RW	0x1	TDC APLL Feedback SDM Order. Selects the order of the SDM controlling the feedback divider for the TDC APLL. <ul style="list-style-type: none"> 0x0 = Integer 0x1 = 1st order 0x2 = 2nd order 0x3 = 3rd order

Table 81. TDC_REF_DIV_CNFG - TDC APLL Reference Divider Configuration

Bit Field	Field Name	Type	Default Value	Description
7:3	reserved	RO	0x0	Reserved.
2:0	tdc_ref_div_cfg	RW	0x1	TDC Reference Divider Control. Controls the divide ratio of the TDC reference (either XO input or reference clock input, selected by apl_ref_sel). This field should be programmed such that the reference to the TDC APLL is between 10MHz and 30MHz. <ul style="list-style-type: none"> 0x0 = Bypass divider 0x1 = Divide by 2 0x2 = Divide by 4 0x3 = Divide by 8 0x4 = Divide by 16

Table 82. TDC_FILTER_STS - TDC APLL Filter Status

Bit Field	Field Name	Type	Default Value	Description
15:0	tdc_filter_status	RO	0x0	TDC Loop Filter Status. Provides the TDC loop filter output value. It is a signed 16-bit number.

11.9 APLL Registers

Table 83. APLL_FB_DIV_FRAC - APLL Feedback Divider Fraction Configuration

Bit Field	Field Name	Type	Default Value	Description
31:27	reserved	RO	0x0	Reserved.
26:0	apll_fb_div_frac	RW	0x0	APLL Feedback Divider Fraction. APLL feedback divider numerator value. The denominator is a fixed value of 2^{27} .

Table 84. APLL_FB_DIV_INT - APLL Feedback Divider Integer Configuration

Bit Field	Field Name	Type	Default Value	Description
15:10	reserved	RO	0x0	Reserved.
9:0	apll_fb_div_int	RW	0x69	APLL Feedback Divider Integer. APLL feedback divider integer value.

Table 85. APLL_FB_SDM_CNFG - APLL Feedback SDM Configuration

Bit Field	Field Name	Type	Default Value	Description
7:6	reserved	RO	0x0	Reserved.
5	apll_fb_dither_en	RW	0x0	APLL Feedback SDM Dither Enable. Dither enable for the SDM controlling the APLL feedback divider. After device startup, should only be changed while filter_update_dis is set to 1. <ul style="list-style-type: none"> ▪ 0x0 = Dither disabled ▪ 0x1 = Dither enabled
4	apll_fb_dither_ns	RW	0x0	APLL Feedback SDM Dither Noise Shaping. Dither noise shaping enable for the SDM controlling the APLL feedback divider. After device startup, should only be changed while filter_update_dis is set to 1. <ul style="list-style-type: none"> ▪ 0x0 = Dither not shaped ▪ 0x1 = Dither shaped
3:2	apll_fb_dither_gain	RW	0x0	APLL Feedback SDM Dither Gain. Gain control for the SDM controlling the APLL feedback divider. After device startup, should only be changed while filter_update_dis is set to 1. <ul style="list-style-type: none"> ▪ 0x0 = LSB ▪ 0x1 = 2*LSB ▪ 0x2 = 4*LSB ▪ 0x3 = 8*LSB
1:0	apll_fb_sdm_order	RW	0x3	APLL Feedback SDM Order. Selects the order of the SDM controlling the feedback divider for the APLL. When the feedback divide ratio is fractional, or to allow xtal_trim or write_freq to operate correctly, the order must be set greater than 0. After device startup, should only be changed while filter_update_dis is set to 1. <ul style="list-style-type: none"> ▪ 0x0 = Integer ▪ 0x1 = 1st order ▪ 0x2 = 2nd order ▪ 0x3 = 3rd order

Table 86. APLL_CNFG - APLL Configuration

Bit Field	Field Name	Type	Default Value	Description
7:2	reserved	RO	0x0	Reserved.
1	doubler_sel	RW	0x0	Frequency Doubler Select. Selects the frequency doubler to use when <code>en_doubler</code> is set to 1. <ul style="list-style-type: none"> ▪ 0x0 = PLL frequency doubler ▪ 0x1 = PFD frequency doubler
0	en_doubler	RW	0x1	Frequency Doubler Enable. Enables the frequency doubler selected by the <code>doubler_sel</code> bit. <ul style="list-style-type: none"> ▪ 0x0 = Disable ▪ 0x1 = Enable

Table 87. CP_CNFG - APLL Charge Pump Configuration

Bit Field	Field Name	Type	Default Value	Description
15:14	reserved	RO	0x0	Reserved.
13	cp_offset_en	RW	0x0	Charge Pump Offset Current Enable. Enables the charge pump offset current. The magnitude of the current is selected by <code>cnf_cp_offset</code> . <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
12	cp_offset_boost	RW	0x0	Charge Pump Offset Current Boost. Increases the magnitude of the offset current. <ul style="list-style-type: none"> ▪ 0x0 = Charge pump offset range from 0uA to 145uA ▪ 0x1 = Charge pump offset range from 0uA to 236uA
11:8	cnf_cp_offset	RW	0x3	Charge Pump Offset Current Setting. Controls the charge pump offset current when enabled by <code>cp_offset_en</code> . When <code>cp_offset_boost</code> is set to 0 / 1, the charge pump current is: <ul style="list-style-type: none"> ▪ 0x0 = 0uA / 0uA ▪ 0x1 = 10.3uA / 99.7uA ▪ 0x2 = 20.5uA / 118.7uA ▪ 0x3 = 30.6uA / 128.1uA ▪ 0x4 = 40.7uA / 137.5uA ▪ 0x5 = 50.5uA / 146.7uA ▪ 0x6 = 60.3uA / 155.9uA ▪ 0x7 = 70.0uA / 165.1uA ▪ 0x8 = 79.7uA / 174.2uA ▪ 0x9 = 89.2uA / 183.2uA ▪ 0xA = 98.7uA / 192.2uA ▪ 0xB = 108.1uA / 201.2uA ▪ 0xC = 117.5uA / 210.0uA ▪ 0xD = 126.7uA / 218.9uA ▪ 0xE = 135.9uA / 227.7uA ▪ 0xF = 145.0uA / 236.0uA
7	reserved	RO	0x0	Reserved.

Table 87. CP_CNFG - APLL Charge Pump Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
6:4	cnf_cp_up	RW	0x3	Charge Pump Up Current Setting. <ul style="list-style-type: none"> ▪ 0x0 = 250uA ▪ 0x1 = 500uA ▪ 0x2 = 750uA ▪ 0x3 = 1mA ▪ 0x4 = 1.25mA ▪ 0x5 = 1.5mA ▪ 0x6 = 1.75mA ▪ 0x7 = 2mA
3	reserved	RO	0x0	Reserved.
2:0	cnf_cp_dn	RW	0x3	Charge Pump Down Current Setting. <ul style="list-style-type: none"> ▪ 0x0 = 250uA ▪ 0x1 = 500uA ▪ 0x2 = 750uA ▪ 0x3 = 1mA ▪ 0x4 = 1.25mA ▪ 0x5 = 1.5mA ▪ 0x6 = 1.75mA ▪ 0x7 = 2mA

Table 88. LPF_CNFG - APLL Loop Filter Configuration

Bit Field	Field Name	Type	Default Value	Description
7	apll_vco_filter_byp	RW	0x0	VCO Current Source Filter Bypass. <ul style="list-style-type: none"> ▪ 0x0 = Filter active ▪ 0x1 = Filter bypassed
6:4	cnf_lpf_cp	RW	0x7	Loop Filter Pole Capacitor Setting. <ul style="list-style-type: none"> ▪ 0x0 = 11pF ▪ 0x1 = 14.7pF ▪ 0x2 = 18.4pF ▪ 0x3 = 22.1pF ▪ 0x4 = 25.8pF ▪ 0x5 = 29.5pF ▪ 0x6 = 33.2pF ▪ 0x7 = 36.9pF

Table 88. LPF_CNFG - APLL Loop Filter Configuration

Bit Field	Field Name	Type	Default Value	Description
3:0	cnf_lpf_res	RW	0x4	Loop Filter Resistor Setting. <ul style="list-style-type: none"> ▪ 0x0 = 0Ω ▪ 0x1 = 400Ω ▪ 0x2 = 800Ω ▪ 0x3 = 1.2kΩ ▪ 0x4 = 1.6kΩ ▪ 0x5 = 2kΩ ▪ 0x6 = 2.4kΩ ▪ 0x7 = 2.8kΩ ▪ 0x8 = 3.2kΩ ▪ 0x9 = 3.6kΩ ▪ 0xA = 4kΩ ▪ 0xB = 4.4kΩ ▪ 0xC = 4.8kΩ ▪ 0xD = 5.2kΩ ▪ 0xE = 5.6kΩ ▪ 0xF = 6kΩ

Table 89. LPF_3RD_CNFG - APLL Loop Filter 3rd Pole Configuration

Bit Field	Field Name	Type	Default Value	Description
7	byp_p3	RW	0x0	Bypass 3rd Pole. This bit can only be set to 1 when operating with an integer feedback divider. <ul style="list-style-type: none"> ▪ 0x0 = 3rd pole active ▪ 0x1 = 3rd pole bypassed
6:4	cnf_lpf_R3	RW	0x4	Loop Filter 3rd Pole Resistor Setting. <ul style="list-style-type: none"> ▪ 0x0 = 0Ω ▪ 0x1 = 800Ω ▪ 0x2 = 1.6kΩ ▪ 0x3 = 2.4kΩ ▪ 0x4 = 3.2kΩ ▪ 0x5 = 4kΩ ▪ 0x6 = 4.8kΩ ▪ 0x7 = 5.6kΩ
3	reserved	RO	0x0	Reserved.
2:0	cnf_lpf_C3	RW	0x4	Loop Filter 3rd Pole Capacitor Setting. <ul style="list-style-type: none"> ▪ 0x0 = 0pF ▪ 0x1 = 1pF ▪ 0x2 = 2pF ▪ 0x3 = 3pF ▪ 0x4 = 4pF ▪ 0x5 = 5pF ▪ 0x6 = 6pF ▪ 0x7 = 7pF

Table 90. APLL_REF_FB_CNFG - APLL Ref and Fb Clock Configuration

Bit Field	Field Name	Type	Default Value	Description
7:4	apll_lol_cnt_thresh	RW	0x0	APLL Loss-of-Lock Counter Threshold. While the APLL Loss-of-Lock counter (apll_lol_cnt) exceeds this threshold, the apll_lol_lmt bit is set.
3	apll_fb_div_dis	RW	0x0	APLL Feedback Divider Disable. Disables the APLL feedback divider. May be set to 1 to reduce power consumption when an external feedback clock is selected with apll_fb_sel . <ul style="list-style-type: none"> ▪ 0x0 = APLL feedback divider enabled ▪ 0x1 = APLL feedback divider disabled
2	apll_fb_sel	RW	0x0	APLL Feedback Clock Selection. Selects the APLL feedback clock source. When an external source is selected, the APLL feedback divider may be disabled by setting apll_fb_div_dis to 1. If the external clock is sourced from an output clock from the device, and out_startup is not set to 0x2, then that output clock's out_dis_group must be set to 0x7. <ul style="list-style-type: none"> ▪ 0x0 = Internal from APLL feedback MMD ▪ 0x1 = External from CLKIN0 – ZDB mode
1:0	apll_ref_sel	RW	0x0	APLL Reference Clock Selection. <ul style="list-style-type: none"> ▪ 0x0 = XIN_REFIN (refin_div) ▪ 0x1 = CLKIN0 (clkin0_div) ▪ 0x2 = CLKIN1 (clkin2_div) ▪ 0x3 = VSS

Table 91. BANK_MUX_CLK_EN - Bank Mux Clock Enable

Bit Field	Field Name	Type	Default Value	Description
31	en_refin_omux	RW	0x1	XO/IB Clock to Bank 5 Output Mux Enable. Enables fanout of the XO/IB clock to Bank 5 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
30	en_clkin2_bnk6	RW	0x1	Reference Clock 2 to Bank 6 Output Mux Enable. Enables fanout of reference clock 2 (CLKIN1) to Bank 6 output mux. When bank 6 is in automatic fanout buffer mode and bank_fanout_mode is set to 2, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
29	en_clkin2_bnk5	RW	0x1	Reference Clock 2 to Bank 5 Output Mux Enable. Enables fanout of reference clock 2 (CLKIN1) to Bank 5 output mux. When bank 5 is in automatic fanout buffer mode and bank_fanout_mode is set to 2, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled

Table 91. BANK_MUX_CLK_EN - Bank Mux Clock Enable (Cont.)

Bit Field	Field Name	Type	Default Value	Description
28	en_clkin2_bnk4	RW	0x1	Reference Clock 2 to Bank 4 Output Mux Enable. Enables fanout of reference clock 2 (CLKIN1) to Bank 4 output mux. When bank 4 is in automatic fanout buffer mode and bank_fanout_mode is set to 2, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
27	en_clkin0_bnk6	RW	0x1	Reference Clock 0 to Bank 6 Output Mux Enable. Enables fanout of reference clock 0 (CLKIN0) to Bank 6 output mux. When bank 6 is in automatic fanout buffer mode and bank_fanout_mode is set to 1, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
26	en_clkin0_bnk5	RW	0x1	Reference Clock 0 to Bank 5 Output Mux Enable. Enables fanout of reference clock 0 (CLKIN0) to Bank 5 output mux. When bank 5 is in automatic fanout buffer mode and bank_fanout_mode is set to 1, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
25	en_clkin0_bnk4	RW	0x1	Reference Clock 0 to Bank 4 Output Mux Enable. Enables fanout of reference clock 0 (CLKIN0) to Bank 4 output mux. When bank 4 is in automatic fanout buffer mode and bank_fanout_mode is set to 1, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
24	en_fod2_bnk6	RW	0x1	FOD 2 to Bank 6 Output Mux Enable. Enables fanout of FOD 2 output clock to Bank 6 output mux. When bank 6 is in automatic fanout buffer mode and output_bank_src is set to 6, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
23	en_fod2_bnk5	RW	0x1	FOD 2 to Bank 5 Output Mux Enable. Enables fanout of FOD 2 output clock to Bank 5 output mux. When bank 4 is in automatic fanout buffer mode and output_bank_src is set to 6, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
22	en_fod2_bnk4	RW	0x1	FOD 2 to Bank 4 Output Mux Enable. Enables fanout of FOD 2 output clock to Bank 4 output mux. When bank 4 is in automatic fanout buffer mode and output_bank_src is set to 6, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled

Table 91. BANK_MUX_CLK_EN - Bank Mux Clock Enable (Cont.)

Bit Field	Field Name	Type	Default Value	Description
21	en_fod2_bnk3	RW	0x1	FOD 2 to Bank 3 Output Mux Enable. Enables fanout of FOD 2 output clock to Bank 3 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
20	en_fod1_bnk6	RW	0x1	FOD 1 to Bank 6 Output Mux Enable. Enables fanout of FOD 1 output clock to Bank 6 output mux. When bank 6 is in automatic fanout buffer mode and output_bank_src is set to 5, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
19	en_fod1_bnk5	RW	0x1	FOD 1 to Bank 5 Output Mux Enable. Enables fanout of FOD 1 output clock to Bank 5 output mux. When bank 5 is in automatic fanout buffer mode and output_bank_src is set to 5, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
18	en_fod1_bnk4	RW	0x1	FOD 1 to Bank 4 Output Mux Enable. Enables fanout of FOD 1 output clock to Bank 4 output mux. When bank 4 is in automatic fanout buffer mode and output_bank_src is set to 5, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
17	en_fod1_bnk3	RW	0x1	FOD 1 to Bank 3 Output Mux Enable. Enables fanout of FOD 1 output clock to Bank 3 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
16	en_fod1_bnk2	RW	0x1	FOD 1 to Bank 2 Output Mux Enable. Enables fanout of FOD 1 output clock to Bank 2 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
15	en_fod1_bnk1	RW	0x1	FOD 1 to Bank 1 Output Mux Enable. Enables fanout of FOD 1 output clock to Bank 1 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
14	en_fod1_bnk0	RW	0x1	FOD 1 to Bank 0 Output Mux Enable. Enables fanout of FOD 1 output clock to Bank 0 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
13	en_fod0_bnk3	RW	0x1	FOD 0 to Bank 3 Output Mux Enable. Enables fanout of FOD 0 output clock to Bank 3 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled

Table 91. BANK_MUX_CLK_EN - Bank Mux Clock Enable (Cont.)

Bit Field	Field Name	Type	Default Value	Description
12	en_fod0_bnk2	RW	0x1	FOD 0 to Bank 2 Output Mux Enable. Enables fanout of FOD 0 output clock to Bank 2 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
11	en_fod0_bnk1	RW	0x1	FOD 0 to Bank 1 Output Mux Enable. Enables fanout of FOD 0 output clock to Bank 1 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
10	en_fod0_bnk0	RW	0x1	FOD 0 to Bank 0 Output Mux Enable. Enables fanout of FOD 0 output clock to Bank 0 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
9	en_iod3_bnk6	RW	0x1	IOD 3 to Bank 6 Output Mux Enable. Enables fanout of IOD 3 output clock to Bank 6 output mux. When bank 6 is in automatic fanout buffer mode and output_bank_src is set to 3, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
8	en_iod3_bnk5	RW	0x1	IOD 3 to Bank 5 Output Mux Enable. Enables fanout of IOD 3 output clock to Bank 5 output mux. When bank 5 is in automatic fanout buffer mode and output_bank_src is set to 3, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
7	en_iod2_bnk6	RW	0x1	IOD 2 to Bank 6 Output Mux Enable. Enables fanout of IOD 2 output clock to Bank 6 output mux. When bank 6 is in automatic fanout buffer mode and output_bank_src is set to 2, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
6	en_iod2_bnk5	RW	0x1	IOD 2 to Bank 5 Output Mux Enable. Enables fanout of IOD 2 output clock to Bank 5 output mux. When bank 5 is in automatic fanout buffer mode and output_bank_src is set to 2, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
5	en_iod2_bnk4	RW	0x1	IOD 2 to Bank 4 Output Mux Enable. Enables fanout of IOD 2 output clock to Bank 4 output mux. When bank 4 is in automatic fanout buffer mode and output_bank_src is set to 2, this bit is automatically controlled according to the output mux selection and cannot be written. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled

Table 91. BANK_MUX_CLK_EN - Bank Mux Clock Enable (Cont.)

Bit Field	Field Name	Type	Default Value	Description
4	en_iod1_bnk2	RW	0x1	IOD 1 to Bank 2 Output Mux Enable. Enables fanout of IOD 1 output clock to Bank 2 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
3	en_iod1_bnk1	RW	0x1	IOD 1 to Bank 1 Output Mux Enable. Enables fanout of IOD 1 output clock to Bank 1 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
2	en_iod1_bnk0	RW	0x1	IOD 1 to Bank 0 Output Mux Enable. Enables fanout of IOD 1 output clock to Bank 0 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
1	en_iod0_bnk1	RW	0x1	IOD 0 to Bank 1 Output Mux Enable. Enables fanout of IOD 0 output clock to Bank 1 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled
0	en_iod0_bnk0	RW	0x1	IOD 0 to Bank 0 Output Mux Enable. Enables fanout of IOD 0 output clock to Bank 0 output mux. <ul style="list-style-type: none"> ▪ 0x0 = Disabled ▪ 0x1 = Enabled

Table 92. APLL_STS - APLL Status

Bit Field	Field Name	Type	Default Value	Description
7:1	reserved	RO	0x0	Reserved.
0	apll_lock_sts	RO	0x0	APLL Lock Status. Set to 1 when the APLL is locked to its reference. <ul style="list-style-type: none"> ▪ 0x0 = Unlocked ▪ 0x1 = Locked

Table 93. APLL_EVENT - APLL Event Status

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3	apll_rail_high_evt	RW1C	0x0	APLL Rail High Event. Set to 1 when the APLL lock detects a rail high status. Once asserted, this bit will remain asserted until cleared by a write of '1' to this bit position.
2	apll_rail_low_evt	RW1C	0x0	APLL Rail Low Event. Set to 1 when the APLL lock detects a rail low status. Once asserted, this bit will remain asserted until cleared by a write of '1' to this bit position.

Table 93. APLL_EVENT - APLL Event Status

Bit Field	Field Name	Type	Default Value	Description
1	apll_lo_lmt	RW1C	0x0	<p>APLL Loss-of-Lock Counter Threshold Exceeded Status.</p> <p>Set while the APLL Loss-of-Lock counter (apll_lo_lmt) exceeds the threshold set in apll_lo_lmt_thresh. This bit cannot be cleared by software while the condition persists.</p> <ul style="list-style-type: none"> 0x0 = Loss-of-lock counter has not exceeded the threshold since the last time the bit was cleared 0x1 = Loss-of-lock counter exceeded the threshold since the last time the bit was cleared
0	apll_lo_l	RW1C	0x0	<p>APLL Loss-of-lock Event.</p> <p>Set to 1 when the APLL lock status transitions from locked to unlocked.</p>

Table 94. APLL_LOL_CNT - APLL Loss-of-Lock Counter

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3:0	apll_lo_lmt	RW	0x0	<p>APLL Loss-of-Lock Counter.</p> <p>This counter increments each time the APLL lock status de-asserts, and saturates at 0xF. It is cleared by writing it to 0x0, and may be preset by writing the desired value.</p>

Table 95. ANA_SPARE_CNFG - Analog Spare Configuration

Bit Field	Field Name	Type	Default Value	Description
15	regulator_dis	RW	0x0	<p>Regulator Disable.</p> <p>This field can disable the following regulators: LD_XO_IB, LDO_IB1, LDO_IB2, LDO_DIG, LDO_CP, LDO_VCO, DIG_LDO_DIV, DIG_LDO_FOD.</p> <ul style="list-style-type: none"> 0x0 = Regulators listed above are enabled. 0x1 = Regulators listed above are disabled.
14	ana_spare	RW	0x0	Reserved
13	sense_mode_sel	RW	0x0	<p>One-shot VDDO Sensing.</p> <p>Provides one-shot VDDO sensing for system clock gating function controlled by sysclk_gate_start and sysclk_gate_bypass. Should be left at 0x0.</p>
12	sysclk_gate_bypass	RW	0x0	<p>System Clock Gating Bypass.</p> <p>Setting this bit to 1 in the last byte of the COMMON OTP will bypass the above function in sysclk_gate_start or sysclk_gate_start may be set to 1.</p>
11	sysclk_gate_start	RW	0x0	<p>System Clock Start.</p> <p>Setting this bit to 1 in the last byte of the COMMON OTP config will allow the part to wait to load the USER OTP config until all VDDO that are not programmed as float_vddo* in DEVICE_CNFG are present.</p>

Table 95. ANA_SPARE_CNFG - Analog Spare Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
10	BNK6_pwrssel	RW	0x0	Bank6 Regulator Select. This bit controls whether to enable or bypass the 1.8V regulator in the output driver. <ul style="list-style-type: none"> 0x0 = Used when VDDO = 2.5V or 3.3V. Enables the 1.8V voltage regulator. 0x1 = Used when VDDO = 1.8V to bypass the 1.8V regulator.
9	BNK5_pwrssel	RW	0x0	Bank5 Regulator Select. This bit controls whether to enable or bypass the 1.8V regulator in the output driver. <ul style="list-style-type: none"> 0x0 = Used when VDDO = 2.5V or 3.3V. Enables the 1.8V voltage regulator. 0x1 = Used when VDDO = 1.8V to bypass the 1.8V regulator.
8	BNK4_pwrssel	RW	0x0	Bank4 Regulator Select. This bit controls whether to enable or bypass the 1.8V regulator in the output driver. <ul style="list-style-type: none"> 0x0 = Used when VDDO = 2.5V or 3.3V. Enables the 1.8V voltage regulator. 0x1 = Used when VDDO = 1.8V to bypass the 1.8V regulator.
7	BNK3_pwrssel	RW	0x0	Bank3 Regulator Select. This bit controls whether to enable or bypass the 1.8V regulator in the output driver. <ul style="list-style-type: none"> 0x0 = Used when VDDO = 2.5V or 3.3V. Enables the 1.8V voltage regulator. 0x1 = Used when VDDO = 1.8V to bypass the 1.8V regulator.
6	BNK2_pwrssel	RW	0x0	Bank2 Regulator Select. This bit controls whether to enable or bypass the 1.8V regulator in the output driver. <ul style="list-style-type: none"> 0x0 = Used when VDDO = 2.5V or 3.3V. Enables the 1.8V voltage regulator. 0x1 = Used when VDDO = 1.8V to bypass the 1.8V regulator.
5	BNK1_pwrssel	RW	0x0	Bank1 Regulator Select. This bit controls whether to enable or bypass the 1.8V regulator in the output driver. <ul style="list-style-type: none"> 0x0 = Used when VDDO = 2.5V or 3.3V. Enables the 1.8V voltage regulator. 0x1 = Used when VDDO = 1.8V to bypass the 1.8V regulator.
4	BNK0_pwrssel	RW	0x0	Bank0 Regulator Select. This bit controls whether to enable or bypass the 1.8V regulator in the output driver. <ul style="list-style-type: none"> 0x0 = Used when VDDO = 2.5V or 3.3V. Enables the 1.8V voltage regulator. 0x1 = Used when VDDO = 1.8V to bypass the 1.8V regulator.
3:0	bg_trim	RW	0x0	Bandgap Trim. PTAT current trimming for bandgap Vbg voltage.

Table 96. ANA_SPARE_STS - Analog Spare Status

Bit Field	Field Name	Type	Default Value	Description
15:0	ana_spare_sts	RO	0x00	Reserved

11.10 DPLL Registers

Table 97. DPLL_REF_FB_CNFG - DPLL Ref and Fb Clock Configuration

Bit Field	Field Name	Type	Default Value	Description
7:6	dpll_ref_sel_mode	RW	0x0	DPLL Reference Clock Selection Mode <ul style="list-style-type: none"> 0x0 = Manual mode, reference selection is based on the setting of dpll_ref_sel 0x1 = Manual mode, reference selection is based on GPI/GPIO pins 0x2 = Auto mode 0x3 = Auto mode
5:4	dpll_ref_sel	RW	0x0	DPLL Manual Reference Clock Selection <ul style="list-style-type: none"> 0x0 = CLKIN0 single-ended or CLKIN0/CLKIN0b differential (clkin0) 0x1 = CLKIN0b single-ended (clkin1) 0x2 = CLKIN1 single-ended or CLKIN1/CLKIN1b differential (clkin2) 0x3 = CLKIN1b single-ended (clkin3)
3:2	dpll_fb_sel	RW	0x1	DPLL Feedback Clock Selection Selects the DPLL feedback clock source. When an external source is selected, the DPLL feedback divider may be disabled by setting dpll_fb_div_dis to 1. If the external clock is sourced from an output clock from the device, and out_startup is not set to 0x2, then that output clock's out_dis_group must be set to 0x7. 0x0 = External from CLKIN1 single-ended or CLKIN1/CLKIN1b differential (clkin2) --- Zero Delay Buffer (ZDB) mode 0x1 = Internal from DPLL feedback MMD
1	dpll_revertive_en	RW	0x0	DPLL Revertive Reference Switch <ul style="list-style-type: none"> 0x0 = Non-revertive 0x1 = Revertive
0	dpll_hitless_en	RW	0x0	DPLL Hitless Reference Switch <ul style="list-style-type: none"> 0x0 = Hitless disabled 0x1 = Hitless enabled

Table 98. DPLL_MODE - DPLL Mode Configuration

Bit Field	Field Name	Type	Default Value	Description
7	bw_damp_sw	RW	0x1	Automatic Bandwidth/Damping Switching. Enables the DPLL to switch to the Locking Loop Filter bandwidth and damping settings when the DPLL is in the Acquire state while locking. Refer to dpll_lock_timer . <ul style="list-style-type: none"> 0x0 = Always use Normal Operation settings. 0x1 = Use Locking settings when the DPLL is in the Acquire state.
6	los_to_freerun	RW	0x0	Reference Loss-of-Signal to Freerun. Controls whether the DPLL enters Freerun or Holdover mode when the current reference clock is invalid. <ul style="list-style-type: none"> 0x0 = Holdover. 0x1 = Freerun.
5:4	dpll_sync_group	RW	0x0	DPLL Feedback Divider Sync Group. Sets the sync group that the DPLL feedback divider belongs to. <ul style="list-style-type: none"> 0x0 = Group0 0x1 = Group1 0x2 = None 0x3 = None

Table 98. DPLL_MODE - DPLL Mode Configuration

Bit Field	Field Name	Type	Default Value	Description
3	filter_update_dis	RW	0x0	DPLL Filter Update Disable. This bit must be set to 1 before reconfiguring any of the APLL feedback SDM register settings after startup, and then must be cleared after the reconfiguration finishes. These settings are: apll_fb_dither_en , apll_fb_dither_ns , apll_fb_dither_gain , and apll_fb_sdm_order .
2	dpll_en	RW	0x0	DPLL Enable. Controls whether the DPLL is enabled. <ul style="list-style-type: none"> 0x0 = Synthesizer/DCO mode. 0x1 = Jitter Attenuator mode. DPLL is enabled.
1:0	dpll_mode	RW	0x1	DPLL Mode Selection. Selects DPLL mode: <ul style="list-style-type: none"> 0x0 = Forces DPLL into Freerun state. 0x1 = Places the DPLL in Normal (automatic) mode. This is the normal setting for Jitter Attenuator mode. 0x2 = Forces DPLL into Holdover state. 0x3 = Places DPLL in Write Frequency mode. This is the normal setting in DCO mode.

Table 99. DPLL_DECIMATOR - DPLL Decimator Configuration

Bit Field	Field Name	Type	Default Value	Description
7	reserved	RO	0x0	Reserved.
6:4	dec_hitless_bw_shift	RW	0x3	Hitless Switch Decimator Bandwidth. Shift to set the decimator bandwidth during a hitless reference switch or holdover-normal switch for measuring the phase offset. If dpll_hitless_en is set to zero, this field is ignored. After device startup, should only be changed while tdc_en is set to 0.
3:0	dec_bw_shift	RW	0x6	Decimator Bandwidth. Shift to set the decimator bandwidth. 0 puts the decimator in feed-through (infinite bandwidth). After device startup, should only be changed while tdc_en is set to 0.

Table 100. DPLL_XTAL_OFFSET - DPLL Crystal Trim Offset Configuration

Bit Field	Field Name	Type	Default Value	Description
7:0	xtal_trim	RW	0x0	Crystal Trim Offset. Crystal fractional frequency offset compensation. This is an 8-bit 2's complement value. Resolution = $2^{-20} \approx 1$ ppm, Range = $\pm 2^{-13} \approx \pm 122$ ppm. apll_fb_sdm_order must be set to a value greater than 0 for xtal_trim to operate correctly.

Table 101. HOLDOVER_CNFG - Holdover Configuration

Bit Field	Field Name	Type	Default Value	Description
15:11	holdover_bw_shift	RW	0x7	Holdover Filter Bandwidth Shift. Coarse control of the holdover bandwidth. A value of zero disables the holdover filter (infinite bandwidth). The valid range is 0 to 20. Values larger than 20 are limited internally to 20.
10:8	holdover_bw_mult	RW	0x0	Holdover Filter Bandwidth Multiplier. Fine control of the holdover filter bandwidth. A value of zero disables the holdover filter (infinite bandwidth), which is also the default setting.
7:4	holdover_history	RW	0x0	Holdover History. <ul style="list-style-type: none"> ▪ 0x0 = Instantaneous (no history) ▪ 0x1 = 1 second ▪ 0x2 = 2 seconds ▪ 0x3 = 3 seconds ▪ 0x4 = 4 seconds ▪ 0x5 = 5 seconds ▪ 0x6 = 6 seconds ▪ 0x7 = 7 seconds ▪ 0x8 = 8 seconds ▪ 0x9 = 9 seconds ▪ 0xA = 10 seconds
3:0	dpll_lof_cnt_thresh	RW	0x0	DPLL Loss-of-Lock Counter Threshold. While the DPLL Loss-of-Lock counter (<i>dpll_lof_cnt</i>) exceeds this threshold, the <i>dpll_lof_lmt</i> bit is set.

Table 102. DPLL_BANDWIDTH - DPLL Bandwidth Configuration

Bit Field	Field Name	Type	Default Value	Description
15:11	acquire_bw_shift	RW	0xE	Acquire Loop Filter Bandwidth Shift. Coarse control of the DPLL loop filter bandwidth in the Acquire state while locking to the input clock. Default bandwidth = 1023Hz.
10:8	acquire_bw_mult	RW	0x0	Acquire Loop Filter Bandwidth Multiplier. Fine control of the DPLL loop filter bandwidth in the Acquire state while locking to the input clock. Default bandwidth = 1023Hz
7:3	normal_bw_shift	RW	0xB	Normal Operation Loop Filter Bandwidth Shift. Coarse control of the DPLL loop filter bandwidth in the Normal state when locked to the input clock. Default bandwidth = 127Hz.
2:0	normal_bw_mult	RW	0x0	Normal Operation Loop Filter Bandwidth Multiplier. Fine control of the DPLL loop filter bandwidth in the Normal state when locked to the input clock. Default bandwidth = 127Hz.

Table 103. DPLL_DAMPING - DPLL Damping Configuration

Bit Field	Field Name	Type	Default Value	Description
15:14	reserved	RO	0x0	Reserved.
13:11	acquire_damping_shift	RW	0x5	Acquire Loop Filter Damping Shift. Coarse control of the DPLL loop filter damping in the Acquire state while locking to the input clock. Default damping causes 1.1 dB peaking in the frequency domain jitter transfer function.

Table 103. DPLL_DAMPING - DPLL Damping Configuration

Bit Field	Field Name	Type	Default Value	Description
10:8	acquire_damping_mult	RW	0x1	Acquire Loop Filter Damping Multiplier. Fine control of the DPLL loop filter damping in the Acquire state while locking to the input clock. Default damping causes 1.1 dB peaking in the frequency domain jitter transfer function.
7:6	reserved	RO	0x0	Reserved.
5:3	normal_damping_shift	RW	0x0	Normal Operation Loop Filter Damping Shift. Coarse control of the DPLL loop filter damping in the Normal state when locked to the input clock. Default damping causes 0.1 dB peaking in the frequency domain jitter transfer function.
2:0	normal_damping_mult	RW	0x0	Normal Operation Loop Filter Damping Multiplier. Fine control of the DPLL loop filter damping in the Normal state when locked to the input clock. Default damping causes 0.1 dB peaking in the frequency domain jitter transfer function.

Table 104. DPLL_PHASE_SLOPE_LIMIT - DPLL Phase Slope Limit Configuration

Bit Field	Field Name	Type	Default Value	Description
31:29	reserved	RO	0x0	Reserved.
28:0	phase_slope_limit	RW	0x1FFFFFFF	Phase Slope Limit. Control of the phase slope limit of the output clocks. This represents the maximum instant relative frequency change of the output clock. This is an unsigned unitless number although it is often expressed as $\mu\text{s/s}$ or ns/s . It is recommended to program a value that is approx. 10% smaller than the required limit to leave some room for the integrator to adjust to frequency offsets. The resolution of 1 LSB is $2^{-35} = 2.91\text{e-}11 = 29.1 \text{ ps/s}$.

Table 105. DPLL_PHASE_OFFSET - DPLL Phase Offset Configuration

Bit Field	Field Name	Type	Default Value	Description
31:30	reserved	RO	0x0	Reserved.
29:0	phase_offset	RW	0x0	Phase Offset. Manually sets the phase offset between the reference and feedback clocks. This is a 30-bit 2's complement value. The resolution is the TDC resolution / 8 ($\approx 2.3 \text{ ps}$) and the range is $\approx \pm 1.26 \text{ ms}$. This allows all outputs to be adjusted in terms of their phase relationship to the input. All outputs move together using this precision setting. This field is not used when hitless switching is enabled. This register is atomic. When the most significant byte (bits [29:24]) is written, the new value is applied to the APLL.

Table 106. DPLL_WRITE_FREQ - DPLL Write Frequency Configuration

Bit Field	Field Name	Type	Default Value	Description
31:29	reserved	RO	0x0	Reserved.
28:0	write_freq	RW	0x0	<p>Write Frequency.</p> <p>Frequency control word for synthesizer/DCO mode. This is a 29-bit 2's complement value. The units are $2^{-40} * 1e6$ [ppm]. The maximum setting is ± 243ppm ($\pm 267,386,880$).</p> <p>apll_fb_sdm_order must be set to a value greater than 0 for write_freq to operate correctly.</p> <p>An update to this multi-byte register will only take effect when the most significant byte (bits [28:24]) are written, the new value is applied to the DPLL.</p>

Table 107. DPLL_FB_DIV_NUM - DPLL Feedback Divider Numerator Configuration

Bit Field	Field Name	Type	Default Value	Description
63:48	reserved	RO	0x0	Reserved.
47:0	fb_div_num	RW	0x0	<p>Feedback Divider Numerator.</p> <p>DPLL feedback divide numerator value. Refer to fb_div_int for details.</p> <p><i>Note:</i> This register field is part of an atomic group consisting of fb_div_num, fb_div_den and fb_div_int. When the most significant byte (bits [47:40]) of fb_div_num or fb_div_den, or the most significant byte (bits 20:16) of fb_div_int is written, the value of all these fields are applied to the DPLL.</p>

Table 108. DPLL_FB_DIV_DEN - DPLL Feedback Divider Denominator Configuration

Bit Field	Field Name	Type	Default Value	Description
63:48	reserved	RO	0x0	Reserved.
47:0	fb_div_den	RW	0x800000	<p>Feedback Divider Denominator.</p> <p>DPLL feedback divide denominator value. Refer to fb_div_int for details.</p> <p><i>Note:</i> The MSB (bit 47) of fb_div_den must be a 1. For an arbitrary fraction M/N, this may be accomplished by left shifting the denominator value N until the MSB becomes 1, and then left shifting the numerator value M by the same number of bits to obtain the fb_div_num value.</p> <p>This register field is part of an atomic group consisting of fb_div_num, fb_div_den and fb_div_int. When the most significant byte (bits [47:40]) of fb_div_num or fb_div_den, or the most significant byte (bits 20:16) of fb_div_int is written, the value of all these fields are applied to the DPLL.</p>

Table 109. DPLL_FB_DIV_INT - DPLL Feedback Divider Integer Configuration

Bit Field	Field Name	Type	Default Value	Description
31:21	reserved	RO	0x0	Reserved.
20:0	fb_div_int	RW	0x190	<p>DPLL Feedback Clock Divider Integer.</p> <p>DPLL feedback divide integer value. The DPLL feedback clock frequency must be no more than 33 MHz, and must be equal to the frequency of the reference clock divided by <i>id_ratio</i>, or equal to the reference clock when the input divider is bypassed by <i>id_byp_en</i>.</p> <p>This register field is part of an atomic group consisting of <i>fb_div_num</i>, <i>fb_div_den</i> and <i>fb_div_int</i>. When the most significant byte (bits [47:40]) of <i>fb_div_num</i> or <i>fb_div_den</i>, or the most significant byte (bits [20:16]) of <i>fb_div_int</i> is written, the value of all these fields are applied to the DPLL.</p>

Table 110. DPLL_FB_CORR - DPLL Feedback Correction Configuration

Bit Field	Field Name	Type	Default Value	Description
15	dpll_fb_div_dis	RW	0x0	<p>DPLL Feedback Divider Disable.</p> <p>Disables the DPLL feedback divider. May be set to 1 to reduce power consumption when an external feedback clock is selected with <i>dpll_fb_sel</i>. The feedback divider is automatically disabled when <i>dpll_en</i> is set to 0.</p> <ul style="list-style-type: none"> ▪ 0x0 = DPLL feedback divider enabled if <i>dpll_en</i> is set to 1 ▪ 0x1 = DPLL feedback divider disabled
14:10	reserved	RO	0x0	Reserved.
9	fine_rev	RW	0x0	<p>TDC Fine Timestamp Bit Reversal.</p> <p>Selects the bit ordering of the fine timestamp signals from the TDC analog to digital. This setting is intended for debug purposes only.</p> <ul style="list-style-type: none"> ▪ 0x0 = Analog 30:0 maps to digital 30:0 ▪ 0x1 = Analog 0:30 maps to digital 30:0
8:7	pec_delay	RW	0x0	<p>PEC Delay.</p> <p>Phase error correction delay. Intended for debug purposes only. After device startup, should only be changed while <i>tdc_en</i> is set to 0.</p> <ul style="list-style-type: none"> ▪ 0x0 = sdm error no delay ▪ 0x1 = sdm error delay one cycle ▪ 0x2 = Same as 0x0 ▪ 0x3 = Same as 0x0
6:0	pec_corr_mult	RW	0x0	<p>Feedback Correction Multiplier.</p> <p>Multiplier to get the FB SDM remainder bits on the same resolution as the TDC phase detector bits. (resolution \approx18.7 ps if the TDC APLL runs at 864MHz). After device startup, should only be changed while <i>tdc_en</i> is set to 0.</p>

Table 111. DPLL_LOCK - DPLL Lock Configuration

Bit Field	Field Name	Type	Default Value	Description
31:16	dpll_lock_timer	RW	0x00FF	DPLL Lock Timer. Specifies the time interval during which the absolute value of the phase detector error must remain below the DPLL lock threshold (dpll_lock_thresh) in order to declare lock. The DPLL switches from the Acquire state to the Normal state when the threshold has been met for half of this time interval. If enabled by bw_damp_sw , the loop filter bandwidth and damping settings revert at this time from the Acquire settings to the Normal settings. When the threshold has been met again for half of this time interval, the DPLL declares lock. The minimum value is 2. The units are ms.
15:0	dpll_lock_thresh	RW	0x0155	DPLL Lock Threshold. Specifies the threshold that the absolute value of the phase detector error must remain below during the DPLL lock timer (dpll_lock_timer) in order to declare lock. The units are 8 * TDC resolution.

Table 112. DPLL_STS - DPLL Status

Bit Field	Field Name	Type	Default Value	Description
7	reserved	RO	0x0	Reserved.
6:4	dpll_state_sts	RO	0x0	DPLL Frequency Switch Mode (FSM) State. Decode as follows: <ul style="list-style-type: none"> ▪ 0x0 = Freerun ▪ 0x1 = Normal / locked ▪ 0x2 = Holdover ▪ 0x3 = Write frequency ▪ 0x4 = Acquire ▪ 0x5 = Hitless switch
3	reserved	RO	0x0	Reserved.
2:1	dpll_ref_sel_sts	RO	0x0	DPLL Reference Clock Selection Status. Indicates the reference clock selected by the DPLL. <ul style="list-style-type: none"> ▪ 0x0 = clkin0 ▪ 0x1 = clkin1 ▪ 0x2 = clkin2 ▪ 0x3 = clkin3
0	dpll_lock_sts	RO	0x0	DPLL Lock Status. Indicates the DPLL lock status: <ul style="list-style-type: none"> ▪ 0x0 = Unlocked ▪ 0x1 = Locked

Table 113. DPLL_EVENT - DPLL Event Status

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3	dpll_state_ch	RW1C	0x0	DPLL State Change Event. Set to 1 when the DPLL state machine changes state. Once asserted, this bit will remain asserted until cleared by a write of 1 to this bit position.

Table 113. DPLL_EVENT - DPLL Event Status

Bit Field	Field Name	Type	Default Value	Description
2	dpll_holdover	RW1C	0x0	DPLL Holdover Event. Set to 1 when the DPLL state machine enters the holdover state. Once asserted, this bit will remain asserted until cleared by a write of 1 to this bit position.
1	dpll_lol_lmt	RW1C	0x0	DPLL Loss-of-Lock Counter Threshold Exceeded Status. Set while the DPLL Loss-of-Lock counter (dpll_lol_cnt) exceeds the threshold set in dpll_lol_cnt_thresh . This bit cannot be cleared by software while the condition persists. <ul style="list-style-type: none"> 0x0 = Loss-of-lock counter has not exceeded the threshold since the last time the bit was cleared 0x1 = Loss-of-lock counter exceeded the threshold since the last time the bit was cleared
0	dpll_lol	RW1C	0x0	DPLL Loss-of-lock Event. Set to 1 when the DPLL lock status transitions from locked to unlocked. Once asserted, this bit will remain asserted until cleared by a write of 1 to this bit position.

Table 114. DPLL_LOL_CNT - DPLL Loss-of-Lock Counter

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3:0	dpll_lol_cnt	RW	0x0	DPLL Loss-of-Lock Counter. This counter increments each time the DPLL lock status de-asserts, and saturates at 0xF. It is cleared by writing it to 0x0, and may be preset by writing the desired value. This register can only be written if the block is not clock gated (dpll_cg) or held in reset (dpll_sw_rst).

Table 115. DPLL_FILTER_STS - DPLL Filter Status

Bit Field	Field Name	Type	Default Value	Description
31:29	reserved	RO	0x0	Reserved.
28:0	filter_status	RO	0x0	DPLL Filter Status. Provides the integrator value from the filter.

Table 116. DPLL_PHASE_STS - DPLL Phase Status

Bit Field	Field Name	Type	Default Value	Description
31:30	reserved	RO	0x0	Reserved.
29:0	phase_status	RO	0x0	DPLL Phase Status. Provides the phase data from the decimator. This is a 32-bit 2's complement value. The units are the TDC APLL VCO period divided by 62*8 (2.333ps for the nominal 864MHz).

11.11 IOD Registers

Table 117. IOD_INT_CNFG - IOD Integer Ratio Configuration

Bit Field	Field Name	Type	Default Value	Description
31	iod_pd	RW	0x0	Integer Output Divider Power Down. Powers down the integer output divider by turning off the regulator. If this bit is set to 1, iod_rst must also be set to 1. When clearing this bit, iod_rst must remain set and then it can be cleared afterwards. <ul style="list-style-type: none"> 0x0 = Divider is powered up 0x1 = Divider is powered down
30	iod_dis	RW	0x0	Integer Output Divider Disable. Disables the integer output divider. If this bit is set to 1, iod_rst must also be set to 1. When clearing this bit, iod_rst must remain set and then it can be cleared afterwards. <ul style="list-style-type: none"> 0x0 = Divider enabled 0x1 = Divider disabled
29	iod_rst	RW	0x0	Integer Output Divider Reset. Resets the integer output divider. <ul style="list-style-type: none"> 0x0 = Divider reset de-asserted 0x1 = Divider reset asserted
28	iod_squelch	RW	0x0	Integer Output Divider Squelch. Synchronously squelches and releases the IOD output clock. <ul style="list-style-type: none"> 0x0 = IOD output is not squelched 0x1 = IOD output is squelched
27:25	reserved	RO	0x0	Reserved.
24:0	iod_int	RW	0x64	Integer Output Divider Ratio Integer output divider ratio. The minimum value is 14. This register is atomic. When the most significant byte (bit [24]) is written, the new value is applied to the IOD.

Table 118. IOD_PHASE_CNFG - IOD Phase Configuration

Bit Field	Field Name	Type	Default Value	Description
15	iod_ph_adj_now	RW1S	0x0	Integer Output Divider Phase Adjustment Now. When this bit is written from 0 to 1, the phase adjustment in iod_phase is applied to the divider. This bit self-clears when the adjust completes.
14	iod_ph_adj_post_sync	RW	0x0	Integer Output Divider Phase Adjustment After Synchronization. When this bit is set to 1, the phase adjustment in iod_phase is applied to the divider whenever the divider is synchronized.
13:11	reserved	RO	0x0	Reserved.

Table 118. IOD_PHASE_CNFG - IOD Phase Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
10:9	iod_sync_group	RW	0x0	Integer Output Divider Sync Group. Sets the sync group that this divider belongs to <ul style="list-style-type: none"> 0x0 = Group0 0x1 = Group1 0x2 = None 0x3 = None
8:0	iod_phase	RW	0x0	Integer Output Divider Phase Configuration. Signed 2's complementary value sets the phase, a positive value means lag from 0 phase, a negative value means lead from 0 phase, in steps of one VCO period. The available range is $\pm 0\sim 255$ steps (approximately $\pm 0\sim 20$ ns). In SYSREF mode (sysref_mode is set to 1), the range is also limited to $\pm (\text{iod_int}/2 - 5)$ steps. This register is atomic. When the most significant byte (bit [8]) is written, the new value is applied to the IOD according to iod_ph_adj_now and iod_ph_adj_post_sync .

Table 119. SYSREF_CNFG - SYSREF Configuration

Bit Field	Field Name	Type	Default Value	Description
15:14	reserved	RO	0x0	Reserved.
13:12	sysref_sync_src_sel	RW	0x0	SYSREF Synchronization Source Select. Selects the source SYSREF instance used to trigger this SYSREF instance. If multiple SYSREF instances are intended to be aligned (part of a SYSREF group), they all must select the same source instance. If a SYSREF instance is independent, this field should be set to its own instance number. The default setting is for SYSREF instance zero to trigger all SYSREF instances. To be used as a synchronization source, a SYSREF instance must: <ul style="list-style-type: none"> Be enabled and not held in reset (iod_pd, iod_dis and iod_rst are set to 0). Select itself if selected by other SYSREF instances
11	reserved	RO	0x0	Reserved.
10	sysref_src	RW	0x0	SYSREF Trigger Source. Selects the source for the SYSREF trigger. <ul style="list-style-type: none"> 0x0 = Trigger from SYSREF_IN 0x1 = Trigger from register sysref_trig
9	sysref_trig	RW	0x0	SYSREF Trigger Signal. Software SYSREF trigger. Writing this bit from 0 to 1 triggers SYSREF if sysref_src selects it.

Table 119. SYSREF_CNFG - SYSREF Configuration

Bit Field	Field Name	Type	Default Value	Description
8	sysref_mode	RW	0x0	<p>SYSREF Modes.</p> <p>This bit defines whether the IOD operates normally (outputting a clock continuously), or whether it operates in SYSREF mode (outputting a burst of clocks after receiving a trigger). This bit must be set to 0 to output the clock from the IOD even if SYSREF functionality is not required.</p> <ul style="list-style-type: none"> 0x0 = Normal mode, continuous output clock 0x1 = SYSREF mode, pulsed output clock (see sysref_pulse_cnt)
7:0	sysref_pulse_cnt	RW	0x0	<p>SYSREF Pulse Counter Configuration.</p> <p>Sets the number of sysref clocks to output after receiving a trigger. The number of clocks is one more than the value of this field, so the possible number of clocks is 1 to 256.</p>

11.12 FOD Registers

Table 120. FOD_INT_CNFG - FOD Integer Configuration

Bit Field	Field Name	Type	Default Value	Description
63	fod_pd	RW	0x0	<p>Fractional Output Divider Power Down.</p> <p>Powers down the fractional output divider by turning off the regulator. If this bit is set to 1, fod_rst must also be set to 1. When clearing this bit, fod_rst must remain set and then it can be cleared afterwards.</p> <ul style="list-style-type: none"> 0x0 = Divider is powered up 0x1 = Divider is powered down
62	fod_dis	RW	0x0	<p>Fractional Output Divider Disable.</p> <p>Disables the fractional output divider. If this bit is set to 1, fod_rst must also be set to 1. When clearing this bit, fod_rst must remain set and then it can be cleared afterwards.</p> <ul style="list-style-type: none"> 0x0 = Divider enabled 0x1 = Divider disabled
61	fod_rst	RW	0x0	<p>Fractional Output Divider Reset.</p> <p>Resets the fractional output divider.</p> <ul style="list-style-type: none"> 0x0 = Divider reset de-asserted 0x1 = Divider reset asserted
60	fod_acc_reset	RW	0x0	<p>Fractional Output Divider Accumulator Reset.</p> <p>Resets the FOD SDM accumulator.</p> <ul style="list-style-type: none"> 0x0 = Accumulator reset de-asserted 0x1 = Accumulator reset asserted
59:26	fod_frac	RW	0x0	<p>Fractional Output Divider Ratio Fraction Portion.</p> <p>Denominator is fixed to 2^{34}.</p> <p>This register field is part of an atomic group consisting of fod_1st_int and fod_frac. When the most significant byte (bits [33:30]) of fod_frac is written, the value of all these fields are applied to the FOD.</p> <p><i>Note:</i> When an FOD has spread-spectrum fod_frac[5:0] <i>must</i> be set to 0x0.</p>

Table 120. FOD_INT_CNFG - FOD Integer Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
25:9	fod_2nd_int	RW	0x0	Fractional Output Divider Ratio 2nd Integer Portion. Half integer divide ratio of second stage. The actual divide ratio is (fod_2nd_int * 2). A setting of 1 is invalid: the minimum divide ratio is 4. Set to 0 to bypass the second stage.
8:0	fod_1st_int	RW	0x64	Fractional Output Divider Ratio 1st Integer Portion. Integer divide ratio of first stage (MMD). The first stage divides the VCO clock down to a range of 33MHz to 650MHz, giving a minimum divide ratio of 9.5GHz / 650MHz = 14.61 and maximum divide ratio of 10.7GHz / 33MHz = 324.25 If the first stage frequency is less than 70MHz, the fod_slow_freq_en bit must be set to 1. This register field is part of an atomic group consisting of fod_1st_int and fod_frac. When the most significant byte (bits [33:30]) of fod_frac is written, the value of all these fields are applied to the FOD. <i>Note:</i> Refer to fod_frac for details about serial bus writes to this register field and automatic updates performed by the over-clocking engine.

Table 121. FOD_PHASE_CNFG - FOD Phase Configuration

Bit Field	Field Name	Type	Default Value	Description
15	fod_ph_adj_now	RW1S	0x0	Fraction Output Divider Phase Adjustment Now. When this bit is written from 0 to 1, the phase adjustment in fod_phase is applied to the divider. This bit self-clears when the adjust completes.
14	fod_ph_adj_post_sync	RW	0x1	Fraction Output Divider Phase Adjustment After Synchronization. When this bit is set to 1, the phase adjustment in fod_phase is applied to the divider whenever the divider is synchronized.
13	fod_slow_freq_en	RW	0x0	FOD Slow Frequency Enable. Must be set to 1 when the MMD (first stage) frequency is under 70MHz.
12	reserved	RO	0x0	Reserved.
11:10	fod_sync_group	RW	0x0	Fraction Output Divider Sync Group. Sets the sync group that this divider belongs to: <ul style="list-style-type: none"> ▪ 0x0 = Group0 ▪ 0x1 = Group1 ▪ 0x2 = None ▪ 0x3 = None
9:0	fod_phase	RW	0x3F0	Fraction Output Divider Phase Configuration. Signed 2's complementary value sets the phase. A positive value means lag from 0 phase, and a negative value means lead from 0 phase, in steps of 1/4 VCO period. The default value of -16 (decimal), or -4.0 VCO periods, approximately aligns the FOD output clock with the IOD output clock, when the FOD is configured with an integer divide ratio. This register is atomic. When the most significant byte (bits [9:8]) is written, the new value is applied to the FOD according to fod_ph_adj_now and fod_ph_adj_post_sync.

11.13 SSC Register

Table 122. SSC_CNFG - Spectrum Spreading Configuration

Bit Field	Field Name	Type	Default Value	Description
31	ssc_en	RW	0x0	<p>Spread-Spectrum Clocking Enable.</p> <p>Enable spread spectrum. The spread configuration is determined by the other register fields in this register.</p> <ul style="list-style-type: none"> 0x0 = SSC disabled 0x1 = SSC enabled <p>If the FOD0 and FOD1 SSC modulation frequencies are the same, the FOD1 SSC phase can be aligned to FOD0 SSC by setting ssc_share to 1.</p> <p><i>Note:</i> When ssc_share is set to 1, then FOD1 ssc_en must be set to 1 before FOD0 ssc_en is set to 1 since FOD1 SSC will start when FOD0 ssc_en is set to 1. This restriction does not apply when loading the device configuration from OTP/EEPROM on startup, but does apply if dynamically changing these settings later through a dynamic configuration load from the OTP/EEPROM, or by writing registers from the serial interface.</p>
30	ssc_mode	RW	0x0	<p>Spectrum Spreading Mode.</p> <ul style="list-style-type: none"> 0x0 = Down spreading 0x1 = Center spreading
29:24	reserved	RO	0x0	Reserved.
23:16	ssc_ampl	RW	0x51	<p>Spectrum Spreading Amplitude.</p> <p>Sets the positive and negative spreading amplitude. For down spread, ssc_ampl is only used for the negative limit and the positive limit is internally set to 0. For center spread, the peak-to-peak spread amplitude is twice the specified amplitude (for a 1% peak-to-peak center spread, define ssc_ampl as 0.5%).</p> $\text{ssc_ampl} = \text{spread_percentage} / 100 * 2^{14}$ <p>For example, for 1% spread, set ssc_ampl to $0.01 * 2^{14} = 163$ decimal, or 0xA3.</p> <p>The default value corresponds to a 0.5% down spread at 31.5kHz.</p>
15:0	ssc_step	RW	0x2B8C	<p>Spectrum Spreading Step Size.</p> <p>Set ramp step size to get the target modulation rate.</p> <p>For down spread:</p> <ul style="list-style-type: none"> $\text{ssc_step} = \text{ssc_ampl} * 2^{16} * \text{ssc_freq} / 15\text{MHz}$ <p>For center spread:</p> <ul style="list-style-type: none"> $\text{ssc_step} = 2 * \text{ssc_ampl} * 2^{16} * \text{ssc_freq} / 15\text{MHz}$ <p>where:</p> <p>ssc_freq is the target modulation rate from 30kHz to 63kHz 15MHz is the system clock divided by 4, assuming the system clock is 60MHz</p> <p><i>Example 1.</i> For a 32kHz 1% down spread: ssc_ampl = 163 $\text{ssc_step} = 163 * 2^{16} * 32\text{kHz} / 15\text{MHz} = 0x5905$</p> <p><i>Example 2.</i> For a 32kHz ± 0.5% center spread: ssc_ampl = 81 $\text{ssc_step} = 2 * 81 * 2^{16} * 32\text{kHz} / 15\text{MHz} = 0x5879$</p> <p>The default value corresponds to a 0.5% down spread at 31.5kHz.</p>

11.14 BANK Register

Table 123. OUT_BANK_CNFG - Output Bank Configuration

Bit Field	Field Name	Type	Default Value	Description
7:6	reserved	RO	0x0	Reserved.
5	bank_pd	RW	0x0	<p>Output Bank Power Down.</p> <p>Powers down the output bank by turning off the regulator. When a bank is powered down, all output driver(s) in that bank should also be powered down by setting their out_pd bit(s) to 1.</p> <ul style="list-style-type: none"> ▪ 0x0 = Bank is powered up ▪ 0x1 = Bank is powered down
4:3	bank_fanout_mode	RW	0x0	<p>Output Bank Fan-out Buffer Mode.</p> <p>Configures the bank selection for fanout buffer mode. Only available on banks 4, 5, and 6.</p> <p>The device must be configured for fanout buffer mode by fanout_buf_mode (CLKIN0) / fanout_buf_mode1 (CLKIN1) for this setting to take effect.</p> <ul style="list-style-type: none"> ▪ 0x0 = Normal operation mode. The output bank source clock is selected by output_bank_src. ▪ 0x1 = CLKIN0 Fan-out buffer mode. When fanout_clkmode is 1, the output bank selects CLKIN0. When fanout_clkmode is 0, the output bank source clock is selected by output_bank_src. ▪ 0x2 = CLKIN1 Fan-out buffer mode. When fanout_clkmode1 is 1, the output bank selects CLKIN1. When fanout_clkmode1 is 0, the output bank source clock is selected by output_bank_src.
2:0	output_bank_src	RW	0x5	<p>Output Bank Source.</p> <p>Sets the clock source of each output bank, in conjunction with bank_fanout_mode. Some configurations can be reserved based on Output Bank Source Mapping table. The bits in BANK_MUX_CLK_EN - Bank Mux Clock Enable must be set appropriately to enable only the selected source for each bank.</p> <ul style="list-style-type: none"> ▪ 0x0 = IOD0 for Banks 0, 1 / clkin2_div (CLKIN1) for Banks 4, 5, 6 ▪ 0x1 = IOD1 for Banks 0, 1, 2 / refin_div (XIN_REF) for Bank 5 ▪ 0x2 = IOD2 for Banks 4, 5, 6 ▪ 0x3 = IOD3 for Banks 5, 6 ▪ 0x4 = FOD0 for Banks 0, 1, 2, 3 ▪ 0x5 = FOD1 ▪ 0x6 = FOD2 for Banks 3, 4, 5, 6 ▪ 0x7 = clkin0_div (CLKIN0) for Banks 4, 5, 6

11.15 OUT Registers

Table 124. ODRV_EN - Output Driver Enable

Bit Field	Field Name	Type	Default Value	Description
7	out_pd	RW	0x0	Output Driver Power Down. Powers down the output clock driver. <ul style="list-style-type: none"> 0x0 = Output driver is powered up 0x1 = Output driver is powered down
6	out_oe_mode	RW	0x0	Output Driver OE Mode. Controls whether the output enable acts synchronously or asynchronously with respect to the output divider clock. Must be set to asynchronous mode when outputting SYSREF. <ul style="list-style-type: none"> 0x0 = OE is synchronized to the divider clock. Enabling and disabling the output clock is glitchless. OE transitions take effect after 1 divider clock cycle. 0x1 = OE is asynchronous to the divider clock. OE transitions while the divider clock is toggling can result in glitches/runt pulses.
5:3	out_dis_group	RW	0x0	Output Driver OE Group Select and Global Output Enable Exclusion. Sets which OE group this driver is in, and if not assigned to a group, can also exclude global output enables from applying to the clock. <ul style="list-style-type: none"> 0x0 = Group0 0x1 = Group1 0x2 = Group2 0x3 = Group3 0x4 = Group4 0x5 = None 0x7 = None, and exclude global output enables When set to 0x7, allows the output clock to be enabled regardless of: <ul style="list-style-type: none"> APLL or DPLL lock status (equivalent to out_startup set to 2) goe register bit GOE pin, if one is assigned with gpi_func/gpio_func The output clock can still be disabled by the out_dis register bit. This setting is intended to allow an output clock to run freely following the configuration load so that it can be used as an external APLL or DPLL feedback clock. In that application, if the output clock's divider is resynchronized after the startup sequence completes, the output clock will stop running for less than 1 μ s and then the APLL or DPLL will re-align the feedback clock to the reference clock.
2:1	out_dis_state	RW	0x3	OUT Driver Disabled State. Controls the state of OUTx / OUTxb when the output driver is disabled. <ul style="list-style-type: none"> 0x0 = Held High / Low 0x1 = Held Low / High 0x2 = Held Hi-Z / Hi-Z 0x3 = Held Low / Low (except LVDS mode is held High / Low)
0	out_dis	RW	0x0	OUTx and/or OUTxb Driver Disable. Forces both OUTx and OUTxb Drivers to be disabled if in differential mode or forces OUT Driver to be disabled if in CMOS mode. For more information, see Output Enable Control . <ul style="list-style-type: none"> 0x0 = OUTx and/or OUTxb Driver is enabled if not disabled by other means 0x1 = OUTx and/or OUTxb Driver is disabled

Table 125. ODRV_CNFG - Output Driver Configuration

Bit Field	Field Name	Type	Default Value	Description
15	out_prog7	RW	0x0	Output Driver Programmability Bit 7. When set to 1, controls the output driver as follows according to CMOS mode / LPHCSL mode / LVDS mode: reserved / flip output polarity / flip output polarity
14	out_prog6	RW	0x0	Output Driver Programmability Bit 6. When set to 1, controls the output driver as follows according to CMOS mode / LPHCSL mode / LVDS mode: reserved / reserved / reserved
13	out_prog5	RW	0x0	Output Driver Programmability Bit 5. When set to 1, controls the output driver as follows according to CMOS mode / LPHCSL mode / LVDS mode: reserved / cross point lower / cross point tune
12	out_prog4	RW	0x0	Output Driver Programmability Bit 4. When set to 1, controls the output driver as follows according to CMOS mode / LPHCSL mode / LVDS mode: reserved / cross point increase for double termination / cross point tune
11	out_prog3	RW	0x0	Output Driver Programmability Bit 3. When set to 1, controls the output driver as follows according to CMOS mode / LPHCSL mode / LVDS mode: tristate OUTx / driver impedance -5% / cross point tune
10	out_prog2	RW	0x0	Output Driver Programmability Bit 2. When set to 1, controls the output driver as follows according to CMOS mode / LPHCSL mode / LVDS mode: tristate OUTxb / driver impedance +5% / cross point tune
9	out_prog1	RW	0x0	Output Driver Programmability Bit 1. When set to 1, controls the output driver as follows according to CMOS mode / LPHCSL mode / LVDS mode: flip OUTx polarity / amplitude -10% / amplitude -10%
8	out_prog0	RW	0x0	Output Driver Programmability Bit 0. When set to 1, controls the output driver as follows according to CMOS mode / LPHCSL mode / LVDS mode: flip OUTxb polarity / amplitude +5% / amplitude +5%
7	reserved	RO	0x0	Reserved.
6	out_lpamp	RW	0x0	Output Driver LPHCSL Amplitude Control. Controls the amplitude of the output driver when LPHCSL mode is selected. <ul style="list-style-type: none"> ▪ 0x0 = 800mV ▪ 0x1 = 900mV
5	out_lpsr	RW	0x1	Output Driver LPHCSL Slew Rate Control. Controls the slew rate of the output driver when LPHCSL mode is selected. Based on 5" transmission line simulation condition. Slew rates are measured from -150mV to +150mV from crossing point. <ul style="list-style-type: none"> ▪ 0x0 = Slow, 2-4 V/ns ▪ 0x1 = Fast, > 4 V/ns

Table 125. ODRV_CNFG - Output Driver Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
4	out_lpimp	RW	0x1	Output Driver LPHCSL Impedance Control. Controls the output impedance of the output driver when LPHCSL mode is selected. <ul style="list-style-type: none"> 0x0 = 85Ω 0x1 = 100Ω
3:2	out_cmdrv	RW	0x3	Output Driver CMOS Slew Rate Control. Controls the slew rate of the output driver (in V/ns) when CMOS mode is selected, according to the supply voltage level of 3.3V / 2.5V / 1.8V: <ul style="list-style-type: none"> 0x0 = 4.2 / 2.7 / 1.8 0x1 = 2.2 / 1.5 / 1.8 0x2 = 2.2 / 1.5 / 1.8 0x3 = 3.4 / 2.0 / 1.9
1:0	out_mode	RW	0x0	Output Driver Type. Selects the output driver type. <ul style="list-style-type: none"> 0x0 = LPHCSL 0x1 = LVDS 0x2 = LVDS 0x3 = CMOS

11.16 GPI Registers

Table 126. GPI_CNFG - GPI Configuration

Bit Field	Field Name	Type	Default Value	Description
15:10	reserved	RO	0x0	Reserved.
9	gpi_pol	RW	0x0	GPI Polarity Sets the pin polarity. This bit is ignored if gpi_func configures the pin as a reference clock input. <ul style="list-style-type: none"> 0x0 = Normal sense. Pin functions denoted with a # are active low, others are active high. 0x1 = Inverted sense. Pin functions denoted with a # are active high, others are active low.
8	gpi_pullup	RW	0x0	GPI Pull-up Enable Sets the internal pull-up mode. This bit is ignored and the internal pull-down is enabled if gpi_func configures the pin as a reference clock input. <ul style="list-style-type: none"> 0x0 = Pull-up disabled 0x1 = Pull-up enabled

Table 126. GPI_CNFG - GPI Configuration

Bit Field	Field Name	Type	Default Value	Description
7	gpi_pulldn	RW	0x0	<p>GPI Pull-down Enable.</p> <p>Sets the internal pull-up or pull-down modes. This bit is ignored and the internal pull-down is enabled if gpi_func configures the pin as a reference clock input.</p> <ul style="list-style-type: none"> ▪ 0x0 = Pull-down disabled ▪ 0x1 = Pull-down enabled
6:0	gpi_func	RW	0x7F	<p>GPI Functions.</p> <p>Sets the general purpose input function.</p> <ul style="list-style-type: none"> ▪ 0x0 = OE[0], input, enable output drivers in OE group 0 ▪ 0x1 = OE[1], input, enable output drivers in OE group 1 ▪ 0x2 = OE[2], input, enable output drivers in OE group 2 ▪ 0x3 = OE[3], input, enable output drivers in OE group 3 ▪ 0x4 = OE[4], input, enable output drivers in OE group 4 ▪ 0x5 = PERST#, input, latches CLKIN0 fanout buffer mode clock selection on active edge ▪ 0x6 = GOE, input, enable all output drivers ▪ 0x7 = DPLL_CLK_SEL[0], input ▪ 0x8 = DPLL_CLK_SEL[1], input ▪ 0x9 = PERST1#, input, latches XO/IB fanout buffer mode clock selection on active edge ▪ 0xA = Reserved ▪ 0xE = SDI, input (SPI 4-wire mode) ▪ 0xF = SYSREF_IN ▪ 0x10 = GPI, input, input status allowed read back via SSI ▪ 0x7F = GPI function disabled, pin used as reference clock input

Table 127. GPI_STS - GPI Status

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3:0	gpi_sts	RO	0x0	<p>GPI Status.</p> <p>Indicates the status of the GPIO/1/2/3 pins without latching and without applying optional polarity inversion (gpi_pol). If a pin is configured to be a reference clock input (see gpi_func), the status reads back as 0.</p> <p>Bit [3] = GPI3 status Bit [2] = GPI2 status Bit [1] = GPI1 status Bit [0] = GPIO status</p>

11.17 GPIO Registers

Table 128. GPIO_CNFG - GPIO Configuration

Bit Field	Field Name	Type	Default Value	Description
15	reserved	RO	0x0	Reserved.
14:13	gpo_drv	RW	0x0	GPO Drive Strength. Applies to the pad when configured as an output (gpio_type is 0x0 or 0x2). Drive strength increases as this setting increases.
12	gpo_ctrl	RW	0x0	GPO Output Control Signal Value. Sets the value to drive the GPO pin when configured as a general purpose output.
11:10	gpio_type	RW	0x1	GPIO Type. Sets the direction and type following reset. <ul style="list-style-type: none"> ▪ 0x0 = Output (driven high/low), or bidirectional if configured as SDIO by gpio_func ▪ 0x1 = Input (2-level) ▪ 0x2 = Output (open-drain) ▪ 0x3 = Input (tri-level). Only valid for GPIO0/1/2 when set to GPI mode or Dynamic CSEL; reserved for GPIO3/4.
9	gpio_pol	RW	0x0	GPIO Polarity. Sets the pin polarity. This bit is ignored if gpio_func configures the pin as a tri-level Dynamic CSEL, GPO, or test clock output. <ul style="list-style-type: none"> ▪ 0x0 = Normal sense. Pin functions denoted with a # are active low, others are active high. ▪ 0x1 = Inverted sense. Pin functions denoted with a # are active high, others are active low.
8	gpio_pullup	RW	0x0	GPIO Pull-up Enable. Sets the internal pull-up mode. <ul style="list-style-type: none"> ▪ 0x0 = Pull-up disabled ▪ 0x1 = Pull-up enabled
7	gpio_pulldn	RW	0x1	GPIO Pull-down Enable. Sets the internal pull-down mode. <ul style="list-style-type: none"> ▪ 0x0 = Pull-down disabled ▪ 0x1 = Pull-down enabled

Table 128. GPIO_CNFG - GPIO Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
6:0	gpio_func	RW	0x10	<p>GPIO Functions.</p> <p>Sets the general purpose input/output function. Refer to pwrnd_sel for PWRGD/PWRDN# assignment.</p> <p>0x0 = OE[0], input, enable output drivers in OE group 0 0x1 = OE[1], input, enable output drivers in OE group 1 0x2 = OE[2], input, enable output drivers in OE group 2 0x3 = OE[3], input, enable output drivers in OE group 3 0x4 = OE[4], input, enable output drivers in OE group 4 0x5 = PERST#, input, latches CLKIN0 fanout buffer mode clock selection on active edge 0x6 = GOE, input, enable all output drivers 0x7 = DPLL_CLK_SEL[0], input 0x8 = DPLL_CLK_SEL[1], input 0x9 = PERST1#, input, latches CLKIN1 fanout buffer mode clock selection on active edge 0xE = SDI, input (SPI 4-wire mode) 0xF = SYSREF_IN, input 0x10 = GPI, input, input status allowed read back via SSI 0x11 = Dynamic CSEL, input, dynamic configuration control. Only valid for GPIO0/1/2. May be tri-level or 2-level. 0x1C = INT, output 0x1D = GPO, output, to control external functions such as LEDs. The output value is set in gpo_ctrl. 0x1E = SDO, output (SPI 4-wire mode) or SDIO, bidirectional (SPI-3-wire mode); gpio_type must be set to 0, and is internally controlled as 0 or 1 by the SPI logic.</p> <p>0x20 = clkIn0 los_sts, output 0x21 = clkIn1 los_sts, output 0x22 = clkIn2 los_sts, output 0x23 = clkIn3 los_sts, output 0x24 = refin los_sts, output 0x25 = apll_lock_sts, output 0x26 = dpll_lock_sts, output 0x28 = clkIn0 los_evt, output 0x29 = clkIn1 los_evt, output 0x2A = clkIn2 los_evt, output 0x2B = clkIn3 los_evt, output 0x2C = refin los_evt, output 0x2D = apll_lol, output 0x2E = dpll_lol, output 0x30 = clkIn0 los_lmt_evt, output 0x31 = clkIn1 los_lmt_evt, output 0x32 = clkIn2 los_lmt_evt, output 0x33 = clkIn3 los_lmt_evt, output 0x34 = refin los_lmt_evt, output 0x35 = apll_lol_lmt, output 0x36 = dpll_lol_lmt, output 0x37 = CLKMODE (fanout_clkmode), output 0x38 = device_ready, output 0x39 = CLKMODE1 (fanout_buf_mode1), output</p>

Table 129. GPIO_STS - GPIO Status

Bit Field	Field Name	Type	Default Value	Description
7:0	gpio_sts	RO	0x0	<p>GPIO Status.</p> <p>Indicates the status of the GPIO0/1/2/3/4 pins without latching and without applying optional polarity inversion (gpio_pol).</p> <p>For GPIO0/1/2, the possible encodings are:</p> <ul style="list-style-type: none"> ▪ 0x0 = Tri-level low, 2-level low ▪ 0x1 = Tri-level mid, 2-level unused ▪ 0x2 = Unused ▪ 0x3 = Tri-level high, 2-level high <p>Bit [7] = GPIO4 status Bit [6] = GPIO3 status Bits [5:4] = GPIO2 status Bits [3:2] = GPIO1 status Bits [1:0] = GPIO0 status</p>

11.18 EEPROM Registers

Table 130. EEPROM_CNFG - EEPROM Load Configuration

Bit Field	Field Name	Type	Default Value	Description
63:56	reserved	RO	0x0	Reserved.
55:44	eeeprom_fall	RW	0x96	<p>EEPROM Falling Edge Time.</p> <p>Cycle number (counting down from eeeprom_cycle) at which the SCL falling edge occurs. The default value is for a 60MHz clock and must be scaled according to the actual system clock frequency.</p>
43:32	eeeprom_rise	RW	0x1C2	<p>EEPROM Rising Edge Time.</p> <p>Cycle number (counting down from eeeprom_cycle) at which the SCL rising edge occurs. The default value is for a 60MHz clock and must be scaled according to the actual system clock frequency.</p>
31:20	eeeprom_cycle	RW	0x258	<p>EEPROM Cycle Time.</p> <p>Number of system clock cycles in one SCL period when running at 100kHz. The default value is for a 60MHz clock and must be scaled according to the actual system clock frequency.</p>
19:15	reserved	RO	0x0	Reserved.
14:13	eeeprom_i2c_drv	RW	0x0	<p>I2C/SMBus Drive Strength.</p> <p>Selects the output driver slew rate of the SDA_nCS and SCL_SCLK pins when the internal I2C master is active. (higher settings means higher drive strength). This setting does not affect the internal timing, refer to eeeprom_i2c_speed.</p> <p>0x0 = 1.8V Standard mode (100 kHz) or 2.5V/3.3V standard (100kHz) and Fast mode (400kHz)</p> <ul style="list-style-type: none"> ▪ 0x1 = 1.8V Fast mode (400 kHz) ▪ 0x2 = Reserved ▪ 0x3 = 1.8V/2.5V/3.3V Fast mode plus (1 MHz)

Table 130. EEPROM_CNFG - EEPROM Load Configuration (Cont.)

Bit Field	Field Name	Type	Default Value	Description
12	eeeprom_ext_ad dr	RW	0x0	EEPROM Extended Address Enable. Allows extended 10-bit addressing with a 1-byte I2C address, if supported by the EEPROM. <ul style="list-style-type: none"> 0x0 = The address is sent outside of the device address. 0x1 = Address bits 10:8 are sent in bits 2:0 of the device address, and address bits 7:0 are sent in the 1-byte address. eeeprom_addr_size must be set to 0.
11	eeeprom_addr_si ze	RW	0x1	EEPROM Address Size. Number of address bytes sent to the EEPROM during a read. 0x0 = 1-byte address 0x1 = 2-byte address
10:7	eeeprom_length	RW	0x4	EEPROM Size. Selects the number of bytes in the EEPROM for storing configurations. <ul style="list-style-type: none"> 0x0 = 128B 0x1 = 256B 0x2 = 512B 0x3 = 1KB 0x4 = 2KB 0x5 = 4KB 0x6 = 8KB 0x7 = 16KB 0x8 = 32KB 0x9 = 64KB
6	eeeprom_load_en	RW	0x0	EEPROM Load Enable. Enables loading of the common and/or user configurations from an external EEPROM device. The device loads configurations in the following order: OTP common, EEPROM common (if eeeprom_load_en is set to 1), OTP user, and EEPROM user (if eeeprom_load_en is set to 1). This bit may be programmed in the OTP common and/or user configurations to control whether the device attempts to load the common and/or user configurations from EEPROM. <i>Warning:</i> If the SDA pin is held low or floating when the I ² C master attempts to read the EEPROM, the I ² C master will wait indefinitely until SDA becomes high before beginning the read request. <ul style="list-style-type: none"> 0x0 = Disabled 0x1 = Enabled
5:4	eeeprom_i2c_spe ed	RW	0x0	EEPROM I2C Speed. Selects the I2C master speed for EEPROM load. When the speed is 400kHz or 1MHz, eeeprom_fall , eeeprom_rise and eeeprom_cycle are internally divided by 4 or 10 respectively to achieve the faster timing. The pad drive strength (eeeprom_i2c_drv) should also be set according to the speed. <ul style="list-style-type: none"> 0x0 = 100kHz 0x1 = 400kHz 0x2 = 1MHz 0x3 = Reserved
3:0	eeeprom_retry_c ount	RW	0x4	EEPROM Load Retry Count. Number of times to attempt to load EEPROM. If eeeprom_bad or load failed (CRC error) after this number of attempts, the eeeprom_load_fail status bit is set.

Table 131. EEPROM_ADDR - EEPROM Address Configuration

Bit Field	Field Name	Type	Default Value	Description
7	reserved	RO	0x0	Reserved.
6:0	eeeprom_addr	RW	0x50	EEPROM Device Address. Sets the I2C device address of the EEPROM to load.

Table 132. EEPROM_EVENT - EEPROM Load Event Status

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3	eeeprom_bad	RW1C	0x0	EEPROM Not Detected. When high, indicates the EEPROM did not acknowledge a read access during device startup or a dynamic configuration load. In this case, eeeprom_load_fail is not set. If EEPROM load is disabled (eeeprom_load_en is set to 0), then VC7 will not attempt to read the EEPROM and this bit cannot be set. Cleared by writing it to 1.
2	eeeprom_config_empty	RW1C	0x0	EEPROM Load of Empty Configuration. When high, indicates the EEPROM load attempted to load a configuration that did not select any blocks, during device startup or a dynamic configuration load. Cleared by writing it to 1.
1	eeeprom_load_fail	RW1C	0x0	EEPROM Load Failure. When high, indicates the EEPROM load failed during device startup or a dynamic configuration load. This bit is not set if the EEPROM does not respond (eeeprom_bad is set instead). Cleared by writing it to 1.
0	eeeprom_crc_err	RW1C	0x0	EEPROM Load CRC Error. When high, indicates the EEPROM load encountered one or more CRC errors during device startup or a dynamic configuration load. Cleared by writing it to 1.

Table 133. EEPROM_ERR_CNT - EEPROM CRC Error Count

Bit Field	Field Name	Type	Default Value	Description
7:4	reserved	RO	0x0	Reserved.
3:0	eeeprom_crc_err_cnt	RW	0x0	EEPROM CRC Error Counter. This counter increments each time the loader detects a CRC error while reading the EEPROM, and saturates at 0xF. It is cleared by writing it to 0x0, and may be preset by writing the desired value. Preset may be used as a debug tool. This register can only be written if the block is not clock gated (otp_cg) or held in reset (otp_sw_rst).

Table 134. OTP_VPPLMT - OTP VPP Monitor Limit

Bit Field	Field Name	Type	Default Value	Description
15:14	reserved	RO	0x0	Reserved.
13:0	vpplmt	RW	0x3D0	OTP VPP Monitor Limit. Number of VPP monitor clock cycles before the VPP monitor issues an error (vpp_error). Counted in multiples of 1024 us. The default value is approximately 1 second.

Table 135. OTP_EVENT - OTP Event Status

Bit Field	Field Name	Type	Default Value	Description
7	manual_rdy	RW1C	0x0	Manual Ready Indicator. When high, indicates a manual request (including Program Assist) completed. Cleared by writing it to 1.
6	status_latched	RW1C	0x0	OTP Latched Status. Latched value of the OTP STATUS pin. Can be cleared by writing 1 to it. If STATUS is still high when clearing is attempted, this bit will immediately be set to 1 again.
5	vpp_error	RW1C	0x0	OTP VPP Error. This error bit signals that the VPP monitor has detected that the OTP internal charge pump was enabled for longer than the time defined in the vpplmt field. This bit gets cleared by writing one to it. It cannot be cleared unless the internal condition has gone away (i.e., VPP_MON has been de-asserted).
4	reserved	RO	0x0	Reserved.
3	pgm_assist_fail	RW1C	0x0	Program Assist Failure. When high, indicates that the Program Assist sequence failed to program one or more bits in the OTP word.
2	otp_config_empty	RW1C	0x0	OTP Load of Empty Configuration. When high, indicates the OTP load attempted to load a configuration that did not select any blocks. Cleared by writing it to 1.
1	otp_load_fail	RW1C	0x0	OTP Load Failure. When high, indicates the OTP load failed during device startup or a dynamic configuration load. Cleared by writing it to 1.
0	otp_crc_err	RW1C	0x0	OTP Load CRC Error. When high, indicates the OTP load encountered one or more CRC errors during device startup or a dynamic configuration load. Cleared by writing it to 1.

11.19 INT Registers

Table 136. SCRATCH0 - Software Scratch Register 0

Bit Field	Field Name	Type	Default Value	Description
31:0	scratch0	RW	0x0	<p>Scratch Register and Power-down Controls.</p> <p>For arbitrary software use.</p> <p>In VC7A+, bits[3:0] have the following function:</p> <ul style="list-style-type: none"> ▪ scratch0[3]: System clock divider disable override; When high, this bit overrides the normal enable pin of the system clock divider and forces it to be low (disabled). This bit should only be set when the digital core is running on the RC oscillator clock. ▪ scratch0[2]: APLL feedback divider disable override; When high, this bit overrides the normal enable pin of the APLL feedback divider and forces it to be low (disabled). scratch0[1]: System clock divider reset; When high, this bit resets the system clock divider. This bit should only be set when the digital core is running on the RC oscillator clock. ▪ scratch0[0]: System clock select; When high, this bit cleanly switches the digital core system clock to the RC oscillator clock. This bit should only be set once the RC oscillator has been enabled (by programming the <code>por_osc_sel</code> field to 0x3) once it is cleanly toggling. To switch the digital core back to the VCO clock, this bit must be written back to zero, but only once the VCO has been properly enabled (see <code>vco_dis</code>) and after the system clock divider has been reset (by writing to one and then zero bit[1] of this register).

Table 137. INT_EN - Interrupt Enable

Bit Field	Field Name	Type	Default Value	Description
31	device_int_en	RW	0x0	<p>Device Interrupt Enable.</p> <p>Overall device interrupt enable. When this field is set to 1, the device interrupt is asserted while <code>device_int_sts</code> is 1.</p>
30	reserved	RO	0x0	Reserved.
29	load_fail_int_en	RW	0x0	<p>Configuration Loader Failure Interrupt Enable.</p> <p>When this field is set to 1, the <code>load_fail_int_sts</code> bit contributes to the device interrupt</p>
28	load_err_int_en	RW	0x0	<p>Configuration Loader Error Interrupt Enable.</p> <p>When this field is set to 1, the <code>load_err_int_sts</code> bit contributes to the device interrupt</p>
27	otp_manual_rdy_int_en	RW	0x0	<p>OTP Manual Request Ready Interrupt Enable.</p> <p>When this field is set to 1, the <code>otp_manual_rdy_int_sts</code> bit contributes to the device interrupt</p>
26	reserved	RO	0x0	Reserved.
25	los4_lmt_int_en	RW	0x0	<p>REFIN Monitor LOS Threshold Exceeded Interrupt Enable.</p> <p>When this field is set to 1, the <code>los4_lmt_int_sts</code> bit contributes to the device interrupt</p>
24	los3_lmt_int_en	RW	0x0	<p>CLKIN3 Monitor LOS Threshold Exceeded Interrupt Enable.</p> <p>When this field is set to 1, the <code>los3_lmt_int_sts</code> bit contributes to the device interrupt</p>
23	los2_lmt_int_en	RW	0x0	<p>CLKIN2 Monitor LOS Threshold Exceeded Interrupt Enable.</p> <p>When this field is set to 1, the <code>los2_lmt_int_sts</code> bit contributes to the device interrupt</p>

Table 137. INT_EN - Interrupt Enable (Cont.)

Bit Field	Field Name	Type	Default Value	Description
22	los1_lmt_int_en	RW	0x0	CLKIN1 Monitor LOS Threshold Exceeded Interrupt Enable. When this field is set to 1, the los1_lmt_int_sts bit contributes to the device interrupt
21	los0_lmt_int_en	RW	0x0	CLKIN0 Monitor LOS Threshold Exceeded Interrupt Enable. When this field is set to 1, the los0_lmt_int_sts bit contributes to the device interrupt
20	dpll_lo_lmt_int_en	RW	0x0	DPLL Loss-of-lock Threshold Exceeded Interrupt Enable. When this field is set to 1, the dpll_lo_lmt_int_sts bit contributes to the device interrupt
19	apll_lo_lmt_int_en	RW	0x0	APLL Loss-of-lock Threshold Exceeded Interrupt Enable. When this field is set to 1, the apll_lo_lmt_int_sts bit contributes to the device interrupt
18	reserved	RO	0x0	Reserved.
17	freq3_int_en	RW	0x0	CLKIN3 Frequency Monitor Interrupt Enable. When this field is set to 1, the freq3_int_sts bit contributes to the device interrupt
16	freq2_int_en	RW	0x0	CLKIN2 Frequency Monitor Interrupt Enable. When this field is set to 1, the freq2_int_sts bit contributes to the device interrupt
15	freq1_int_en	RW	0x0	CLKIN1 Frequency Monitor Interrupt Enable. When this field is set to 1, the freq1_int_sts bit contributes to the device interrupt
14	freq0_int_en	RW	0x0	CLKIN0 Frequency Monitor Interrupt Enable. When this field is set to 1, the freq0_int_sts bit contributes to the device interrupt.
13:9	reserved	RO	0x0	Reserved.
8	los4_int_en	RW	0x0	REFIN Monitor Loss-of-Signal interrupt Enable. When this field is set to 1, the los4_int_sts bit contributes to the device interrupt
7	los3_int_en	RW	0x0	CLKIN3 Monitor Loss-of-Signal Interrupt Enable. When this field is set to 1, the los3_int_sts bit contributes to the device interrupt
6	los2_int_en	RW	0x0	CLKIN2 Monitor Loss-of-Signal Interrupt Enable. When this field is set to 1, the los2_int_sts bit contributes to the device interrupt
5	los1_int_en	RW	0x0	CLKIN1 Monitor Loss-of-Signal Interrupt Enable. When this field is set to 1, the los1_int_sts bit contributes to the device interrupt
4	los0_int_en	RW	0x0	CLKIN0 Monitor Loss-of-Signal Interrupt Enable. When this field is set to 1, the los0_int_sts bit contributes to the device interrupt.
3	dpll_state_ch_int_en	RW	0x0	DPLL State Change Interrupt Enable. When this field is set to 1, the dpll_state_ch_int_sts bit contributes to the device interrupt.
2	dpll_holdover_int_en	RW	0x0	DPLL Holdover Interrupt Enable. When this field is set to 1, the dpll_holdover_int_sts bit contributes to the device interrupt.

Table 137. INT_EN - Interrupt Enable (Cont.)

Bit Field	Field Name	Type	Default Value	Description
1	dpll_lol_int_en	RW	0x0	DPLL Loss-of-Lock Interrupt Enable. When this field is set to 1, the dpll_lol_int_sts bit contributes to the device interrupt.
0	apll_lol_int_en	RW	0x0	APLL Loss-of-Lock Interrupt Enable. When this field is set to 1, the apll_lol_int_sts bit contributes to the device interrupt.

Table 138. INT_STS - Interrupt Status

Bit Field	Field Name	Type	Default Value	Description
31	device_int_sts	RO	0x0	Device Interrupt Status. Overall device interrupt status. This bit is the OR of all the other interrupt status bits in this register after masking by their respective interrupt enable bits in the INT_EN - Interrupt Enable register. This bit is masked by device_int_en . The resulting signal can be output on the assigned GPIO pin.
30	reserved	RO	0x0	Reserved.
29	load_fail_int_sts	RO	0x0	Configuration Loader Failure Interrupt Status. The logical OR of the otp_load_fail and eeprom_load_fail event bits
28	load_err_int_sts	RO	0x0	Configuration Loader Error Interrupt Status. The logical OR of the otp_crc_err and eeprom_crc_err event bits
27	otp_manual_rdy_int_sts	RO	0x0	OTP Manual Request Ready Interrupt Status. Mirrors the OTP manual_rdy event bit
26	reserved	RO	0x0	Reserved.
25	los4_lmt_int_sts	RO	0x0	REFIN Monitor LOS Threshold Exceeded Interrupt Status. Mirrors the REFIN los_lmt_evt event bit
24	los3_lmt_int_sts	RO	0x0	CLKIN3 Monitor LOS Threshold Exceeded Interrupt Status. Mirrors the CLKIN3 los_lmt_evt event bit
23	los2_lmt_int_sts	RO	0x0	CLKIN2 Monitor LOS Threshold Exceeded Interrupt Status. Mirrors the CLKIN2 los_lmt_evt event bit
22	los1_lmt_int_sts	RO	0x0	CLKIN1 Monitor LOS Threshold Exceeded Interrupt Status. Mirrors the CLKIN1 los_lmt_evt event bit
21	los0_lmt_int_sts	RO	0x0	CLKIN0 Monitor LOS Threshold Exceeded Interrupt Status. Mirrors the CLKIN0 los_lmt_evt event bit
20	dpll_lol_lmt_int_sts	RO	0x0	DPLL Loss-of-lock Threshold Exceeded Interrupt Status. Mirrors the dpll_lol_lmt event bit
19	apll_lol_lmt_int_sts	RO	0x0	APLL Loss-of-lock Threshold Exceeded Interrupt Status. Mirrors the apll_lol_lmt event bit
18	reserved	RO	0x0	Reserved.
17	freq3_int_sts	RO	0x0	CLKIN3 Frequency Monitor Interrupt Status. Mirrors the CLKIN3 freq_evt event bit
16	freq2_int_sts	RO	0x0	CLKIN2 Frequency Monitor Interrupt Status. Mirrors the CLKIN2 freq_evt event bit
15	freq1_int_sts	RO	0x0	CLKIN1 Frequency Monitor Interrupt Status. Mirrors the CLKIN1 freq_evt event bit

Table 138. INT_STS - Interrupt Status (Cont.)

Bit Field	Field Name	Type	Default Value	Description
14	freq0_int_sts	RO	0x0	CLKIN0 Frequency Monitor Interrupt Status. Mirrors the CLKIN0 freq_evt event bit
13:9	reserved	RO	0x0	Reserved.
8	los4_int_sts	RO	0x0	REFIN Monitor Loss-of-Signal Interrupt Status. Mirrors the REFIN los_evt event bit
7	los3_int_sts	RO	0x0	CLKIN3 Monitor Loss-of-Signal Interrupt Status. Mirrors the CLKIN3 los_evt event bit
6	los2_int_sts	RO	0x0	CLKIN2 Monitor Loss-of-Signal Interrupt Status. Mirrors the CLKIN2 los_evt event bit
5	los1_int_sts	RO	0x0	CLKIN1 Monitor Loss-of-Signal Interrupt Status. Mirrors the CLKIN1 los_evt event bit
4	los0_int_sts	RO	0x0	CLKIN0 Monitor Loss-of-Signal Interrupt Status. Mirrors the CLKIN0 los_evt event bit
3	dpll_state_ch_int_sts	RO	0x0	DPLL State Change Interrupt Status. Mirrors the dpll_state_ch event bit
2	dpll_holdover_int_sts	RO	0x0	DPLL Holdover Interrupt Status. Mirrors the dpll_holdover event bit
1	dpll_lol_int_sts	RO	0x0	DPLL Loss-of-lock Interrupt Status. Mirrors the dpll_lol event bit
0	apll_lol_int_sts	RO	0x0	APLL Loss-of-lock Interrupt Status. Mirrors the apll_lol event bit

12. Revision History

Revision	Date	Description
1.01	Aug 14, 2023	<ul style="list-style-type: none"> ▪ Updated part number references to RC310xx ▪ Updated device_revision in Table 42 (DEVICE_REV) ▪ Updated the description of en_cap_x2 and en_cap_x1 in Table 61 (XO_CNFG) ▪ Added Table 95 (ANA_SPARE_CNFG) and Table 96 (ANA_SPARE_STS)
1.00	Oct 26, 2022	Initial release.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.