

RZ FAMILY MICROPROCESSORS

64-Bit & 32-Bit High-performance MPUs



THE NEXT-GENERATION PROCESSOR TO MEET THE NEEDS OF THE SMART SOCIETY HAS ARRIVED.



CONTENTS

RZ FAMILY PORTFOLIO	04
RZ/V SERIES	06
RZ/N SERIES	12
RZ/T SERIES	20
RZ/G SERIES	30
RZ/A SERIES	40
PACKAGE LINEUP	46

The utilization of intelligent technology is advancing in all aspects of our lives, including electric household appliances, industrial equipment, building management, power grids, and transportation. The cloud-connected “smart society” is coming ever closer to realization. Microcontrollers are now expected to provide powerful capabilities not available previously, such as high-performance and energy-efficient control combined with interoperability with IT networks, support for human-machine interfaces, and more. To meet the demands of this new age, Renesas has drawn on its unmatched expertise in microcontrollers to create the RZ family of embedded processors. The lineup of these “next-generation processors that are as easy to use as conventional microcontrollers” to meet different customer requirements.

The Zenith of the Renesas micro

As embedded processors to help build the next generation of advanced products, the RZ family offers features not available elsewhere and brings new value to customer applications.

Positioning of the RZ Family

	Microcontrollers & Microprocessors, System-on-Chips (SoCs)	Analog and Power Devices
	High-end 32/64-bit MPUs High-resolution HMI, Industrial network & real-time control	<ul style="list-style-type: none"> ▪ Analog products ▪ Clocks & Timing ▪ Interface & Connectivity ▪ Memory & Logic ▪ Power & Power management ▪ Programmable Mixed-signal, ASIC, & IP products <hr/> <ul style="list-style-type: none"> ▪ Timing ▪ Wireless Power ▪ Battery Management ▪ Power Devices
	Advanced 32-bit MCUs Arm ecosystem, Advanced security, Intelligent IoT	
	High Power Efficiently 32-bit MCUs Motor control, Capacitive touch, Functional safety, GUI	
	RISC-V products <ul style="list-style-type: none"> General-purpose 64-bit MPUs (RZ/Five Group) Application-specific 32-bit MCUs 	
	Ultra-low Energy 8/16-bit MCUs Bluetooth® Low Energy, SubGHz, LoRa®-based Solutions Automotive actuators & sensors, Low-end ECUs	
	Automotive 32-bit MCUs Rich functional safety and embedded security features	
	Automotive SoCs Next generation of automotive computing	
		<ul style="list-style-type: none"> ▪ RF products ▪ Sensor products ▪ Space & Harsh environment
		<ul style="list-style-type: none"> ▪ Power Management ▪ Sensors ▪ Video & Display

RZ Family Portfolio

RZ/V Series

64-bit Cortex®-A CPU, Up to 1.8GHz
Low-power Embedded AI
for Vision-AI Application

RZ/N Series

32-bit Cortex®-A/M/R CPU, Up to 500MHz
Multi-protocol Industrial Network and TSN
for PLC, Remote IO, Gateway

RZ/T Series

32-bit Cortex®-R CPU, Up to 800MHz
Real-time Control
Multi-protocol Industrial Network and TSN, Multi-protocol Encoder I/F
for AC servo, Actuator, Inverter

RZ/G Series

32/64-bit Cortex®-A CPU, Up to 1.5Hz
64-bit RISC-V CPU, Up to 1.0GHz
for HMI and IoT Application

RZ/A Series

32/64-bit Cortex®-A CPU, Up to 1GHz
- DDR3L/4 (RZ/A3UL)
- Up to 10MB Embedded RAM for HMI Application

Linux / Android™ / Multi-OS with RTOS

RTOS

<p>Vision AI RZ/V Series</p>	<p>RZ/V2M 1.0GHz Dual-core Cortex-A53, DRP-AI(576-MAC), 4K-ISP</p>	<p>RZ/V2H 1.8GHz Quad-core Cortex-A55, DRP-AI3(4K-MAC), 4K-ISP, 3D-GPU</p>		
<p>Industrial Network RZ/N Series</p>	<p>RZ/V2MA 1.0GHz Dual-core Cortex-A55, DRP-AI(576-MAC), OpenCV Accelerator</p>	<p>RZ/V2L 1.2GHz Dual-core Cortex-A55, DRP-AI(576-MAC), 3D-GPU</p>	<p>RZ/N1S 500MHz Cortex-A7, 125MHz Cortex-M3, Industrial Ethernet</p>	<p>RZ/N2L 400MHz Cortex-R52, Industrial Ethernet</p>
<p>Real-time Control RZ/T Series</p>			<p>RZ/N1L 125MHz Cortex-M3, Industrial Ethernet</p>	<p>RZ/T1 600MHz Cortex-R4, 150MHz Cortex-M3, 1-axis motor control, Industrial Ethernet</p>
<p>IoT Edge RZ/G Series</p>	<p>RZ/T2M 800MHz Dual-core Cortex-R52, 2-axis motor control, Industrial Ethernet</p>	<p>RZ/T2L 800MHz Cortex-R52, 2-axis motor control, EtherCAT</p>	<p>RZ/G3S 1.1GHz Cortex-A55, 250MHz Dual-core Cortex-M33, LPDDR4/DDR4</p>	<p>RZ/Five RISC-V, 1.0GHz AX45MP, DDR4/3L, GbEthernet, CAN-FD</p>
<p>HMI RZ/G Series RZ/A Series</p>	<p>RZ/G1H 1.4GHz Quad-core Cortex-A15 + Cortex-A7, DDR3, 3DG, H.264</p>	<p>RZ/G2H 1.5GHz Quad-core Cortex-A57 + Cortex-A53, LPDDR4, 3DG, H.264/5</p>	<p>RZ/A1H 400MHz Cortex-A9, 10MB RAM, LCDC, JPEG, Ethernet, USB</p>	<p>RZ/A2M 528MHz Cortex-A9, 4MB RAM, LCDC, JPEG, MIPI-CSI, Ethernet, USB</p>
<p>RZ/G1M 1.5GHz Dual-core Cortex-A15, DDR3L, 3DG, H.264</p>	<p>RZ/G2M 1.5GHz Dual-core Cortex-A57 + Cortex-A53, LPDDR4, 3DG, H.264/5</p>	<p>RZ/A1M 400MHz Cortex-A9, 5MB RAM, LCDC, JPEG, Ethernet, USB</p>	<p>RZ/A3UL 1.0GHz Cortex-A55, DDR4/3L, LCDC, GbEthernet, USB</p>	
<p>RZ/G1N 1.5GHz Dual-core Cortex-A15, DDR3L, 3DG, H.264</p>	<p>RZ/G2N 1.5GHz Dual-core Cortex-A57, LPDDR4, 3DG, H.264/5</p>	<p>RZ/A1LU 400MHz Cortex-A9, 3MB RAM, LCDC, JPEG, Ethernet, USB</p>		
<p>RZ/G1E 1.0GHz Dual-core Cortex-A7, DDR3, 3DG, H.264</p>	<p>RZ/G2E 1.2GHz Dual-core Cortex-A53, DDR3L, 3DG, H.264/5</p>	<p>RZ/A1L 400MHz Cortex-A9, 3MB RAM, LCDC, Ethernet, USB</p>		
<p>RZ/G2L 1.2GHz Dual-core Cortex-A55, DDR4/3L, 3DG, H.264, CAN-FD</p>		<p>RZ/A1LC 400MHz Cortex-A9, 2MB RAM, LCDC, Ethernet, USB</p>		
<p>RZ/G2LC 1.2GHz Dual-core Cortex-A55, DDR4/3L, 3DG, CAN-FD</p>				
<p>RZ/G2UL 1.0GHz Cortex-A55, DDR4/3L, CAN-FD, ADC</p>				

Android is a trademark of Google LLC.

RZ/V Series

RZ/V Series Features

- AI performance scalability to cover wide range of applications
- Integrates Renesas original AI accelerator DRP-AI to deliver up to 80TOPS
- Realize best AI power efficiency up to 10TOPS/W
- Integrated ISP (upto 4k) and Video Codec
- Provides Vision Processing Accelerator (OpenCV) as DRP library
- Equipped with a 3D Graphics Engine for fast image rendering

* DRP: Dynamically Reconfigurable Processor

RZ/V Series Application



Service Robot



Smart City



Retail



Smart Home



Industrial




AGV/AMR



AI Camera



Agriculture




Healthcare



Smart Building

Features of DRP-AI

DRP-AI consists of AI-MAC (multiply-accumulate processor) and DRP (reconfigurable processor). AI processing can be executed at high speed by assigning AI-MAC for operations on the convolution layer and fully connected layer, and DRP for other complex processing such as preprocessing and pooling layer.




For more detailed technical information on DRP-AI, please refer to the following white paper.

White Paper: [Embedded AI-Accelerator DRP-AI](#)

[Next Generation Highly Power-Efficient AI Accelerator \(DRP-AI3\): 10x Faster Embedded Processing in Advanced AI for Autonomous Systems](#)

While most AI accelerators specialize only in AI inference and rely on the CPU for pre- and post-processing, DRP-AI integrates pre- and post-processing and AI inference into a single DRP-AI hardware to achieve superior AI processing performance.

	Other AI Accelerator	DRP-AI
Pre-processing	CPU	DRP-AI
Inference	AI Accelerator	DRP-AI
Post-processing	CPU	DRP-AI



RZ/V Series Specification

Items	NEW RZ/V2H	RZ/V2MA	RZ/V2M	RZ/V2L
Main CPU	Cortex®-A55 × 4 Cortex®-R8 × 2	Cortex®-A53 × 2	Cortex®-A53 × 2	Cortex®-A55 × 2
Sub CPU	Cortex®-M33	–	–	Cortex®-M33
AI Accelerator Performance (DRP-AI)	10 TOPS/W Max. 80 TOPS Resnet50: 830 fps	1 TOPS/W Max. 1 TOPS Resnet50: 28 fps	1 TOPS/W Max. 1 TOPS Resnet50: 28 fps	1 TOPS/W Max. 0.5 TOPS Resnet50: 17 fps
ISP for Camera	4K ISP (option) (hardware)	–	4K ISP (hardware)	Simple ISP (software)
MIPI-CS2 I/F	4-lane × 4ch	–	4-lane × 1ch	4-lane × 1ch
Computer Vision Accelerator	OpenCV Accelerator	OpenCV Accelerator	–	OpenCV Accelerator
Video Codec	H.265, H.264	H.265, H.264	H.265, H.264	H.264
Graphics	3D Graphics (option)	–	2D Graphics	3D Graphics
Package	1368pin FHBGA, 19mm × 19mm 0.5mm ball pitch	841pin FCBGA, 15mm × 15mm 0.5mm ball pitch	841pin FCBGA, 15mm × 15mm 0.5mm ball pitch	551pin PBGA, 21mm × 21mm 0.8mm ball pitch 456pin PBGA, 15mm × 15mm 0.5mm ball pitch

RZ/V2M Group

CPU

- 2× Cortex-A53 (up to 1.0GHz)

Vision and AI

- AI Accelerator; DRP-AI at 1.0 TOPS/W class
- Image Signal Processor (ISP) of multi-stream available
- Camera Interface; 2× MIPI CSI-2
- Face and Human Detection Engine

Video and Graphics

- H.265/H.264 Multi Codec
- JPEG Codec Engine
- 2D Graphics Engine

Display Interface

- MIPI-DSI (4-lane)
- HDMI 1.4a

Audio Interface

- Serial Sound Interface × 1ch

Communication Interface

- SD Host × 2ch
- PCI-Express 2.0 (2-lane) × 1ch
- Gigabit Ethernet × 1ch
- USB3.1 Gen1 Host/Function × 1ch
- I²C Bus × 4ch
- SCI × 6ch
- UART × 2ch

Memory Interface

- NAND Flash Interface ONFI1.0 × 1ch
- eMMC 4.5.1 × 1ch
- 32-bit LPDDR4-3200 × 1ch

Security

- Hardware Security Engine

RZ/V2L Group

CPU

- 2× Cortex-A55 or 1× Cortex-A55 (up to 1.2GHz)
- 1× Cortex-M33 (up to 200MHz)

Vision and AI

- AI Accelerator; DRP-AI
- * Image Signal Processor (Simple ISP) Function is provided as DRP Library
- Camera Interface; 1× MIPI CSI-2 / 1× Digital Parallel

Video and Graphics

- H.264 Codec
- 3D Graphics Engine

Display Interface

- MIPI-DSI (4-lane)
- Digital Parallel

Audio Interface

- Serial Sound Interface × 4ch

Communication Interface

- Gigabit Ethernet × 2ch
- USB2.0 Host × 1ch
- USB2.0 Host/Function × 1ch
- I²C Bus × 4ch
- SCI × 2ch
- UART × 5ch


Memory Interface

- SPI Multi I/O (8bit DDR) × 1ch
- SDHI (UHS-I) / eMMC × 1ch
- 16-bit DDR3L-1333/DDR4-1600 × 1ch


Security

- Hardware Security Engine (Option)

RZ/V2M block diagram



RZ/V2L block diagram



RZ/V2MA Group

CPU

- 2× Cortex-A53 (up to 1.0GHz)

Vision and AI

- AI Accelerator; DRP-AI at 1.0 TOPS/W class
- OpenCV Accelerator (DRP)

Video and Graphics

- H.265/H.264 Multi Codec


Communication Interface

- SD Host × 2ch
- PCI-Express 2.0 (2-lane) × 1ch
- Gigabit Ethernet × 1ch
- USB3.1 Gen1 Host/Function × 1ch
- I²C Bus × 4ch
- SCI × 6ch
- UART × 2ch

Memory Interface

- eMMC 4.5.1 × 1ch
- 32-bit LPDDR4-3200 × 1ch

RZ/V2MA block diagram



RZ/V2H Group

CPU

- 4× Cortex-A55 (up to 1.8GHz)
- 2× Cortex-R8 (up to 800MHz)
- 1× Cortex-M33 (up to 200MHz)

Vision and AI

- AI Accelerator: DRP-AI at 10TOPS/W class
- OpenCV Accelerator (DRP)
- Camera Interface: MIPI-CSI2 (1/2/4lane) × 4ch

Video and Graphics

- H.265/H.264 Multi Codec
- 3D Graphics Engine Mali-G31 (Option)
- Image Signal Processor (ISP) Mali-C55 (Option)
- Display OUT: MIPI-DSI (1/2/4lane) × 1ch

Communication Interface


- SD Host × 2ch
- PCI-Express 3.0 (4lane × 1/2lane × 2)
- Gigabit Ethernet × 2ch
- USB3.2 × 2ch, USB2.0 × 1ch

Memory Interface

- eMMC 4.5.1 × 1ch
- 32bit LPDDR4/4X-3200 × 2ch

Security


- Hardware Security Engine (Option)



Flexible Development Kits


These products are evaluation boards with RZ/V series configured as the key device and are capable of easily implementing software development such as camera sensor input image processing, low power consumption AI inference, video streaming, and etc.

RZ/V2H Evaluation Board Kit



- P/N: RTK0EF0168C04000BJ
- LPDDR4X: 8GB × 2
- xSPI Flash Memory: 64MB
- micro SD × 2
- High Speed Interface
 - Gigabit Ethernet × 2
 - USB3.2 Gen2 × 2
 - USB2.0 × 2 (OTG × 1, Host-only × 1)
 - PCIe Gen3 × 1 (4 lanes max)
 - MIPI CSI-2 Camera Interface × 4
 - MIPI DSI Display Interface × 1

RZ/V2L Evaluation Board Kit




- P/N: RTK9754L23S01000BE
- P/N: RTK9754L27S01000BE (Secure Type)
- DDR4 SDRAM: 2GB
- eMMC: 64GB
- QSPI NOR Flash: 512MB
- microSD × 1
- A/D Converter Interface

RZ/V2M Evaluation Board Kit



- P/N: V2M_EVK
- CMOS image sensor equipped board included (SONY/IMX415, CS mount equipped)
- LPDDR4: 32Gbit
- eMMC: 16GB
- HDMI Type-A × 1
- USB3.1 Gen1 Type-C × 1
- microSD × 1

RZ/V2MA Evaluation Board Kit



- P/N: SBEV-RZ/V2MA-KIT
- LPDDR4: 32Gbit
- eMMC: 16GB
- Ethernet × 1
- USB3.1 Gen1 Type-C × 1
- microSD × 1
- PCIe × 4 slot (2-lanes available)

"Easy to Use" with AI SDK



Visit the webpage below for the latest information on AI SDK
https://renesas-rz.github.io/rzv_ai_sdk/latest/

AI SDK eliminates complex build tasks and enables immediate AI evaluation

Renesas RZ/V AI
2.10

The best solution for starting your AI applications.

Provided by Renesas Electronics Corporation

To keep you updated, Watch our GitHub repository

[Watch](#)

▼ AI SDK

AI Applications and AI SDK on RZ/V series

The best solution for starting your AI applications.

AI Applications and AI SDK are quick and easy solutions for starting AI. It provides various AI applications for free.

AI Applications

Application Binary (one-build)
Application Source Code

OR

RZ/V2L AI SDK

Develop/Build

Deploy

Run

RZ/V2L Evaluation Board Kit

1 Choose AI Application based on your use case.

2 Deploy Application with AI SDK. Application Source code build is also available.

3 Run Application on the Board.

[View AI Applications >](#)

[View AI SDK >](#)

The customers only need to select their use case w/o requiring AI training.
 Provided as a free Open-Source Software on Github and can be used in MP.

Agriculture

Apple scab is detected

Smart Building

Illegal intrusion!

Helmet **OK**
Vest **OK**

Smart City

UNAUTHORISED VEHICLES

Bicycle enters in restricted area

Smart Home

Father **World NEWS**

Industrial

Crack Detected

85 people

Retail

Mascaroni

Age: 30~39
Purchased

Healthcare

Need rescue

RZ/N Series


RZ/N Series Features

1. Provides optimized microcontrollers for a variety of industrial network applications
2. Integrated Ethernet switch and EtherCAT slave controller alongside support for major Industrial Ethernet protocols and TSN
3. Redundant network configuration reduces network downtime to zero

1. Provides optimized microcontrollers for a variety of industrial network applications


The RZ/N1 series lineup provides a choice of three CPU options and features the Renesas R-IN engine (“R-IN engine”) and an on-chip 5-port Gigabit Ethernet switch, making it ideal for a variety of industrial network applications. Integrating the functionality of a communication CPU and key peripheral components helps reduce the BOM cost.

The RZ/N2L is optimized for the role of dedicated network companion chip, simplifying the task of adding network functionality to industrial equipment. Since it handles network-related processing independently of the external CPU, Industrial Ethernet support can be implemented without the need to make major changes to the existing application software.



2. Integrated Ethernet switch and EtherCAT slave controller alongside support for major Industrial Ethernet protocols and TSN

A wide range of Industrial Ethernet protocols are supported. Separating application processing and network processing allows for more efficient application control.



3. Redundant network configuration reduces network downtime to zero

Advanced redundant network configuration support helps eliminate network downtime.

- Redundant network connections: Parallel Redundancy Protocol (PRP)
- Looped network connections: HSR (High-availability Seamless Redundancy), DLR (Device Level Ring), RSTP (Rapid Spanning Trees)

RZ/N Series Application



RZ/N2L Group

CPU core

- Arm® Cortex®-R52
- Operating frequency: 400MHz/200MHz
- Single-precision/double-precision floating-point unit

On-chip memory

- Tightly Coupled Memory: 128KB (w/ ECC) + 128KB (w/ ECC)
- 1.5MB on-chip RAM (with ECC)

Features

- TSN support
- 3-port Gigabit Ethernet switch
- EtherCAT slave controller
- Parallel host/serial host interface
- PWM timer
- $\Delta\Sigma$ interface
- ADC
- Trigonometric function unit
- CAN-FD
- USB2.0
- SPI, SCI, I²C
- xSPI


Safety functions

- Register write protection, input clock oscillation stop detection, and CRC
- Isolated peripheral function access via MPU

Packages

- 225-pin FBGA (13mm × 13mm, 0.8mm pitch)
- 121-pin FBGA (10mm × 10mm, 0.8mm pitch)
- T_j = -45°C to +125°C

RZ/N2L Group block diagram



RZ/N2L Product Lineup

Part Number	R9A07G084M08GBG	R9A07G084M04GBG	R9A07G084M08GBA	R9A07G084M04GBA
CPU	Cortex®-R52 (Max 400MHz)			
Tightly Coupled Memory	ATCM 128KB (w/ECC) / BTCM 128KB (w/ECC)			
RAM	1.5MB (w/ECC)			
External bus	8, 16bit		Not Supported	
Host I/F	Serial Host	OSPI/QSPI		QSPI
	Parallel Host	8, 16bit		Not Supported
Industrial Ethernet Protocol	EtherCAT®, PROFINET RT/IRT, EtherNet/IP™, TSN (IEC/IEEE 60802 Industrial Profile), CC-Link IE Field Basic, OPC UA over TSN			
Ether Port	3 ports		2 ports	
Motor Control Peripherals	PWM Timer (MTU3, GPT), ADC*, $\Sigma\Delta$ Interface, Trigonometric function unit			
Security	Supported	Not Supported	Supported	Not Supported
Power	1.1V, 1.8V, 3.3V			
Operating Temperature	T _j = -40 to +125°C			
Package	FBGA		FBGA	
Pin Count	225pin		121pin	
Package Information	13mm × 13mm, 0.8mm pitch		10mm × 10mm, 0.8mm pitch	

* 225pin only

RZ/N1D Group

CPU core

- Arm® Cortex®-A7 dual-core processor
- Operating frequency: 500MHz

Cache memory

- L1 I-cache: 16KB × 2, D-cache: 16KB × 2
- L2: 256KB

Internal memory

- 2MB (ECC)

External memory

- DDR2/DDR3 controller
- Quad I/O SPI
- SDIO eMMC
- NAND flash controller

R-IN engine

- Arm® Cortex®-M3
- Operating frequency: 125MHz
- HW-RTOS accelerator
- Ethernet accelerator

Main Ethernet communication functions

- EtherCAT slave controller
- Sercos® III slave controller
- HSR switch (400-pin)
- 5-port Ethernet switch

Other communication functions

- UART × 8 channels
- I²C × 2 channels
- USB Host/Function × 1 channel, Host 1 channel
- SPI × 6 channels (master × 4 channels, slave × 2 channels)
- CAN

Other functions

- LCD controller
- ADC: 12-bit × 8 channels × 2 units (400-pin)
- ADC: 12-bit × 8 channels × 1 unit (324-pin)
- PWM timer, GPT


Package

- 400-pin: LFBGA, 17 × 17mm, 0.8mm pin pitch
- 324-pin: LFBGA, 15 × 15mm, 0.8mm pin pitch


Operating temperature

- T_j = -40°C to +110°C

RZ/N1D Group block diagram



Application example: Programmable logic controller block diagram



RZ/N1S Group

CPU core

- Arm® Cortex®-A7 single-core processor
- Operating frequency: 500MHz

Cache memory

- L1 I-cache: 16KB, D-cache: 16KB
- L2: 128KB

Internal memory

- 6MB (ECC)

External memory

- Quad I/O SPI
- SDIO eMMC
- NAND flash controller

R-IN engine

- Arm® Cortex®-M3
- Operating frequency: 125MHz
- HW-RTOS accelerator
- Ethernet accelerator

Main Ethernet communication functions

- EtherCAT slave controller
- Sercos® III slave controller
- 5-port Ethernet switch

Other communication functions

- UART × 8 channels
- I²C × 2 channels
- USB Host/Function × 1 channel, Host 1 channel
- SPI × 6 channels (master × 4 channels, slave × 2 channels)
- CAN

Other functions

- LCD controller
- ADC: 12-bit × 8 channels × 1 unit
- PWM timer, GPT


Package

- 324-pin: LFBGA, 15 × 15mm, 0.8mm pin pitch
- 196-pin: LFBGA, 12 × 12mm, 0.8mm pin pitch


Operating temperature

- T_j = -40°C to +110°C

RZ/N1S Group block diagram



Application example: Sensor Hub block diagram



RZ/N1L Group

R-IN engine

- Arm® Cortex®-M3
- Operating frequency: 125MHz
- HW-RTOS accelerator
- Ethernet accelerator

Internal memory

- 6MB (ECC)

External memory

- Quad I/O SPI
- SDIO eMMC
- NAND flash controller

Main Ethernet communication functions

- EtherCAT slave controller
- Sercos® III slave controller
- GbE Ethernet switch

Other communication functions

- UART × 8 channels
- I²C × 2 channels
- USB Host/Function × 1 channel, Host 1 channel
- SPI × 6 channels (master × 4 channels, slave × 2 channels)
- CAN × 2 channels

Other functions

- LCD controller
- ADC: 12-bit × 8 channels × 1 unit
- PWM timer, GPT


Package

- 196-pin: LFBGA, 12 × 12mm, 0.8mm pin pitch







Operating temperature

- T_j = -40°C to +110°C

RZ/N1L Group block diagram



RZ/N2L: Development Environments (Integrated Development Environments)

		
Development environments	<ul style="list-style-type: none"> • IAR Embedded Workbench® for Arm® 	<ul style="list-style-type: none"> • e² studio*¹ 
Compilers	<ul style="list-style-type: none"> • IAR C/C++ compiler*² 	<ul style="list-style-type: none"> • GNU tool*⁴
Other tools	<ul style="list-style-type: none"> • AP4 and FSP Smart Configurator code generation tools from Renesas can be used. 	<ul style="list-style-type: none"> • Code generation function available as a plug-in.
ICEs	<ul style="list-style-type: none"> • I-jet™/I-jet Trace™ for Arm Cortex®-A/R/M • JTAGjet-Trace 	<ul style="list-style-type: none"> • J-Link LITE from Segger • J-Link series from Segger*⁵ 

*1. Eclipse-based development environment from Renesas (<http://renesas.com/e2studio>)










*2. Two versions of the software are available for download free of charge. One limits the code size to 32KB and can be used with no time limitation. The other has no limit on code size and expires after 30 days. (<https://www.iar.com/EWARM>)

*3. Arm CC is included in DS-5. In addition to the popularly priced DS-5 RZ/A and RZ/T editions, a fully functional evaluation version of DS-5 that expires after 30 days is available free of charge. Contact your DS-5 dealer for details.

*4. GNU TOOLS & SUPPORT Website (<https://lvm-gcc-renesas.com/>)

*5. Renesas does not handle ICEs from Segger. Contact a sales agent for details.

RZ/N2L: Development Tools (Debuggers, ICes)

	 KMC Kyoto Microcomputer Co., Ltd.	 DTS INSIGHT Our insight, your value	 LAUTERBACH DEVELOPMENT TOOLS
Debuggers	<ul style="list-style-type: none"> • PARTNER-Jet2 	<ul style="list-style-type: none"> • microVIEW-PLUS 	<ul style="list-style-type: none"> • TRACE32 PowerView 
ICes		<ul style="list-style-type: none"> • adviceLUNA II 	<ul style="list-style-type: none"> • TRACE32 PowerDebug & PowerTrace 
Supported compilers	<ul style="list-style-type: none"> • exeGCC from Kyoto Microcomputer • GNU tool*¹ • Arm CC*² • IAR C/C++ compiler,*³ etc. 	<ul style="list-style-type: none"> • Arm CC*² • GNU tool,*¹ etc. 	<ul style="list-style-type: none"> • Arm CC*² • GNU tool*¹ • IAR C/C++ compiler*³ etc.

*1. GNU TOOLS & SUPPORT Website (<https://lvm-gcc-renesas.com/>)

*2. Arm CC is included in DS-5. In addition to the popularly priced DS-5 RZ/A and RZ/T editions, a fully functional evaluation version of DS-5 that expires after 30 days is available free of charge. Contact your DS-5 dealer for details.

*3. Two versions of the software are available for download free of charge. One limits the code size to 32KB and can be used with no time limitation. The other has no limit on code size and expires after 30 days. (<https://www.iar.com/EWARm>)

Code Generation Support: Flexible Software Package (FSP) + Smart Configurator (SC)


The FSP includes everything you'll need to start developing software: board-dependent programs, peripheral function drivers, middleware, and documentation on how to use them.

Smart Configurator is a utility based on the concept of "combining software components freely." The intuitive GUI makes it easy to configure pins and FSP driver settings and to generate source code customized for your use case. It works together with integrated development environments such as IAR Embedded Workbench® for Arm from IAR Systems and e² studio.

Flexible Software Package (FSP)

FreeRTOS Real-time tasks: Mutexes Software timer execution trace function Stack overflow detection RAM allocation Preemptive scheduler Inter-task communication Memory management	Connectivity FreeRTOS + TCP					
	Hardware Abstraction Layer (HAL) Drivers					
USBHS	ADC	Data Signal Interface	IOPORT	POE3	POEG	
SCI I2C	xSPI	GPT	CMT	ELC	GMAC	
SCI SPI			CMTW			
PC Master PC Slave	CRC	WDT	Core to Core	DMA	Ethernet Switch	
MTU3	CAN CANFD	RTC	CGC	DOC	TSU	
LPM	ERROR	ICU	SHM			

Board Support Package (BSP)



Renesas Starter Kit+ for RZ/N2L

<https://www.renesas.com/rskrzn2l> 

- The board is mounted with a RZ/N2L with a 225BGA package and can be used to evaluate almost all of the device's functions.
- Emulator circuit is mounted, can start program debugging by simply connecting USB cable to PC.
- Ordering number: RTK9RZN2LOS00000BE



- 225-pin RZ/N2L MPU (R9A07G084M04GBG)
- Gigabit Ethernet PHY
- Octal flash memory
- Pmod™, Grove®, QWIIC®, and mikroBUS™ connectors
- Pin header for external expansion
- Includes a USB power cable that can also be used to connect an emulator.

RZ/N2L Industrial Network SOM Kit

<https://www.renesas.com/yconnect-it-rzn2l> 

- YCONNECT-IT-RZN2L is a compact reference kit for evaluating applications using Industrial Ethernet communication
- Flexible power supply from either USB or 24V DC terminal or Arduino host board
- Ordering number: YCONNECT-IT-RZN2L



- 2x Gigabit Industrial Ethernet connectors
- 2x PMOD connectors
- Arduino dual-use connector
- 9-pin connector for external debugger connection and Segger J-Link OB for debugging via USB

CONNECT IT! ETHERNET RZ/N

<https://www.renesas.com/RZN-YConnect-It> 

- CONNECT IT! ETHERNET RZ/N is the perfect solution kit for developers new to developing with the RZ/N1.
- The kit comes with not only an evaluation board, but also a JTAG emulator and various sample software.
- It is possible to evaluate master communication / slave communication of industrial networks.



- JTAG emulator
 - IAR I-jet Lite (20-pin flat ribbon/USB cable)
- 2 USB cables
- Startup manuals
- Pin setting tool
- RZ/N Solution Kit DVD
 - User's manual
 - OS (Linux, ThreadX®(Evaluation version), HW-RTOS)
 - Software PLC Codesys
 - Protocol stacks

RZ Ecosystem Solutions from Partner Companies

Visit the webpage below for the information on RZ/N series solutions from partner companies.
<https://www.renesas.com/products/microcontrollers-microprocessors/rz-mpus/rz-partner-solutions> 




RZ/T Series

RZ/T Series Features


- High-performance, high-speed real-time control
- Integrated peripheral functions

High-performance, high-speed real-time control



- High-speed RAM directly coupled to the CPU allows fast processing and bypassing of the cache for reliable real-time responsiveness.
- ECC for enhanced reliability
- Assures responsive interrupt handling suitable for embedded control applications.

■ Integrated peripheral functions




- Integrates communication ASSP that would previously have been implemented as an external device.
- Integrates encoder interface that would previously have been implemented by an FPGA or ASIC.

	EnDat 2.2	BiSS-C	NIKON A-format	FA-CODER	HIPERFACE DSL
Related specifications	Heidenhain Corp http://www.heidenhain.de	iC-Haus GmbH http://www.biss-interface.com	NIKON Corporation http://www.nikon.co.jp	TAMAGAWA SEIKI CO.,LTD. http://www.tamagawa-seiki.co.jp	SICK STEGMANN GmbH http://www.sick.com
Communication system	Clock synchronous	Clock synchronous	Asynchronous	Asynchronous	Asynchronous
Transmission link	RS-485	RS-422	RS-485	RS-485	RS-485
Supported frequencies/data transfer rates	100kHz to 16.7MHz	62.5kHz to 10MHz	2.5Mbps, 4Mbps, 6.67Mbps, 8Mbps, 16Mbps	2.5Mbps	9.375Mbps
I/O pin count/signal level	4/3.3V TTL level	2 / 3.3V TTL level	3 / 3.3V TTL level	3 / 3.3V TTL level	3 / 3.3V TTL level
Compatible functions on T series	<ul style="list-style-type: none"> - Propagation delay function - Not supported for incremental signals 	<ul style="list-style-type: none"> - Delay compensation function - Supported in C mode (not supported in B mode) - Not supported for incremental signals - Supported on 1-to-1 connections (not supported on bus connections) 	<ul style="list-style-type: none"> - Supported on 1-to-1 connections and bus connections 	<ul style="list-style-type: none"> - Baseband NRZ code support - Not supported for incremental signals or synchronous Manchester code 	<ul style="list-style-type: none"> - External synchronous communication (sync mode) - Asynchronous communication (free running mode) - Estimator function (position estimation when error occurs) - RSSI, quality monitoring

RZ/T Series Application

A fast CPU operating at 300MHz to 800MHz and large-capacity tightly-coupled memory provide the high performance and advanced functionality required by industrial applications such as industrial motors or AC servo drives. The RZ/T series is powerful enough to handle Industrial Ethernet processing of various types while still maintaining real-time performance.



RZ/T2M Group

CPU core

- Arm® Cortex®-R52 × 2
- Operating frequency: 800MHz/400MHz/200MHz
- Single-precision/double-precision floating-point unit

On-chip memory

- Tightly Coupled Memory: 512KB (W/ ECC) + 64KB (W/ ECC)
- 2MB on-chip RAM (with ECC)

Features

- Low latency peripheral port (LLPP) bus
- TSN support
- 3-port Gigabit Ethernet switch
- EtherCAT slave controller
- Encoder interface
- PWM timer
- $\Delta\Sigma$ interface
- ADC
- Trigonometric function unit
- xSPI
- CAN-FD
- USB2.0
- SPI, SCI, I²C


Safety functions

- Register write protection, input clock oscillation stop detection, and CRC
- Isolated peripheral function access via MPU

Packages

- 320-pin FBGA (17mm × 17mm, 0.8mm pitch)
- 225-pin FBGA (13mm × 13mm, 0.8mm pitch)
- 176-pin LQFP (24mm × 24mm, 0.5mm pitch)
- 128-pin LQFP (14mm × 20mm, 0.5mm pitch)
- T_j = -45°C to +125°C

RZ/T2M Group block diagram



RZ/T2M Product Lineup

Security	R9A07G075M28GBG	R9A07G075M26GBG	R9A07G075M28GBA	R9A07G075M26GBA	R9A07G075M27GBA	—	R9A07G075M05GFP	R9A07G075M05GFA
Non-Security	R9A07G075M24GBG	R9A07G075M22GBG	R9A07G075M24GBA	R9A07G075M22GBA	—	R9A07G075M21GBA	R9A07G075M01GFP	R9A07G075M01GFA
CPU	Dual Cortex®-R52 (800+800MHz)						Single Cortex®-R52 (800MHz)	
System RAM	2.0MB w/ECC						1.5MB w/ECC	
TCM Memory	CPU0 : ATCM: 512KB w/ECC, BTCM: 64KB w/ECC CPU1 : ATCM: none, BTCM: none						CPU0 : ATCM: 512KB w/ECC, BTCM: 64KB w/ECC	
$\Sigma\Delta$ interface	3ch \times 2 units							
Encoder I/F Protocol	A-format™, BiSS-C, EnDat2.2, FA-CODER®, HIPERFACE DSL®							
Motor Control Peripherals	PWM Timer (MTU3, GPT), $\Sigma\Delta$ Interface, 12bit ADC, Encoder Interface, Trigonometric Accelerator							
Ethernet Port	3ports (100/1000Mbps)				None			
EtherCAT Port	Max 3ports (Exclusive with Ethernet)				None			
Industrial Ethernet Protocol	EtherCAT®, PROFINET RT/IRT, EtherNet/IP™, CC-Link IE Basic, TSN (IEC/IEEE 60802 Industrial Profile), OPC UA over TSN				None			
CAN	CAN FD \times 2ch	Classic CAN \times 2ch	CAN FD \times 2ch	Classic CAN \times 2ch	CAN FD \times 2ch	Classic CAN \times 2ch	Classic CAN \times 2ch	Classic CAN \times 2ch
Package	BGA320 (17mm \times 17mm, 0.8mm pitch)		BGA225 (13mm \times 13mm, 0.8mm pitch)			QFP176 (24mm \times 24mm, 0.5mm pitch)		QFP128 (14mm \times 20mm, 0.5mm pitch)
Power Supply	1.1V, 1.8V, 3.3V							
Operating Temperature	Tj = -40 to +125°C							

* More protocols will be supported in the future

RZ/T2L Group

CPU core

- Arm® Cortex®-R52
- Operating frequency: 800MHz/400MHz/200MHz
- Single-precision/double-precision floating-point unit

On-chip memory

- Tightly Coupled Memory: 512KB (W/ ECC) + 64KB (W/ ECC)
- 1MB on-chip RAM (with ECC)

Features

- Low latency peripheral port (LLPP) bus
- EtherCAT slave controller
- Gigabit Ether MAC
- Encoder interface
- PWM timer
- $\Delta\Sigma$ interface
- ADC
- Trigonometric function unit
- Serial host interface
- xSPI
- CAN-FD
- USB2.0
- SPI, SCI, I²C


Safety functions

- Register write protection, input clock oscillation stop detection, and CRC
- Isolated peripheral function access via MPU


Packages

- FBGA 196pin (12mm × 12mm, 0.8mm pitch)
- T_j = -45°C to +125°C

Application example: AC servo system block diagram



RZ/T2L Group block diagram



RZ/T2L Product Lineup

Part Number	R9A07G074M08GBG	R9A07G074M05GBG	R9A07G074M04GBG	R9A07G074M01GBG
CPU	Cortex®-R52 (Max 800MHz)			
System RAM	1.0MB (w/ECC)			
TCM Memory	ATCM 512KB (w/ECC) / BTCM 64KB (w/ECC)			
External bus	8, 16 bit			
Peripheral functions for motor control	PWM Timer (MTU3, GPT), ADC, $\Delta\Sigma$ interface, Trigonometric function unit			
GMAC	1 ch			
Ethernet Port	3 ports			
EtherCAT	Supported	Not Supported	Supported	Not Supported
CAN	CAN-FD	CAN	CAN-FD	CAN
Security	Supported	Supported	Not Supported	Not Supported
Package	BGA196 (12mm × 12mm, 0.8mm pitch)			
Power Supply	1.1V, s1.8V, 3.3V			
Operating Temperature	T _j = -40 to +125°C			

RZ/T1 Group

CPU core

- Arm® Cortex®-R4
- Operating frequency: 600MHz/400MHz/300Hz
- High-performance, high-speed real-time control
- Single-precision/double-precision floating-point unit

Renesas R-IN engine ("R-IN engine")

- Arm® Cortex®-M3
- Operating frequency: 125MHz
- HW-RTOS accelerator
- R-IN engine instruction memory: 512KB (w/ ECC) + data memory: 512KB (w/ ECC)

On-chip memory

- Tightly Coupled Memory: 512KB (w/ ECC) + 32KB (w/ ECC)
- Extended RAM instruction memory 512KB (w/ ECC) + data memory: 512KB (w/ ECC)


Features

- Industrial Ethernet communication accelerator with multi-protocol support (R-IN engine)
- EtherCAT slave controller
- PWM timer: MTU3a, GPT
- Encoder interface (Nikon A-format™/BiSS-C/EnDat2.2/HIPERFACE DSL®/FA-CODER®)

Note: 2ch encoder support depends on the combination of the selected protocol.

- High Speed USB
 - Secure boot (option)
 - Safety functions
 - ECC memory
 - CRC (32-bit)
 - Independent WDT: Operating on dedicated on-chip oscillator
 - $\Delta\Sigma$ interface
 - 100Mbps EtherMAC (with Ethernet switch)
 - Ethernet accelerator
 - Power supply voltage: 1.2V, 3.3V
- ### Package
- FBGA 320pin (17mm × 17mm, 0.8mm pitch)
 - QFP 176pin (20mm × 20mm, 0.4mm pitch)
 - Tj = -45°C to +125°C

RZ/T1 Group block diagram



RZ/T1 Product Lineup

CPU	Tightly coupled memory	Extended RAM							
600 MHz + R-IN Engine (150MHz)	512KB+32KB	– (1MB for R-IN)						R7S910017	R7S910018
450 MHz + R-IN Engine (150MHz)	512KB+32KB	– (1MB for R-IN)						R7S910015	R7S910016
600 MHz	512KB+32KB	1MB		R7S910007	R7S910013	R7S910027	R7S910028		
450 MHz	512KB+32KB	1MB		R7S910006		R7S910025	R7S910026		
		–	R7S910001	R7S910002	R7S910011				
300 MHz	512KB+32KB	–				R7S910035	R7S910036		
Package			176 QFP	320 BGA	320 BGA	320 BGA	320 BGA	320 BGA	320 BGA
Encoder I/F			–		Yes	–	Yes	–	Yes
Industrial Ethernet			– (Standard Ethernet)			EtherCAT		Multi-protocol support	

Utilizing the Arm® Ecosystem

Utilizing Renesas' Experience and the Arm® Ecosystem

Customers can benefit from solutions combining Renesas' accumulated experience in the microcontroller industry and the global ecosystem of Arm® partners. Products such as development environments, OS, and middleware are available from partner companies supporting the RZ/T series.



RZ/T Series: Development Environments (Integrated Development Environments)

Development environments	<ul style="list-style-type: none"> IAR Embedded Workbench® for Arm® 	<ul style="list-style-type: none"> e² studio*1
Compilers	<ul style="list-style-type: none"> IAR C/C++ compiler*2 	<ul style="list-style-type: none"> GNU tool*4
Other tools	<ul style="list-style-type: none"> AP4 and FSP Smart Configurator code generation tools from Renesas can be used. 	<ul style="list-style-type: none"> Code generation function available as a plug-in.
ICEs	<ul style="list-style-type: none"> I-jet™/I-jet Trace™ for Arm Cortex®-A/R/M JTAGjet-Trace 	<ul style="list-style-type: none"> J-Link LITE from Segger J-Link series from Segger*5

*1. Eclipse-based development environment from Renesas (<http://renesas.com/e2studio>)

*2. Two versions of the software are available for download free of charge. One limits the code size to 32KB and can be used with no time limitation. The other has no limit on code size and expires after 30 days. (<https://www.iar.com/EWARM>)

*3. Arm CC is included in DS-5. In addition to the popularly priced DS-5 RZ/A and RZ/T editions, a fully functional evaluation version of DS-5 that expires after 30 days is available free of charge. Contact your DS-5 dealer for details.

*4. GNU TOOLS & SUPPORT Website (<https://lvm-gcc-renesas.com/>)

*5. Renesas does not handle ICEs from Segger. Contact a sales agent for details.

RZ/T Series: Development Tools (Debuggers, ICEs)

	 Kyoto Microcomputer Co., Ltd.	 Our insight, your value	 DEVELOPMENT TOOLS	
Debuggers	<ul style="list-style-type: none"> PARTNER-Jet2 	<ul style="list-style-type: none"> microVIEW-PLUS 	<ul style="list-style-type: none"> TRACE32 PowerView 	<ul style="list-style-type: none"> CSIDE version 7
ICEs		<ul style="list-style-type: none"> adviceLUNA II 	<ul style="list-style-type: none"> TRACE32 PowerDebug & PowerTrace 	<ul style="list-style-type: none"> PALMiCE4 <p>JTAG model Large capacity trace model</p>
Supported compilers	<ul style="list-style-type: none"> exeGCC from Kyoto Microcomputer GNU tool*1 Arm CC*2 IAR C/C++ compiler,*3 etc. 	<ul style="list-style-type: none"> Arm CC*2 GNU tool,*1 etc. 	<ul style="list-style-type: none"> Arm CC*2 GNU tool*1 IAR C/C++ compiler*3 etc. 	<ul style="list-style-type: none"> Arm CC*2 IAR C/C++ compiler*3 GNU tool,*1 etc.
Supported product	RZ/T1, RZ/T2M		RZ/T1, RZ/T2M, RZ/T2L	RZ/T1

*1. GNU TOOLS & SUPPORT Website (<https://lvm-gcc-renesas.com/>)

*2. Arm CC is included in DS-5. In addition to the popularly priced DS-5 RZ/A and RZ/T editions, a fully functional evaluation version of DS-5 that expires after 30 days is available free of charge. Contact your DS-5 dealer for details.

*3. Two versions of the software are available for download free of charge. One limits the code size to 32KB and can be used with no time limitation. The other has no limit on code size and expires after 30 days. (<https://www.iar.com/EWARM>)

Code Generation Support: Flexible Software Package (FSP) + Smart Configurator (SC)

(Supported product: RZ/T2M, RZ/T2L)


The FSP includes everything you'll need to start developing software: board-dependent programs, peripheral function drivers, middleware, and documentation on how to use them.

Smart Configurator is a utility based on the concept of "combining software components freely." The intuitive GUI makes it easy to configure pins and FSP driver settings and to generate source code customized for your use case. It works together with integrated development environments such as IAR Embedded Workbench® for Arm from IAR Systems and e² studio.

Flexible Software Package (FSP)

FreeRTOS Real-time tasks Mutexes Software time execution trace function Stack overflow detection RAM allocation Preemptive scheduler Inter-task communication Memory management	Connectivity FreeRTOS + TCP					
Hardware Abstraction Layer (HAL) Drivers						
USBHS USBFS	ADC	Dts+Sigma Interface	IOPORT	POE3	PDEG	
SCI I2C SCI SPI	xSPI	GPT	CM1 CMTW	ELC	GMAC	
IC Master IC Slave	CRC	WDT	Core to Core		Ethernet Switch	
MTU3	CAN CANFD	RTC	CGC	DOC	TSU	
LPM	ERROR	ICU	SHM			

Board Support Package (BSP)





Code Generation Support Tool: AP4

(Supported product: RZ/T1)

AP4 is a standalone tool that automatically generates peripheral function control programs (device driver programs) based on settings entered by the user. The build tool (compiler) is selectable. This makes it possible to generate peripheral function control program code to match a specific build tool and enables interoperation with integrated development environments. (<https://www.renesas.com/ap4>)

The version of AP4 that is compatible with the RZ/T1 group can generate compatible source code for IAR Embedded Workbench® for Arm® from IAR Systems, Development Studio (DS-5™) from Arm®, and e² studio (GNU Tools).



RZ Ecosystem Solutions from Partner Companies

Visit the webpage below for the information on RZ/T series solutions from partner companies. <https://www.renesas.com/products/microcontrollers-microprocessors/rz-mpus/rz-partner-solutions>



Development Kits

RZ/T2 Starter Kit mounted emulator circuit by SEGGER, user can start program debugging by simply connecting USB cable to PC. The AC servo solution kit can easily be used for initial evaluation and advance development of servo system or motion controller development using RZ/T2M, RZ/T2L, or RZ/N2L.

Renesas Starter Kit+ for RZ/T2M



<https://www.renesas.com/rskrzt2m>



- 320-pin RZ/T2M MPU (R9A07G075M24GBG)
- Gigabit Ethernet PHY
- Octal flash memory
- Pmod™, Grove®, QWIIC®, and mikroBUS™ connectors
- Pin header for external expansion
- Includes a USB power cable that can also be used to connect an emulator.
- Ordering number: RTK9RZT2M0S00000BE

Renesas Starter Kit+ for RZ/T2L



www.renesas.com/rskrzt2l



- 196-pin RZ/T2L MPU (R9A07G074M04GBG)
- Gigabit Ethernet PHY
- Octal flash memory
- Pmod™, Grove®, QWIIC®, and mikroBUS™ connectors
- Pin header for external expansion
- Includes a USB power cable that can also be used to connect an emulator.
- Ordering number: RTK9RZT2L0S00000BJ

RZ/T1-Starter-Kit-Plus



<https://www.renesas.com/RZT1-Starter-Kit-Plus>



- RZ/T1 (R7S910018)
- QSPI FlashROM: 64MB
- SDRAM: 64MB × 2
- NOR Flash: 64MB × 2
- Rich interface
- Serial, USB, CAN
- Digilent Pmod I/F (PMOD connector)
- $\Delta\Sigma$ I/F (DSMI connector)
- Ethernet (10/100Base, EtherCAT) I/F etc.
- Audio codec
- Includes SEGGER's simple debug probe "J-Link LITE"
- Includes LCD for debugging
- Ordering number: RTK7910018S01000BE

AC servo solution kit



<https://www.renesas.com/AC-servo-solution-kit>



- Controller board (equipped with RZ/T2M, RZ/T2L or RZ/N2L)
- Inverter board that can drive 220V AC servo motor
- 220V AC Servo Motor
- Renesas offers the utility tool on a PC that can operate the motor with position or speed control by sending control commands via serial communication.

RZ/G Series

RZ/G3 Highlights

Inherits features such as RZ/G2's 64-bit Arm Cortex-A and CIP Linux, and enhances low power consumption, high-speed interface, and security functions.

- 5G Connectivity
 - Enhanced features for high-speed connectivity such as PCI-Express, LTE, and WiFi-6
- Real-time sensing
 - Sub system for real-time sensing powered by Cortex®-M + RTOS, not only main system by Cortex®-A + Linux
- μ W class ultra low power consumption standby mode
 - Enables μ W class ultra low power consumption standby and quick return in Linux applications
- Security with tamper detection
 - Enhanced security for tamper detection in addition to fundamental security features required for IoT applications

RZ/G3S Features and Specification

The RZ/G3S microprocessor is equipped with one Cortex®-A55 (1.1GHz) CPU core and two Cortex®-M33 (250MHz) CPU cores and is an entry-class device for IoT applications that supports ultra-low power consumption mode. It has interfaces suitable for IoT edge devices such as 16-bit LPDDR4 or DDR4, PCIe, CAN-FD, and 12-bit ADC.

Items	RZ/G3S
CPU Cortex-A®	1× Cortex®-A55@1.1GHz L1,L3 Parity/ECC
CPU Cortex-M®	2× Cortex®-M33@250MHz
DRAM I/F	16-bit ×1ch LPDDR4/DDR4-1600 w/ECC
USB	USB2.0×2ch (1Host, 1Host/Function/OTG)
PCIe	PCI-Express Gen2 1ch *14mm Sq Package only
Gbit Ether	2ch
CAN	2ch
12-bit ADC	2ch
Package	359pin, LFBGA, 14mm x 14mm, 0.5mm pitch 361pin, LFBGA, 13mm x 13mm, 0.5mm pitch

RZ/G2 Highlights

- High Performance
 - 64-bit Arm Cortex-A cores, plus powerful 3D graphics engine and video engine capable of supporting up to 4K UHD, to offer the highest performance
- Wide Coverage
 - Entry-level RZ/G2L Group 3 products equipped with Cortex-A55 with improved processing performance have been newly added to the RZ/G2 lineup
- High Reliability
 - Built-in Error Correction Code (ECC) for internal and external memory, which is essential for high-reliability mission critical systems
- Super Long Term Support (SLTS)
 - Applying Civil Infrastructure Platform (CIP) Linux, the Linux kernel will be provided with over 10 years of maintenance
- Verified Linux Package
 - Renesas verifies and provides a Linux package that combines CIP and Linux basic software. Minimize your Linux maintenance resources

RZ/G2 Specification 1

Items	RZ/G2L	RZ/G2LC	RZ/G2UL (Type2) Pin compatible with RZ/G2LC	RZ/G2UL (Type1) Full function
CPU (Arm® Cortex®-A)	1× or 2× Cortex®-A55@1.2GHz L1,L3 Parity/ECC	1× or 2× Cortex®-A55@1.2GHz L1,L3 Parity/ECC	1× Cortex®-A55@1.0GHz L1,L3 Parity/ECC	1× Cortex®-A55@1.0GHz L1,L3 Parity/ECC
CPU (Arm® Cortex®-M)	1× Cortex®-M33@200MHz	1× Cortex®-M33@200MHz	1× Cortex®-M33@200MHz	1× Cortex®-M33@200MHz
DRAM I/F	16-bit ×1ch DDR4-1600/DDR3L-1333 w/ECC	16-bit ×1ch DDR4-1600/DDR3L-1333 w/ECC	16-bit ×1ch DDR4-1600/DDR3L-1333 w/ECC	16-bit ×1ch DDR4-1600/DDR3L-1333 w/ECC
Video in	1×MIPI CSI-2 or 1×Digital Parallel input	1×MIPI CSI-2	1×MIPI CSI-2	1×MIPI CSI-2
Video Codec	Support up to Full HD @30fps resolutions Encoding and Decoding: H.264	–	–	–
3D GFX	Arm Mali-G31 GPU @500MHz	Arm Mali-G31 GPU @500MHz	–	–
Display out	1×MIPI DSI or 1×Digital Parallel output	1×MIPI DSI	–	1×Digital Parallel output
USB	USB2.0×2ch (1Host, 1Host/Function/OTG)	USB2.0×2ch (1Host, 1Host/Function/OTG)	USB2.0×2ch (1Host, 1Host/Function/OTG)	USB2.0×2ch (1Host, 1Host/Function/OTG)
Gbit Ether	2ch	1ch	1ch	2ch
CAN	2ch (support CAN-FD)	2ch (support CAN-FD)	2ch (support CAN-FD)	2ch (support CAN-FD)
12-bit ADC	8ch	–	–	2ch
Package	551pin LFBGA, 21mm×21mm 0.8mm ball pitch 456pin LFBGA, 15mm×15mm 0.5mm ball pitch	361pin LFBGA, 13mm×13mm 0.5mm ball pitch	361pin LFBGA, 13mm×13mm 0.5mm ball pitch	361pin LFBGA, 13mm×13mm 0.5mm ball pitch

← Pin Compatible →

RZ/G2 Specification 2

Items	RZ/G2H	RZ/G2M	RZ/G2N	RZ/G2E
CPU (Arm® Cortex®-A)	4× Cortex®-A57@1.5GHz 4× Cortex®-A53@1.2GHz L1,L2 Parity/ECC	2× Cortex®-A57@1.5GHz 4× Cortex®-A53@1.2GHz L1,L2 Parity/ECC	2× Cortex®-A57@1.5GHz L1,L2 Parity/ECC	2× Cortex®-A53@1.2GHz L1,L2 Parity/ECC
CPU (Arm® Cortex®-R)	1× Cortex®-R7@800MHz L1,TCM w/ECC	1× Cortex®-R7@800MHz L1,TCM w/ECC	1× Cortex®-R7@800MHz L1,TCM w/ECC	1× Cortex®-R7@800MHz L1,TCM w/ECC
DRAM I/F	32-bit ×2ch LPDDR4(3200)	32-bit ×2ch LPDDR4(3200)	32-bit ×1ch LPDDR4(3200)	32-bit ×1ch DDR3L(1856)
Video in	2×MIPI-CSI2, 2×Digital (RGB/YCbCr) up to 8 input image can be captured	2×MIPI-CSI2, 2×Digital (RGB/YCbCr) up to 8 input image can be captured	2×MIPI-CSI2, 2×Digital (RGB/YCbCr) up to 8 input image can be captured	1×MIPI-CSI2, 1×Digital(RGB/YCbCr) up to 2 input image can be captured
Video Codec	Support up to 4k resolutions Decoding: H.265, Encoding and Decoding: H.264	Support up to 4k resolutions Decoding: H.265, Encoding and Decoding: H.264	Support up to 4k resolutions Decoding: H.265, Encoding and Decoding: H.264	Support up to FHD resolutions Decoding: H.265, Encoding and Decoding: H.264
3D GFX	PowerVR GX6650@600MHz	PowerVR GX6250@600MHz	PowerVR GE7800@600MHz	PowerVR GE8300@600MHz
Display out	1×HDMI, 1×LVDS, 1×Digital RGB	1×HDMI, 1×LVDS, 1×Digital RGB	1×HDMI, 1×LVDS, 1×Digital RGB	2×LVDS or 1×LVDS, 1×Digital RGB
USB	USB2.0×2ch (1H, 1H/F/OTG) USB3.0/2.0×1ch (DRD)	USB2.0×2ch (1H, 1H/F/OTG) USB3.0/2.0×1ch (DRD)	USB2.0×2ch (1H, 1H/F/OTG) USB3.0/2.0×1ch (DRD)	USB2.0×1ch (H/F) USB3.0/2.0×1ch (DRD)
Gbit Ether	1ch	1ch	1ch	1ch
CAN	2ch (support CAN-FD)	2ch (support CAN-FD)	2ch (support CAN-FD)	2ch (support CAN-FD)
PCIe	2ch (Rev2.0 1Lane) one of the 2ch is shared with SATA	2ch (Rev2.0 1Lane)	2ch (Rev2.0 1Lane) one of the 2ch is shared with SATA	1ch (Rev2.0 1Lane)
SATA	1ch (Pin Shared)	No	1ch (Pin Shared)	No
Package	1022pin FCBGA, 29mm×29mm 0.8mm ball pitch	1022pin FCBGA, 29mm×29mm 0.8mm ball pitch	1022pin FCBGA, 29mm×29mm 0.8mm ball pitch	552pin FCBGA, 21mm×21mm 0.8mm ball pitch

← Pin Compatible →

RZ/Five (RISC-V) Features and Specification

The RZ/Five is an entry-class general-purpose Linux MPU with a 64-bit RISC-V architecture.

- General-purpose MPU adopting an Open Instruction Set Architecture RISC-V
- Provide development environment to easy mutual migration between ARM and RISC-V
- General-purpose MPU specialized for IoT Edge


Items	RZ/Five
CPU	64bit RISC-V CPU Core AndesCore™ AX45MP Single core 1.0 GHz
DRAM I/F	16-bit × 1ch DDR4-1600/DDR3L-1333 w/ECC
USB	USB2.0 × 2ch (1Host, 1Host/Function/OTG)
Gbit Ether	2ch : 13mm × 13mm Package 1ch : 11mm × 11mm Package
CAN	2ch (support CAN-FD)
12-bit ADC	2ch
Package	361pin, LFBGA, 13mm × 13mm, 0.5mm pitch 266pin, LFBGA, 11mm × 11mm, 0.5mm pitch

Super Long Term Software Support

Renesas RZ/G and RZ/V microprocessors are the only embedded MPUs that meet the long-term support demands for industrial and infrastructure equipment manufacturers through the 10+ year support offered by the Super Long Term Support (SLTS) kernel maintained by the Civil Infrastructure Platform (CIP). The CIP SLTS Linux kernel supports countermeasures against vulnerability to security attacks with a long-term maintenance period of 10 years or more. This reduces Linux maintenance costs and simplifies adoption of reliable industrial-grade Linux.

Verified Linux Package(VLP) Reduces Cost and Simplifies Design

The “Verified Linux Package (VLP)” for the RZ/G and RZ/V series is a combination of the Civil Infrastructure Platform (CIP) Core Package and the basic software (Linux BSP, multimedia, graphics, security, etc.) for IoT devices. This packaged software is verified by Renesas and is available from the Renesas RZ Linux platform site. With VLPs, you can start developing applications quickly while minimizing Linux maintenance resources.




*1: RZ/G Reference Board is used for Kernel development as a software development platform for CIP projects.

Flexible Development Kits

RZ/G2 development kits support the industry standard 96Boards specification and SMARC specification to enable evaluation and speed development with wide variety of mezzanine boards and existing carrier boards. Renesas provides circuit schematics, component BOMs, and board layout data to make it easy to spin your own custom hardware.

RZ/G3S SMARC Module + Carrier Board II



- RZ/G3S SMARC Module
 - Size: 82mm × 80mm
 - Processor: RZ/G3S
 - Main Memory: 1GB DDR4 (1GB × 1)
 - QSPI NOR FLASH: 16MB
 - eMMC Memory: 64GB
 - External Storage: micro SD × 2
 - A/D Converter
 - JTAG connector


Carrier Board II

- Size: 190mm × 130mm
- PCIe 4-lane slot
- M.2 Key E interface, M.2 Key B interface and SIM card interface
- Gigabit Ethernet × 2
- USB2.0 × 2ch (OTG × 1ch, Host × 1ch)
- CAN-FD × 2
- MIPI CSI-2 Camera connector (can connect to Google Coral Camera)
- Micro HDMI (output) connector
- External Storage: micro SD × 1
- Audio Line In × 1
- Audio Line Out × 1
- PMOD × 2
- USB-Type C for Power Input

RZ SMARC v2.1 Module + Carrier Board



- RZ/G2L, RZ/G2LC, RZ/G2UL SMARC Module
 - Size: 82mm × 50mm
 - Processor: RZ/G2L, RZ/G2LC, RZ/G2UL (Type-1)
 - Main Memory: 2GB DDR4 (1GB × 2) *G2UL: 1GB (1GB × 1)
 - QSPI NOR FLASH: 16MB
 - eMMC Memory: 64GB
 - External Storage: micro SD × 1
 - A/D Converter Interface × 2
 - JTAG connector




- RZ/Five SMARC Module
 - Size: 82mm × 50mm
 - Processor: RZ/Five
 - Main Memory: 1GB DDR4 (1GB × 1)
 - QSPI NOR FLASH: 16MB
 - eMMC Memory: 64GB
 - External Storage: micro SD × 1
 - A/D Converter Interface × 2
 - JTAG connector

Carrier Board


- Size: 160mm × 100mm
- Gigabit Ethernet × 2
- USB2.0 × 2ch (OTG × 1ch, Host × 1ch)
- MIPI CSI-2 Camera connector (can connect to Google Coral Camera)
- Micro HDMI (output) connector
- CAN-FD × 2
- External Storage: micro SD × 1
- Audio Line In × 1
- Audio Line Out × 1
- PMOD × 2
- USB-Type C for Power Input

RZ/G2H, G2M, G2N Development Kit (96Boards format compatible)



- Main Memory: 4 GB DDR4
- QSPI NOR FLASH: 64MB
- I²C EEPROM: 512bytes
- External Storage: micro SD × 1
- Connectivity: USB 2.0 × 2ch, USB 3.0 × 1ch, GbE × 1
- HDMI out / LVDS out or MIPI DSI out
- Wi-Fi + BT


RZ/G2E Development Kit (96Boards format compatible)



- Main Memory: 2 GB DDR3L
- QSPI NOR FLASH: 64MB
- I²C EEPROM: 512bytes
- External Storage: micro SD × 1
- Connectivity: USB 2.0 × 2ch, USB 3.0 × 1ch, GbE × 1
- HDMI out / LVDS out or MIPI DSI out
- Wi-Fi + BT

RZ/G Series Application

[IoT Application] Optimized for IoT devices by taking advantage of CPU performance, various interface functions, and security functions



RZ/G3S (R9A08G045Sxx)

CPU core

- Arm® Cortex®-A55 single-core
Max. operating frequency: 1.1GHz
- Arm® Cortex®-M33 core x2
Max. operating frequency: 250MHz
Cache memory (Cortex®-A55)
- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L3 cache: 256KB

External memory

- Ability to connect LDDR4-SDRAM / DDR4-SDRAM via DDR dedicated bus
- Data bus width: 16 bits × 1 channel


Storage interfaces

- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 2 channels
- Multimedia card interface × 1 channel (Shared with SDHI)

Other peripheral functions

- 16-bit timer × 8 channels
- I²C bus interface × 4 channels
- Serial communication interface with FIFO (SCIF) × 6 channels
- SPI Multi I/O Bus Controller × 1 channel (4bit Double data rate)
- Serial Peripheral Interface (RSPI) × 5 channels
- Gigabit Ethernet controller × 2 channels
- Controller area network (CAN) interface × 2 channels (support CAN FD)
- 12-bit A/D converter × 8 channels
- Interrupt controller
- Clock generator (CPG): on-chip PLL
- On-chip debug function

RZ/G3S (R9A08G045Sxx) block diagram



RZ/Five [RISC-V] (R9A07G043Fxx)

CPU core

- 64bit RISC-V CPU Core AndesCore™ AX45MP Single core 1.0GHz

Cache memory

- L1 instruction Cache: 32KB
- L1 data cache: 32KB
- L2 cache: 256KB

External memory

- Ability to connect DDR4-SDRAM / DDR3L-SDRAM via DDR dedicated bus
- Data bus width: 16 bits × 1 channel

Audio functions

- Sampling rate converter × 1 channel
- Serial sound interface × 4 channels


Storage interfaces

- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 2 channels
- Multimedia card interface × 1 channel (Shared with SDHI)

Other peripheral functions

- 16-bit timer × 8 channels
- I²C bus interface × 4 channels
- Serial communication interface with FIFO (SCIF) × 5 channels
- Serial communication interface (SCI) × 2 channels
- SPI Multi I/O Bus Controller × 1 channel (4bit Double data rate)
- Serial Peripheral Interface (RSPI) × 3 channels
- Gigabit Ethernet controller × 2 channels
- Controller area network (CAN) interface × 2 channels (support CAN FD)
- 12-bit A/D converter × 2 channels
- Interrupt controller
- Clock generator (CPG): on-chip PLL
- On-chip debug function

RZ/Five [RISC-V] (R9A07G043Fxx) block diagram




*: The 266-pin package has one channel of Gigabit Ethernet.

Package Information: 361-pin, 13 × 13mm PBGA (0.5mm pitch)
266-pin, 11 × 11mm PBGA (0.5mm pitch)

[HMI Application] The HMI can be made more expressive by making full use of the 3D graphics and video capabilities.



HMI Solutions



RZ/G2L (R9A07G044Lxx)

CPU core

- Arm® Cortex®-A55, dual-core or single-core
Max. operating frequency: 1.2GHz
- Arm® Cortex®-M33, single-core
Max. operating frequency: 200MHz

Cache memory (Cortex®-A55)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L3 cache: 256KB

External memory

- Ability to connect DDR4-SDRAM / DDR3L-SDRAM via DDR dedicated bus
- Data bus width: 16 bits × 1 channel

3D graphics

- Arm Mali™-G31 GPU

Video functions

- Video display interface:
MIPI DSI × 1 channel or Digital parallel output × 1 channel
- Video input interface:
MIPI CSI-2 × 1 channel or Digital parallel input × 1 channel
- Video codec module: VCPL4 × 1 channel
- Video image processing functions
(Resizer and Color Space / Color Format Conversion)

Audio functions

- Sampling rate converter × 1 channel
- Serial sound interface × 4 channels


Storage interfaces

- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 2 channels
- Multimedia card interface × 1 channel (Shared with SDHI)

Other peripheral functions

- 32-bit timer × 1 channel
- 16-bit timer × 8 channels
- PWM timer × 8 channels
- I²C bus interface × 4 channels
- Serial communication interface with FIFO (SCIF) × 5 channels
- Serial communication interface (SCI) × 2 channels
- SPI Multi I/O Bus Controller × 1 channel (8bit Double data rate)
- Serial Peripheral Interface (RSPI) × 3 channels
- Gigabit Ethernet controller × 2 channels
- Controller area network (CAN) interface × 2 channels (support CAN FD)
- 12-bit A/D converter × 8 channels
- Interrupt controller
- Clock generator (CPG): on-chip PLL
- On-chip debug function

RZ/G2L(R9A07G044Lxx) block diagram



*Shared

RZ/G2LC (R9A07G044Cxx)

CPU core

- Arm® Cortex®-A55, dual-core or single-core
Max. operating frequency: 1.2GHz
- Arm® Cortex®-M33, single-core
Max. operating frequency: 200MHz

Cache memory (Cortex®-A55)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L3 cache: 256KB

External memory

- Ability to connect DDR4-SDRAM / DDR3L-SDRAM via DDR dedicated bus
- Data bus width: 16 bits × 1 channel

3D graphics

- Arm Mali™-G31 GPU

Video functions

- Video display interface:
MIPI DSI × 1 channel
- Video input interface:
MIPI CSI-2 × 1 channel
- Video image processing functions
(Resizer and Color Space / Color Format Conversion)

Audio functions

- Sampling rate converter × 1 channel
- Serial sound interface × 2 channels


Storage interfaces

- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 2 channels
- Multimedia card interface × 1 channel (Shared with SDHI)

Other peripheral functions

- 32-bit timer × 1 channel
- 16-bit timer × 5 channels
- PWM timer × 4 channels
- I²C bus interface × 4 channels
- Serial communication interface with FIFO (SCIF) × 3 channels
- Serial communication interface (SCI) × 2 channels
- SPI Multi I/O Bus Controller × 1 channel (4bit Double data rate)
- Serial Peripheral Interface (RSPI) × 3 channels
- Gigabit Ethernet controller × 1 channel
- Controller area network (CAN) interface × 2 channels (support CAN FD)
- Interrupt controller
- Clock generator (CPG): on-chip PLL
- On-chip debug function

RZ/G2LC(R9A07G044Cxx) block diagram



*Shared

RZ/G2UL (R9A07G043Uxx)

CPU core

- Arm® Cortex®-A55, single-core
Max. operating frequency: 1.0GHz
- Arm® Cortex®-M33, single-core
Max. operating frequency: 200MHz

Cache memory (Cortex®-A55)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L3 cache: 256KB

External memory

- Ability to connect DDR4-SDRAM / DDR3L-SDRAM via DDR dedicated bus
- Data bus width: 16 bits × 1 channel

Video functions

- Video display interface:
Digital parallel output × 1 channel
- Video input interface:
MIPI CSI-2 × 1 channel
- Video image processing functions
(Resizer and Color Space / Color Format Conversion)

Audio functions

- Sampling rate converter × 1 channel
- Serial sound interface × 4 channels


Storage interfaces

- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 2 channels
- Multimedia card interface × 1 channel (Shared with SDHI)

Other peripheral functions

- 16-bit timer × 8 channels
- I²C bus interface × 4 channels
- Serial communication interface with FIFO (SCIF) × 5 channels
- Serial communication interface (SCI) × 2 channels
- SPI Multi I/O Bus Controller × 1 channel (4bit Double data rate)
- Serial Peripheral Interface (RSPI) × 3 channels
- Gigabit Ethernet controller × 2 channels
- Controller area network (CAN) interface × 2 channels (support CAN FD)
- 12-bit A/D converter × 2 channels
- Interrupt controller
- Clock generator (CPG): on-chip PLL
- On-chip debug function

RZ/G2UL(R9A07G043Uxx) block diagram



(#) There are 2 types in RZ/G2UL.
[Type-1] Full function version
- This block diagram is Type-1.

[Type-2] RZ/G2LC pin compatible version
- No support: Display out, Parallel-IF
- 1×Ether MAC, 3×SCIF, 3×SSI

*Shared

RZ/G2H (R8A774Ex)

CPU core

- Arm® Cortex®-A57, quad-core
Max. operating frequency: 1.5GHz
- Arm® Cortex®-A53, quad-core
Max. operating frequency: 1.2GHz
- Arm® Cortex®-R7, single-core
Max. operating frequency: 800MHz

Cache memory (Cortex®-A57)

- L1 instruction cache: 48KB
- L1 data cache: 32KB
- L2 cache: 2MB

Cache memory (Cortex®-A53)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L2 cache: 512KB

Cache memory (Cortex®-R7)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- I-TCM: 32KB
- D-TCM: 32KB

External memory

- Ability to connect LPDDR4-SDRAM via DDR dedicated bus
- Data bus width: 32 bits × 2 channels
- External expansion
- Ability to connect flash ROM or SRAM directly
- Data bus width: 8/16 bits
- PCI Express 2.0 : 1 Lane × 2 channels (one of PHY is shared with Serial ATA)

3D graphics

- PowerVR™ GX6650

Video functions

- Video display interface × 3 channels (1 channel: HDMI(option), 1 channel: LVDS, 1 channel: RGB888)
- Video input interface × 4 channels (2 channels: MIPI-CSI2, 2 channels: Digital(RGB/YCbCr))

- Video codec module: VCP4 × 1 channel
- IP converter module
- Video image processing functions (color conversion, image enlargement/reduction, filtering)

Audio functions

- Sampling rate converter × 10 channels
- Serial sound interface × 10 channels


Storage interfaces

- USB 3.0 DRD × 1 channel
- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 4 channels
- Multimedia card interface × 2 channels
- Serial ATA interface × 1 channel

Other peripheral functions

- 32-bit timer × 15 channels
- PWM timer × 7 channels
- I²C bus interface × 7 channels
- Serial communication interface (SCIF) × 6 channels
- Quad serial peripheral interface (QSPI) × 2 channels (boot support)
- Clock-synchronous serial interface (MSIOF) × 4 channels (SPI/IIS support)
- Ethernet controller with AVB support (support for IEEE 802.1BA, IEEE 802.1AS, IEEE 802.1Qav, and IEEE 1722)
- Controller area network (CAN) interface × 2 channels
- Interrupt controller (INTC)
- Clock generator (CPG): on-chip PLL
- On-chip debug function

RZ/G2H (R8A774Ex) block diagram



FC-BGA: 29 × 29mm² 1022-pins, 0.8mm pitch

RZ/G2M (R8A774Ax)

CPU core

- Arm® Cortex®-A57, dual-core
Max. operating frequency: 1.5GHz
- Arm® Cortex®-A53, quad-core
Max. operating frequency: 1.2GHz
- Arm® Cortex®-R7, single-core
Max. operating frequency: 800MHz

Cache memory (Cortex®-A57)

- L1 instruction cache: 48KB
- L1 data cache: 32KB
- L2 cache: 2MB

Cache memory (Cortex®-A53)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L2 cache: 512KB

Cache memory (Cortex®-R7)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- I-TCM: 32KB
- D-TCM: 32KB

External memory

- Ability to connect LPDDR4-SDRAM via DDR dedicated bus
- Data bus width: 32 bits × 2 channels

External expansion

- Ability to connect flash ROM or SRAM directly
- Data bus width: 8/16 bits
- PCI Express 2.0 : 1 Lane × 2 channels (one of PHY is shared with Serial ATA)

3D graphics

- PowerVR™ GX6250

Video functions

- Video display interface × 3 channels (1 channel: HDMI(option), 1 channel: LVDS, 1 channel: RGB888)
- Video input interface × 4 channels (2 channels: MIPI-CS12, 2 channels: Digital(RGB/YCbCr))

- Video codec module: VCP4 × 1 channel
- IP converter module
- Video image processing functions (color conversion, image enlargement/reduction, filtering)

Audio functions

- Sampling rate converter × 10 channels
- Serial sound interface × 10 channels


Storage interfaces

- USB 3.0 DRD × 1 channel
- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 4 channels
- Multimedia card interface × 2 channels

Other peripheral functions

- 32-bit timer × 15 channels
- PWM timer × 7 channels
- I²C bus interface × 7 channels
- Serial communication interface (SCIF) × 6 channels
- Quad serial peripheral interface (QSPI) × 2 channels (boot support)
- Clock-synchronous serial interface (MSIOF) × 4 channels (SPI/IIS support)
- Ethernet controller with AVB support (support for IEEE 802.1BA, IEEE 802.1AS, IEEE 802.1Qav, and IEEE 1722, GMII/MII interface, PHY device connection support)
- Ethernet controller with AVB support (support for IEEE 802.1BA, IEEE 802.1AS, IEEE 802.1Qav, and IEEE 1722)
- Controller area network (CAN) interface × 2 channels
- Interrupt controller (INTC)
- Clock generator (CPG): on-chip PLL
- On-chip debug function

RZ/G2M (R8A774Ax) block diagram



RZ/G2N (R8A774Bx)

CPU core

- Arm® Cortex®-A57, quad-core
Max. operating frequency: 1.5GHz
- Arm® Cortex®-R7, single-core
Max. operating frequency: 800MHz

Cache memory (Cortex®-A57)

- L1 instruction cache: 48KB
- L1 data cache: 32KB
- L2 cache: 2MB

Cache memory (Cortex®-R7)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- I-TCM: 32KB
- D-TCM: 32KB

External memory

- Ability to connect LPDDR4-SDRAM via DDR dedicated bus
- Data bus width: 32 bits × 1 channel

External expansion

- Ability to connect flash ROM or SRAM directly
- Data bus width: 8/16 bits
- PCI Express 2.0 : 1 Lane × 2 channels (one of PHY is shared with Serial ATA)

3D graphics

- PowerVR™ GE7800

Video functions

- Video display interface × 3 channels (1 channel: HDMI(option), 1 channel: LVDS, 1 channel: RGB888)
- Video input interface × 4 channels (2 channels: MIPI-CS12, 2 channels: Digital(RGB/YCbCr))

- Video codec module: VCP4 × 1 channel
- IP converter module
- Video image processing functions (color conversion, image enlargement/reduction, filtering)

Audio functions

- Sampling rate converter × 10 channels
- Serial sound interface × 10 channels


Storage interfaces

- USB 3.0 DRD × 1 channel
- USB 2.0 × 2 channels (Host only 1 channel/Host-Function 1 channel)
- SD host interface × 4 channels
- Multimedia card interface × 2 channels
- Serial ATA interface × 1 channel

Other peripheral functions

- 32-bit timer × 15 channels
- PWM timer × 7 channels
- I²C bus interface × 7 channels
- Serial communication interface (SCIF) × 6 channels
- Quad serial peripheral interface (QSPI) × 2 channels (boot support)
- Clock-synchronous serial interface (MSIOF) × 4 channels (SPI/IIS support)
- Ethernet controller with AVB support (support for IEEE 802.1BA, IEEE 802.1AS, IEEE 802.1Qav, and IEEE 1722)
- Controller area network (CAN) interface × 2 channels
- Interrupt controller (INTC)
- Clock generator (CPG): on-chip PLL
- On-chip debug function

RZ/G2N (R8A774Bx) block diagram



RZ/G2E (R8A774C0)

CPU core

- Arm® Cortex®-A53, quad-core
Max. operating frequency: 1.2GHz
- Arm® Cortex®-R7, single-core
Max. operating frequency: 800MHz

Cache memory (Cortex®-A53)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- L2 cache: 256KB

Cache memory (Cortex®-R7)

- L1 instruction cache: 32KB
- L1 data cache: 32KB
- I-TCM: 32KB
- D-TCM: 32KB

External memory

- Ability to connect DDR3L-SDRAM via
DDR dedicated bus

- Data bus width: 32 bits × 1 channel

External expansion

- Ability to connect flash ROM or SRAM
directly

- Data bus width: 8/16 bits

- PCI Express 2.0 : 1 Lane × 1 channel

3D graphics

- PowerVR™ GE8300

Video functions

- Video display interface × 2 channels (2
channels: LVDS, 1 channel: RGB888)
- Video input interface × 3 channels (1
channels: MIPI-CSI2, 2 channels:
Digital(RGB/YCbCr))

- Video codec module: VCP4 × 1 channel
- IP converter module
- Video image processing functions (color
conversion, image enlargement/
reduction, filtering)

Audio functions

- Sampling rate converter × 10 channels
- Serial sound interface × 10 channels

Storage interfaces

- USB 3.0 DRD × 1 channel
- USB 2.0 × 1 channel (Host-Function 1
channel)

- SD host interface × 3 channels

- Multimedia card interface × 1 channel

Other peripheral functions

- 32-bit timer × 15 channels
- PWM timer × 7 channels

- I²C bus interface × 8 channels

- Serial communication interface (SCIF) ×
6 channels

- Quad serial peripheral interface (QSPI)
× 2 channels (boot support)

- Clock-synchronous serial interface
(MSIOF) × 4 channels (SPI/IIS support)

- Ethernet controller with AVB support
(support for IEEE 802.1BA, IEEE 802.1AS,
IEEE 802.1Qav, and IEEE 1722)


- Controller area network (CAN) interface
× 2 channels

- Interrupt controller (INTC)

- Clock generator (CPG): on-chip PLL


- On-chip debug function

RZ/G2E (R8A774C0) block diagram



RZ Partner Ecosystem Solutions

Visit the webpage below for the latest information on RZ partner ecosystem.

<https://www.renesas.com/products/microcontrollers-microprocessors/rz-mpus/rz-partner-solutions> 




RZ/A Series

RZ/A Series Application



Benefits of RZ/A Series — Develop like MCUs

RZ/A series MPUs retain the ease-of-use of Renesas MCUs due to rich integrated development environments, and deliver higher performance than MCUs.




This is an example using Free RTOS.
^{*1} embedded Graphics Multiplatform Library
^{*2} Guiliani Streaming Editor

Benefits of RZ/A3UL


- 64bit CPU@1GHz RTOS MPU
- Choice of two memory I/Fs for different applications
 - Octal-SPI Flash/Octal-SPI RAM: For simple and low cost PCB design
 - DDR3L/DDR4: For high resolution HMI and camera use cases
- Pin-compatible RZ/A3UL (RTOS) and RZ/G2UL (Linux) for easy migration
 - The 361-pin package is pin-compatible between RZ/A3UL and RZ/G2UL

Benefits of RZ/A1 Group, and RZ/A2M MPUs

- Eliminate the need to design a high-speed interface
- Reduced mounting area
- Reduced PCB cost
- No DRAM procurement issues
- Reduced EMI noise



- Include on-chip graphics display and camera input capabilities



DRP Library


- RZ/A2M MPUs with DRP improve image processing performance by 10X over RZ/A1 MPUs
 - Dynamically Reconfigurable Processor (DRP) technology accelerates image processing
 - Enables hybrid e-AI solutions with DRP for image processing + CPU for inference

The RZ/A2M is designed around e-AI for smart appliances, network cameras, service robots, scanner products, and industrial equipment requiring high-speed image processing. The RZ/A2M combines a general-purpose MPU with Renesas' proprietary DRP technology for unique hybrid processing for image recognition and machine vision (MV), and AI processing works in conjunction with the Cortex®-A9, which pre-processes image data at high speed and extracts features for recognition target.

RZ/A3UL Group

- 64-bit Arm® Cortex®-A55 (1 GHz, single core)
- 16bit DDR3L/DDR4-1600 (in line ECC)
- Octal-SPI Flash/RAM IF
- Camera IF; MIPI-CSI2 (4 lanes)
- Display IF; Parallel RGB888/RGB666
- 2x Gigabit Ethernet
- 2x CAN (CAN-FD)
- 2x USB2.0 (Host, Host/Peripheral)
- 2x SDHI (UHS-I, UHS-I/MMC)

RZ/A3UL block diagram



RZ/A2M Group

CPU (Arm® Cortex®-A9)

- Operating frequency: 528MHz
- Single-precision/double-precision FPU
- Arm® NEON™

On-chip memory

- 4MB

Main graphics and camera input functions

- Video display controller (VDC6): 1 channel
LCD output: Max. WXGA
Screen superimposition: 3 layers
Video input: Max. XGA

- CMOS camera input (CEU): 1 channel
- MIPI-CSI2 interface: 1 channel
- Distortion compensation unit (IMR): 1 channel
- 2D graphics engine: 1 channel
- Sprite engine: 1 channel
- JPEG coding engine: 1 channel

Main memory interface functions

- NOR flash, SDRAM, NAND flash
- Serial flash: 1-bit/4-bit/8-bit: 1 channel, 8-bit: 1 channel
(ability to run stored programs directly)
- SD/MMC host interface: 2 channels

Main communication functions

- USB 2.0 High Speed: 2 channels (Host/Function switchable)
- 10M/100M EtherMAC: 2 channels
- SCIF: 5 channels
- I²C: 4 channels
- SSI: 4 channels
- RSPI: 3 channels
- CAN-FD: 2 channels


Optional functions

- DRP (Dynamically Reconfigurable Processor)

Package

- 176-LFBGA (13mm×13mm, 0.8mm pitch)
- 256-LFBGA (11mm×11mm, 0.5mm pitch)
- 272-FBGA (17mm×17mm, 0.8mm pitch)
- 324-FBGA (19mm×19mm, 0.8mm pitch)

RZ/A2M block diagram



RZ/A1H Group and RZ/A1M Group (Pin Compatible)

CPU (Arm® Cortex®-A9)

- Operating frequency: 400MHz
- Single-precision/double-precision FPU
- Arm® NEON™

On-chip memory

- RZ/A1H: 10MB
- RZ/A1M: 5MB

Main graphics and camera input functions

- Video display controller (VDC5): 2 channels
LCD output: Max. WXGA
Screen superimposition: 4 layers
Video input: Max. XGA (CVBS analog input supported)
- CMOS camera input (CEU): 1 channel
- PAL/NTSC decoder (DVDEC): 2 channels
- Distortion compensation unit (IMR): 1 channel

Main memory interface functions

- NOR flash, SDRAM, NAND flash
- QSPI serial flash: 2 channels (ability to run stored programs directly)
- SD host interface: 2 channels
- MMC host interface: 1 channel

Main communication functions

- USB 2.0 High Speed: 2 channels (Host/Function switchable)
- 10M/100M EtherMAC: 1channel
- SCIF: 8 channels
- I²C: 4 channels
- SSI: 6 channels
- RSPI: 5 channels
- Ethernet AVB: 1 channel
- CAN: 5 channels

Package

- 256-LFBGA (11mm × 11mm, 0.5mm pitch)
- 256-LFQFP (28mm × 28mm, 0.4mm pitch)
- 324-FBGA (19mm × 19mm, 0.8mm pitch)

RZ/A1LU Group

CPU (Arm® Cortex®-A9)

- Operating frequency: 400MHz
- Single-precision/double-precision FPU
- Arm® NEON™

On-chip memory

- 3MB

Main graphics and camera input functions

- LCD controller (VDC5): 1 channel
LCD output: Max. WXGA
Screen superimposition: 3 layers
Video input: Max. XGA
- CMOS camera input (CEU): 1 channel
- JPEG coding engine: 1 channel

Main memory interface functions

- NOR flash, SDRAM
- QSPI serial flash: 1 channel (ability to run stored programs directly)
- SD host interface: 2 channels
- MMC host interface: 1 channel


Main communication functions

- USB 2.0 High Speed: 2 channels (Host/Function switchable)
- 10M/100M EtherMAC: 1channel
- SCIF: 5 channels
- I²C: 4 channels
- SSI: 4 channels
- RSPI: 3 channels
- Ethernet AVB: 1 channel
- CAN: 2 channels


Package

- 176-LFBGA (8mm × 8mm, 0.5mm pitch)
- 176-LFQFP (24mm × 24mm, 0.5mm pitch)
- 208-LFQFP (28mm × 28mm, 0.5mm pitch)

RZ/A1H, and RZ/A1M block diagram



RZ/A1LU block diagram



RZ/A1L, RZ/A1LC Group

CPU (Arm® Cortex®-A9)

- Operating frequency: 400MHz
- Single-precision/double-precision FPU
- Arm® NEON™

On-chip memory

- RZ/A1L: 3MB
- RZ/A1LC: 2MB

Main graphics and camera input functions

- LCD controller (VDC5): 1 channel
LCD output: Max. WXGA
Screen superimposition: 3 layers
Video input: Max. XGA

- CMOS camera input (CEU): 1 channel

Main memory interface functions

- NOR flash, SDRAM, NAND flash
- QSPI serial flash: 1 channel (ability to run stored programs directly)
- SD host interface: 2 channels
- MMC host interface: 1 channel


Main communication functions

- USB 2.0 High Speed: 2 channels (Host/Function switchable)
- 10M/100M EtherMAC: 1 channel
- SCIF: 5 channels
- I²C: 4 channels
- SSI: 4 channels
- RSPI: 3 channels
- CAN: 2 channels

Package










- 176-LFBGA (8mm × 8mm, 0.5mm pitch)
- 176-LFQFP (24mm × 24mm, 0.5mm pitch)
- 208-LFQFP (28mm × 28mm, 0.5mm pitch)
- 233-FBGA (15mm × 15mm, 0.8mm pitch)

RZ/A1L, RZ/A1LC block diagram



* RZ/A1L Group specification only.

RZ/A Series: Development Environments (Integrated Development Environments)

			
Development environments	<ul style="list-style-type: none"> e² studio*¹ 	<ul style="list-style-type: none"> Arm® DS 	<ul style="list-style-type: none"> IAR Embedded Workbench® for Arm® 
Compilers	<ul style="list-style-type: none"> GNU Arm Embedded Toolchain 	<ul style="list-style-type: none"> Arm Compiler 	<ul style="list-style-type: none"> IAR C/C++ compiler*³
ICEs	<ul style="list-style-type: none"> J-Link LITE from Segger J-Link series from Segger*² 	<ul style="list-style-type: none"> DSTREAM™ ULINKpro™ ULINKproD™ ULINK2™ 	<ul style="list-style-type: none"> I-jet™/I-jet Trace™ for Arm® Cortex®-A/R/M JTAGjet-Trace 

*1: Eclipse-based development environment from Renesas (<https://www.renesas.com/e2studio>)

*2: Renesas does not handle ICEs from Segger. Contact a sales agent for details.

*3: A free evaluation license is available provided the 14-day time-limited evaluation or the code size-limited evaluation.

RZ/A Series: Development Tools (Debuggers, ICEs)

	 Kyoto Microcomputer Co., Ltd.		 LAUTERBACH DEVELOPMENT TOOLS
Debuggers	<ul style="list-style-type: none"> PARTNER-Jet2 	<ul style="list-style-type: none"> Ozone e² studio 	<ul style="list-style-type: none"> PowerView 
ICEs		<ul style="list-style-type: none"> J-Link Series 	<ul style="list-style-type: none"> PowerDebug 
Supported compilers	<ul style="list-style-type: none"> exeGCC from Kyoto Microcomputer GNU Arm Embedded Toolchain Arm compiler IAR C/C++ compiler, etc. 	<ul style="list-style-type: none"> GNU Arm Embedded Toolchain Arm compiler IAR C/C++ compiler, etc. 	<ul style="list-style-type: none"> GNU Arm Embedded Toolchain Arm compiler IAR C/C++ compiler, etc.

RZ/A Series: Solutions from Partner Companies

Visit the webpage below for the latest information on RZ/A Series development tools, including solutions from partner companies.
<https://www.renesas.com/products/microcontrollers-microprocessors/rz-mpus/rz-partner-solutions> 



RZ Family Package Lineup

Pin-type:	121-LFBGA	128-LFQFP	176-HLQFP	176-LFBGA	176-LFBGA	176-LFQFP
Size:	10 x 10 mm	14 x 20 mm	20 x 20 mm	8 x 8 mm	13 x 13 mm	24 x 24 mm
Pitch:	0.80 mm	0.50 mm	0.40 mm	0.50 mm	0.80 mm	0.50 mm
Thickness:	1.40 mm	1.60 mm	1.70 mm	1.40 mm	1.40 mm	1.60 mm
Group:	RZ/N2L	RZ/T2M	RZ/T1	RZ/A1L, A1LC, A1LU	RZ/A2M	RZ/T2M
Pin-type:	176-LFQFP	196-LFBGA	208-LFQFP	225-LFBGA	233-FBGA	256-LFBGA
Size:	24 x 24 mm	12 x 12 mm	28 x 28 mm	13 x 13 mm	15 x 15 mm	11 x 11 mm
Pitch:	0.50 mm	0.80 mm	0.50 mm	0.80 mm	0.80 mm	0.50 mm
Thickness:	1.70 mm	1.70 mm	1.70 mm	1.40 mm	1.9 mm	1.40 mm
Group:	RZ/A1L, A1LU	RZ/N1L, N1S, RZ/T2L	RZ/A1L, A1LU	RZ/T2M, RZ/N2L	RZ/A1LU	RZ/A2M, A1H, A1M
Pin-type:	256-LFQFP	266-LFBGA	272-FBGA	320-FBGA	324-FBGA	324-FBGA
Size:	28 x 28 mm	11 x 11 mm	17 x 17 mm	17 x 17 mm	19 x 19 mm	19 x 19 mm
Pitch:	0.40 mm	0.40 mm	0.8 mm	0.80 mm	0.80 mm	0.80 mm
Thickness:	1.70 mm	1.40 mm	1.90 mm	2.30 mm	1.40 mm	2.10 mm
Group:	RZ/A1H, A1M	RZ/Five	RZ/A2M	RZ/T1	RZ/T2M	RZ/A2M, A1H, A1M
Pin-type:	324-LFBGA	359-LFBGA	361-LFBGA	361-LFBGA	400-LFBGA	400-LFBGA
Size:	15 x 15 mm	14 x 14 mm	13 x 13 mm	13 x 13 mm	17 x 17 mm	17 x 17 mm
Pitch:	0.80 mm	0.50 mm	0.50 mm	0.50 mm	0.80 mm	0.80 mm
Thickness:	1.70 mm	1.40 mm	1.40 mm	1.40 mm	1.70 mm	1.70 mm
Group:	RZ/N1D, N1S	RZ/G3S	RZ/G2LC, G2UL, RZ/Five	RZ/G3S	RZ/N1D	RZ/N1D
Pin-type:	456-LFBGA	501-FBGA	551-LFBGA	551-LFBGA	552-FBGA	552-FBGA
Size:	15 x 15 mm	21 x 21 mm	21 x 21 mm	21 x 21 mm	21 x 21 mm	21 x 21 mm
Pitch:	0.50 mm	0.80 mm	0.80 mm	0.80 mm	0.80 mm	0.80 mm
Thickness:	1.40 mm	2.40 mm	1.40 mm	1.40 mm	2.45 mm	2.45 mm
Group:	RZ/G2L, V2L	RZ/G1E, G1C	RZ/G2L, V2L	RZ/G2L, V2L	RZ/G2E	RZ/G2E
Pin-type:	831-FBGA	841-FCBGA	1022-FBGA	1022-FBGA	1368-HFBGA	1368-HFBGA
Size:	27 x 27 mm	15 x 15 mm	29 x 29 mm	29 x 29 mm	19 x 19 mm	19 x 19 mm
Pitch:	0.80 mm	0.50 mm	0.80 mm	0.80 mm	0.50 mm	0.50 mm
Thickness:	2.40 mm	1.90 mm ± 0.2 mm	2.5 mm	2.5 mm	2.65 mm	2.65 mm
Group:	RZ/G1H, G1M, G1N	RZ/V2M, RZ/V2MA	RZ/G2M, G2N	3.15 mm RZ/G2H	RZ/V2H	RZ/V2H

Renesas Electronics Corporation TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
 5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
 Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
 7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
 8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
 13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
 14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
 (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 2020.10)

Contact Us

<https://www.renesas.com/contact-us>



Renesas Electronics Corporation

www.renesas.com