

General Description


The 8312 is a low skew, 1-to-12 LVCMOS/ LVTTL Fanout Buffer and a member of the family of High Performance Clock Solutions from IDT. The 8312 single-ended clock input accepts LVCMOS or LVTTL input levels. The low impedance LVCMOS outputs are designed to drive 50Ω series or parallel terminated transmission lines. The effective fanout can be increased from 12 to 24 by utilizing the ability of the outputs to drive two series terminated lines.

The 8312 is characterized at full 3.3V, 2.5V, and 1.8V, mixed 3.3V/2.5V, 3.3V/1.8V and 2.5V/1.8V output operating supply modes. Guaranteed output and part-to-part skew characteristics along with the 1.8V output capabilities makes the 8312 ideal for high performance, single ended applications that also require a limited output voltage.


Features

- Twelve LVCMOS/LVTTL outputs
- CLK input supports the following input types: LVCMOS, LVTTL
- Maximum output frequency: 250MHz
- Output skew: 150ps (maximum)
- Supply modes:
Core/Output
3.3V/3.3V
3.3V/2.5V
3.3V/1.8V
2.5V/2.5V
2.5V/1.8V
1.8V/1.8V
- 0°C to 85°C ambient operating temperature
- Available in lead-free (RoHS 6) package

Block Diagram



Pin Assignment



8312

32-Lead LQFP

7mm x 7mm x 1.4mm package body

Y Package

Top View

Table 1. Pin Descriptions

| Number | Name | Type | | Description |
|---|--|--------|----------|--|
| 1, 5, 8, 12, 16, 17, 21, 25, 29 | GND | Power | | Power supply ground. |
| 2, 7 | V _{DD} | Power | | Positive supply pins. |
| 3 | CLK_EN | Input | Pullup | Synchronous control for enabling and disabling clock outputs. LVCMOS / LVTTTL interface levels. |
| 4 | CLK | Input | Pulldown | Single-ended clock input. LVCMOS/LVTTTL interface levels. |
| 6 | OE | Input | Pullup | Output enable. Controls enabling and disabling of outputs Q[0:11]. LVCMOS / LVTTTL interface levels. |
| 9, 11, 13, 15, 18, 20, 22, 24, 26, 28, 30, 32 | Q11, Q10, Q9, Q8, Q7, Q6, Q5, Q4, Q3, Q2, Q1, Q0 | Output | | Single-ended clock outputs. LVCMOS/LVTTTL interface levels. |
| 10, 14, 19, 23, 27, 31 | V _{DDO} | Power | | Output supply pins. |

NOTE: Pullup and Pulldown refer to internal input resistors. See Table 2, Pin Characteristics, for typical values.

Table 2. Pin Characteristics

| Symbol | Parameter | Test Conditions | Minimum | Typical | Maximum | Units |
|-----------------------|--|--------------------------------|---------|---------|---------|-------|
| C _{IN} | Input Capacitance | | | 4 | | pF |
| R _{PULLUP} | Input Pullup Resistor | | | 51 | | kΩ |
| R _{PULLDOWN} | Input Pulldown Resistor | | | 51 | | kΩ |
| C _{PD} | Power Dissipation Capacitance (per output) | V _{DDO} = 3.465V | | | 19 | pF |
| | | V _{DDO} = 2.625V | | | 18 | pF |
| | | V _{DDO} = 2V | | | 16 | pF |
| R _{OUT} | Output Impedance | V _{DDO} = 3.3V ± 5% | | 7 | | Ω |
| | | V _{DDO} = 2.5V ± 5% | | 7 | | Ω |
| | | V _{DDO} = 1.8V ± 0.2V | | 10 | | Ω |

Function Tables

Table 3A. Output Enable and Clock Enable Function Table

| Inputs | | Outputs |
|--------|--------|-------------------|
| OE | CLK_EN | Q [0:11] |
| 0 | X | Hi-Z |
| 1 | 0 | LOW |
| 1 | 1 | Follows CLK input |

Table 3B. Output Enable and Clock Enable Function Table

| Inputs | | | Outputs |
|--------|--------|-----|----------|
| OE | CLK_EN | CLK | Q [0:11] |
| 1 | 1 | 0 | LOW |
| 1 | 1 | 1 | HIGH |

Absolute Maximum Ratings

NOTE: Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These ratings are stress specifications only. Functional operation of product at these conditions or any conditions beyond those listed in the *DC Characteristics* or *AC Characteristics* is not implied. Exposure to absolute maximum rating conditions for extended periods may affect product reliability.

| Item | Rating |
|--|---------------------------|
| Supply Voltage, V_{DD} | 4.6V |
| Inputs, V_I | -0.5V to $V_{DD} + 0.5V$ |
| Outputs, V_O | -0.5V to $V_{DDO} + 0.5V$ |
| Package Thermal Impedance, θ_{JA} | 47.9°C/W (0 lfm) |
| Storage Temperature, T_{STG} | -65°C to 150°C |

DC Electrical Characteristics

Table 4A. Power Supply DC Characteristics, $V_{DD} = V_{DDO} = 3.3V \pm 5\%$, $T_A = 0^\circ C$ to $85^\circ C$

| Symbol | Parameter | Test Conditions | Minimum | Typical | Maximum | Units |
|-----------|-------------------------|-----------------|---------|---------|---------|-------|
| V_{DD} | Positive Supply Voltage | | 3.135 | 3.3 | 3.465 | V |
| V_{DDO} | Output Supply Voltage | | 3.135 | 3.3 | 3.465 | V |
| I_{DD} | Power Supply Current | | | | 10 | mA |
| I_{DDO} | Output Supply Current | | | | 10 | mA |

Table 4B. Power Supply DC Characteristics, $V_{DD} = V_{DDO} = 2.5V \pm 5\%$, $T_A = 0^\circ C$ to $85^\circ C$

| Symbol | Parameter | Test Conditions | Minimum | Typical | Maximum | Units |
|-----------|-------------------------|-----------------|---------|---------|---------|-------|
| V_{DD} | Positive Supply Voltage | | 2.375 | 2.5 | 2.625 | V |
| V_{DDO} | Output Supply Voltage | | 2.375 | 2.5 | 2.625 | V |
| I_{DD} | Power Supply Current | | | | 10 | mA |
| I_{DDO} | Output Supply Current | | | | 10 | mA |

Table 4C. Power Supply DC Characteristics, $V_{DD} = V_{DDO} = 1.8V \pm 0.2V$, $T_A = 0^\circ C$ to $85^\circ C$

| Symbol | Parameter | Test Conditions | Minimum | Typical | Maximum | Units |
|-----------|-------------------------|-----------------|---------|---------|---------|-------|
| V_{DD} | Positive Supply Voltage | | 1.6 | 1.8 | 2.0 | V |
| V_{DDO} | Output Supply Voltage | | 1.6 | 1.8 | 2.0 | V |
| I_{DD} | Power Supply Current | | | | 10 | mA |
| I_{DDO} | Output Supply Current | | | | 10 | mA |

Table 4D. Power Supply DC Characteristics, $V_{DD} = 3.3V \pm 5\%$, $V_{DDO} = 2.5V \pm 5\%$, $T_A = 0^\circ C$ to $85^\circ C$

| Symbol | Parameter | Test Conditions | Minimum | Typical | Maximum | Units |
|-----------|-------------------------|-----------------|---------|---------|---------|-------|
| V_{DD} | Positive Supply Voltage | | 3.135 | 3.3 | 3.465 | V |
| V_{DDO} | Output Supply Voltage | | 2.375 | 2.5 | 2.625 | V |
| I_{DD} | Power Supply Current | | | | 10 | mA |
| I_{DDO} | Output Supply Current | | | | 10 | mA |

Table 4E. Power Supply DC Characteristics, $V_{DD} = 3.3V \pm 5\%$, $V_{DDO} = 1.8V \pm 0.2V$, $T_A = 0^\circ C$ to $85^\circ C$

| Symbol | Parameter | Test Conditions | Minimum | Typical | Maximum | Units |
|-----------|-------------------------|-----------------|---------|---------|---------|-------|
| V_{DD} | Positive Supply Voltage | | 3.135 | 3.3 | 3.465 | V |
| V_{DDO} | Output Supply Voltage | | 1.6 | 1.8 | 2.0 | V |
| I_{DD} | Power Supply Current | | | | 10 | mA |
| I_{DDO} | Output Supply Current | | | | 10 | mA |

Table 4F. Power Supply DC Characteristics, $V_{DD} = 2.5V \pm 5\%$, $V_{DDO} = 1.8V \pm 0.2V$, $T_A = 0^\circ C$ to $85^\circ C$

| Symbol | Parameter | Test Conditions | Minimum | Typical | Maximum | Units |
|-----------|-------------------------|-----------------|---------|---------|---------|-------|
| V_{DD} | Positive Supply Voltage | | 2.375 | 2.5 | 2.625 | V |
| V_{DDO} | Output Supply Voltage | | 1.6 | 1.8 | 2.0 | V |
| I_{DD} | Power Supply Current | | | | 10 | mA |
| I_{DDO} | Output Supply Current | | | | 10 | mA |

Table 4G. LVC MOS/LVTTL DC Characteristics, $T_A = 0^\circ\text{C}$ to 85°C

| Symbol | Parameter | | Test Conditions | Minimum | Typical | Maximum | Units |
|----------|-----------------------------|------------|--|---------------------|---------|---------------------|---------------|
| V_{IH} | Input High Voltage | | $V_{DD} = 3.465\text{V}$ | 2 | | $V_{DD} + 0.3$ | V |
| | | | $V_{DD} = 2.625\text{V}$ | 1.7 | | $V_{DD} + 0.3$ | V |
| | | | $V_{DD} = 2.0\text{V}$ | $0.65 \cdot V_{DD}$ | | $V_{DD} + 0.3$ | V |
| V_{IL} | Input Low Voltage | | $V_{DD} = 3.465\text{V}$ | -0.3 | | 1.3 | V |
| | | | $V_{DD} = 2.625\text{V}$ | -0.3 | | 0.7 | V |
| | | | $V_{DD} = 2.0\text{V}$ | -0.3 | | $0.35 \cdot V_{DD}$ | V |
| I_{IH} | Input High Current | CLK | $V_{DD} = V_{IN} = 3.465\text{V}$ or 2.625V or 2.0V | | | 150 | μA |
| | | OE, CLK_EN | $V_{DD} = V_{IN} = 3.465\text{V}$ or 2.625V or 2.0V | | | 5 | μA |
| I_{IL} | Input Low Current | CLK | $V_{DD} = 3.465\text{V}$ or 2.625V or 2.0V , $V_{IN} = 0\text{V}$ | -5 | | | μA |
| | | OE, CLK_EN | $V_{DD} = 3.465\text{V}$ or 2.625V or 2.0V , $V_{IN} = 0\text{V}$ | -150 | | | μA |
| V_{OH} | Output High Voltage; NOTE 1 | | $V_{DDO} = 3.3\text{V} \pm 5\%$ | 2.6 | | | V |
| | | | $V_{DDO} = 2.5\text{V} \pm 5\%$; | 1.8 | | | V |
| | | | $V_{DDO} = 2.5\text{V} \pm 5\%$; $I_{OH} = -1\text{mA}$ | 2 | | | V |
| | | | $V_{DDO} = 1.8\text{V} \pm 0.2\text{V}$ | $V_{DD} - 0.3$ | | | V |
| | | | $V_{DDO} = 1.8\text{V} \pm 0.2\text{V}$; $I_{OH} = -100\mu\text{A}$ | $V_{DD} - 0.2$ | | | V |
| V_{OL} | Output Low Voltage; NOTE 1 | | $V_{DDO} = 3.3\text{V} \pm 5\%$ | | | 0.5 | V |
| | | | $V_{DDO} = 2.5\text{V} \pm 5\%$; | | | 0.45 | V |
| | | | $V_{DDO} = 2.5\text{V} \pm 5\%$; $I_{OL} = 1\text{mA}$ | | | 0.4 | V |
| | | | $V_{DDO} = 1.8\text{V} \pm 0.2\text{V}$ | | | 0.35 | V |
| | | | $V_{DDO} = 1.8\text{V} \pm 0.2\text{V}$; $I_{OL} = 100\mu\text{A}$ | | | 0.2 | V |

NOTE 1: Outputs terminated with 50Ω to $V_{DDO}/2$. See Parameter Measurement Information, *Output Load Test Circuit diagrams*.

AC Electrical Characteristics

Table 5A. AC Characteristics, $V_{DD} = V_{DDO} = 3.3V \pm 5\%$, $T_A = 0^\circ\text{C}$ to 85°C

| Parameter | Symbol | Test Conditions | Minimum | Typical | Maximum | Units |
|-------------|---|--|---------|---------|---------|-------|
| f_{MAX} | Output Frequency | | | | 250 | MHz |
| tp_{LH} | Propagation Delay, Low to High; NOTE 1 | $f \leq 250\text{MHz}$ | 1.2 | 1.9 | 2.5 | ns |
| tjit | Buffer Additive Phase Jitter, RMS; refer to Additive Phase Jitter Section | 100MHz, Integration Range: 12kHz – 20MHz | | 0.037 | | ps |
| $tsk(o)$ | Output Skew; NOTE 2, 5 | | | | 125 | ps |
| $tsk(pp)$ | Part-to-Part Skew; NOTE 3, 5 | | | | 800 | ps |
| t_R / t_F | Output Rise/Fall Time; NOTE 5 | 20% to 80% | 200 | | 700 | ps |
| odc | Output Duty Cycle | $f \leq 200\text{MHz}$ | 45 | | 55 | % |

All parameters measured at f_{MAX} unless noted otherwise.

NOTE 1: Measured from the $V_{DD}/2$ of the input to $V_{DDO}/2$ of the output.

NOTE 2: Defined as skew between outputs at the same supply voltage and with equal load conditions. Measured at $V_{DDO}/2$.

NOTE 3: Defined as skew between outputs on different devices operating at the same supply voltage and with equal load conditions. Using the same type of input on each device, the output is measured at $V_{DDO}/2$.

NOTE 4: These parameters are guaranteed by characterization. Not tested in production.

NOTE 5: This parameter is defined in accordance with JEDEC Standard 65.

Table 5B. AC Characteristics, $V_{DD} = V_{DDO} = 2.5V \pm 5\%$, $T_A = 0^\circ\text{C}$ to 85°C

| Parameter | Symbol | Test Conditions | Minimum | Typical | Maximum | Units |
|-------------|---|--|---------|---------|---------|-------|
| f_{MAX} | Output Frequency | | | | 250 | MHz |
| tp_{LH} | Propagation Delay, Low to High; NOTE 1 | $f \leq 250\text{MHz}$ | 1.4 | 2.3 | 3.2 | ns |
| tjit | Buffer Additive Phase Jitter, RMS; refer to Additive Phase Jitter Section | 100MHz, Integration Range: 12kHz – 20MHz | | 0.022 | | ps |
| $tsk(o)$ | Output Skew; NOTE 2, 5 | | | | 150 | ps |
| $tsk(pp)$ | Part-to-Part Skew; NOTE 3, 5 | | | | 1.1 | ns |
| t_R / t_F | Output Rise/Fall Time; NOTE 5 | 20% to 80% | 200 | | 700 | ps |
| odc | Output Duty Cycle | $f \leq 150\text{MHz}$ | 45 | | 55 | % |

All parameters measured at f_{MAX} unless noted otherwise.

NOTE 1: Measured from the $V_{DD}/2$ of the input to $V_{DDO}/2$ of the output.

NOTE 2: Defined as skew between outputs at the same supply voltage and with equal load conditions. Measured at $V_{DDO}/2$.

NOTE 3: Defined as skew between outputs on different devices operating at the same supply voltage and with equal load conditions. Using the same type of input on each device, the output is measured at $V_{DDO}/2$.

NOTE 4: These parameters are guaranteed by characterization. Not tested in production.

NOTE 5: This parameter is defined in accordance with JEDEC Standard 65.

Table 5C. AC Characteristics, $V_{DD} = V_{DDO} = 1.8V \pm 0.2V$, $T_A = 0^{\circ}C$ to $85^{\circ}C$

| Parameter | Symbol | Test Conditions | Minimum | Typical | Maximum | Units |
|--------------|---|--|---------|---------|---------|-------|
| f_{MAX} | Output Frequency | | | | 200 | MHz |
| tp_{LH} | Propagation Delay, Low to High; NOTE 1 | $f \leq 200MHz$ | 1.6 | 3.3 | 4.8 | ns |
| t_{jit} | Buffer Additive Phase Jitter, RMS; refer to Additive Phase Jitter Section | 100MHz, Integration Range: 12kHz – 20MHz | | 0.172 | | ps |
| $t_{sk(o)}$ | Output Skew; NOTE 2, 5 | | | | 140 | ps |
| $t_{sk(pp)}$ | Part-to-Part Skew; NOTE 3, 5 | | | | 2.3 | ns |
| t_R / t_F | Output Rise/Fall Time; NOTE 5 | 20% to 80% | 200 | | 800 | ps |
| odc | Output Duty Cycle | $f \leq 100MHz$ | 45 | | 55 | % |

All parameters measured at f_{MAX} unless noted otherwise.

NOTE 1: Measured from the $V_{DD}/2$ of the input to $V_{DDO}/2$ of the output.

NOTE 2: Defined as skew between outputs at the same supply voltage and with equal load conditions. Measured at $V_{DDO}/2$.

NOTE 3: Defined as skew between outputs on different devices operating at the same supply voltage and with equal load conditions.

Using the same type of input on each device, the output is measured at $V_{DDO}/2$.

NOTE 4: These parameters are guaranteed by characterization. Not tested in production.

NOTE 5: This parameter is defined in accordance with JEDEC Standard 65.

Table 5D. AC Characteristics, $V_{DD} = 3.3V \pm 5\%$, $V_{DDO} = 2.5V \pm 5\%$, $T_A = 0^{\circ}C$ to $85^{\circ}C$

| Parameter | Symbol | Test Conditions | Minimum | Typical | Maximum | Units |
|--------------|---|--|---------|---------|---------|-------|
| f_{MAX} | Output Frequency | | | | 250 | MHz |
| tp_{LH} | Propagation Delay, Low to High; NOTE 1 | $f \leq 250MHz$ | 1.4 | 2.1 | 2.7 | ns |
| t_{jit} | Buffer Additive Phase Jitter, RMS; refer to Additive Phase Jitter Section | 100MHz, Integration Range: 12kHz – 20MHz | | 0.045 | | ps |
| $t_{sk(o)}$ | Output Skew; NOTE 2, 5 | | | | 135 | ps |
| $t_{sk(pp)}$ | Part-to-Part Skew; NOTE 3, 5 | | | | 900 | ps |
| t_R / t_F | Output Rise/Fall Time; NOTE 5 | 20% to 80% | 200 | | 700 | ps |
| odc | Output Duty Cycle | $f \leq 150MHz$ | 45 | | 55 | % |

All parameters measured at f_{MAX} unless noted otherwise.

NOTE 1: Measured from the $V_{DD}/2$ of the input to $V_{DDO}/2$ of the output.

NOTE 2: Defined as skew between outputs at the same supply voltage and with equal load conditions. Measured at $V_{DDO}/2$.

NOTE 3: Defined as skew between outputs on different devices operating at the same supply voltage and with equal load conditions.

Using the same type of input on each device, the output is measured at $V_{DDO}/2$.

NOTE 4: These parameters are guaranteed by characterization. Not tested in production.

NOTE 5: This parameter is defined in accordance with JEDEC Standard 65.

Table 5E. AC Characteristics, $V_{DD} = 3.3V \pm 5\%$, $V_{DDO} = 1.8V \pm 0.2V$, $T_A = 0^\circ C$ to $85^\circ C$

| Parameter | Symbol | Test Conditions | Minimum | Typical | Maximum | Units |
|--------------|---|--|---------|---------|---------|-------|
| f_{MAX} | Output Frequency | | | | 200 | MHz |
| tp_{LH} | Propagation Delay, Low to High; NOTE 1 | $f \leq 200MHz$ | 1.4 | 2.4 | 3.4 | ns |
| t_{jit} | Buffer Additive Phase Jitter, RMS; refer to Additive Phase Jitter Section | 100MHz, Integration Range: 12kHz – 20MHz | | 0.136 | | ps |
| $t_{sk(o)}$ | Output Skew; NOTE 2, 5 | | | | 145 | ps |
| $t_{sk(pp)}$ | Part-to-Part Skew; NOTE 3, 5 | | | | 1.3 | ns |
| t_R / t_F | Output Rise/Fall Time; NOTE 5 | 20% to 80% | 200 | | 700 | ps |
| odc | Output Duty Cycle | $f \leq 100MHz$ | 45 | | 55 | % |

All parameters measured at f_{MAX} unless noted otherwise.

NOTE 1: Measured from the $V_{DD}/2$ of the input to $V_{DDO}/2$ of the output.

NOTE 2: Defined as skew between outputs at the same supply voltage and with equal load conditions. Measured at $V_{DDO}/2$.

NOTE 3: Defined as skew between outputs on different devices operating at the same supply voltage and with equal load conditions.

Using the same type of input on each device, the output is measured at $V_{DDO}/2$.

NOTE 4: These parameters are guaranteed by characterization. Not tested in production.

NOTE 5: This parameter is defined in accordance with JEDEC Standard 65.

Table 5F. AC Characteristics, $V_{DD} = 2.5V \pm 5\%$, $V_{DDO} = 1.8V \pm 0.2V$, $T_A = 0^\circ C$ to $85^\circ C$

| Parameter | Symbol | Test Conditions | Minimum | Typical | Maximum | Units |
|--------------|---|--|---------|---------|---------|-------|
| f_{MAX} | Output Frequency | | | | 200 | MHz |
| tp_{LH} | Propagation Delay, Low to High; NOTE 1 | $f \leq 200MHz$ | 1.5 | 2.6 | 3.7 | ns |
| t_{jit} | Buffer Additive Phase Jitter, RMS; refer to Additive Phase Jitter Section | 100MHz, Integration Range: 12kHz – 20MHz | | 0.114 | | ps |
| $t_{sk(o)}$ | Output Skew; NOTE 2, 5 | | | | 150 | ps |
| $t_{sk(pp)}$ | Part-to-Part Skew; NOTE 3, 5 | | | | 1.5 | ns |
| t_R / t_F | Output Rise/Fall Time; NOTE 5 | 20% to 80% | 200 | | 700 | ps |
| odc | Output Duty Cycle | $f \leq 100MHz$ | 45 | | 55 | % |

All parameters measured at f_{MAX} unless noted otherwise.

NOTE 1: Measured from the $V_{DD}/2$ of the input to $V_{DDO}/2$ of the output.

NOTE 2: Defined as skew between outputs at the same supply voltage and with equal load conditions. Measured at $V_{DDO}/2$.

NOTE 3: Defined as skew between outputs on different devices operating at the same supply voltage and with equal load conditions.

Using the same type of input on each device, the output is measured at $V_{DDO}/2$.


NOTE 4: These parameters are guaranteed by characterization. Not tested in production.

NOTE 5: This parameter is defined in accordance with JEDEC Standard 65.

Additive Phase Jitter

The spectral purity in a band at a specific offset from the fundamental compared to the power of the fundamental is called the **dBc Phase Noise**. This value is normally expressed using a Phase noise plot and is most often the specified plot in many applications. Phase noise is defined as the ratio of the noise power present in a 1Hz band at a specified offset from the fundamental frequency to the power value of the fundamental. This ratio is expressed in decibels (dBm) or a ratio of the power in the 1Hz band


to the power in the fundamental. When the required offset is specified, the phase noise is called a **dBc** value, which simply means dBm at a specified offset from the fundamental. By investigating jitter in the frequency domain, we get a better understanding of its effects on the desired application over the entire time record of the signal. It is mathematically possible to calculate an expected bit error rate given a phase noise plot.




As with most timing specifications, phase noise measurements has issues relating to the limitations of the equipment. Often the noise floor of the equipment is higher than the noise floor of the

device. This is illustrated above. The device meets the noise floor of what is shown, but can actually be lower. The phase noise is dependant on the input source and measurement equipment.


Parameter Measurement Information




3.3V Core/3.3V LVC MOS Output Load AC Test Circuit




2.5V Core/2.5V LVC MOS Output Load AC Test Circuit




1.8V Core/1.8V LVC MOS Output Load AC Test Circuit



3.3V Core/2.5V LVC MOS Output Load AC Test Circuit




3.3V Core/1.8V LVC MOS Output Load AC Test Circuit




2.5V Core/1.8V LVC MOS Output Load AC Test Circuit


Parameter Measurement Information, continued




Output Skew




Part-to-Part Skew



Propagation Delay



Output Duty Cycle/Pulse Width/Period



Output Rise/Fall Time

Application Information

Recommendations for Unused Input and Output Pins

Inputs:**LVC MOS Control Pins:**

All control pins have internal pull-ups or pull-downs; additional resistance is not required but can be added for additional protection. A 1k Ω resistor can be used.

Outputs:**LVC MOS Outputs:**

All unused LVC MOS output can be left floating. There should be no trace attached.

Reliability Information

Table 6. θ_{JA} vs. Air Flow Table for a 32 Lead LQFP

| θ_{JA} vs. Air Flow | | | |
|--|----------|----------|----------|
| Linear Feet per Minute | 0 | 200 | 500 |
| Single-Layer PCB, JEDEC Standard Test Boards | 67.8°C/W | 55.9°C/W | 50.1°C/W |
| Multi-Layer PCB, JEDEC Standard Test Boards | 47.9°C/W | 42.1°C/W | 39.4°C/W |

NOTE: Most modern PCB design use multi-layered boards. The data in the second row pertains to most designs.

Transistor Count

The transistor count for 8312 is: 339

Package Outline and Package Dimensions

Package Outline - Y Suffix for 32 Lead LQFP




Table 7. Package Dimensions for 32 Lead LQFP

| JEDEC Variation: ABC - HD | | | |
|-------------------------------|------------|---------|---------|
| All Dimensions in Millimeters | | | |
| Symbol | Minimum | Nominal | Maximum |
| N | 32 | | |
| A | | | 1.60 |
| A1 | 0.05 | 0.10 | 0.15 |
| A2 | 1.35 | 1.40 | 1.45 |
| b | 0.30 | 0.37 | 0.45 |
| c | 0.09 | | 0.20 |
| D & E | 9.00 Basic | | |
| D1 & E1 | 7.00 Basic | | |
| D2 & E2 | 5.60 Ref. | | |
| e | 0.80 Basic | | |
| L | 0.45 | 0.60 | 0.75 |
| theta | 0° | | 7° |
| ccc | | | 0.10 |
| N | 32 | | |

Reference Document: JEDEC Publication 95, MS-026

Ordering Information

Table 8. Ordering Information

| Part/Order Number | Marking | Package | Shipping Packaging | Temperature |
|-------------------|-------------|--------------------------|--------------------|-------------|
| 8312AYLF | ICS8312AYLF | "Lead-Free" 32 Lead LQFP | Tray | 0°C to 85°C |
| 8312AYLFT | ICS8312AYLF | "Lead-Free" 32 Lead LQFP | Tape & Reel | 0°C to 85°C |

Revision History Sheet

| Rev | Table | Page | Description of Change | Date |
|-----|-----------------|-------|--|----------|
| B | T2 T4A - T4F | 2 | Pin Characteristics table - added category C_{PD} . | 2/25/03 |
| | | 3 | Power Supply tables - changed I_{DD} & I_{DDO} max. current spec to 10 μ A and removed typical value. | |
| C | T2 | 1 | Features section - corrected Output Skew typo error from 160ps to 150ps. | 5/17/04 |
| | | 2 | Pin Characteristics table - changed C_{IN} 4pF max. to 4pF typical. | |
| C | T8 | 11 | Added Lead-Free part number to Ordering Information Table. | 6/14/04 |
| D | T5A - T5F | 7 - 9 | Added Additive Phase Jitter specs to AC Tables. | 7/3/08 |
| | | 10 | Added Additive Phase Jitter Plot. | |
| | | 13 | Added <i>Recommendations for Unused Input & Output Pins</i> section. Updated datasheet to new format. | |
| D | T8 | 16 | Removed leaded orderable parts from Ordering Information table | 11/14/12 |
| D | | 1 | Removed ICS Chip and HiPerClockS under General Description. | 12/11/15 |
| | | 1 | Removed ICS in the part numbers. | |
| | | 16 | Removed reference to leaded parts in the Features Section. | |
| | | 16 | Removed LF note at the bottom of the Ordering Information table. Removed the quantity of 1000 from the Tape & Reel in the Ordering information table. Updated datasheet header and footer. | |

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.